



Product Description

MASTER TL5 High Output 90 De Luxe

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Benefits

- Allows system miniaturisation and maximum luminaire design freedom, with lamp lengths defined for easy fitting into ceiling module systems
- Virtually constant lumen level with good lumen maintenance
- Excellent colour rendering

Features


- 40% thinner than existing TL-D lamps
- Highly efficient multi-band fluorescent coating in combination with precoating and high lamp load
- Specifically designed for operation with electronic gear and well suited for dimming
- Maximum light output reached at approx. 35 °C in free-burning position if an electronic ballast without additional electrode heating is used
- Can be ignited from -15 to +50 °C

Application


- Where a high colour recognition is needed: first aid and treatment rooms in hospitals, printing rooms, jewellery manufacturing, dentists, hairdressing, museums and shops

MASTER TL5 High Output 90 De Luxe

Versions



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 90 De Luxe 54W/965 1SL20	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

