



# Product Description

## MASTER TL-D 90 De Luxe

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Benefits

- Very good colour rendering. Making colours appear rich, deep and enhanced as they do in daylight, making products appear more attractive
- 25% More light than competition
- Enabling customer to switch to 900-colours with (almost) no decrease of light level
- Enabling customers (in certain segments) to respect the new European standard for lighting of indoor workplaces (CEN 12464-1), without investing in new luminaires
- Attractive packaging configuration
- Direct retrofit for all Standard and Super 80 TL-D lamps operating on conventional or HF gear
- Possible to create atmospheres from warm white to cool daylight

### Features

- High-quality fluorescent coating
- Available in various colour designations

### Application

- Used in applications where good colour rendering is crucial, such as shops (flower, fashion, department, etc.), hairdresser, museums, hospitals, etc

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MASTER TL-D 90 De Luxe

## Versions



LPPR TL-D9HLM G13

## Dimensional drawing



| Product                                  | D (max) | A (max)  | B (max)  | B (min)  | C (max) |
|------------------------------------------|---------|----------|----------|----------|---------|
| MASTER TL-D 90 De Luxe<br>18W/965 SLV/10 | 28 mm   | 589.8 mm | 596.9 mm | 594.5 mm | 604 mm  |

