



Red, Green and Blue fluorescent lighting

TL-D Colored

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

Benefits

- · Choice of attractive colors
- · Choice of attractive colors

Features

- The fluorescent powders of Red and Yellow lamps are mixed with a pigment to filter out unwanted wavelengths
- The fluorescent powders of Red and Yellow lamps are mixed with a pigment to filter out unwanted wavelengths
- \cdot Can be used with conventional or electronic gear
- · Can be used with conventional or electronic gear
- · Depending on the control gear, dimming is possible
- · Depending on the control gear, dimming is possible

Application

- For color effects in stage lighting, shop-window lighting, festive lighting, bars, dance halls etc.
- For color effects in stage lighting, shop-window lighting, festive lighting, bars, dance halls etc.

TL-D Colored

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR TL-DCOL Blue G13

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 18W Blue 1SL/25	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.