



# Product Description

## TL-D Standard Colours

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Benefits

- Create atmospheres from warm white to cool daylight

### Features

- Standard colours with moderate colour rendering
- Available in various colour designations


### Application

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where colour rendering is not an important factor

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/54-765 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm