



Product Description

TL-D Standard Colours

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Benefits

- Create atmospheres from warm white to cool daylight

Features

- Standard colours with moderate colour rendering
- Available in various colour designations

Application

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where colour rendering is not an important factor

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR TL-DSTD G13

TL-D Standard Colours

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/54-765 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 30W/54-765 1SL/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm
TL-D 36W/54-765 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Cool Daylight
Color rendering index (CRI)	72
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8

General Information

Order Code	Full Product Name	Nominal lifetime
928025405451	TL-D 30W/54-765 1SL/25	-
928048005436	TL-D 18W/54-765 1SL/25	13000 hour(s)

Order Code	Full Product Name	Nominal lifetime
928048505436	TL-D 36W/54-765 1SL/25	13000 hour(s)

Light Technical

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux
928025405451	TL-D 30W/54-765 1SL/25	6200 K	1825 lm
928048005436	TL-D 18W/54-765 1SL/25	6200 K	1050 lm

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux
928048505436	TL-D 36W/54-765 1SL/25	6500 K	2500 lm

Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928025405451	TL-D 30W/54-765 1SL/25	0.360 A	98 V	30.0 W
928048005436	TL-D 18W/54-765 1SL/25	0.360 A	59 V	18.0 W

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928048505436	TL-D 36W/54-765 1SL/25	0.440 A	103 V	36.0 W

Approval and Application

TL-D Standard Colours

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
928025405451	TL-D 30W/54-765 1SL/25	36 kWh	5.0 mg
928048005436	TL-D 18W/54-765 1SL/25	22 kWh	8.0 mg

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
928048505436	TL-D 36W/54-765 1SL/25	43 kWh	8.0 mg

