



Product Description

TL-D Standard Colours

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Benefits

- · Create atmospheres from warm white to cool daylight
- \cdot Create atmospheres from warm white to cool daylight

Features

- · Standard colors with moderate color rendering
- · Standard colours with moderate colour rendering
- · Available in various color designations
- · Available in various colour designations

Application


- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where color rendering is not an important factor
- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where colour rendering is not an important factor

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

TL-D Standard Colours

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 10W/54-765 1SL/50	28 mm	331.5 mm	338.6 mm	336.2 mm	345.7 mm
TL-D 15W/54-765 1SL/50	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
TL-D 30W/54-765 1SL/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm
TL-D 58W/54-765 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

General Information	
Cap-Base	G13
Light Technical	
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	Т8

General Information

Order Code	Full Product Name	Nominal lifetime
928024005436	TL-D 10W/54-765 1SL/50	-
928024805436	TL-D 15W/54-765 1SL/50	-

Order Code	Full Product Name	Nominal lifetime
928025405482	TL-D 30W/54-765 1SL/25	13,000 hour(s)
928049005482	TL-D 58W/54-765 1SL/25	13,000 hour(s)

Light Technical

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Flux
928024005436	TL-D 10W/54-765 1SL/50	75	390 lm
928024805436	TL-D 15W/54-765 1SL/50	72	725 lm

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Flux
928025405482	TL-D 30W/54-765 1SL/25	72	1,825 lm
928049005482	TL-D 58W/54-765 1SL/25	72	4,000 lm

Operating and Electrical

		Lamp		
		Current	Voltage	Power
Order Code	Full Product Name	(Nom)	(Nom)	Consumption
928024005436	TL-D 10W/54-765	0.230 A	46 V	10.0 W
	1SL/50			
928024805436	TL-D 15W/54-765	0.310 A	51 V	15.0 W
	1SL/50			

		Lamp		
		Current	Voltage	Power
Order Code	Full Product Name	(Nom)	(Nom)	Consumption
928025405482	TL-D 30W/54-765	0.360 A	98 V	30.0 W
	1SL/25			
928049005482	TL-D 58W/54-765	0.670 A	111 V	58.5 W
	1SL/25			

Approval and Application

TL-D Standard Colours

		Energy Consumption	Mercury (Hg)
Order Code	Full Product Name	kWh/1000 h	Content (Nom)
928024005436	TL-D 10W/54-765 1SL/50	-	8.0 mg
928024805436	TL-D 15W/54-765 1SL/50	20 kWh	8.0 mg

		Energy Consumption	Mercury (Hg)
Order Code	Full Product Name	kWh/1000 h	Content (Nom)
928025405482	TL-D 30W/54-765 1SL/25	36 kWh	5.0 mg
928049005482	TL-D 58W/54-765 1SL/25	68 kWh	5.0 mg



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.