



# **Product Description**

### **MASTER TL-D Xtreme**

Low-pressure mercury discharge lamp with a tubular 26mm envelope

#### **Benefits**

- Longer lifetime and less early failures lead to less hassle and lower maintenance costs and facilitate the change from spot to group replacement
- · Less waste and disposal cost at end-of-life
- · Special fluorescent coating gives good colour rendering

#### **Features**

- Significant reduction of early failures based upon a new technology (patent pending)
- Extreme long and reliable lifetime
- Highly efficient 3-band fluorescent coating in combination with New Generation pre-coating technology
- · Low mercury dose for a long-life lamp (5 mg)
- Fully recyclable lamp technology
- End-cap has an x-shaped green bottom plate to distinguish lamp from other fluorescent lamps

#### **Application**

• Suitable for use in applications where maintenance costs (high ceilings, difficult to reach) and disruptive costs are high (stopping of production process, closure of tunnels), or where lamp failure is not acceptable for e.g. safety reasons: tunnels, process, food and petrochemical industries

#### **Warnings and Safety**

- To achieve published lifetimes for 100% operation, do not dim below 30%
- When used on electromagnetic gear, it is strongly recommended to apply only Philips S10 or S10E starters (for 18W types S2 or S2E) to achieve the published lifetimes, and to install new starters when relamping.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

# **MASTER TL-D Xtreme**

## Versions



# Dimensional drawing

| Product            | D (max) | A (max)   | B (max)   | B (min)   | C (max)   |
|--------------------|---------|-----------|-----------|-----------|-----------|
| MASTER TL-D Xtreme | 28 mm   | 1500.0 mm | 1507.1 mm | 1504.7 mm | 1514.2 mm |
| 58W/865 SLV        |         |           |           |           |           |
| MASTER TL-D Xtreme | 28 mm   | 1199.4 mm | 1206.5 mm | 1204.1 mm | 1213.6 mm |
| 36W/865 SLV        |         |           |           |           |           |

# **MASTER TL-D Xtreme**

| A                                   |               |
|-------------------------------------|---------------|
| Approval and Application            |               |
| Energy Efficiency Label (EEL)       | А             |
| Mercury (Hg) Content (Nom)          | 3.0 mg        |
|                                     |               |
| Controls and Dimming                |               |
| Dimmable                            | yes           |
|                                     |               |
| General Information                 |               |
| Cap-Base                            | G13           |
| Life To 50% Failures Preheat (Nom)  | 79000 h       |
| Life To 50% Failures (Nom)          | 47000 h       |
| LSF 12000 h Rated                   | 99 %          |
| LSF 16000 h Rated                   | 99 %          |
| LSF 2000 h Rated                    | 100 %         |
| LSF 20000 h Rated                   | 99 %          |
| LSF 4000 h Rated                    | 99 %          |
| LSF 6000 h Rated                    | 99 %          |
| LSF 8000 h Rated                    | 99 %          |
|                                     |               |
| Light Technical                     |               |
| Colour Code                         | 865           |
| Colour Designation                  | Cool Daylight |
| Correlated Colour Temperature (Nom) | 6500 K        |
| Colour Rendering Index (Nom)        | >80           |
| LLMF 12000 h Rated                  | 92 %          |
| LLMF 16000 h Rated                  | 91 %          |
| LLMF 2000 h Rated                   | 96 %          |
| LLMF 20000 h Rated                  | 90 %          |
| LLMF 4000 h Rated                   | 95 %          |
| LLMF 6000 h Rated                   | 94 %          |
| LLMF 8000 h Rated                   | 93 %          |
|                                     |               |
| Mechanical and Housing              |               |
| Bulb Shape                          | Т8            |
|                                     |               |
| Temperature                         |               |
| Design Temperature (Nom)            | 25 ℃          |

## **Approval and Application**

| Order Code   | Full Product Name              | Energy Consumption kWh/1000 h |
|--------------|--------------------------------|-------------------------------|
| 927982386514 | MASTER TL-D Xtreme 36W/865 SLV | 42 kWh                        |
| 927983386514 | MASTER TL-D Xtreme 58W/865 SLV | 68 kWh                        |
| 927983386514 | MASTER TL-D Xtreme 58W/865 SLV | 68 kWh                        |

# Operating and Electrical

|              |                            | Lamp Current | Power (Rated) |
|--------------|----------------------------|--------------|---------------|
| Order Code   | Full Product Name          | (Nom)        | (Nom)         |
| 927982386514 | MASTER TL-D Xtreme 36W/865 | 0.430 A      | 36.0 W        |
|              | SLV                        |              |               |

|              |                            | Lamp Current | Power (Rated) |
|--------------|----------------------------|--------------|---------------|
| Order Code   | Full Product Name          | (Nom)        | (Nom)         |
| 927983386514 | MASTER TL-D Xtreme 58W/865 | 0.665 A      | 58.5 W        |
|              | SLV                        |              |               |

## **Light Technical**

|              |                   | Luminous         |               |               |  |
|--------------|-------------------|------------------|---------------|---------------|--|
|              |                   | Efficacy (rated) | Luminous Flux | Luminous Flux |  |
| Order Code   | Full Product Name | (Nom)            | (Nom)         | (Rated) (Nom) |  |
| 927982386514 | MASTER TL-D       | 88 lm/W          | 3150 lm       | 3150 lm       |  |
|              | Xtreme 36W/865    |                  |               |               |  |
|              | SLV               |                  |               |               |  |

## **MASTER TL-D Xtreme**

|              |                   | Luminous         |               |               |
|--------------|-------------------|------------------|---------------|---------------|
|              |                   | Efficacy (rated) | Luminous Flux | Luminous Flux |
| Order Code   | Full Product Name | (Nom)            | (Nom)         | (Rated) (Nom) |
| 927983386514 | MASTER TL-D       | 86 lm/W          | 5000 lm       | 5000 lm       |
|              | Xtreme 58W/865    |                  |               |               |
|              | SLV               |                  |               |               |



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.