PHILIPS

Lighting



T12 lamp with reliable ignition

TL Rapid Start Standard Colours

The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.

Benefits

- Creating atmospheres from warm white to cool daylight
- Creating atmospheres from warm white to cool daylight
- Fast, well-defined ignition at low temperatures
- Fast, well-defined ignition at low temperatures

Features

- RS (Rapid Start) lamps with an external silicon coating
- RS (Rapid Start) lamps with an external silicon coating
- Standard colors with moderate color rendering
- Standard colors with moderate color rendering
- Available in varying color designations
- Available in varying color designations

Application

- Mostly used in applications where color rendering is not an important factor
- Mostly used in applications where color rendering is not an important factor

TL Rapid Start Standard Colours


Versions



LPPR TL-RS G13

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL RS 40W/54-765 1SL/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.