



T12 lamp with reliable ignition

TL Rapid Start Standard Colours

The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.

Benefits

- · Creating atmospheres from warm white to cool daylight
- \cdot Fast, well-defined ignition at low temperatures

Features

- · RS (Rapid Start) lamps with an external silicon coating
- · Standard colors with moderate color rendering
- · Available in varying color designations

Application

· Mostly used in applications where color rendering is not an important factor


TL Rapid Start Standard Colours

Versions



LPPR TL-RS G13

Dimensional drawing



General Information	
Cap-Base	G13
Light Technical	
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Operating and Electrical	
Power Consumption	39.0 W
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T12
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg

Light Technical

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 40W/54-765 RSYL	28.0 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
1SL/25					
TL RS 40W/54-765 1SL/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

TL Rapid Start Standard Colours

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous
928011305430	TL RS 40W/54-765	72	64 lm/W	2,500 lm
	1SL/25			

		Color	Luminous Efficacy (rated)	Luminous
Order Code	Full Product Name	index (CRI)	(Nom)	Flux
928012305430	TL 40W/54-765	75	68.5 lm/W	2,700 lm
	RSYL 1SL/25			

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)
928011305430	TL RS 40W/54-765 1SL/25	0.430 A	101 V

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)
928012305430	TL 40W/54-765 RSYL 1SL/25	0.440 A	103 V

