



Product Description

TL-X XL

Single-pin low-pressure mercury discharge lamps with a tubular 38 mm envelope

Benefits

- In combination with a special lampholder all possible sparking effects during ignition are eliminated
- Extended lifetime compared with standard TL lamps

Features

- 40W and 65W lamps with internal ignition strip for instant start, non-preheat, starterless operation

Application


- Used in flameproof and increased-safety luminaires for both indoor and outdoor applications
- Used in applications like petro-chemical industry, offshore, mines and any locations where traces of explosive gases may be found

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

TL-X XL

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-X XL 20W/33-640 SLV/25	40.5 mm	574 mm	592.5 mm	589 mm	611 mm
TL-X XL 40W/33-640 SLV/25	40.5 mm	1,183.5 mm	1,202 mm	1,198.5 mm	1,220.5 mm

General Information	
Cap base	FA6
Light Technical	
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Colour designation	Cool White (CW)
Correlated Colour Temperature	4000 K
Colour rendering index (CRI)	60
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	T12
Approval and Application	
Mercury (Hg) content (max.)	12 mg
Mercury (Hg) content (nom.)	12.0 mg

Light Technical

Order Code	Full Product Name	Luminous efficacy (rated) (nom.)	Luminous Flux
26135940	TL-X XL 20W/33-640 SLV/25	47 lm/W	940 lm
26137340	TL-X XL 40W/33-640 SLV/25	58 lm/W	2,300 lm

Operating and Electrical

Order Code	Full Product Name	Lamp current (nom.)	Voltage (nom.)	Power Consumption
26135940	TL-X XL 20W/33-640 SLV/25	0.380 A	58 V	20.0 W



TL-X XL

Order Code	Full Product Name	Lamp current (nom.)	Voltage (nom.)	Power Consumption
26137340	TL-X XL 40W/33-640 SLV/25	0.430 A	103 V	40.0 W

Approval and Application

Order Code	Full Product Name	Energy consumption kWh/1,000 hours
26135940	TL-X XL 20W/33-640 SLV/25	20 kWh

Order Code	Full Product Name	Energy consumption kWh/1,000 hours
26137340	TL-X XL 40W/33-640 SLV/25	40 kWh

