



CoreLine Wall-mounted – the clear choice for LED

CoreLine Wall-mounted

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Wall-mounted range of LED products can be used to replace traditional wall-mounted luminaires incorporating compact fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Benefits

- Up to 55% energy savings compared with luminaires with PL-C lamps
- Direct replacement for traditional wall-mounted luminaires
- Complete range covering all application requirements in one product (light levels, IP65, IK10, certified emergency lighting, built-in controls)

Features

- Unobtrusive design
- Three lumen packages replacing traditional wall-mounted luminaires with 1x18 W / 2x18 W / 2x26 W PL-C
- Water- and vandal-proof as standard
- Phase-cut dimming as standard
- Frosted diffuser ensuring homogeneous light effect and visual comfort
- Optional emergency lighting
- Optional on/off movement detection or programmed 100%-10%-0% corridor dimming functionality

CoreLine Wall-mounted

Application

- Corridors
- Staircases
- Public entrance areas
- Bathrooms
- Emergency exits
- Parking garages
- Outdoor safety lighting

Specifications

Type	WL120V (round version)
	WL121V (oval version)
Light source	Non-replaceable LED module
Power (+/-10%)	8 W (LED5S version)
	18 W (LED12S version)
	24 W (LED16S version)
Beam angle	120°
Luminous flux	500 lm (LED5S version)
	1200 lm (LED12S version)
	1600 lm (LED16S version)
Correlated Color	3000 or 4000 K
Temperature	
Color Rendering Index	≥ 80
Median useful life	50,000 hours
L70B50	
Median useful life	30,000 hours
L80B50	
Median useful life	15,000 hours
L90B50	
Average ambient temperature	+25 °C
Operating temperature range	-20 to +35 °C (wall-mounted position)
	-20 to +25 °C (ceiling-mounted position)
	0 to +25 °C (emergency lighting)

Driver	Built-in, replaceable
Mains voltage	220-240V / 50-60 Hz
Dimming	TE/LE dimming, compatible with most commercial available ELV dimmers
Options	Emergency lighting (integrated): 3 hours (EL3)
	Movement detection unit (integrated): on/off switch with day light override (MDU)
	DALI driver and movement detection unit (integrated): corridor functionality (PSD MDU)
Material	Housing: nylon 30% fiber glass re-inforced, UV resistant Difuser: high grade polycarbonate, UV resistant
Color	White (RAL 9010)
	Grey (RAL 7043)
Optical cover	Polycarbonate difuser
Connection	Push-in connector with pull relief (PIP)
Maintenance	LED module closed, no internal cleaning required
Installation	Screw mounting, directly onto surface
	4-point screw installation of housing to wall
	4-point torx screw connection difuser to housing Through-wiring not possible

Versions




CoreLine Wall-Mounted Gen2

CoreLine Wall-mounted

Product details



CoreLine_Wall-mounted-
WL131V_D35_CTO_PSD-DPP.TIF




CoreLine_Wall-mounted-
WL130V-2DPP.TIF



CoreLine_Wall-mounted-
WL131V_D35_CTO_PSR_MDU-
DPP.TIF



CoreLine_Wall-mounted-
WL130V_CTO-DPP.TIF



CoreLine_Wall-mounted-
WL130V-1DPP.TIF



CoreLine_Wall-mounted-
WL130V_D35_CTO_MDU-DPP.TIF

CoreLine Wall-mounted

Application Conditions

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP65

General Information

Beam angle of light source	120 °
CE mark	CE mark
Protection class IEC	Safety class II (II)
Optical cover/lens type	OP
Driver included	Yes
ENEC mark	ENEC mark
Light source replaceable	No
Number of gear units	1 unit
Optic type	Opal prismatic reflector

Initial Performance (IEC Compliant)

Init. Colour Rendering Index	80
Luminous flux tolerance	+/-10%

Mechanical and Housing

Colour	White
--------	-------

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
40268600	WL131V LED12S/830 PSED EL3 WH	10%	No
40269300	WL131V LED12S/840 PSED EL3 WH	10%	No
40270900	WL131V LED20S/830 PSED EL3 WH	10%	No
40271600	WL131V LED20S/840 PSED EL3 WH	10%	No
40272300	WL131V LED34S/830 PSED WH	10%	No
40273000	WL131V LED34S/840 PSED WH	10%	No
40274700	WL131V LED34S/830 PSED EL3 WH	10%	No
40275400	WL131V LED34S/840 PSED EL3 WH	10%	No
40282200	WL131V LED12S/830 PSR EL3 MDU WH	20%	Yes
40283900	WL131V LED12S/840 PSR EL3 MDU WH	20%	Yes
40284600	WL131V LED20S/830 PSR EL3 MDU WH	20%	Yes
40285300	WL131V LED20S/840 PSR EL3 MDU WH	20%	Yes
40286000	WL131V LED34S/830 PSR EL3 MDU WH	20%	Yes
40287700	WL131V LED34S/840 PSR EL3 MDU WH	20%	Yes
34003699	WL131V LED20S/840 PSU WH	Not applicable	Not applicable
38784699	WL131V LED34S/830 PSU WH	Not applicable	Yes
38785399	WL131V LED34S/840 PSU WH	Not applicable	Yes
38786099	WL131V LED12S/830 PSR MDU WH	10%	Yes
38787799	WL131V LED12S/840 PSR MDU WH	10%	Yes
38788499	WL131V LED20S/830 PSR MDU WH	10%	Yes
38789199	WL131V LED20S/840 PSR MDU WH	10%	Yes
38790799	WL131V LED34S/830 PSR MDU WH	10%	Yes
38791499	WL131V LED34S/840 PSR MDU WH	10%	Yes
38792199	WL131V LED12S/830 PSED WH	10%	Yes
38793899	WL131V LED12S/840 PSED WH	10%	Yes
38794599	WL131V LED20S/830 PSED WH	10%	Yes
38795299	WL131V LED20S/840 PSED WH	10%	Yes
38778599	WL130V LED12S/830 PSU WH	Not applicable	Yes
38779299	WL130V LED12S/840 PSU WH	Not applicable	Yes
38780899	WL130V LED20S/830 PSU WH	Not applicable	Yes
38781599	WL130V LED20S/840 PSU WH	Not applicable	Yes
38782299	WL130V LED20S/830 PSU MDU WH	Not applicable	Yes
38783999	WL130V LED20S/840 PSU MDU WH	Not applicable	Yes

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
40268600	WL131V LED12S/830 PSED EL3 WH	Yes	40287700	WL131V LED34S/840 PSR EL3 MDU WH	Yes
40269300	WL131V LED12S/840 PSED EL3 WH	Yes	34003699	WL131V LED20S/840 PSU WH	No
40270900	WL131V LED20S/830 PSED EL3 WH	Yes	38784699	WL131V LED34S/830 PSU WH	No
40271600	WL131V LED20S/840 PSED EL3 WH	Yes	38785399	WL131V LED34S/840 PSU WH	No
40272300	WL131V LED34S/830 PSED WH	Yes	38786099	WL131V LED12S/830 PSR MDU WH	Yes
40273000	WL131V LED34S/840 PSED WH	Yes	38787799	WL131V LED12S/840 PSR MDU WH	Yes
40274700	WL131V LED34S/830 PSED EL3 WH	Yes	38788499	WL131V LED20S/830 PSR MDU WH	Yes
40275400	WL131V LED34S/840 PSED EL3 WH	Yes	38789199	WL131V LED20S/840 PSR MDU WH	Yes
40282200	WL131V LED12S/830 PSR EL3 MDU WH	Yes	38790799	WL131V LED34S/830 PSR MDU WH	Yes
40283900	WL131V LED12S/840 PSR EL3 MDU WH	Yes	38791499	WL131V LED34S/840 PSR MDU WH	Yes
40284600	WL131V LED20S/830 PSR EL3 MDU WH	Yes	38792199	WL131V LED12S/830 PSED WH	Yes
40285300	WL131V LED20S/840 PSR EL3 MDU WH	Yes	38793899	WL131V LED12S/840 PSED WH	Yes
40286000	WL131V LED34S/830 PSR EL3 MDU WH	Yes	38794599	WL131V LED20S/830 PSED WH	Yes

CoreLine Wall-mounted

Order Code	Full Product Name	Dimmable
38795299	WL131V LED20S/840 PSED WH	Yes
38778599	WL130V LED12S/830 PSU WH	No
38779299	WL130V LED12S/840 PSU WH	No
38780899	WL130V LED20S/830 PSU WH	No

Order Code	Full Product Name	Dimmable
38781599	WL130V LED20S/840 PSU WH	No
38782299	WL130V LED20S/830 PSU MDU WH	No
38783999	WL130V LED20S/840 PSU MDU WH	No

Operating and Electrical

Order Code	Full Product Name	Input Voltage
40268600	WL131V LED12S/830 PSED EL3 WH	220-240 V
40269300	WL131V LED12S/840 PSED EL3 WH	220-240 V
40270900	WL131V LED20S/830 PSED EL3 WH	220-240 V
40271600	WL131V LED20S/840 PSED EL3 WH	220-240 V
40272300	WL131V LED34S/830 PSED WH	220-240 V
40273000	WL131V LED34S/840 PSED WH	220-240 V
40274700	WL131V LED34S/830 PSED EL3 WH	220-240 V
40275400	WL131V LED34S/840 PSED EL3 WH	220-240 V
40282200	WL131V LED12S/830 PSR EL3 MDU WH	220-240 V
40283900	WL131V LED12S/840 PSR EL3 MDU WH	220-240 V
40284600	WL131V LED20S/830 PSR EL3 MDU WH	220-240 V
40285300	WL131V LED20S/840 PSR EL3 MDU WH	220-240 V
40286000	WL131V LED34S/830 PSR EL3 MDU WH	220-240 V
40287700	WL131V LED34S/840 PSR EL3 MDU WH	220-240 V
34003699	WL131V LED20S/840 PSU WH	220/240 V
38784699	WL131V LED34S/830 PSU WH	220-240 V
38785399	WL131V LED34S/840 PSU WH	220-240 V

Order Code	Full Product Name	Input Voltage
38786099	WL131V LED12S/830 PSR MDU WH	220-240 V
38787799	WL131V LED12S/840 PSR MDU WH	220-240 V
38788499	WL131V LED20S/830 PSR MDU WH	220-240 V
38789199	WL131V LED20S/840 PSR MDU WH	220-240 V
38790799	WL131V LED34S/830 PSR MDU WH	220-240 V
38791499	WL131V LED34S/840 PSR MDU WH	220-240 V
38792199	WL131V LED12S/830 PSED WH	220-240 V
38793899	WL131V LED12S/840 PSED WH	220-240 V
38794599	WL131V LED20S/830 PSED WH	220-240 V
38795299	WL131V LED20S/840 PSED WH	220-240 V
38778599	WL130V LED12S/830 PSU WH	220-240 V
38779299	WL130V LED12S/840 PSU WH	220-240 V
38780899	WL130V LED20S/830 PSU WH	220-240 V
38781599	WL130V LED20S/840 PSU WH	220-240 V
38782299	WL130V LED20S/830 PSU MDU WH	220-240 V
38783999	WL130V LED20S/840 PSU MDU WH	220-240 V

General Information (1/2)

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
40268600	WL131V LED12S/830 PSED EL3 WH	EL3	NO	-	850/30
40269300	WL131V LED12S/840 PSED EL3 WH	EL3	NO	-	850/30
40270900	WL131V LED20S/830 PSED EL3 WH	EL3	NO	-	850/30
40271600	WL131V LED20S/840 PSED EL3 WH	EL3	NO	-	850/30
40272300	WL131V LED34S/830 PSED WH	No	NO	-	850/30
40273000	WL131V LED34S/840 PSED WH	No	NO	-	850/30
40274700	WL131V LED34S/830 PSED EL3 WH	EL3	NO	-	850/30
40275400	WL131V LED34S/840 PSED EL3 WH	EL3	NO	-	850/30
40282200	WL131V LED12S/830 PSR EL3 MDU WH	EL3	NO	-	850/30
40283900	WL131V LED12S/840 PSR EL3 MDU WH	EL3	NO	-	850/30

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
40284600	WL131V LED20S/830 PSR EL3 MDU WH	EL3	NO	-	850/30
40285300	WL131V LED20S/840 PSR EL3 MDU WH	EL3	NO	-	850/30
40286000	WL131V LED34S/830 PSR EL3 MDU WH	EL3	NO	-	850/30
40287700	WL131V LED34S/840 PSR EL3 MDU WH	EL3	NO	-	850/30
34003699	WL131V LED20S/840 PSU WH	-	D	-	650/30
38784699	WL131V LED34S/830 PSU WH	-	NO	-	650/30
38785399	WL131V LED34S/840 PSU WH	-	NO	-	650/30
38786099	WL131V LED12S/830 PSR MDU WH	-	NO	-	650/30
38787799	WL131V LED12S/840 PSR MDU WH	-	NO	-	650/30
38788499	WL131V LED20S/830 PSR MDU WH	-	NO	-	650/30

CoreLine Wall-mounted

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
38789199	WL131V LED20S/840 PSR MDU WH	-	NO	-	650/30
38790799	WL131V LED34S/830 PSR MDU WH	-	NO	-	650/30
38791499	WL131V LED34S/840 PSR MDU WH	-	NO	-	650/30
38792199	WL131V LED12S/830 PSED WH	-	NO	-	650/30
38793899	WL131V LED12S/840 PSED WH	-	NO	-	650/30
38794599	WL131V LED20S/830 PSED WH	-	NO	-	650/30
38795299	WL131V LED20S/840 PSED WH	-	NO	-	650/30

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
38778599	WL130V LED12S/830 PSU WH	-	NO	-	650/30
38779299	WL130V LED12S/840 PSU WH	-	NO	-	650/30
38780899	WL130V LED20S/830 PSU WH	-	NO	-	650/30
38781599	WL130V LED20S/840 PSU WH	-	NO	-	650/30
38782299	WL130V LED20S/830 PSU MDU WH	-	NO	-	650/30
38783999	WL130V LED20S/840 PSU MDU WH	-	NO	-	650/30

General Information (2/2)

Order Code	Full Product Name	Lamp family code	Embedded control	Product Family Code
40268600	WL131V LED12S/830 PSED EL3 WH	LED12	No	WL131V
40269300	WL131V LED12S/840 PSED EL3 WH	LED12	No	WL131V
40270900	WL131V LED20S/830 PSED EL3 WH	LED20	No	WL131V
40271600	WL131V LED20S/840 PSED EL3 WH	LED20	No	WL131V
40272300	WL131V LED34S/830 PSED WH	LED34S	No	WL131V
40273000	WL131V LED34S/840 PSED WH	LED34S	No	WL131V
40274700	WL131V LED34S/830 PSED EL3 WH	LED34S	No	WL131V
40275400	WL131V LED34S/840 PSED EL3 WH	LED34S	No	WL131V
40282200	WL131V LED12S/830 PSR EL3 MDU WH	LED12	MDU	WL131V
40283900	WL131V LED12S/840 PSR EL3 MDU WH	LED12	MDU	WL131V
40284600	WL131V LED20S/830 PSR EL3 MDU WH	LED20	MDU	WL131V
40285300	WL131V LED20S/840 PSR EL3 MDU WH	LED20	MDU	WL131V
40286000	WL131V LED34S/830 PSR EL3 MDU WH	LED34S	MDU	WL131V
40287700	WL131V LED34S/840 PSR EL3 MDU WH	LED34S	MDU	WL131V
34003699	WL131V LED20S/840 PSU WH	LED20	-	-

Order Code	Full Product Name	Lamp family code	Embedded control	Product Family Code
38784699	WL131V LED34S/830 PSU WH	LED34S	-	-
38785399	WL131V LED34S/840 PSU WH	LED34S	-	-
38786099	WL131V LED12S/830 PSR MDU WH	LED12	MDU	-
38787799	WL131V LED12S/840 PSR MDU WH	LED12	MDU	-
38788499	WL131V LED20S/830 PSR MDU WH	LED20	MDU	-
38789199	WL131V LED20S/840 PSR MDU WH	LED20	MDU	-
38790799	WL131V LED34S/830 PSR MDU WH	LED34S	MDU	-
38791499	WL131V LED34S/840 PSR MDU WH	LED34S	MDU	-
38792199	WL131V LED12S/830 PSED WH	LED12	-	-
38793899	WL131V LED12S/840 PSED WH	LED12	-	-
38794599	WL131V LED20S/830 PSED WH	LED20	-	-
38795299	WL131V LED20S/840 PSED WH	LED20	-	-
38778599	WL130V LED12S/830 PSU WH	LED12	-	-
38779299	WL130V LED12S/840 PSU WH	LED12	-	-
38780899	WL130V LED20S/830 PSU WH	LED20	-	-
38781599	WL130V LED20S/840 PSU WH	LED20	-	-
38782299	WL130V LED20S/830 PSU MDU WH	LED20	MDU	-
38783999	WL130V LED20S/840 PSU MDU WH	LED20	MDU	-

Initial Performance (IEC Compliant) (1/2)

CoreLine Wall-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
40268600	WL131V LED12S/830 PSED EL3 WH	(0.44, 0.41) SDCM<3	3000 K	100 lm/W	1200 lm
40269300	WL131V LED12S/840 PSED EL3 WH	(0.39, 0.39) SDCM<3	4000 K	100 lm/W	1200 lm
40270900	WL131V LED20S/830 PSED EL3 WH	(0.44, 0.41) SDCM<3	3000 K	91 lm/W	2000 lm
40271600	WL131V LED20S/840 PSED EL3 WH	(0.39, 0.39) SDCM<3	4000 K	91 lm/W	2000 lm
40272300	WL131V LED34S/830 PSED WH	(0.44, 0.41) SDCM<3	3000 K	94 lm/W	3400 lm
40273000	WL131V LED34S/840 PSED WH	(0.39, 0.39) SDCM<3	4000 K	94 lm/W	3400 lm
40274700	WL131V LED34S/830 PSED EL3 WH	(0.44, 0.41) SDCM<3	3000 K	94 lm/W	3400 lm
40275400	WL131V LED34S/840 PSED EL3 WH	(0.39, 0.39) SDCM<3	4000 K	94 lm/W	3400 lm
40282200	WL131V LED12S/830 PSR EL3 MDU WH	(0.44, 0.41) SDCM<3	3000 K	100 lm/W	1200 lm
40283900	WL131V LED12S/840 PSR EL3 MDU WH	(0.39, 0.39) SDCM<3	4000 K	100 lm/W	1200 lm
40284600	WL131V LED20S/830 PSR EL3 MDU WH	(0.44, 0.41) SDCM<3	3000 K	91 lm/W	2000 lm
40285300	WL131V LED20S/840 PSR EL3 MDU WH	(0.39, 0.39) SDCM<3	4000 K	91 lm/W	2000 lm
40286000	WL131V LED34S/830 PSR EL3 MDU WH	(0.44, 0.41) SDCM<3	3000 K	94 lm/W	3400 lm
40287700	WL131V LED34S/840 PSR EL3 MDU WH	(0.39, 0.39) SDCM<3	4000 K	94 lm/W	3400 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
34003699	WL131V LED20S/840 PSU WH	(0.39, 0.39) SDCM<3	4000 K	90 lm/W	2000 lm
38784699	WL131V LED34S/830 PSU WH	(0.44, 0.41) SDCM<3	3000 K	95 lm/W	3400 lm
38785399	WL131V LED34S/840 PSU WH	(0.39, 0.39) SDCM<3	4000 K	95 lm/W	3400 lm
38786099	WL131V LED12S/830 PSR MDU WH	(0.44, 0.41) SDCM<3	3000 K	80 lm/W	1200 lm
38787799	WL131V LED12S/840 PSR MDU WH	(0.39, 0.39) SDCM<3	4000 K	80 lm/W	1200 lm
38788499	WL131V LED20S/830 PSR MDU WH	(0.44, 0.41) SDCM<3	3000 K	80 lm/W	2000 lm
38789199	WL131V LED20S/840 PSR MDU WH	(0.39, 0.39) SDCM<3	4000 K	80 lm/W	2000 lm
38790799	WL131V LED34S/830 PSR MDU WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	3400 lm
38791499	WL131V LED34S/840 PSR MDU WH	(0.39, 0.39) SDCM<3	4000 K	90 lm/W	3400 lm
38792199	WL131V LED12S/830 PSED WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	1200 lm
38793899	WL131V LED12S/840 PSED WH	(0.39, 0.39) SDCM<3	4000 K	90 lm/W	1200 lm
38794599	WL131V LED20S/830 PSED WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	2000 lm
38795299	WL131V LED20S/840 PSED WH	(0.39, 0.39) SDCM<3	4000 K	90 lm/W	2000 lm
38778599	WL130V LED12S/830 PSU WH	(0.44, 0.41) SDCM<3	3000 K	100 lm/W	1200 lm
38779299	WL130V LED12S/840 PSU WH	(0.39, 0.39) SDCM<3	4000 K	100 lm/W	1200 lm
38780899	WL130V LED20S/830 PSU WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	2000 lm

CoreLine Wall-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
38781599	WL130V LED20S/840 PSU WH	(0.44, 0.41) SDCM<3	4000 K	90 lm/W	2000 lm
38782299	WL130V LED20S/830 PSU MDU WH	(0.44, 0.41) SDCM<3	3000 K	80 lm/W	2000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Initial LED luminaire efficacy	Initial luminous flux
38783999	WL130V LED20S/840 PSU MDU WH	(0.39, 0.39) SDCM<3	4000 K	80 lm/W	2000 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
40268600	WL131V LED12S/830 PSED EL3 WH	12 W
40269300	WL131V LED12S/840 PSED EL3 WH	12 W
40270900	WL131V LED20S/830 PSED EL3 WH	22 W
40271600	WL131V LED20S/840 PSED EL3 WH	22 W
40272300	WL131V LED34S/830 PSED WH	36 W
40273000	WL131V LED34S/840 PSED WH	36 W
40274700	WL131V LED34S/830 PSED EL3 WH	36 W
40275400	WL131V LED34S/840 PSED EL3 WH	36 W
40282200	WL131V LED12S/830 PSR EL3 MDU WH	12 W
40283900	WL131V LED12S/840 PSR EL3 MDU WH	12 W
40284600	WL131V LED20S/830 PSR EL3 MDU WH	22 W
40285300	WL131V LED20S/840 PSR EL3 MDU WH	22 W
40286000	WL131V LED34S/830 PSR EL3 MDU WH	36 W
40287700	WL131V LED34S/840 PSR EL3 MDU WH	36 W
34003699	WL131V LED20S/840 PSU WH	22 W
38784699	WL131V LED34S/830 PSU WH	36 W
38785399	WL131V LED34S/840 PSU WH	36 W

Order Code	Full Product Name	Initial input power
38786099	WL131V LED12S/830 PSR MDU WH	15 W
38787799	WL131V LED12S/840 PSR MDU WH	15 W
38788499	WL131V LED20S/830 PSR MDU WH	25 W
38789199	WL131V LED20S/840 PSR MDU WH	25 W
38790799	WL131V LED34S/830 PSR MDU WH	38 W
38791499	WL131V LED34S/840 PSR MDU WH	38 W
38792199	WL131V LED12S/830 PSED WH	13 W
38793899	WL131V LED12S/840 PSED WH	13 W
38794599	WL131V LED20S/830 PSED WH	23 W
38795299	WL131V LED20S/840 PSED WH	23 W
38778599	WL130V LED12S/830 PSU WH	12 W
38779299	WL130V LED12S/840 PSU WH	12 W
38780899	WL130V LED20S/830 PSU WH	22 W
38781599	WL130V LED20S/840 PSU WH	22 W
38782299	WL130V LED20S/830 PSU MDU WH	23 W
38783999	WL130V LED20S/840 PSU MDU WH	23 W

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
40268600	WL131V LED12S/830 PSED EL3 WH	-	-
40269300	WL131V LED12S/840 PSED EL3 WH	-	-
40270900	WL131V LED20S/830 PSED EL3 WH	-	-
40271600	WL131V LED20S/840 PSED EL3 WH	-	-
40272300	WL131V LED34S/830 PSED WH	-	-
40273000	WL131V LED34S/840 PSED WH	-	-
40274700	WL131V LED34S/830 PSED EL3 WH	-	-
40275400	WL131V LED34S/840 PSED EL3 WH	-	-
40282200	WL131V LED12S/830 PSR EL3 MDU WH	-	-
40283900	WL131V LED12S/840 PSR EL3 MDU WH	-	-
40284600	WL131V LED20S/830 PSR EL3 MDU WH	-	-
40285300	WL131V LED20S/840 PSR EL3 MDU WH	-	-
40286000	WL131V LED34S/830 PSR EL3 MDU WH	-	-
40287700	WL131V LED34S/840 PSR EL3 MDU WH	-	-
34003699	WL131V LED20S/840 PSU WH	-	-
38784699	WL131V LED34S/830 PSU WH	38000 h	18000 h
38785399	WL131V LED34S/840 PSU WH	38000 h	18000 h

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
38786099	WL131V LED12S/830 PSR MDU WH	38000 h	18000 h
38787799	WL131V LED12S/840 PSR MDU WH	38000 h	18000 h
38788499	WL131V LED20S/830 PSR MDU WH	38000 h	18000 h
38789199	WL131V LED20S/840 PSR MDU WH	38000 h	18000 h
38790799	WL131V LED34S/830 PSR MDU WH	38000 h	18000 h
38791499	WL131V LED34S/840 PSR MDU WH	38000 h	18000 h
38792199	WL131V LED12S/830 PSED WH	38000 h	18000 h
38793899	WL131V LED12S/840 PSED WH	38000 h	18000 h
38794599	WL131V LED20S/830 PSED WH	38000 h	18000 h
38795299	WL131V LED20S/840 PSED WH	38000 h	18000 h
38778599	WL130V LED12S/830 PSU WH	-	-
38779299	WL130V LED12S/840 PSU WH	-	-
38780899	WL130V LED20S/830 PSU WH	-	-
38781599	WL130V LED20S/840 PSU WH	-	-
38782299	WL130V LED20S/830 PSU MDU WH	-	-
38783999	WL130V LED20S/840 PSU MDU WH	-	-

CoreLine Wall-mounted

