



CoreLine Wall-mounted – the clear choice for LED

CoreLine Wall-mounted

CoreLine Wall-mounted is a circular-shaped surface-mounted luminaire that is easy to apply in circulation areas such as hallways and staircases. The modern unobtrusive design, in combination with its homogeneous light distribution it delivers, ensures that this luminaire blends into most building architectures. With the push-in connectors, installation is fast and straightforward.

Benefits

- Universal solution covering various application requirements
- Slim and unobtrusive design
- Delivering the right visual comfort in common areas
- Direct replacement for traditional wall-mounted luminaires

Features

- Homogeneous light effect to cater for visual comfort
- Three lumen packages to cater for diverse applications
- Water- and vandal-proof as standard
- Easy installation with push-in connectors and through wiring possibility
- Optional emergency lighting (incl. self-test)
- Optional motion detector, including daylight sensing, dimming and grouping function
- Optional DALI versions

CoreLine Wall-mounted

Application

- Corridors
- Staircases
- Entrance areas
- Restrooms
- Emergency exits
- Parking garages
- Outdoor safety lighting

Specifications

Type	WL130V (slim version)
	WL131V (deeper version)
Light source	Non-replaceable LED module
Power (+/-10%)	12 W (LED12S version)
	22 W (LED20S version)
	36 W (LED34S version)
Beam angle	120°
Luminous flux	1200 lm (LED12S version)
	2000 lm (LED20S version)
	3400 lm (LED34S version)
Correlated Color Temperature	3000 or 4000 K
Color Rendering Index	≥ 80
Median useful life	50,000 hours
L70B50	
Median useful life	38,000 hours
L80B50	
Median useful life	18,000 hours
L90B50	
Average ambient temperature	+25 °C

Operating temperature range	-20 to +35 °C (wall-mounted position)
	-20 to +25 °C (ceiling-mounted position)
	0 to +25 °C (emergency lighting)
Driver	Built-in, replaceable
Mains voltage	220-240V / 50-60 Hz
Dimming	Non-dimmable (PSU versions)
	Dimmable (PSR and DALI versions)
Options	Emergency lighting (integrated): 3 hours (EL3)
	Movement detection unit (integrated): on/off switch with day light override including grouping functionality (MDU)
	DALI driver and movement detection unit (integrated)
Material	Housing: Polyamide
	Difuser: high grade polycarbonate, UV resistant
Color	White (RAL 9003)
Optical cover	Polycarbonate difuser
Connection	Push-in connector
Maintenance	LED module closed, no internal cleaning required
Installation	Screw mounting, directly onto surface
	4-point screw installation of housing to wall
	Twist lock connection diffuser to housing
	Through-wiring possible

Versions



CoreLine Wall-mounted




CoreLine Wall-Mounted Gen2

CoreLine Wall-mounted

Product details



CoreLine_Wall-mounted-
WL131V_D35_CTO_PSD-DPP.TIF




CoreLine_Wall-mounted-
WL130V-2DPP.TIF



CoreLine_Wall-mounted-
WL131V_D35_CTO_PSR_MDU-
DPP.TIF



CoreLine_Wall-mounted-
WL130V_CTO-DPP.TIF



CoreLine_Wall-mounted-
WL130V-1DPP.TIF



CoreLine_Wall-mounted-
WL130V_D35_CTO_MDU-DPP.TIF

CoreLine Wall-mounted

Application Conditions

Ambient temperature range -20 to +40 °C

Approval and Application

Mech. impact protection code IK08

Ingress protection code IP65

General Information

Beam angle of light source 120 °

CE mark CE mark

Protection class IEC Safety class II

Optical cover/lens type Opal bowl with painted cover

Driver included Yes

ENEC mark ENEC mark

Light source replaceable No

Number of gear units 1 unit

Optic type Opal prismatic reflector

Initial Performance (IEC Compliant)

Init. Color Rendering Index 80

Luminous flux tolerance +/-10%

Mechanical and Housing

Color White

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
910500465390	WL131V LED12S/830 PSED EL3 WH	10%	No
910500465391	WL131V LED12S/840 PSED EL3 WH	10%	No
910500465392	WL131V LED20S/830 PSED EL3 WH	10%	No
910500465393	WL131V LED20S/840 PSED EL3 WH	10%	No
910500465394	WL131V LED34S/830 PSED WH	10%	No
910500465395	WL131V LED34S/840 PSED WH	10%	No
910500465396	WL131V LED34S/830 PSED EL3 WH	10%	No
910500465397	WL131V LED34S/840 PSED EL3 WH	10%	No
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	20%	Yes
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	20%	Yes
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	20%	Yes
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	20%	Yes
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	20%	Yes
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	20%	Yes
910500465894	WL131V LED12S/830 PSU EL3 WH	Not applicable	Yes
910500465895	WL131V LED12S/840 PSU EL3 WH	Not applicable	Yes
910500465896	WL131V LED20S/830 PSU EL3 WH	Not applicable	Yes
910500465897	WL131V LED20S/840 PSU EL3 WH	Not applicable	Yes
911401807080	WL131V LED12S/830 PSU WH	Not applicable	Not applicable
911401807180	WL131V LED12S/840 PSU WH	Not applicable	Not applicable
911401807280	WL131V LED20S/830 PSU WH	Not applicable	Not applicable
911401807380	WL131V LED20S/840 PSU WH	Not applicable	Not applicable
912401483188	WL131V LED34S/830 PSU WH	Not applicable	Yes
912401483189	WL131V LED34S/840 PSU WH	Not applicable	Yes
912401483190	WL131V LED12S/830 PSR MDU WH	10%	Yes
912401483191	WL131V LED12S/840 PSR MDU WH	10%	Yes
912401483192	WL131V LED20S/830 PSR MDU WH	10%	Yes
912401483193	WL131V LED20S/840 PSR MDU WH	10%	Yes
912401483194	WL131V LED34S/830 PSR MDU WH	10%	Yes
912401483195	WL131V LED34S/840 PSR MDU WH	10%	Yes
912401483196	WL131V LED12S/830 PSED WH	10%	Yes
912401483197	WL131V LED12S/840 PSED WH	10%	Yes
912401483198	WL131V LED20S/830 PSED WH	10%	Yes
912401483199	WL131V LED20S/840 PSED WH	10%	Yes
912401483182	WL130V LED12S/830 PSU WH	Not applicable	Yes
912401483183	WL130V LED12S/840 PSU WH	Not applicable	Yes
912401483184	WL130V LED20S/830 PSU WH	Not applicable	Yes
912401483185	WL130V LED20S/840 PSU WH	Not applicable	Yes
912401483186	WL130V LED20S/830 PSU MDU WH	Not applicable	Yes
912401483187	WL130V LED20S/840 PSU MDU WH	Not applicable	Yes

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910500465390	WL131V LED12S/830 PSED EL3 WH	Yes	910500465396	WL131V LED34S/830 PSED EL3 WH	Yes
910500465391	WL131V LED12S/840 PSED EL3 WH	Yes	910500465397	WL131V LED34S/840 PSED EL3 WH	Yes
910500465392	WL131V LED20S/830 PSED EL3 WH	Yes	910500465405	WL131V LED12S/830 PSR EL3 MDU WH	Yes
910500465393	WL131V LED20S/840 PSED EL3 WH	Yes	910500465406	WL131V LED12S/840 PSR EL3 MDU WH	Yes
910500465394	WL131V LED34S/830 PSED WH	Yes	910500465407	WL131V LED20S/830 PSR EL3 MDU WH	Yes
910500465395	WL131V LED34S/840 PSED WH	Yes	910500465408	WL131V LED20S/840 PSR EL3 MDU WH	Yes

CoreLine Wall-mounted

Order Code	Full Product Name	Dimmable
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	Yes
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	Yes
910500465894	WL131V LED12S/830 PSU EL3 WH	No
910500465895	WL131V LED12S/840 PSU EL3 WH	No
910500465896	WL131V LED20S/830 PSU EL3 WH	No
910500465897	WL131V LED20S/840 PSU EL3 WH	No
911401807080	WL131V LED12S/830 PSU WH	No
911401807180	WL131V LED12S/840 PSU WH	No
911401807280	WL131V LED20S/830 PSU WH	No
911401807380	WL131V LED20S/840 PSU WH	No
912401483188	WL131V LED34S/830 PSU WH	No
912401483189	WL131V LED34S/840 PSU WH	No
912401483190	WL131V LED12S/830 PSR MDU WH	Yes
912401483191	WL131V LED12S/840 PSR MDU WH	Yes

Order Code	Full Product Name	Dimmable
912401483192	WL131V LED20S/830 PSR MDU WH	Yes
912401483193	WL131V LED20S/840 PSR MDU WH	Yes
912401483194	WL131V LED34S/830 PSR MDU WH	Yes
912401483195	WL131V LED34S/840 PSR MDU WH	Yes
912401483196	WL131V LED12S/830 PSED WH	Yes
912401483197	WL131V LED12S/840 PSED WH	Yes
912401483198	WL131V LED20S/830 PSED WH	Yes
912401483199	WL131V LED20S/840 PSED WH	Yes
912401483182	WL130V LED12S/830 PSU WH	No
912401483183	WL130V LED12S/840 PSU WH	No
912401483184	WL130V LED20S/830 PSU WH	No
912401483185	WL130V LED20S/840 PSU WH	No
912401483186	WL130V LED20S/830 PSU MDU WH	No
912401483187	WL130V LED20S/840 PSU MDU WH	No

Operating and Electrical

Order Code	Full Product Name	Input Voltage
910500465390	WL131V LED12S/830 PSED EL3 WH	220-240 V
910500465391	WL131V LED12S/840 PSED EL3 WH	220-240 V
910500465392	WL131V LED20S/830 PSED EL3 WH	220-240 V
910500465393	WL131V LED20S/840 PSED EL3 WH	220-240 V
910500465394	WL131V LED34S/830 PSED WH	220-240 V
910500465395	WL131V LED34S/840 PSED WH	220-240 V
910500465396	WL131V LED34S/830 PSED EL3 WH	220-240 V
910500465397	WL131V LED34S/840 PSED EL3 WH	220-240 V
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	220-240 V
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	220-240 V
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	220-240 V
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	220-240 V
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	220-240 V
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	220-240 V
910500465894	WL131V LED12S/830 PSU EL3 WH	220/240 V
910500465895	WL131V LED12S/840 PSU EL3 WH	220/240 V
910500465896	WL131V LED20S/830 PSU EL3 WH	220/240 V
910500465897	WL131V LED20S/840 PSU EL3 WH	220/240 V
911401807080	WL131V LED12S/830 PSU WH	220/240 V
911401807180	WL131V LED12S/840 PSU WH	220/240 V

Order Code	Full Product Name	Input Voltage
911401807280	WL131V LED20S/830 PSU WH	220/240 V
911401807380	WL131V LED20S/840 PSU WH	220/240 V
912401483188	WL131V LED34S/830 PSU WH	220-240 V
912401483189	WL131V LED34S/840 PSU WH	220-240 V
912401483190	WL131V LED12S/830 PSR MDU WH	220-240 V
912401483191	WL131V LED12S/840 PSR MDU WH	220-240 V
912401483192	WL131V LED20S/830 PSR MDU WH	220-240 V
912401483193	WL131V LED20S/840 PSR MDU WH	220-240 V
912401483194	WL131V LED34S/830 PSR MDU WH	220-240 V
912401483195	WL131V LED34S/840 PSR MDU WH	220-240 V
912401483196	WL131V LED12S/830 PSED WH	220-240 V
912401483197	WL131V LED12S/840 PSED WH	220-240 V
912401483198	WL131V LED20S/830 PSED WH	220-240 V
912401483199	WL131V LED20S/840 PSED WH	220-240 V
912401483182	WL130V LED12S/830 PSU WH	220-240 V
912401483183	WL130V LED12S/840 PSU WH	220-240 V
912401483184	WL130V LED20S/830 PSU WH	220-240 V
912401483185	WL130V LED20S/840 PSU WH	220-240 V
912401483186	WL130V LED20S/830 PSU MDU WH	220-240 V
912401483187	WL130V LED20S/840 PSU MDU WH	220-240 V

General Information (1/2)

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	
				Gear	Glow-wire test
910500465390	WL131V	Emergency lighting	-	-	Temperature 850
	LED12S/830	lighting 3			°C, duration 30 s
	PSED EL3	hours			
	WH	duration			
910500465391	WL131V	Emergency lighting	-	-	Temperature 850
	LED12S/840	lighting 3			°C, duration 30 s
	PSED EL3	hours			
	WH	duration			

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	
				Gear	Glow-wire test
910500465392	WL131V	Emergency lighting	-	-	Temperature 850
	LED20S/830	lighting 3			°C, duration 30 s
	PSED EL3	hours			
	WH	duration			
910500465393	WL131V	Emergency lighting	-	-	Temperature 850
	LED20S/840	lighting 3			°C, duration 30 s
	PSED EL3	hours			
	WH	duration			

CoreLine Wall-mounted

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
910500465394	WL131V LED34S/830 PSED WH	-	-	-	Temperature 850 °C, duration 30 s
910500465395	WL131V LED34S/840 PSED WH	-	-	-	Temperature 850 °C, duration 30 s
910500465396	WL131V LED34S/830 PSED EL3 WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465397	WL131V LED34S/840 PSED EL3 WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	Emergency lighting 3 hours duration	-	-	Temperature 850 °C, duration 30 s
910500465894	WL131V LED12S/830 PSU EL3 WH	Emergency lighting 3 hours duration	For mounting on easily flammable surfaces	-	Temperature 850 °C, duration 30 s
910500465895	WL131V LED12S/840 PSU EL3 WH	Emergency lighting 3 hours duration	For mounting on easily flammable surfaces	-	Temperature 850 °C, duration 30 s
910500465896	WL131V LED20S/830 PSU EL3 WH	Emergency lighting 3 hours duration	For mounting on easily flammable surfaces	-	Temperature 850 °C, duration 30 s

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
910500465897	WL131V LED20S/840 PSU EL3 WH	Emergency lighting 3 hours duration	For mounting on easily flammable surfaces	-	Temperature 850 °C, duration 30 s
911401807080	WL131V LED12S/830 PSU WH	-	For mounting on easily flammable surfaces	-	Temperature 650 °C, duration 30 s
911401807180	WL131V LED12S/840 PSU WH	-	For mounting on easily flammable surfaces	-	Temperature 650 °C, duration 30 s
911401807280	WL131V LED20S/830 PSU WH	-	For mounting on easily flammable surfaces	-	Temperature 650 °C, duration 30 s
911401807380	WL131V LED20S/840 PSU WH	-	For mounting on easily flammable surfaces	-	Temperature 650 °C, duration 30 s
912401483188	WL131V LED34S/830 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483189	WL131V LED34S/840 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483190	WL131V LED12S/830 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483191	WL131V LED12S/840 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483192	WL131V LED20S/830 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483193	WL131V LED20S/840 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483194	WL131V LED34S/830 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483195	WL131V LED34S/840 PSR MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483196	WL131V LED12S/830 PSED WH	-	-	-	Temperature 650 °C, duration 30 s
912401483197	WL131V LED12S/840 PSED WH	-	-	-	Temperature 650 °C, duration 30 s

CoreLine Wall-mounted

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
912401483198	WL131V LED20S/830 PSED WH	-	-	-	Temperature 650 °C, duration 30 s
912401483199	WL131V LED20S/840 PSED WH	-	-	-	Temperature 650 °C, duration 30 s
912401483182	WL130V LED12S/830 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483183	WL130V LED12S/840 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483184	WL130V LED20S/830 PSU WH	-	-	-	Temperature 650 °C, duration 30 s

Order Code	Full Product Name	Emergency lighting	Flammability mark	Gear	Glow-wire test
912401483185	WL130V LED20S/840 PSU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483186	WL130V LED20S/830 PSU MDU WH	-	-	-	Temperature 650 °C, duration 30 s
912401483187	WL130V LED20S/840 PSU MDU WH	-	-	-	Temperature 650 °C, duration 30 s

General Information (2/2)

Order Code	Full Product Name	Lamp family code	Embedded control	Product Family Code	Service tag
910500465390	WL131V LED12S/830 PSED EL3 WH	LED12	-	WL131V	-
910500465391	WL131V LED12S/840 PSED EL3 WH	LED12	-	WL131V	-
910500465392	WL131V LED20S/830 PSED EL3 WH	LED20	-	WL131V	-
910500465393	WL131V LED20S/840 PSED EL3 WH	LED20	-	WL131V	-
910500465394	WL131V LED34S/830 PSED WH	LED34S	-	WL131V	-
910500465395	WL131V LED34S/840 PSED WH	LED34S	-	WL131V	-
910500465396	WL131V LED34S/830 PSED EL3 WH	LED34S	-	WL131V	-
910500465397	WL131V LED34S/840 PSED EL3 WH	LED34S	-	WL131V	-
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	LED12	Movement detection unit	WL131V	-
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	LED12	Movement detection unit	WL131V	-
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	LED20	Movement detection unit	WL131V	-
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	LED20	Movement detection unit	WL131V	-
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	LED34S	Movement detection unit	WL131V	-
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	LED34S	Movement detection unit	WL131V	-

Order Code	Full Product Name	Lamp family code	Embedded control	Product Family Code	Service tag
910500465894	WL131V LED12S/830 PSU EL3 WH	LED12	-	WL131V	-
910500465895	WL131V LED12S/840 PSU EL3 WH	LED12	-	WL131V	-
910500465896	WL131V LED20S/830 PSU EL3 WH	LED20	-	WL131V	-
910500465897	WL131V LED20S/840 PSU EL3 WH	LED20	-	WL131V	-
911401807080	WL131V LED12S/830 PSU WH	LED12	-	-	-
911401807180	WL131V LED12S/840 PSU WH	LED12	-	-	-
911401807280	WL131V LED20S/830 PSU WH	LED20	-	-	-
911401807380	WL131V LED20S/840 PSU WH	LED20	-	-	-
912401483188	WL131V LED34S/830 PSU WH	LED34S	-	-	Yes
912401483189	WL131V LED34S/840 PSU WH	LED34S	-	-	Yes
912401483190	WL131V LED12S/830 PSR MDU WH	LED12	Movement detection unit	-	Yes
912401483191	WL131V LED12S/840 PSR MDU WH	LED12	Movement detection unit	-	Yes
912401483192	WL131V LED20S/830 PSR MDU WH	LED20	Movement detection unit	-	Yes

CoreLine Wall-mounted

Order Code	Full Product Name	Lamp family code	Embedded control	Product Family Code	Service tag
912401483193	WL131V LED20S/840 PSR MDU WH	LED20	Movement detection unit	-	Yes
912401483194	WL131V LED34S/830 PSR MDU WH	LED34S	Movement detection unit	-	Yes
912401483195	WL131V LED34S/840 PSR MDU WH	LED34S	Movement detection unit	-	Yes
912401483196	WL131V LED12S/830 PSED WH	LED12	-	-	Yes
912401483197	WL131V LED12S/840 PSED WH	LED12	-	-	Yes
912401483198	WL131V LED20S/830 PSED WH	LED20	-	-	Yes
912401483199	WL131V LED20S/840 PSED WH	LED20	-	-	Yes
912401483182	WL130V LED12S/830 PSU WH	LED12	-	-	Yes

Order Code	Full Product Name	Lamp family code	Embedded control	Product Family Code	Service tag
912401483183	WL130V LED12S/840 PSU WH	LED12	-	-	Yes
912401483184	WL130V LED20S/830 PSU WH	LED20	-	-	Yes
912401483185	WL130V LED20S/840 PSU WH	LED20	-	-	Yes
912401483186	WL130V LED20S/830 PSU MDU WH	LED20	Movement detection unit	-	Yes
912401483187	WL130V LED20S/840 PSU MDU WH	LED20	Movement detection unit	-	Yes

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910500465390	WL131V LED12S/830 PSED EL3 WH	(0.44, 0.41)	3000 K	100 lm/W	1200 lm
910500465391	WL131V LED12S/840 PSED EL3 WH	(0.39, 0.39)	4000 K	100 lm/W	1200 lm
910500465392	WL131V LED20S/830 PSED EL3 WH	(0.44, 0.41)	3000 K	91 lm/W	2000 lm
910500465393	WL131V LED20S/840 PSED EL3 WH	(0.39, 0.39)	4000 K	91 lm/W	2000 lm
910500465394	WL131V LED34S/830 PSED WH	(0.44, 0.41)	3000 K	94 lm/W	3400 lm
910500465395	WL131V LED34S/840 PSED WH	(0.39, 0.39)	4000 K	94 lm/W	3400 lm
910500465396	WL131V LED34S/830 PSED EL3 WH	(0.44, 0.41)	3000 K	94 lm/W	3400 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
910500465397	WL131V LED34S/840 PSED EL3 WH	(0.39, 0.39)	4000 K	94 lm/W	3400 lm
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	(0.44, 0.41)	3000 K	100 lm/W	1200 lm
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	(0.39, 0.39)	4000 K	100 lm/W	1200 lm
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	(0.44, 0.41)	3000 K	91 lm/W	2000 lm
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	(0.39, 0.39)	4000 K	91 lm/W	2000 lm
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	(0.44, 0.41)	3000 K	94 lm/W	3400 lm
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	(0.39, 0.39)	4000 K	94 lm/W	3400 lm

CoreLine Wall-mounted

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSR EL3 MDU WH				
910500465894	WL131V LED12S/830 PSU EL3 WH	(0.44, 0.41) SDCM<3	3000 K	80 lm/W	1200 lm
910500465895	WL131V LED12S/840 PSU EL3 WH	(0.39, 0.39) SDCM<3	4000 K	80 lm/W	1200 lm
910500465896	WL131V LED20S/830 PSU EL3 WH	(0.44, 0.41) SDCM<3	3000 K	80 lm/W	2000 lm
910500465897	WL131V LED20S/840 PSU EL3 WH	(0.39, 0.39) SDCM<3	4000 K	80 lm/W	2000 lm
911401807080	WL131V LED12S/830 PSU WH	(0.44, 0.41) SDCM<3	3000 K	100 lm/W	1200 lm
911401807180	WL131V LED12S/840 PSU WH	(0.39, 0.39) SDCM<3	4000 K	100 lm/W	1200 lm
911401807280	WL131V LED20S/830 PSU WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	2000 lm
911401807380	WL131V LED20S/840 PSU WH	(0.39, 0.39) SDCM<3	4000 K	90 lm/W	2000 lm
912401483188	WL131V LED34S/830 PSU WH	(0.44, 0.41) SDCM<3	3000 K	95 lm/W	3400 lm
912401483189	WL131V LED34S/840 PSU WH	(0.39, 0.39) SDCM<3	4000 K	95 lm/W	3400 lm
912401483190	WL131V LED12S/830 PSR MDU WH	(0.44, 0.41) SDCM<3	3000 K	80 lm/W	1200 lm
912401483191	WL131V LED12S/840 PSR MDU WH	(0.39, 0.39) SDCM<3	4000 K	80 lm/W	1200 lm
912401483192	WL131V LED20S/830	(0.44, 0.41) SDCM<3	3000 K	80 lm/W	2000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	PSR MDU WH				
912401483193	WL131V LED20S/840 PSR MDU WH	(0.39, 0.39) SDCM<3	4000 K	80 lm/W	2000 lm
912401483194	WL131V LED34S/830 PSR MDU WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	3400 lm
912401483195	WL131V LED34S/840 PSR MDU WH	(0.39, 0.39) SDCM<3	4000 K	90 lm/W	3400 lm
912401483196	WL131V LED12S/830 PSED WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	1200 lm
912401483197	WL131V LED12S/840 PSED WH	(0.39, 0.39) SDCM<3	4000 K	90 lm/W	1200 lm
912401483198	WL131V LED20S/830 PSED WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	2000 lm
912401483199	WL131V LED20S/840 PSED WH	(0.39, 0.39) SDCM<3	4000 K	90 lm/W	2000 lm
912401483182	WL130V LED12S/830 PSU WH	(0.44, 0.41) SDCM<3	3000 K	100 lm/W	1200 lm
912401483183	WL130V LED12S/840 PSU WH	(0.39, 0.39) SDCM<3	4000 K	100 lm/W	1200 lm
912401483184	WL130V LED20S/830 PSU WH	(0.44, 0.41) SDCM<3	3000 K	90 lm/W	2000 lm
912401483185	WL130V LED20S/840 PSU WH	(0.44, 0.41) SDCM<3	4000 K	90 lm/W	2000 lm
912401483186	WL130V LED20S/830 PSU MDU WH	(0.44, 0.41) SDCM<3	3000 K	80 lm/W	2000 lm
912401483187	WL130V LED20S/840 PSU MDU WH	(0.39, 0.39) SDCM<3	4000 K	80 lm/W	2000 lm

Initial Performance (IEC Compliant) (2/2)

CoreLine Wall-mounted

Order Code	Full Product Name	Initial input power
910500465390	WL131V LED12S/830 PSED EL3 WH	12 W
910500465391	WL131V LED12S/840 PSED EL3 WH	12 W
910500465392	WL131V LED20S/830 PSED EL3 WH	22 W
910500465393	WL131V LED20S/840 PSED EL3 WH	22 W
910500465394	WL131V LED34S/830 PSED WH	36 W
910500465395	WL131V LED34S/840 PSED WH	36 W
910500465396	WL131V LED34S/830 PSED EL3 WH	36 W
910500465397	WL131V LED34S/840 PSED EL3 WH	36 W
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	12 W
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	12 W
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	22 W
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	22 W
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	36 W
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	36 W
910500465894	WL131V LED12S/830 PSU EL3 WH	15 W
910500465895	WL131V LED12S/840 PSU EL3 WH	15 W
910500465896	WL131V LED20S/830 PSU EL3 WH	25 W
910500465897	WL131V LED20S/840 PSU EL3 WH	25 W
911401807080	WL131V LED12S/830 PSU WH	12 W
911401807180	WL131V LED12S/840 PSU WH	12 W

Order Code	Full Product Name	Initial input power
911401807280	WL131V LED20S/830 PSU WH	22 W
911401807380	WL131V LED20S/840 PSU WH	22 W
912401483188	WL131V LED34S/830 PSU WH	36 W
912401483189	WL131V LED34S/840 PSU WH	36 W
912401483190	WL131V LED12S/830 PSR MDU WH	15 W
912401483191	WL131V LED12S/840 PSR MDU WH	15 W
912401483192	WL131V LED20S/830 PSR MDU WH	25 W
912401483193	WL131V LED20S/840 PSR MDU WH	25 W
912401483194	WL131V LED34S/830 PSR MDU WH	38 W
912401483195	WL131V LED34S/840 PSR MDU WH	38 W
912401483196	WL131V LED12S/830 PSED WH	13 W
912401483197	WL131V LED12S/840 PSED WH	13 W
912401483198	WL131V LED20S/830 PSED WH	23 W
912401483199	WL131V LED20S/840 PSED WH	23 W
912401483182	WL130V LED12S/830 PSU WH	12 W
912401483183	WL130V LED12S/840 PSU WH	12 W
912401483184	WL130V LED20S/830 PSU WH	22 W
912401483185	WL130V LED20S/840 PSU WH	22 W
912401483186	WL130V LED20S/830 PSU MDU WH	23 W
912401483187	WL130V LED20S/840 PSU MDU WH	23 W

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
910500465390	WL131V LED12S/830 PSED EL3 WH	-	-
910500465391	WL131V LED12S/840 PSED EL3 WH	-	-
910500465392	WL131V LED20S/830 PSED EL3 WH	-	-
910500465393	WL131V LED20S/840 PSED EL3 WH	-	-
910500465394	WL131V LED34S/830 PSED WH	-	-
910500465395	WL131V LED34S/840 PSED WH	-	-
910500465396	WL131V LED34S/830 PSED EL3 WH	-	-
910500465397	WL131V LED34S/840 PSED EL3 WH	-	-
910500465405	WL131V LED12S/830 PSR EL3 MDU WH	-	-
910500465406	WL131V LED12S/840 PSR EL3 MDU WH	-	-
910500465407	WL131V LED20S/830 PSR EL3 MDU WH	-	-
910500465408	WL131V LED20S/840 PSR EL3 MDU WH	-	-
910500465409	WL131V LED34S/830 PSR EL3 MDU WH	-	-
910500465410	WL131V LED34S/840 PSR EL3 MDU WH	-	-
910500465894	WL131V LED12S/830 PSU EL3 WH	-	-
910500465895	WL131V LED12S/840 PSU EL3 WH	-	-
910500465896	WL131V LED20S/830 PSU EL3 WH	-	-

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
910500465897	WL131V LED20S/840 PSU EL3 WH	-	-
911401807080	WL131V LED12S/830 PSU WH	-	-
911401807180	WL131V LED12S/840 PSU WH	-	-
911401807280	WL131V LED20S/830 PSU WH	-	-
911401807380	WL131V LED20S/840 PSU WH	-	-
912401483188	WL131V LED34S/830 PSU WH	38000 h	18000 h
912401483189	WL131V LED34S/840 PSU WH	38000 h	18000 h
912401483190	WL131V LED12S/830 PSR MDU WH	38000 h	18000 h
912401483191	WL131V LED12S/840 PSR MDU WH	38000 h	18000 h
912401483192	WL131V LED20S/830 PSR MDU WH	38000 h	18000 h
912401483193	WL131V LED20S/840 PSR MDU WH	38000 h	18000 h
912401483194	WL131V LED34S/830 PSR MDU WH	38000 h	18000 h
912401483195	WL131V LED34S/840 PSR MDU WH	38000 h	18000 h
912401483196	WL131V LED12S/830 PSED WH	38000 h	18000 h
912401483197	WL131V LED12S/840 PSED WH	38000 h	18000 h
912401483198	WL131V LED20S/830 PSED WH	38000 h	18000 h
912401483199	WL131V LED20S/840 PSED WH	38000 h	18000 h
912401483182	WL130V LED12S/830 PSU WH	-	-
912401483183	WL130V LED12S/840 PSU WH	-	-
912401483184	WL130V LED20S/830 PSU WH	-	-
912401483185	WL130V LED20S/840 PSU WH	-	-
912401483186	WL130V LED20S/830 PSU MDU WH	-	-
912401483187	WL130V LED20S/840 PSU MDU WH	-	-

CoreLine Wall-mounted

