



CDM-SA/T – the greener way to light up the night

CDM-SA/T

With a high luminous efficacy producing more lumens per watt than standard Architainment lamps, the CDM-SA/T is the greener alternative to light up the night. In addition, the optimal lamp filling and short arc of the lamp create a high beam intensity and excellent color rendering.

Benefits

- High lumen output
- High beam intensity
- Excellent colors

Features

- High luminous efficacy
- Compact arc
- Optimal lamp filling

Application

- Advertising/text projection
- Fibre optics
- Decorative outdoor, architectural lighting
- Shops and shop windows

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

CDM-SA/T

Versions



Dimensional drawing



Product

CDM-SA/T 150W/942 1CT/12

Colour Rendering Diagrams



