



# MSD Platinum – The power to light your creativity

## MSD Platinum (Touring/Stage)

The MSD Platinum lamps open up new levels of creative freedom in entertainment lighting, with powerful, compact and brilliantly intense light. Their compact, lightweight design provides the freedom to create smaller, lighter luminaires – for use at any location on stage. And their short arc, high color temperature and innovative reflector produce a sparkling, high beam intensity for outstanding color reproduction. They also offer long and reliable lifetime, high efficacy and fast replacement times. It all adds up to an intensely exciting creative experience.

### Benefits

- High beam intensity
- Freedom to create smaller and lighter fixtures
- High perceived brightness
- A long and reliable performance

### Features

- Very short arc
- Compact system
- High correlated color temperature
- Philips Platinum technology

### Application

- Events
- Shows/Theater
- Touring/Stage

# MSD Platinum (Touring/Stage)

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions



MSD Platinum 5 R and 14 R




MSD Platinum 15 R, 16 R



MSD Platinum 11 R / 17 RA

## Dimensional drawing




Product	D (max)	T (max)	O	C (max)
MSD Platinum 17 RA 1CT/8	51.4 mm	10.0 mm	1.0 mm	63 mm

Product	D (max)	T (max)	O	C (max)
MSD Platinum 5 R 1CT/8	51.4 mm	6.8 mm	1.0 mm	57.1 mm
MSD Platinum 14 R 1CT/8	51.5 mm	6.8 mm	0.95 mm	57.1 mm

# MSD Platinum (Touring/Stage)

## Dimensional drawing



### Product

MSD Platinum 15 R 1CT/8

### Controls and Dimming

Dimmable Yes

### General Information

Cap-Base -  
Main Application Stage/Touring  
Operating Position UNIVERSAL

### Light Technical

Color Code 2

## Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
928190805314	MSD Platinum 5 R 1CT/8	189 W
928196105314	MSD Platinum 14 R 1CT/8	280 W

Order Code	Full Product Name	Power (Rated) (Nom)
928191605314	MSD Platinum 15 R 1CT/8	300 W
928197305314	MSD Platinum 17 RA 1CT/8	350.0 W

## General Information

Order Code	Full Product Name	Life To 50% Failures (Nom)	System Description
928190805314	MSD Platinum 5 R 1CT/8	3000 h	Reflector-E20.6
928196105314	MSD Platinum 14 R 1CT/8	2000 h	Reflector-E20.6

Order Code	Full Product Name	Life To 50% Failures (Nom)	System Description
928191605314	MSD Platinum 15 R 1CT/8	2000 h	na
928197305314	MSD Platinum 17 RA 1CT/8	1500 h	Reflector-E20.9

## Light Technical

Order Code	Full Product Name	Correlated Color	Color Rendering	Luminous Flux (Min)	Luminous Flux (Nom)
		Temperature (Nom)	Index (Nom)		
928190805314	MSD Platinum 5 R 1CT/8	8000 K	-	7100 lm	7950 lm
928196105314	MSD Platinum 14 R 1CT/8	7800 K	-	-	12350 lm

Order Code	Full Product Name	Correlated Color	Color Rendering	Luminous Flux (Min)	Luminous Flux (Nom)
		Temperature (Nom)	Index (Nom)		
928191605314	MSD Platinum 15 R 1CT/8	8000 K	-	11000 lm	13500 lm
928197305314	MSD Platinum 17 RA 1CT/8	7000 K	85	-	15250 lm

## MSD Platinum (Touring/Stage)

