



Product Description

MSR Hot Restrike

High-efficiency hot restrike metal halide lamps designed for optimum light collection

Benefits

- High luminous efficacy
- Compact arc (5 - 20 mm)
- Excellent colour rendering
- Dimmable with a stable colour temperature

Features

- Run-up time 2 minutes
- Frosted top of outer bulb to avoid excessively bright centre beam in open face luminaires
- Universal burning position

Application

- Indoor and outdoor filming
- Studios and theatres
- Professional photography
- Solar simulation

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MSR Hot Restrike

Versions



Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 1200	40 mm	10.0	106	108 mm	107	200	67 mm	65	63 mm
HR 1CT/2		mm	mm		mm	mm		mm	

