



Product Description

Flexo Print

Tubular low-pressure mercury vapour discharge lamps

Benefits

- Best match with photo sensitizers
- Highest output on irradiated area

Features

- Internally coated with a white fluorescent powder to convert the short-wave UV radiation into useful actinic radiation
- Emit radiation in the range 380 – 480 nm with a maximum at 420 nm
- Spectral energy distribution in accordance with the spectral sensitivity of a number of diazo copying papers
- For maximum beauty of marine aquaria, TL /03 "Aqua Coral" lamps can be used in combination with full-spectrum "Natural Daylight" fluorescent lamps

Application

- Diazo copying machines
- Marine aquaria
- Phototherapy (neonatal jaundice treatment)

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Flexo Print

Versions



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 60W/10-R SLV/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

