PHILIPS Lighting



Actinic BL TL(-K)/TL-D(-K) – optimized for Electronic Fly Killers

Actinic BL TL(-K)/TL-D(-K)

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- \cdot Design freedom

Features

- \cdot Emits long-wave UV-A radiation in the 350-400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280-315nm)
- 100% lead-free
- \cdot Low mercury content
- Wide power range

Application

Insect traps, Electronic Fly Killers (EFKs)

Actinic BL TL(-K)/TL-D(-K)

Versions






TL-D (K) G13

TL-D(K) G13

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 18W/10	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					

D (max) A (max) B (max) B (min) C (max)

ACTINIC BL TL-DK -	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
30W/10 1SL					

Product



General Information	
Cap-Base	G13
Light Technical	
Color Code	10
Color Designation	Actinic
Mechanical and Housing	
Bulb Shape	Т8

Approval and Application

Actinic BL TL(-K)/TL-D(-K)

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
928019501029	ACTINIC BL TL-DK - 30W/10 1SL	8.0 mg

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
928048001003	Actinic BL TL-D 18W/10 1SL/25	5.0 mg

Operating and Electrical

				Power
		Lamp Current	Voltage	(Rated)
Order Code	Full Product Name	(Nom)	(Nom)	(Nom)
928019501029	ACTINIC BL TL-DK -	0.805 A	45 V	30 W
	30W/10 1SL			

				Power
		Lamp Current	Voltage	(Rated)
Order Code	Full Product Name	(Nom)	(Nom)	(Nom)
928048001003	Actinic BL TL-D 18W/10	0.36 A	59 V	18 W
	1SL/25			

General Information

		Life To 50%	Useful Life	
Order Code	Full Product Name	Failures (Nom)	(Nom)	Main Application
928019501029	ACTINIC BL TL-DK -	2000 h	2000 h	Insect traps
	30W/10 1SL			

		Life To 50%	Useful Life	
Order Code	Full Product Name	Failures (Nom)	(Nom)	Main Application
928048001003	Actinic BL TL-D	13000 h	9000 h	Reprography (R)
	18W/10 1SL/25			

υv

		UV-A Radiation	UV-B/UV-A
Order Code	Full Product Name	100Hr (IEC)	(IEC)
928019501029	ACTINIC BL TL-DK - 30W/10	6.6 W	02 %
	1SL		

		UV-A Radiation	UV-B/UV-A
Order Code	Full Product Name	100Hr (IEC)	(IEC)
928048001003	Actinic BL TL-D 18W/10 1SL/25	5.0 W	0.2 %



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2019, July 19 - data subject to change