



Energy-efficient lighting for industrial and commercial applications

Greenperform Batten

GreenPerform Batten BN208C Dali is a high quality LED batten that delivers significant energy savings of up to 50% comparing to conventional T8 battens. BN208X incorporates the reliable structure, long lifetime LED lighting and the global standard ZigBee control system, to achieve an easy-to-use networked solution. In the mean time, it helps to further increase energy saving maximum to 80% with daylight harvest and occupancy sensor.

Benefits

- High energy saving – up to 50% comparing to TL-8 batten
- Comfort light with accurate colour
- Safe and reliable
- Installation flexibility
- Networking lighting

Features

- System efficacy 117 lm/W, 4,000/6,000 lm
- Frosted PC cover, CRI 80
- Lifetime 50 Khrs @L70, CB/EMC/CE/ASNZ
- Suitable for surface and suspension mounting
- ActiLume Wireless 4.1+PIR/DDR sensor

Greenperform Batten

Application

- General lighting
- Cove lighting
- Indoor parking

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress and as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

Accessories



Ordercode 911401567501,
911401567601, 911401568001,
911401568201, 911401568301

