



Best TCO payback story LED specification Downlight

GreenSpace Downlight G4

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

Benefits

- Energy saving counting on high system efficacy
- Easy
- Integral light weight design, saving installation cost
- Diversity
- 4 lumen package, 3 CCT, 3 Cut-out size, UGR22/25, Fixed/DALI to cater to customers' needs

Features

- System efficiency 95~100lm/W
- CRI 80+, SDCM ≤ 5
- High reliability, 50k hours (L70@25deg)

Application

- Shopping mall
- Retail store
- Office
- Hotel

GreenSpace Downlight G4

Versions



DN290B 1xDLED PSU

DN291B 1xDLED

Application Conditions

Ambient temperature range -20 to +40 °C

Approval and Application

Mech. impact protection code IK02

Ingress protection code IP20

Controls and Dimming

Dimmable No

Operating and Electrical

Input Voltage 220-240 V

General Information

CE mark CE mark

Optical cover/lens type TW

ENEC mark -

Glow-wire test 650/30

Light source replaceable No

Number of gear units 1 unit

Number of light sources 1

Optic type 60-120

UL mark No

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-10%

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial input power
911401564321	DN290B 1xDLED-3000 PSU WH	6.5 W
911401564921	DN291B 1xDLED-3000 PSU WH	11.6 W

GreenSpace Downlight G4

