



Best TCO payback story LED specification Downlight

GreenSpace Downlight G4

GreenSpace Gen4 is the new LED downlight with high efficacy (95~ 100lm/W) delivering substantial energy saving. It offers diverse configurations within 600~2,000lm. GreenSpace Gen4 could apply to shopping mall, retail store and office application with different variants . The lifetime is 50,000 hours (L70 @ 25C)

Benefits

- Energy saving counting on high system efficacy
- Easy
- Integral light weight design, saving installation cost
- Diversity
- 4 lumen package, 3 CCT, 3 Cut-out size, UGR22/25, Fixed/DALI to cater to customers' needs

Features

- System efficiency 95~100lm/W
- CRI 80+, SDCM <5
- High reliability, 50k hours (L70@25deg)

Application

- Shopping mall
- Retail store
- Office
- Hotel

GreenSpace Downlight G4

Versions



DN292B/DN293B 1xDLED ALU

DN291B 1xDLED

DN290B 1xDLED PSU

DN291B 1xDLED



DN292B/DN293B 1xDLED WH

Application Conditions

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Approval and Application

Mech. impact protection code	IK02
Ingress protection code	IP20

Operating and Electrical

Input Voltage	220-240 V
---------------	-----------

General Information

CE mark	CE mark
Optical cover/lens type	TW
ENEC mark	-
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Number of light sources	1
Optic type	60-120
UL mark	No

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401567021	DN293B 1xDLED-3000 PSU ALU	No
911401568721	DN291B 1xDLED-4000 PSD ALU CAU	-
911401579521	DN290B 1xDLED-4000 PSU WH WP	No
911401580321	DN290B 1xDLED-4000 PSU WH CAU WP	No
911401580721	DN291B 1xDLED-4000 PSU WH CAU	No
911401581121	DN292B 1xDLED-4000 PSU WH CAU	No
911401581321	DN293B 1xDLED-4000 PSU WH CAU	No

General Information

GreenSpace Downlight G4

Order Code	Full Product Name	Lamp family code
911401567021	DN293B 1xDLED-3000 PSU ALU	LED26
911401568721	DN291B 1xDLED-4000 PSD ALU CAU	-
911401579521	DN290B 1xDLED-4000 PSU WH WP	-
911401580321	DN290B 1xDLED-4000 PSU WH CAU WP	-

Order Code	Full Product Name	Lamp family code
911401580721	DN291B 1xDLED-4000 PSU WH CAU	-
911401581121	DN292B 1xDLED-4000 PSU WH CAU	-
911401581321	DN293B 1xDLED-4000 PSU WH CAU	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial input power
911401567021	DN293B 1xDLED-3000 PSU ALU	-	22 W
911401568721	DN291B 1xDLED-4000 PSD ALU CAU	4000 K	11.6 W
911401579521	DN290B 1xDLED-4000 PSU WH WP	4000 K	6.5 W
911401580321	DN290B 1xDLED-4000 PSU WH CAU WP	4000 K	6.5 W

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial input power
911401580721	DN291B 1xDLED-4000 PSU WH CAU	4000 K	11.6 W
911401581121	DN292B 1xDLED-4000 PSU WH CAU	4000 K	16 W
911401581321	DN293B 1xDLED-4000 PSU WH CAU	4000 K	22 W

