



# Best Area Lighting Luminaire within Your Budget

## Tango G2 LED

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

### Benefits

- Energy saving: more than 50% of energy saving when compared to conventional floodlight
- Free from lamp replacement
- Low maintenance cost: IP65 housing ensures low maintenance with no need for internal cleaning, resulting in a lower total cost of ownership

### Features



- Optical beam choice of symmetric and asymmetric fulfils majority needs of lighting application
- Painted non-corrosive die-cast aluminum housing and steel bracket
- Universal "U" shape mounting bracket

### Application


- Area lighting
- Industry area
- Façade

# Tango G2 LED

## Versions



BVP282 220-240 V



BVP283 220-240V

### Controls and Dimming

Dimmable No

### General Information

CE mark CE mark

Driver included Yes

### Mechanical and Housing

Colour Aluminum and gray

## Application Conditions

Order Code	Full Product Name	Maximum dim level
01660504	BVP281 LED101/CW 80W 220-240V SWB	-
01660704	BVP281 LED101/CW 80W 220-240V AMB	-
01660804	BVP281 LED50/CW 40W 220-240V SWB	-
01660904	BVP281 LED101/WW 80W 220-240V SMB	-
01661104	BVP281 LED101/WW 80W 220-240V AMB	-
01661204	BVP281 LED50/NW 40W 220-240V SMB	-
01661304	BVP281 LED50/NW 40W 220-240V AMB	-
01661404	BVP281 LED50/CW 40W 220-240V SMB	-
01661604	BVP281 LED50/CW 40W 220-240V AMB	-
01661704	BVP281 LED50/WW 40W 220-240V SMB	-
01661804	BVP281 LED101/CW 80W 220-240V SMB	-
01661904	BVP281 LED101/NW 80W 220-240V AMB	-
01662004	BVP281 LED151/CW 120W 220-240V AMB	-
01662104	BVP281 LED151/WW 120W 220-240V AMB	-
01662204	BVP281 LED151/NW 120W 220-240V AMB	-
01662304	BVP281 LED101/NW 80W 220-240V SWB	-
01662404	BVP281 LED151/CW 120W 220-240V SMB	-
01662504	BVP281 LED151/WW 120W 220-240V SMB	-
01662604	BVP281 LED151/CW 120W 220-240V SWB	-
01662704	BVP281 LED101/NW 80W 220-240V SMB	-
01662804	BVP281 LED151/NW 120W 220-240V SWB	-
01662904	BVP281 LED151/NW 120W 220-240V SMB	-
01663004	BVP282 LED202/WW 160W 220-240V AMB	-

Order Code	Full Product Name	Maximum dim level
01663104	BVP282 LED202/WW 160W 220-240V SWB	-
01663204	BVP282 LED202/NW 160W 220-240V SWB	-
01663304	BVP282 LED202/NW 160W 220-240V AMB	-
01663404	BVP282 LED202/CW 160W 220-240V SMB	-
01663504	BVP282 LED202/CW 160W 220-240V AMB	-
01663604	BVP282 LED202/NW 160W 220-240V SMB	-
01663704	BVP282 LED202/CW 160W 220-240V SWB	-
01663804	BVP282 LED252/WW 200W 220-240V SMB	-
01663904	BVP282 LED252/CW 200W 220-240V SWB	-
01664004	BVP282 LED252/WW 200W 220-240V SWB	-
01664104	BVP282 LED252/NW 200W 220-240V AMB	-
01664204	BVP282 LED252/WW 200W 220-240V AMB	-
01664304	BVP282 LED252/CW 200W 220-240V SMB	-
32985700	BVP282 LED252/CW 200W 220-240V AMB	-
01664504	BVP282 LED252/NW 200W 220-240V SWB	-
01664604	BVP282 LED252/NW 200W 220-240V SMB	-
01664704	BVP282 LED202/WW 160W 220-240V SMB	-
01667002	BVP283 LED311/WW 335W 220-240V NB	-
01667102	BVP283 LED293/WW 315W 220-240V NB	-
01667202	BVP283 LED256/WW 280W 220-240V NB	-
01667302	BVP283 LED224/WW 245W 220-240V NB	-
01667402	BVP283 LED192/WW 210W 220-240V NB	-
01668002	BVP283 LED340/NW 335W 220-240V NB	-

## Tango G2 LED

Order Code	Full Product Name	Maximum dim level
01668102	BVP283 LED320/NW 315W 220-240V NB	-
01668202	BVP283 LED280/NW 280W 220-240V NB	-
01668302	BVP283 LED245/NW 245W 220-240V NB	-
01668402	BVP283 LED210/NW 210W 220-240V NB	-
01668502	BVP283 LED311/WW 335W 220-240V SWB	-
01668602	BVP283 LED307/WW 315W 220-240V SWB	-
01668702	BVP283 LED224/WW 245W 220-240V SWB	-
01668802	BVP283 LED256/WW 280W 220-240V SWB	-
01668902	BVP283 LED192/WW 210W 220-240V SWB	-
01669502	BVP283 LED340/NW 335W 220-240V SWB	-
01669602	BVP283 LED320/NW 315W 220-240V SWB	Not applicable
01669702	BVP283 LED280/NW 280W 220-240V SWB	Not applicable
01669802	BVP283 LED245/NW 245W 220-240V SWB	Not applicable
01669902	BVP283 LED210/NW 210W 220-240V SWB	-
01670002	BVP283 LED311/WW 335W 220-240V AWB	-
01670102	BVP283 LED293/WW 315W 220-240V AWB	-
01670202	BVP283 LED256/WW 280W 220-240V AWB	-
01670302	BVP283 LED224/WW 245W 220-240V AWB	-
01670402	BVP283 LED192/WW 210W 220-240V AWB	-
01671002	BVP283 LED340/NW 335W 220-240V AWB	-
01671102	BVP283 LED320/NW 315W 220-240V AWB	Not applicable
01671202	BVP283 LED280/NW 280W 220-240V AWB	Not applicable
01671302	BVP283 LED245/NW 245W 220-240V AWB	Not applicable
01671402	BVP283 LED210/NW 210W 220-240V AWB	-
01689102	BVP283 LED327/WW 350W 220-240V NB	-
01689202	BVP283 LED355/NW 350W 220-240V AWB	Not applicable
01689402	BVP283 LED327/WW 350W 220-240V AWB	-
01689502	BVP283 LED355/NW 350W 220-240V SWB	Not applicable
01689702	BVP283 LED327/WW 350W 220-240V SWB	-
01689802	BVP283 LED355/NW 350W 220-240V NB	-
01692505	BVP283 LED262/CW 200W 220-240V AWB	-
01692605	BVP283 LED262/CW 200W 220-240V AWBE	-
01692705	BVP283 LED262/CW 200W 220-240V NB	-
01692805	BVP283 LED262/CW 200W 220-240V SWB	-
01692905	BVP283 LED262/NW 200W 220-240V AWB	-
01693005	BVP283 LED262/NW 200W 220-240V AWBE	-
01693105	BVP283 LED262/NW 200W 220-240V NB	-
01693205	BVP283 LED262/NW 200W 220-240V SWB	-
01693505	BVP283 LED281/WW 235W 220-240V AWB	-
01693605	BVP283 LED281/WW 235W 220-240V AWBE	-

Order Code	Full Product Name	Maximum dim level
01693705	BVP283 LED306/CW 235W 220-240V AWB	-
01693805	BVP283 LED306/CW 235W 220-240V AWBE	-
01693905	BVP283 LED306/NW 235W 220-240V AWB	-
01694005	BVP283 LED306/NW 235W 220-240V AWBE	-
01694105	BVP283 LED319/WW 270W 220-240V AWBE	-
01694205	BVP283 LED319/WW 270W 220-240V NB	-
01694305	BVP283 LED347/CW 270W 220-240V AWBE	-
01694405	BVP283 LED347/CW 270W 220-240V NB	-
01694505	BVP283 LED347/NW 270W 220-240V AWBE	-
01694605	BVP283 LED347/NW 270W 220-240V NB	-
01694905	BVP283 LED390/CW 305W 220-240V AWBE	-
01695005	BVP283 LED390/CW 305W 220-240V NB	-
01695105	BVP283 LED390/CW 305W 220-240V SWB	-
01695205	BVP283 LED390/NW 305W 220-240V AWBE	-
01695305	BVP283 LED390/NW 305W 220-240V NB	-
01695405	BVP283 LED390/NW 305W 220-240V SWB	-
01695505	BVP283 LED375/WW 320W 220-240V AWB	-
01695605	BVP283 LED375/WW 320W 220-240V AWBE	-
01695705	BVP283 LED375/WW 320W 220-240V NB	-
01695805	BVP283 LED375/WW 320W 220-240V SWB	-
01695905	BVP283 LED408/CW 320W 220-240V AWB	-
01696005	BVP283 LED408/CW 320W 220-240V AWBE	-
01696105	BVP283 LED408/CW 320W 220-240V NB	-
01696205	BVP283 LED408/CW 320W 220-240V SWB	-
01696305	BVP283 LED408/NW 320W 220-240V AWB	-
01696405	BVP283 LED408/NW 320W 220-240V AWBE	-
01696505	BVP283 LED408/NW 320W 220-240V NB	-
01696605	BVP283 LED408/NW 320W 220-240V SWB	-
01696905	BVP283 LED395/WW 335W 220-240V AWB	-
01697005	BVP283 LED395/WW 335W 220-240V AWBE	-
01697105	BVP283 LED395/WW 335W 220-240V NB	-
01697205	BVP283 LED395/WW 335W 220-240V SWB	-
01697305	BVP283 LED430/CW 335W 220-240V AWB	-
01697405	BVP283 LED430/CW 335W 220-240V AWBE	-
01697505	BVP283 LED430/CW 335W 220-240V NB	-
01697605	BVP283 LED430/CW 335W 220-240V SWB	-
01697705	BVP283 LED430/NW 335W 220-240V AWB	-
01697805	BVP283 LED430/NW 335W 220-240V AWBE	-
01697905	BVP283 LED430/NW 335W 220-240V NB	-
01698005	BVP283 LED430/NW 335W 220-240V SWB	-

### Approval and Application

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
01660504	BVP281 LED101/CW 80W 220-240V SWB	IK07	Surge protection level until 10 kV
01660704	BVP281 LED101/CW 80W 220-240V AWB	IK07	Surge protection level until 10 kV
01660804	BVP281 LED50/CW 40W 220-240V SWB	IK07	Surge protection level until 10 kV

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
01660904	BVP281 LED101/WW 80W 220-240V SMB	IK07	Surge protection level until 10 kV
01661104	BVP281 LED101/WW 80W 220-240V AWB	IK07	Surge protection level until 10 kV
01661204	BVP281 LED50/NW 40W 220-240V SMB	IK07	Surge protection level until 10 kV

## Tango G2 LED

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
01661304	BVP281 LED50/NW 40W 220-240V AMB	IK07	Surge protection level until 10 kV
01661404	BVP281 LED50/CW 40W 220-240V SMB	IK07	Surge protection level until 10 kV
01661604	BVP281 LED50/CW 40W 220-240V AMB	IK07	Surge protection level until 10 kV
01661704	BVP281 LED50/WW 40W 220-240V SMB	IK07	Surge protection level until 10 kV
01661804	BVP281 LED101/CW 80W 220-240V SMB	IK07	Surge protection level until 10 kV
01661904	BVP281 LED101/NW 80W 220-240V AMB	IK07	Surge protection level until 10 kV
01662004	BVP281 LED151/CW 120W 220-240V AMB	IK07	Surge protection level until 10 kV
01662104	BVP281 LED151/WW 120W 220-240V AMB	IK07	Surge protection level until 10 kV
01662204	BVP281 LED151/NW 120W 220-240V AMB	IK07	Surge protection level until 10 kV
01662304	BVP281 LED101/NW 80W 220-240V SWB	IK07	Surge protection level until 10 kV
01662404	BVP281 LED151/CW 120W 220-240V SMB	IK07	Surge protection level until 10 kV
01662504	BVP281 LED151/WW 120W 220-240V SMB	IK07	Surge protection level until 10 kV
01662604	BVP281 LED151/CW 120W 220-240V SWB	IK07	Surge protection level until 10 kV
01662704	BVP281 LED101/NW 80W 220-240V SMB	IK07	Surge protection level until 10 kV
01662804	BVP281 LED151/NW 120W 220-240V SWB	IK07	Surge protection level until 10 kV
01662904	BVP281 LED151/NW 120W 220-240V SMB	IK07	Surge protection level until 10 kV
01663004	BVP282 LED202/WW 160W 220-240V AMB	IK07	Surge protection level until 10 kV
01663104	BVP282 LED202/WW 160W 220-240V SWB	IK07	Surge protection level until 10 kV
01663204	BVP282 LED202/NW 160W 220-240V SWB	IK07	Surge protection level until 10 kV
01663304	BVP282 LED202/NW 160W 220-240V AMB	IK07	Surge protection level until 10 kV
01663404	BVP282 LED202/CW 160W 220-240V SMB	IK07	Surge protection level until 10 kV
01663504	BVP282 LED202/CW 160W 220-240V AMB	IK07	Surge protection level until 10 kV
01663604	BVP282 LED202/NW 160W 220-240V SMB	IK07	Surge protection level until 10 kV
01663704	BVP282 LED202/CW 160W 220-240V SWB	IK07	Surge protection level until 10 kV
01663804	BVP282 LED252/WW 200W 220-240V SMB	IK07	Surge protection level until 10 kV

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
01663904	BVP282 LED252/CW 200W 220-240V SWB	IK07	Surge protection level until 10 kV
01664004	BVP282 LED252/WW 200W 220-240V SWB	IK07	Surge protection level until 10 kV
01664104	BVP282 LED252/NW 200W 220-240V AMB	IK07	Surge protection level until 10 kV
01664204	BVP282 LED252/WW 200W 220-240V AMB	IK07	Surge protection level until 10 kV
01664304	BVP282 LED252/CW 200W 220-240V SMB	IK07	Surge protection level until 10 kV
32985700	BVP282 LED252/CW 200W 220-240V AMB	IK07	Surge protection level until 10 kV
01664504	BVP282 LED252/NW 200W 220-240V SWB	IK07	Surge protection level until 10 kV
01664604	BVP282 LED252/NW 200W 220-240V SMB	IK07	Surge protection level until 10 kV
01664704	BVP282 LED202/WW 160W 220-240V SMB	IK07	Surge protection level until 10 kV
01667002	BVP283 LED311/WW 335W 220-240V NB	IK07	-
01667102	BVP283 LED293/WW 315W 220-240V NB	IK07	-
01667202	BVP283 LED256/WW 280W 220-240V NB	IK07	-
01667302	BVP283 LED224/WW 245W 220-240V NB	IK07	-
01667402	BVP283 LED192/WW 210W 220-240V NB	IK07	-
01668002	BVP283 LED340/NW 335W 220-240V NB	IK07	-
01668102	BVP283 LED320/NW 315W 220-240V NB	IK07	-
01668202	BVP283 LED280/NW 280W 220-240V NB	IK07	-
01668302	BVP283 LED245/NW 245W 220-240V NB	IK07	-
01668402	BVP283 LED210/NW 210W 220-240V NB	IK07	Surge protection level until 10 kV
01668502	BVP283 LED311/WW 335W 220-240V SWB	IK07	-
01668602	BVP283 LED307/WW 315W 220-240V SWB	IK07	-
01668702	BVP283 LED224/WW 245W 220-240V SWB	IK07	-
01668802	BVP283 LED256/WW 280W 220-240V SWB	IK07	-
01668902	BVP283 LED192/WW 210W 220-240V SWB	IK07	-
01669502	BVP283 LED340/NW 335W 220-240V SWB	IK07	-

## Tango G2 LED

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
01669602	BVP283 LED320/NW 315W 220-240V SWB	IK07	Surge protection level until 10 kV
01669702	BVP283 LED280/NW 280W 220-240V SWB	IK07	Surge protection level until 10 kV
01669802	BVP283 LED245/NW 245W 220-240V SWB	IK07	Surge protection level until 10 kV
01669902	BVP283 LED210/NW 210W 220-240V SWB	IK07	Surge protection level until 10 kV
01670002	BVP283 LED311/WW 335W 220-240V AWB	IK07	-
01670102	BVP283 LED293/WW 315W 220-240V AWB	IK07	-
01670202	BVP283 LED256/WW 280W 220-240V AWB	IK07	-
01670302	BVP283 LED224/WW 245W 220-240V AWB	IK07	-
01670402	BVP283 LED192/WW 210W 220-240V AWB	IK07	-
01671002	BVP283 LED340/NW 335W 220-240V AWB	IK07	-
01671102	BVP283 LED320/NW 315W 220-240V AWB	IK07	Surge protection level until 10 kV
01671202	BVP283 LED280/NW 280W 220-240V AWB	IK07	Surge protection level until 10 kV
01671302	BVP283 LED245/NW 245W 220-240V AWB	IK07	Surge protection level until 10 kV
01671402	BVP283 LED210/NW 210W 220-240V AWB	IK07	Surge protection level until 10 kV
01689102	BVP283 LED327/WW 350W 220-240V NB	IK07	-
01689202	BVP283 LED355/NW 350W 220-240V AWB	IK07	Surge protection level until 10 kV
01689402	BVP283 LED327/WW 350W 220-240V AWB	IK07	-
01689502	BVP283 LED355/NW 350W 220-240V SWB	IK07	Surge protection level until 10 kV
01689702	BVP283 LED327/WW 350W 220-240V SWB	IK07	-
01689802	BVP283 LED355/NW 350W 220-240V NB	IK07	-
01692505	BVP283 LED262/CW 200W 220-240V AWB	IK08	-
01692605	BVP283 LED262/CW 200W 220-240V AWBE	IK08	-
01692705	BVP283 LED262/CW 200W 220-240V NB	IK08	-
01692805	BVP283 LED262/CW 200W 220-240V SWB	IK08	-
01692905	BVP283 LED262/NW 200W 220-240V AWB	IK08	-

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
01693005	BVP283 LED262/NW 200W 220-240V AWBE	IK08	-
01693105	BVP283 LED262/NW 200W 220-240V NB	IK08	-
01693205	BVP283 LED262/NW 200W 220-240V SWB	IK08	-
01693505	BVP283 LED281/WW 235W 220-240V AWB	IK08	-
01693605	BVP283 LED281/WW 235W 220-240V AWBE	IK08	-
01693705	BVP283 LED306/CW 235W 220-240V AWB	IK08	-
01693805	BVP283 LED306/CW 235W 220-240V AWBE	IK08	-
01693905	BVP283 LED306/NW 235W 220-240V AWB	IK08	-
01694005	BVP283 LED306/NW 235W 220-240V AWBE	IK08	-
01694105	BVP283 LED319/WW 270W 220-240V AWBE	IK08	-
01694205	BVP283 LED319/WW 270W 220-240V NB	IK08	-
01694305	BVP283 LED347/CW 270W 220-240V AWBE	IK08	-
01694405	BVP283 LED347/CW 270W 220-240V NB	IK08	-
01694505	BVP283 LED347/NW 270W 220-240V AWBE	IK08	-
01694605	BVP283 LED347/NW 270W 220-240V NB	IK08	-
01694905	BVP283 LED390/CW 305W 220-240V AWBE	IK08	-
01695005	BVP283 LED390/CW 305W 220-240V NB	IK08	-
01695105	BVP283 LED390/CW 305W 220-240V SWB	IK08	-
01695205	BVP283 LED390/NW 305W 220-240V AWBE	IK08	-
01695305	BVP283 LED390/NW 305W 220-240V NB	IK08	-
01695405	BVP283 LED390/NW 305W 220-240V SWB	IK08	-
01695505	BVP283 LED375/WW 320W 220-240V AWB	IK08	-
01695605	BVP283 LED375/WW 320W 220-240V AWBE	IK08	-
01695705	BVP283 LED375/WW 320W 220-240V NB	IK08	-
01695805	BVP283 LED375/WW 320W 220-240V SWB	IK08	-

## Tango G2 LED

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
01695905	BVP283 LED408/CW 320W 220-240V AWB	IK08	-
01696005	BVP283 LED408/CW 320W 220-240V AWBE	IK08	-
01696105	BVP283 LED408/CW 320W 220-240V NB	IK08	-
01696205	BVP283 LED408/CW 320W 220-240V SWB	IK08	-
01696305	BVP283 LED408/NW 320W 220-240V AWB	IK08	-
01696405	BVP283 LED408/NW 320W 220-240V AWBE	IK08	-
01696505	BVP283 LED408/NW 320W 220-240V NB	IK08	-
01696605	BVP283 LED408/NW 320W 220-240V SWB	IK08	-
01696905	BVP283 LED395/WW 335W 220-240V AWB	IK08	-
01697005	BVP283 LED395/WW 335W 220-240V AWBE	IK08	-

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
01697105	BVP283 LED395/WW 335W 220-240V NB	IK08	-
01697205	BVP283 LED395/WW 335W 220-240V SWB	IK08	-
01697305	BVP283 LED430/CW 335W 220-240V AWB	IK08	-
01697405	BVP283 LED430/CW 335W 220-240V AWBE	IK08	-
01697505	BVP283 LED430/CW 335W 220-240V NB	IK08	-
01697605	BVP283 LED430/CW 335W 220-240V SWB	IK08	-
01697705	BVP283 LED430/NW 335W 220-240V AWB	IK08	-
01697805	BVP283 LED430/NW 335W 220-240V AWBE	IK08	-
01697905	BVP283 LED430/NW 335W 220-240V NB	IK08	-
01698005	BVP283 LED430/NW 335W 220-240V SWB	IK08	-

### General Information (1/2)

Order Code	Full Product Name	Luminaire light		Optical cover/ lens type	Flammability mark	Lamp family code	Light source replaceable	Number of gear units
		beam spread	Light source colour					
01660504	BVP281 LED101/CW 80W 220-240V SWB	100°	Cool white	PC-MLO	NO	-	Yes	-
01660704	BVP281 LED101/CW 80W 220-240V AMB	100° x 30°	Cool white	PC-MLO	NO	-	Yes	-
01660804	BVP281 LED50/CW 40W 220-240V SWB	100°	Cool white	PC-MLO	NO	-	Yes	-
01660904	BVP281 LED101/WW 80W 220-240V SMB	54°	Warm white	PC-MLO	NO	-	Yes	-
01661104	BVP281 LED101/WW 80W 220-240V AMB	100° x 30°	Warm white	PC-MLO	NO	-	Yes	-
01661204	BVP281 LED50/NW 40W 220-240V SMB	54°	Neutral white	PC-MLO	NO	-	Yes	-
01661304	BVP281 LED50/NW 40W 220-240V AMB	100° x 30°	Neutral white	PC-MLO	NO	-	Yes	-
01661404	BVP281 LED50/CW 40W 220-240V SMB	54°	Cool white	PC-MLO	NO	-	Yes	-
01661604	BVP281 LED50/CW 40W 220-240V AMB	100° x 30°	Cool white	PC-MLO	NO	-	Yes	-
01661704	BVP281 LED50/WW 40W 220-240V SMB	54°	Warm white	PC-MLO	NO	-	Yes	-
01661804	BVP281 LED101/CW 80W 220-240V SMB	54°	Cool white	PC-MLO	NO	-	Yes	-
01661904	BVP281 LED101/NW 80W 220-240V AMB	100° x 30°	Neutral white	PC-MLO	NO	-	Yes	-
01662004	BVP281 LED151/CW 120W 220-240V AMB	100° x 30°	Cool white	PC-MLO	NO	-	Yes	-
01662104	BVP281 LED151/WW 120W 220-240V AMB	100° x 30°	Warm white	PC-MLO	NO	-	Yes	-
01662204	BVP281 LED151/NW 120W 220-240V AMB	100° x 30°	Neutral white	PC-MLO	NO	-	Yes	-
01662304	BVP281 LED101/NW 80W 220-240V SWB	100°	Neutral white	PC-MLO	NO	-	Yes	-
01662404	BVP281 LED151/CW 120W 220-240V SMB	54°	Cool white	PC-MLO	NO	-	Yes	-
01662504	BVP281 LED151/WW 120W 220-240V SMB	54°	Warm white	PC-MLO	NO	-	Yes	-
01662604	BVP281 LED151/CW 120W 220-240V SWB	100°	Cool white	PC-MLO	NO	-	Yes	-
01662704	BVP281 LED101/NW 80W 220-240V SMB	54°	Neutral white	PC-MLO	NO	-	Yes	-
01662804	BVP281 LED151/NW 120W 220-240V SWB	100°	Neutral white	PC-MLO	NO	-	Yes	-
01662904	BVP281 LED151/NW 120W 220-240V SMB	54°	Neutral white	PC-MLO	NO	-	Yes	-
01663004	BVP282 LED202/WW 160W 220-240V AMB	100° x 30°	Warm white	PC-MLO	NO	-	Yes	-

## Tango G2 LED

Order Code	Full Product Name	Luminaire light		Optical cover/ lens type	Flammability mark	Lamp family code	Light source replaceable	Number of gear units
		beam spread	Light source colour					
01663104	BVP282 LED202/WW 160W 220-240V SWB	100°	Warm white	PC-MLO	NO	-	Yes	-
01663204	BVP282 LED202/NW 160W 220-240V SWB	100°	Neutral white	PC-MLO	NO	-	Yes	-
01663304	BVP282 LED202/NW 160W 220-240V AMB	100° x 30°	Neutral white	PC-MLO	NO	-	Yes	-
01663404	BVP282 LED202/CW 160W 220-240V SMB	54°	Cool white	PC-MLO	NO	-	Yes	-
01663504	BVP282 LED202/CW 160W 220-240V AMB	100° x 30°	Cool white	PC-MLO	NO	-	Yes	-
01663604	BVP282 LED202/NW 160W 220-240V SMB	54°	Neutral white	PC-MLO	NO	-	Yes	-
01663704	BVP282 LED202/CW 160W 220-240V SWB	100°	Cool white	PC-MLO	NO	-	Yes	-
01663804	BVP282 LED252/WW 200W 220-240V SMB	54°	Warm white	PC-MLO	NO	-	Yes	-
01663904	BVP282 LED252/CW 200W 220-240V SWB	100°	Cool white	PC-MLO	NO	-	Yes	-
01664004	BVP282 LED252/WW 200W 220-240V SWB	100°	Warm white	PC-MLO	NO	-	Yes	-
01664104	BVP282 LED252/NW 200W 220-240V AMB	100° x 30°	Neutral white	PC-MLO	NO	-	Yes	-
01664204	BVP282 LED252/WW 200W 220-240V AMB	100° x 30°	Warm white	PC-MLO	NO	-	Yes	-
01664304	BVP282 LED252/CW 200W 220-240V SMB	54°	Cool white	PC-MLO	NO	-	Yes	-
32985700	BVP282 LED252/CW 200W 220-240V AMB	100° x 30°	Cool white	PC-MLO	NO	-	Yes	-
01664504	BVP282 LED252/NW 200W 220-240V SWB	100°	Neutral white	PC-MLO	NO	-	Yes	-
01664604	BVP282 LED252/NW 200W 220-240V SMB	54°	Neutral white	PC-MLO	NO	-	Yes	-
01664704	BVP282 LED202/WW 160W 220-240V SMB	54°	Warm white	PC-MLO	NO	-	Yes	-
01667002	BVP283 LED311/WW 335W 220-240V NB	-	740 neutral white	G	-	-	-	-
01667102	BVP283 LED293/WW 315W 220-240V NB	-	740 neutral white	G	-	-	-	-
01667202	BVP283 LED256/WW 280W 220-240V NB	-	740 neutral white	G	-	-	-	-
01667302	BVP283 LED224/WW 245W 220-240V NB	-	740 neutral white	G	-	-	-	-
01667402	BVP283 LED192/WW 210W 220-240V NB	-	730 warm white	G	-	-	-	-
01668002	BVP283 LED340/NW 335W 220-240V NB	-	740 neutral white	G	-	-	-	-
01668102	BVP283 LED320/NW 315W 220-240V NB	-	740 neutral white	G	-	-	-	-
01668202	BVP283 LED280/NW 280W 220-240V NB	-	740 neutral white	G	-	-	-	-
01668302	BVP283 LED245/NW 245W 220-240V NB	-	740 neutral white	G	-	-	-	-
01668402	BVP283 LED210/NW 210W 220-240V NB	20° x 20°	740 neutral white	G	-	-	Yes	-
01668502	BVP283 LED311/WW 335W 220-240V SWB	-	740 neutral white	G	-	-	-	-
01668602	BVP283 LED307/WW 315W 220-240V SWB	-	740 neutral white	G	-	-	-	-
01668702	BVP283 LED224/WW 245W 220-240V SWB	-	740 neutral white	G	-	-	-	-

## Tango G2 LED

Order Code	Full Product Name	Luminaire light		Optical cover/	Flammability	Lamp	Light source	Number of
		beam spread	Light source colour	lens type	mark	family code	replaceable	
01668802	BVP283 LED256/WW 280W 220-240V SWB	-	740 neutral white	G	-	-	-	-
01668902	BVP283 LED192/WW 210W 220-240V SWB	-	730 warm white	G	-	-	-	-
01669502	BVP283 LED340/NW 335W 220-240V SWB	-	740 neutral white	G	-	-	-	-
01669602	BVP283 LED320/NW 315W 220-240V SWB	30° x 80°	740 neutral white	G	-	-	Yes	-
01669702	BVP283 LED280/NW 280W 220-240V SWB	30° x 80°	740 neutral white	G	-	-	Yes	-
01669802	BVP283 LED245/NW 245W 220-240V SWB	30° x 80°	740 neutral white	G	-	-	Yes	-
01669902	BVP283 LED210/NW 210W 220-240V SWB	30° x 80°	740 neutral white	G	-	-	Yes	-
01670002	BVP283 LED311/WW 335W 220-240V AWB	-	740 neutral white	G	-	-	-	-
01670102	BVP283 LED293/WW 315W 220-240V AWB	-	740 neutral white	G	-	-	-	-
01670202	BVP283 LED256/WW 280W 220-240V AWB	-	740 neutral white	G	-	-	-	-
01670302	BVP283 LED224/WW 245W 220-240V AWB	-	740 neutral white	G	-	-	-	-
01670402	BVP283 LED192/WW 210W 220-240V AWB	-	730 warm white	G	-	-	-	-
01671002	BVP283 LED340/NW 335W 220-240V AWB	-	740 neutral white	G	-	-	-	-
01671102	BVP283 LED320/NW 315W 220-240V AWB	40° x 95°	740 neutral white	G	-	-	Yes	-
01671202	BVP283 LED280/NW 280W 220-240V AWB	40° x 95°	740 neutral white	G	-	-	Yes	-
01671302	BVP283 LED245/NW 245W 220-240V AWB	40° x 95°	740 neutral white	G	-	-	Yes	-
01671402	BVP283 LED210/NW 210W 220-240V AWB	40° x 95°	740 neutral white	G	-	-	Yes	-
01689102	BVP283 LED327/WW 350W 220-240V NB	-	740 neutral white	G	-	-	-	-
01689202	BVP283 LED355/NW 350W 220-240V AWB	40° x 95°	740 neutral white	G	-	-	Yes	-
01689402	BVP283 LED327/WW 350W 220-240V AWB	-	740 neutral white	G	-	-	-	-
01689502	BVP283 LED355/NW 350W 220-240V SWB	30° x 80°	740 neutral white	G	-	-	Yes	-
01689702	BVP283 LED327/WW 350W 220-240V SWB	-	740 neutral white	G	-	-	-	-
01689802	BVP283 LED355/NW 350W 220-240V NB	-	740 neutral white	G	-	-	-	-
01692505	BVP283 LED262/CW 200W 220-240V AWB	-	757 cool white	PC-MLO	-	-	-	-
01692605	BVP283 LED262/CW 200W 220-240V AWBE	-	757 cool white	PC-MLO	-	-	-	-
01692705	BVP283 LED262/CW 200W 220-240V NB	-	757 cool white	PC-MLO	-	-	-	-
01692805	BVP283 LED262/CW 200W 220-240V SWB	-	757 cool white	PC-MLO	-	-	-	-



## Tango G2 LED

Order Code	Full Product Name	Luminaire light		Optical cover/	Flammability	Lamp	Light source	Number of
		beam spread	Light source colour	lens type	mark	family code	replaceable	
01692905	BVP283 LED262/NW 200W 220-240V AWB	-	740 neutral white	PC-MLO	-	-	-	-
01693005	BVP283 LED262/NW 200W 220-240V AWBE	-	740 neutral white	PC-MLO	-	-	-	-
01693105	BVP283 LED262/NW 200W 220-240V NB	-	740 neutral white	PC-MLO	-	-	-	-
01693205	BVP283 LED262/NW 200W 220-240V SWB	-	740 neutral white	PC-MLO	-	-	-	-
01693505	BVP283 LED281/WW 235W 220-240V AWB	-	730 warm white	PC-MLO	-	-	-	-
01693605	BVP283 LED281/WW 235W 220-240V AWBE	-	730 warm white	PC-MLO	-	-	-	-
01693705	BVP283 LED306/CW 235W 220-240V AWB	-	757 cool white	PC-MLO	-	-	-	-
01693805	BVP283 LED306/CW 235W 220-240V AWBE	-	757 cool white	PC-MLO	-	-	-	-
01693905	BVP283 LED306/NW 235W 220-240V AWB	-	740 neutral white	PC-MLO	-	-	-	-
01694005	BVP283 LED306/NW 235W 220-240V AWBE	-	740 neutral white	PC-MLO	-	-	-	-
01694105	BVP283 LED319/WW 270W 220-240V AWBE	-	730 warm white	PC-MLO	-	-	-	-
01694205	BVP283 LED319/WW 270W 220-240V NB	-	730 warm white	PC-MLO	-	-	-	-
01694305	BVP283 LED347/CW 270W 220-240V AWBE	-	757 cool white	PC-MLO	-	-	-	-
01694405	BVP283 LED347/CW 270W 220-240V NB	-	757 cool white	PC-MLO	-	-	-	-
01694505	BVP283 LED347/NW 270W 220-240V AWBE	-	740 neutral white	PC-MLO	-	-	-	-
01694605	BVP283 LED347/NW 270W 220-240V NB	-	740 neutral white	PC-MLO	-	-	-	-
01694905	BVP283 LED390/CW 305W 220-240V AWBE	-	757 cool white	PC-MLO	-	-	-	-
01695005	BVP283 LED390/CW 305W 220-240V NB	-	757 cool white	PC-MLO	-	-	-	-
01695105	BVP283 LED390/CW 305W 220-240V SWB	-	757 cool white	PC-MLO	-	-	-	-
01695205	BVP283 LED390/NW 305W 220-240V AWBE	-	740 neutral white	PC-MLO	-	-	-	-
01695305	BVP283 LED390/NW 305W 220-240V NB	-	740 neutral white	PC-MLO	-	-	-	-
01695405	BVP283 LED390/NW 305W 220-240V SWB	-	740 neutral white	PC-MLO	-	-	-	-
01695505	BVP283 LED375/WW 320W 220-240V AWB	-	730 warm white	PC-MLO	-	-	-	-
01695605	BVP283 LED375/WW 320W 220-240V AWBE	-	730 warm white	PC-MLO	-	-	-	-
01695705	BVP283 LED375/WW 320W 220-240V NB	-	730 warm white	PC-MLO	-	-	-	-
01695805	BVP283 LED375/WW 320W 220-240V SWB	-	730 warm white	PC-MLO	-	-	-	-
01695905	BVP283 LED408/CW 320W 220-240V AWB	-	757 cool white	PC-MLO	-	-	-	-
01696005	BVP283 LED408/CW 320W 220-240V AWBE	-	757 cool white	PC-MLO	-	-	-	-
01696105	BVP283 LED408/CW 320W 220-240V NB	-	757 cool white	PC-MLO	-	-	-	-

## Tango G2 LED

Order Code	Full Product Name	Luminaire light		Optical cover/	Flammability	Lamp	Light source	Number of
		beam spread	Light source colour	lens type	mark	family code	replaceable	
01696205	BVP283 LED408/CW 320W 220-240V SWB	-	757 cool white	PC-MLO	-	-	-	-
01696305	BVP283 LED408/NW 320W 220-240V AWB	-	740 neutral white	PC-MLO	-	-	-	-
01696405	BVP283 LED408/NW 320W 220-240V AWBE	-	740 neutral white	PC-MLO	-	-	-	-
01696505	BVP283 LED408/NW 320W 220-240V NB	-	740 neutral white	PC-MLO	-	-	-	-
01696605	BVP283 LED408/NW 320W 220-240V SWB	-	740 neutral white	PC-MLO	-	-	-	-
01696905	BVP283 LED395/WW 335W 220-240V AWB	-	730 warm white	PC-MLO	-	-	-	-
01697005	BVP283 LED395/WW 335W 220-240V AWBE	-	730 warm white	PC-MLO	-	-	-	-
01697105	BVP283 LED395/WW 335W 220-240V NB	-	730 warm white	PC-MLO	-	-	-	-
01697205	BVP283 LED395/WW 335W 220-240V SWB	-	730 warm white	PC-MLO	-	-	-	-
01697305	BVP283 LED430/CW 335W 220-240V AWB	-	757 cool white	PC-MLO	-	-	-	-
01697405	BVP283 LED430/CW 335W 220-240V AWBE	-	757 cool white	PC-MLO	-	-	-	-
01697505	BVP283 LED430/CW 335W 220-240V NB	-	757 cool white	PC-MLO	-	-	-	-
01697605	BVP283 LED430/CW 335W 220-240V SWB	-	757 cool white	PC-MLO	-	-	-	-
01697705	BVP283 LED430/NW 335W 220-240V AWB	-	740 neutral white	PC-MLO	-	-	-	-
01697805	BVP283 LED430/NW 335W 220-240V AWBE	-	740 neutral white	PC-MLO	-	-	-	-
01697905	BVP283 LED430/NW 335W 220-240V NB	-	740 neutral white	PC-MLO	-	-	-	-
01698005	BVP283 LED430/NW 335W 220-240V SWB	-	740 neutral white	PC-MLO	-	-	-	-

### General Information (2/2)

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
01660504	BVP281 LED101/CW 80W 220-240V SWB	Symmetrical wide beam	01662504	BVP281 LED151/WW 120W 220-240V SMB	Symmetrical medium beam
01660704	BVP281 LED101/CW 80W 220-240V AMB	Asymmetrical medium beam	01662604	BVP281 LED151/CW 120W 220-240V SWB	Symmetrical wide beam
01660804	BVP281 LED50/CW 40W 220-240V SWB	Symmetrical wide beam	01662704	BVP281 LED101/NW 80W 220-240V SMB	Symmetrical medium beam
01660904	BVP281 LED101/WW 80W 220-240V SMB	Symmetrical medium beam	01662804	BVP281 LED151/NW 120W 220-240V SWB	Symmetrical wide beam
01661104	BVP281 LED101/WW 80W 220-240V AMB	Asymmetrical medium beam	01662904	BVP281 LED151/NW 120W 220-240V SMB	Symmetrical medium beam
01661204	BVP281 LED50/NW 40W 220-240V SMB	Symmetrical medium beam	01663004	BVP282 LED202/WW 160W 220-240V AMB	Asymmetrical medium beam
01661304	BVP281 LED50/NW 40W 220-240V AMB	Asymmetrical medium beam	01663104	BVP282 LED202/WW 160W 220-240V SWB	Symmetrical wide beam
01661404	BVP281 LED50/CW 40W 220-240V SMB	Symmetrical medium beam	01663204	BVP282 LED202/NW 160W 220-240V SWB	Symmetrical wide beam
01661604	BVP281 LED50/CW 40W 220-240V AMB	Asymmetrical medium beam	01663304	BVP282 LED202/NW 160W 220-240V AMB	Asymmetrical medium beam
01661704	BVP281 LED50/WW 40W 220-240V SMB	Symmetrical medium beam	01663404	BVP282 LED202/CW 160W 220-240V SMB	Symmetrical medium beam
01661804	BVP281 LED101/CW 80W 220-240V SMB	Symmetrical medium beam	01663504	BVP282 LED202/CW 160W 220-240V AMB	Asymmetrical medium beam
01661904	BVP281 LED101/NW 80W 220-240V AMB	Asymmetrical medium beam	01663604	BVP282 LED202/NW 160W 220-240V SMB	Symmetrical medium beam
01662004	BVP281 LED151/CW 120W 220-240V AMB	Asymmetrical medium beam	01663704	BVP282 LED202/CW 160W 220-240V SWB	Symmetrical wide beam
01662104	BVP281 LED151/WW 120W 220-240V AMB	Asymmetrical medium beam	01663804	BVP282 LED252/WW 200W 220-240V SMB	Symmetrical medium beam
01662204	BVP281 LED151/NW 120W 220-240V AMB	Asymmetrical medium beam	01663904	BVP282 LED252/CW 200W 220-240V SWB	Symmetrical wide beam
01662304	BVP281 LED101/NW 80W 220-240V SWB	Symmetrical wide beam	01664004	BVP282 LED252/WW 200W 220-240V SWB	Symmetrical wide beam
01662404	BVP281 LED151/CW 120W 220-240V SMB	Symmetrical medium beam	01664104	BVP282 LED252/NW 200W 220-240V AMB	Asymmetrical medium beam

## Tango G2 LED

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
01664204	BVP282 LED252/WW 200W 220-240V AMB	Asymmetrical medium beam	01692905	BVP283 LED262/NW 200W 220-240V AWB	-
01664304	BVP282 LED252/CW 200W 220-240V SMB	Symmetrical medium beam	01693005	BVP283 LED262/NW 200W 220-240V AWBE	-
32985700	BVP282 LED252/CW 200W 220-240V AMB	Asymmetrical medium beam	01693105	BVP283 LED262/NW 200W 220-240V NB	-
01664504	BVP282 LED252/NW 200W 220-240V SWB	Symmetrical wide beam	01693205	BVP283 LED262/NW 200W 220-240V SWB	-
01664604	BVP282 LED252/NW 200W 220-240V SMB	Symmetrical medium beam	01693505	BVP283 LED281/WW 235W 220-240V AWB	-
01664704	BVP282 LED202/WW 160W 220-240V SMB	Symmetrical medium beam	01693605	BVP283 LED281/WW 235W 220-240V AWBE	-
01667002	BVP283 LED311/WW 335W 220-240V NB	-	01693705	BVP283 LED306/CW 235W 220-240V AWB	-
01667102	BVP283 LED293/WW 315W 220-240V NB	-	01693805	BVP283 LED306/CW 235W 220-240V AWBE	-
01667202	BVP283 LED256/WW 280W 220-240V NB	-	01693905	BVP283 LED306/NW 235W 220-240V AWB	-
01667302	BVP283 LED224/WW 245W 220-240V NB	-	01694005	BVP283 LED306/NW 235W 220-240V AWBE	-
01667402	BVP283 LED192/WW 210W 220-240V NB	-	01694105	BVP283 LED319/WW 270W 220-240V AWBE	-
01668002	BVP283 LED340/NW 335W 220-240V NB	-	01694205	BVP283 LED319/WW 270W 220-240V NB	-
01668102	BVP283 LED320/NW 315W 220-240V NB	-	01694305	BVP283 LED347/CW 270W 220-240V AWBE	-
01668202	BVP283 LED280/NW 280W 220-240V NB	-	01694405	BVP283 LED347/CW 270W 220-240V NB	-
01668302	BVP283 LED245/NW 245W 220-240V NB	-	01694505	BVP283 LED347/NW 270W 220-240V AWBE	-
01668402	BVP283 LED210/NW 210W 220-240V NB	Narrow beam	01694605	BVP283 LED347/NW 270W 220-240V NB	-
01668502	BVP283 LED311/WW 335W 220-240V SWB	-	01694905	BVP283 LED390/CW 305W 220-240V AWBE	-
01668602	BVP283 LED307/WW 315W 220-240V SWB	-	01695005	BVP283 LED390/CW 305W 220-240V NB	-
01668702	BVP283 LED224/WW 245W 220-240V SWB	-	01695105	BVP283 LED390/CW 305W 220-240V SWB	-
01668802	BVP283 LED256/WW 280W 220-240V SWB	-	01695205	BVP283 LED390/NW 305W 220-240V AWBE	-
01668902	BVP283 LED192/WW 210W 220-240V SWB	-	01695305	BVP283 LED390/NW 305W 220-240V NB	-
01669502	BVP283 LED340/NW 335W 220-240V SWB	-	01695405	BVP283 LED390/NW 305W 220-240V SWB	-
01669602	BVP283 LED320/NW 315W 220-240V SWB	Symmetrical wide beam	01695505	BVP283 LED375/WW 320W 220-240V AWB	-
01669702	BVP283 LED280/NW 280W 220-240V SWB	Symmetrical wide beam	01695605	BVP283 LED375/WW 320W 220-240V AWBE	-
01669802	BVP283 LED245/NW 245W 220-240V SWB	Symmetrical wide beam	01695705	BVP283 LED375/WW 320W 220-240V NB	-
01669902	BVP283 LED210/NW 210W 220-240V SWB	Symmetrical wide beam	01695805	BVP283 LED375/WW 320W 220-240V SWB	-
01670002	BVP283 LED311/WW 335W 220-240V AWB	-	01695905	BVP283 LED408/CW 320W 220-240V AWB	-
01670102	BVP283 LED293/WW 315W 220-240V AWB	-	01696005	BVP283 LED408/CW 320W 220-240V AWBE	-
01670202	BVP283 LED256/WW 280W 220-240V AWB	-	01696105	BVP283 LED408/CW 320W 220-240V NB	-
01670302	BVP283 LED224/WW 245W 220-240V AWB	-	01696205	BVP283 LED408/CW 320W 220-240V SWB	-
01670402	BVP283 LED192/WW 210W 220-240V AWB	-	01696305	BVP283 LED408/NW 320W 220-240V AWB	-
01671002	BVP283 LED340/NW 335W 220-240V AWB	-	01696405	BVP283 LED408/NW 320W 220-240V AWBE	-
01671102	BVP283 LED320/NW 315W 220-240V AWB	Asymmetrical wide beam	01696505	BVP283 LED408/NW 320W 220-240V NB	-
01671202	BVP283 LED280/NW 280W 220-240V AWB	Asymmetrical wide beam	01696605	BVP283 LED408/NW 320W 220-240V SWB	-
01671302	BVP283 LED245/NW 245W 220-240V AWB	Asymmetrical wide beam	01696905	BVP283 LED395/WW 335W 220-240V AWB	-
01671402	BVP283 LED210/NW 210W 220-240V AWB	Asymmetrical wide beam	01697005	BVP283 LED395/WW 335W 220-240V AWBE	-
01689102	BVP283 LED327/WW 350W 220-240V NB	-	01697105	BVP283 LED395/WW 335W 220-240V NB	-
01689202	BVP283 LED355/NW 350W 220-240V AWB	Asymmetrical wide beam	01697205	BVP283 LED395/WW 335W 220-240V SWB	-
01689402	BVP283 LED327/WW 350W 220-240V AWB	-	01697305	BVP283 LED430/CW 335W 220-240V AWB	-
01689502	BVP283 LED355/NW 350W 220-240V SWB	Symmetrical wide beam	01697405	BVP283 LED430/CW 335W 220-240V AWBE	-
01689702	BVP283 LED327/WW 350W 220-240V SWB	-	01697505	BVP283 LED430/CW 335W 220-240V NB	-
01689802	BVP283 LED355/NW 350W 220-240V NB	-	01697605	BVP283 LED430/CW 335W 220-240V SWB	-
01692505	BVP283 LED262/CW 200W 220-240V AWB	-	01697705	BVP283 LED430/NW 335W 220-240V AWB	-
01692605	BVP283 LED262/CW 200W 220-240V AWBE	-	01697805	BVP283 LED430/NW 335W 220-240V AWBE	-
01692705	BVP283 LED262/CW 200W 220-240V NB	-	01697905	BVP283 LED430/NW 335W 220-240V NB	-
01692805	BVP283 LED262/CW 200W 220-240V SWB	-	01698005	BVP283 LED430/NW 335W 220-240V SWB	-

### Initial Performance (IEC Compliant)

## Tango G2 LED

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
01660504	BVP281 LED101/CW 80W 220-240V SWB	5700 K	70	10100 lm
01660704	BVP281 LED101/CW 80W 220-240V AMB	5700 K	70	10100 lm
01660804	BVP281 LED50/CW 40W 220-240V SWB	5700 K	70	5000 lm
01660904	BVP281 LED101/WW 80W 220-240V SMB	3000 K	70	10100 lm
01661104	BVP281 LED101/WW 80W 220-240V AMB	3000 K	70	10100 lm
01661204	BVP281 LED50/NW 40W 220-240V SMB	4000 K	70	5000 lm
01661304	BVP281 LED50/NW 40W 220-240V AMB	4000 K	70	5000 lm
01661404	BVP281 LED50/CW 40W 220-240V SMB	5700 K	70	5000 lm
01661604	BVP281 LED50/CW 40W 220-240V AMB	5700 K	70	5000 lm
01661704	BVP281 LED50/WW 40W 220-240V SMB	3000 K	70	5000 lm
01661804	BVP281 LED101/CW 80W 220-240V SMB	5700 K	70	10100 lm
01661904	BVP281 LED101/NW 80W 220-240V AMB	4000 K	70	10100 lm
01662004	BVP281 LED151/CW 120W 220-240V AMB	5700 K	70	15100 lm
01662104	BVP281 LED151/WW 120W 220-240V AMB	3000 K	70	15100 lm
01662204	BVP281 LED151/NW 120W 220-240V AMB	4000 K	70	15100 lm
01662304	BVP281 LED101/NW 80W 220-240V SWB	4000 K	70	10100 lm
01662404	BVP281 LED151/CW 120W 220-240V SMB	5700 K	70	15100 lm
01662504	BVP281 LED151/WW 120W 220-240V SMB	3000 K	70	15100 lm
01662604	BVP281 LED151/CW 120W 220-240V SWB	5700 K	70	15100 lm
01662704	BVP281 LED101/NW 80W 220-240V SMB	4000 K	70	10100 lm
01662804	BVP281 LED151/NW 120W 220-240V SWB	4000 K	70	15100 lm
01662904	BVP281 LED151/NW 120W 220-240V SMB	4000 K	70	15100 lm
01663004	BVP282 LED202/WW 160W 220-240V AMB	3000 K	70	20200 lm
01663104	BVP282 LED202/WW 160W 220-240V SWB	3000 K	70	20200 lm
01663204	BVP282 LED202/NW 160W 220-240V SWB	4000 K	70	20200 lm

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
01663304	BVP282 LED202/NW 160W 220-240V AMB	4000 K	70	20200 lm
01663404	BVP282 LED202/CW 160W 220-240V SMB	5700 K	70	20200 lm
01663504	BVP282 LED202/CW 160W 220-240V AMB	5700 K	70	20200 lm
01663604	BVP282 LED202/NW 160W 220-240V SMB	4000 K	70	20200 lm
01663704	BVP282 LED202/CW 160W 220-240V SWB	5700 K	70	20200 lm
01663804	BVP282 LED252/WW 200W 220-240V SMB	3000 K	70	25200 lm
01663904	BVP282 LED252/CW 200W 220-240V SWB	5700 K	70	25200 lm
01664004	BVP282 LED252/WW 200W 220-240V SWB	3000 K	70	25200 lm
01664104	BVP282 LED252/NW 200W 220-240V AMB	4000 K	70	25200 lm
01664204	BVP282 LED252/WW 200W 220-240V AMB	3000 K	70	25200 lm
01664304	BVP282 LED252/CW 200W 220-240V SMB	5700 K	70	25200 lm
32985700	BVP282 LED252/CW 200W 220-240V AMB	5700 K	70	25200 lm
01664504	BVP282 LED252/NW 200W 220-240V SWB	4000 K	70	25200 lm
01664604	BVP282 LED252/NW 200W 220-240V SMB	4000 K	70	25200 lm
01664704	BVP282 LED202/WW 160W 220-240V SMB	3000 K	70	20200 lm
01667002	BVP283 LED311/WW 335W 220-240V NB	3000 K	>70	31100 lm
01667102	BVP283 LED293/WW 315W 220-240V NB	3000 K	>70	29300 lm
01667202	BVP283 LED256/WW 280W 220-240V NB	3000 K	>70	25600 lm
01667302	BVP283 LED224/WW 245W 220-240V NB	3000 K	>70	22400 lm
01667402	BVP283 LED192/WW 210W 220-240V NB	3000 K	>70	19200 lm
01668002	BVP283 LED340/NW 335W 220-240V NB	4000 K	>70	34000 lm
01668102	BVP283 LED320/NW 315W 220-240V NB	4000 K	>70	32000 lm
01668202	BVP283 LED280/NW 280W 220-240V NB	4000 K	>70	28000 lm
01668302	BVP283 LED245/NW 245W 220-240V NB	4000 K	>70	24500 lm
01668402	BVP283 LED210/NW 210W 220-240V NB	4000 K	>70	21000 lm

## Tango G2 LED

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
01668502	BVP283 LED311/WW 335W 220-240V SWB	3000 K	>70	31100 lm
01668602	BVP283 LED307/WW 315W 220-240V SWB	3000 K	>70	29300 lm
01668702	BVP283 LED224/WW 245W 220-240V SWB	3000 K	>70	22400 lm
01668802	BVP283 LED256/WW 280W 220-240V SWB	3000 K	>70	25600 lm
01668902	BVP283 LED192/WW 210W 220-240V SWB	3000 K	>70	19200 lm
01669502	BVP283 LED340/NW 335W 220-240V SWB	4000 K	>70	34000 lm
01669602	BVP283 LED320/NW 315W 220-240V SWB	4000 K	>70	32000 lm
01669702	BVP283 LED280/NW 280W 220-240V SWB	4000 K	>70	28000 lm
01669802	BVP283 LED245/NW 245W 220-240V SWB	4000 K	>70	24500 lm
01669902	BVP283 LED210/NW 210W 220-240V SWB	4000 K	>70	21000 lm
01670002	BVP283 LED311/WW 335W 220-240V AWB	3000 K	>70	31100 lm
01670102	BVP283 LED293/WW 315W 220-240V AWB	3000 K	>70	29300 lm
01670202	BVP283 LED256/WW 280W 220-240V AWB	3000 K	>70	25600 lm
01670302	BVP283 LED224/WW 245W 220-240V AWB	3000 K	>70	22400 lm
01670402	BVP283 LED192/WW 210W 220-240V AWB	3000 K	>70	19200 lm
01671002	BVP283 LED340/NW 335W 220-240V AWB	4000 K	>70	34000 lm
01671102	BVP283 LED320/NW 315W 220-240V AWB	4000 K	>70	32000 lm
01671202	BVP283 LED280/NW 280W 220-240V AWB	4000 K	>70	28000 lm
01671302	BVP283 LED245/NW 245W 220-240V AWB	4000 K	>70	24500 lm
01671402	BVP283 LED210/NW 210W 220-240V AWB	4000 K	>70	21000 lm
01689102	BVP283 LED327/WW 350W 220-240V NB	3000 K	>70	32700 lm
01689202	BVP283 LED355/NW 350W 220-240V AWB	4000 K	>70	35500 lm
01689402	BVP283 LED327/WW 350W 220-240V AWB	3000 K	>70	32700 lm
01689502	BVP283 LED355/NW 350W 220-240V SWB	4000 K	>70	35500 lm
01689702	BVP283 LED327/WW 350W 220-240V SWB	3000 K	>70	32700 lm

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
01689802	BVP283 LED355/NW 350W 220-240V NB	4000 K	>70	35500 lm
01692505	BVP283 LED262/CW 200W 220-240V AWB	5700 K	>70	26200 lm
01692605	BVP283 LED262/CW 200W 220-240V AWBE	5700 K	>70	26200 lm
01692705	BVP283 LED262/CW 200W 220-240V NB	5700 K	>70	26200 lm
01692805	BVP283 LED262/CW 200W 220-240V SWB	5700 K	>70	26200 lm
01692905	BVP283 LED262/NW 200W 220-240V AWB	4000 K	>70	26200 lm
01693005	BVP283 LED262/NW 200W 220-240V AWBE	4000 K	>70	26200 lm
01693105	BVP283 LED262/NW 200W 220-240V NB	4000 K	>70	26200 lm
01693205	BVP283 LED262/NW 200W 220-240V SWB	4000 K	>70	26200 lm
01693505	BVP283 LED281/WW 235W 220-240V AWB	3000 K	>70	28100 lm
01693605	BVP283 LED281/WW 235W 220-240V AWBE	3000 K	>70	28100 lm
01693705	BVP283 LED306/CW 235W 220-240V AWB	5700 K	>70	30600 lm
01693805	BVP283 LED306/CW 235W 220-240V AWBE	5700 K	>70	30600 lm
01693905	BVP283 LED306/NW 235W 220-240V AWB	4000 K	>70	30600 lm
01694005	BVP283 LED306/NW 235W 220-240V AWBE	4000 K	>70	30600 lm
01694105	BVP283 LED319/WW 270W 220-240V AWBE	3000 K	>70	31900 lm
01694205	BVP283 LED319/WW 270W 220-240V NB	3000 K	>70	31900 lm
01694305	BVP283 LED347/CW 270W 220-240V AWBE	5700 K	>70	34700 lm
01694405	BVP283 LED347/CW 270W 220-240V NB	5700 K	>70	34700 lm
01694505	BVP283 LED347/NW 270W 220-240V AWBE	4000 K	>70	34700 lm
01694605	BVP283 LED347/NW 270W 220-240V NB	4000 K	>70	34700 lm
01694905	BVP283 LED390/CW 305W 220-240V AWBE	5700 K	>70	39000 lm
01695005	BVP283 LED390/CW 305W 220-240V NB	5700 K	>70	39000 lm
01695105	BVP283 LED390/CW 305W 220-240V SWB	5700 K	>70	39000 lm
01695205	BVP283 LED390/NW 305W 220-240V AWBE	4000 K	>70	39000 lm

## Tango G2 LED

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
01695305	BVP283 LED390/NW 305W 220-240V NB	4000 K	>70	39000 lm
01695405	BVP283 LED390/NW 305W 220-240V SWB	4000 K	>70	39000 lm
01695505	BVP283 LED375/WW 320W 220-240V AWB	3000 K	>70	37500 lm
01695605	BVP283 LED375/WW 320W 220-240V AWBE	3000 K	>70	37500 lm
01695705	BVP283 LED375/WW 320W 220-240V NB	3000 K	>70	37500 lm
01695805	BVP283 LED375/WW 320W 220-240V SWB	3000 K	>70	37500 lm
01695905	BVP283 LED408/CW 320W 220-240V AWB	5700 K	>70	40800 lm
01696005	BVP283 LED408/CW 320W 220-240V AWBE	5700 K	>70	40800 lm
01696105	BVP283 LED408/CW 320W 220-240V NB	5700 K	>70	40800 lm
01696205	BVP283 LED408/CW 320W 220-240V SWB	5700 K	>70	40800 lm
01696305	BVP283 LED408/NW 320W 220-240V AWB	4000 K	>70	40800 lm
01696405	BVP283 LED408/NW 320W 220-240V AWBE	4000 K	>70	40800 lm
01696505	BVP283 LED408/NW 320W 220-240V NB	4000 K	>70	40800 lm

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
01696605	BVP283 LED408/NW 320W 220-240V SWB	4000 K	>70	40800 lm
01696905	BVP283 LED395/WW 335W 220-240V AWB	3000 K	>70	39500 lm
01697005	BVP283 LED395/WW 335W 220-240V AWBE	3000 K	>70	39500 lm
01697105	BVP283 LED395/WW 335W 220-240V NB	3000 K	>70	39500 lm
01697205	BVP283 LED395/WW 335W 220-240V SWB	3000 K	>70	39500 lm
01697305	BVP283 LED430/CW 335W 220-240V AWB	5700 K	>70	43000 lm
01697405	BVP283 LED430/CW 335W 220-240V AWBE	5700 K	>70	43000 lm
01697505	BVP283 LED430/CW 335W 220-240V NB	5700 K	>70	43000 lm
01697605	BVP283 LED430/CW 335W 220-240V SWB	5700 K	>70	43000 lm
01697705	BVP283 LED430/NW 335W 220-240V AWB	4000 K	>70	43000 lm
01697805	BVP283 LED430/NW 335W 220-240V AWBE	4000 K	>70	43000 lm
01697905	BVP283 LED430/NW 335W 220-240V NB	4000 K	>70	43000 lm
01698005	BVP283 LED430/NW 335W 220-240V SWB	4000 K	>70	43000 lm

### Light Technical

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
01660504	BVP281 LED101/CW 80W 220-240V SWB	-	-
01660704	BVP281 LED101/CW 80W 220-240V AMB	-	-
01660804	BVP281 LED50/CW 40W 220-240V SWB	-	-
01660904	BVP281 LED101/WW 80W 220-240V SMB	-	-
01661104	BVP281 LED101/WW 80W 220-240V AMB	-	-
01661204	BVP281 LED50/NW 40W 220-240V SMB	-	-
01661304	BVP281 LED50/NW 40W 220-240V AMB	-	-
01661404	BVP281 LED50/CW 40W 220-240V SMB	-	-
01661604	BVP281 LED50/CW 40W 220-240V AMB	-	-
01661704	BVP281 LED50/WW 40W 220-240V SMB	-	-
01661804	BVP281 LED101/CW 80W 220-240V SMB	-	-
01661904	BVP281 LED101/NW 80W 220-240V AMB	-	-
01662004	BVP281 LED151/CW 120W 220-240V AMB	-	-
01662104	BVP281 LED151/WW 120W 220-240V AMB	-	-
01662204	BVP281 LED151/NW 120W 220-240V AMB	-	-
01662304	BVP281 LED101/NW 80W 220-240V SWB	-	-
01662404	BVP281 LED151/CW 120W 220-240V SMB	-	-
01662504	BVP281 LED151/WW 120W 220-240V SMB	-	-

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
01662604	BVP281 LED151/CW 120W 220-240V SWB	-	-
01662704	BVP281 LED101/NW 80W 220-240V SMB	-	-
01662804	BVP281 LED151/NW 120W 220-240V SWB	-	-
01662904	BVP281 LED151/NW 120W 220-240V SMB	-	-
01663004	BVP282 LED202/WW 160W 220-240V AMB	-	-
01663104	BVP282 LED202/WW 160W 220-240V SWB	-	-
01663204	BVP282 LED202/NW 160W 220-240V SWB	-	-
01663304	BVP282 LED202/NW 160W 220-240V AMB	-	-
01663404	BVP282 LED202/CW 160W 220-240V SMB	-	-
01663504	BVP282 LED202/CW 160W 220-240V AMB	-	-
01663604	BVP282 LED202/NW 160W 220-240V SMB	-	-

## Tango G2 LED

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
01663704	BVP282 LED202/CW 160W 220-240V SWB	-	-
01663804	BVP282 LED252/WW 200W 220-240V SMB	-	-
01663904	BVP282 LED252/CW 200W 220-240V SWB	-	-
01664004	BVP282 LED252/WW 200W 220-240V SWB	-	-
01664104	BVP282 LED252/NW 200W 220-240V AMB	-	-
01664204	BVP282 LED252/WW 200W 220-240V AMB	-	-
01664304	BVP282 LED252/CW 200W 220-240V SMB	-	-
32985700	BVP282 LED252/CW 200W 220-240V AMB	-	-
01664504	BVP282 LED252/NW 200W 220-240V SWB	-	-
01664604	BVP282 LED252/NW 200W 220-240V SMB	-	-
01664704	BVP282 LED202/WW 160W 220-240V SMB	-	-
01667002	BVP283 LED311/WW 335W 220-240V NB	-	-
01667102	BVP283 LED293/WW 315W 220-240V NB	-	-
01667202	BVP283 LED256/WW 280W 220-240V NB	-	-
01667302	BVP283 LED224/WW 245W 220-240V NB	-	-
01667402	BVP283 LED192/WW 210W 220-240V NB	-	-
01668002	BVP283 LED340/NW 335W 220-240V NB	-	-
01668102	BVP283 LED320/NW 315W 220-240V NB	-	-
01668202	BVP283 LED280/NW 280W 220-240V NB	-	-
01668302	BVP283 LED245/NW 245W 220-240V NB	-	-
01668402	BVP283 LED210/NW 210W 220-240V NB	-	-
01668502	BVP283 LED311/WW 335W 220-240V SWB	-	-
01668602	BVP283 LED307/WW 315W 220-240V SWB	-	-
01668702	BVP283 LED224/WW 245W 220-240V SWB	-	-
01668802	BVP283 LED256/WW 280W 220-240V SWB	-	-
01668902	BVP283 LED192/WW 210W 220-240V SWB	-	-
01669502	BVP283 LED340/NW 335W 220-240V SWB	-	-
01669602	BVP283 LED320/NW 315W 220-240V SWB	-	-
01669702	BVP283 LED280/NW 280W 220-240V SWB	-	-
01669802	BVP283 LED245/NW 245W 220-240V SWB	-	-

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
01669902	BVP283 LED210/NW 210W 220-240V SWB	-	-
01670002	BVP283 LED311/WW 335W 220-240V AWB	-	-
01670102	BVP283 LED293/WW 315W 220-240V AWB	-	-
01670202	BVP283 LED256/WW 280W 220-240V AWB	-	-
01670302	BVP283 LED224/WW 245W 220-240V AWB	-	-
01670402	BVP283 LED192/WW 210W 220-240V AWB	-	-
01671002	BVP283 LED340/NW 335W 220-240V AWB	-	-
01671102	BVP283 LED320/NW 315W 220-240V AWB	-	-
01671202	BVP283 LED280/NW 280W 220-240V AWB	-	-
01671302	BVP283 LED245/NW 245W 220-240V AWB	-	-
01671402	BVP283 LED210/NW 210W 220-240V AWB	-	-
01689102	BVP283 LED327/WW 350W 220-240V NB	-	-
01689202	BVP283 LED355/NW 350W 220-240V AWB	-	-
01689402	BVP283 LED327/WW 350W 220-240V AWB	-	-
01689502	BVP283 LED355/NW 350W 220-240V SWB	-	-
01689702	BVP283 LED327/WW 350W 220-240V SWB	-	-
01689802	BVP283 LED355/NW 350W 220-240V NB	-	-
01692505	BVP283 LED262/CW 200W 220-240V AWB	-	-
01692605	BVP283 LED262/CW 200W 220-240V AWBE	-	-
01692705	BVP283 LED262/CW 200W 220-240V NB	-	-
01692805	BVP283 LED262/CW 200W 220-240V SWB	-	-
01692905	BVP283 LED262/NW 200W 220-240V AWB	-	-
01693005	BVP283 LED262/NW 200W 220-240V AWBE	-	-
01693105	BVP283 LED262/NW 200W 220-240V NB	-	-
01693205	BVP283 LED262/NW 200W 220-240V SWB	-	-
01693505	BVP283 LED281/WW 235W 220-240V AWB	-	-
01693605	BVP283 LED281/WW 235W 220-240V AWBE	-	-

## Tango G2 LED

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
01693705	BVP283 LED306/CW 235W 220-240V AWB	-	-
01693805	BVP283 LED306/CW 235W 220-240V AWBE	-	-
01693905	BVP283 LED306/NW 235W 220-240V AWB	-	-
01694005	BVP283 LED306/NW 235W 220-240V AWBE	-	-
01694105	BVP283 LED319/WW 270W 220-240V AWBE	-	-
01694205	BVP283 LED319/WW 270W 220-240V NB	-	-
01694305	BVP283 LED347/CW 270W 220-240V AWBE	-	-
01694405	BVP283 LED347/CW 270W 220-240V NB	-	-
01694505	BVP283 LED347/NW 270W 220-240V AWBE	-	-
01694605	BVP283 LED347/NW 270W 220-240V NB	-	-
01694905	BVP283 LED390/CW 305W 220-240V AWBE	-	-
01695005	BVP283 LED390/CW 305W 220-240V NB	-	-
01695105	BVP283 LED390/CW 305W 220-240V SWB	-	-
01695205	BVP283 LED390/NW 305W 220-240V AWBE	-	-
01695305	BVP283 LED390/NW 305W 220-240V NB	-	-
01695405	BVP283 LED390/NW 305W 220-240V SWB	-	-
01695505	BVP283 LED375/WW 320W 220-240V AWB	-	-
01695605	BVP283 LED375/WW 320W 220-240V AWBE	-	-
01695705	BVP283 LED375/WW 320W 220-240V NB	-	-
01695805	BVP283 LED375/WW 320W 220-240V SWB	-	-
01695905	BVP283 LED408/CW 320W 220-240V AWB	-	-

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
01696005	BVP283 LED408/CW 320W 220-240V AWBE	-	-
01696105	BVP283 LED408/CW 320W 220-240V NB	-	-
01696205	BVP283 LED408/CW 320W 220-240V SWB	-	-
01696305	BVP283 LED408/NW 320W 220-240V AWB	-	-
01696405	BVP283 LED408/NW 320W 220-240V AWBE	-	-
01696505	BVP283 LED408/NW 320W 220-240V NB	-	-
01696605	BVP283 LED408/NW 320W 220-240V SWB	-	-
01696905	BVP283 LED395/WW 335W 220-240V AWB	-	-
01697005	BVP283 LED395/WW 335W 220-240V AWBE	-	-
01697105	BVP283 LED395/WW 335W 220-240V NB	-	-
01697205	BVP283 LED395/WW 335W 220-240V SWB	-	-
01697305	BVP283 LED430/CW 335W 220-240V AWB	-	-
01697405	BVP283 LED430/CW 335W 220-240V AWBE	-	-
01697505	BVP283 LED430/CW 335W 220-240V NB	-	-
01697605	BVP283 LED430/CW 335W 220-240V SWB	-	-
01697705	BVP283 LED430/NW 335W 220-240V AWB	-	-
01697805	BVP283 LED430/NW 335W 220-240V AWBE	-	-
01697905	BVP283 LED430/NW 335W 220-240V NB	-	-
01698005	BVP283 LED430/NW 335W 220-240V SWB	-	-

