



# Best Area Lighting Luminaire within Your Budget

## Tango G2 LED

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

### Benefits

- Energy saving: more than 50% of energy saving when compared to conventional floodlight
- Free from lamp replacement
- Low maintenance cost: IP65 housing ensures low maintenance with no need for internal cleaning, resulting in a lower total cost of ownership

### Features



- Optical beam choice of symmetric and asymmetric fulfils majority needs of lighting application
- Painted non-corrosive die-cast aluminum housing and steel bracket
- Universal "U" shape mounting bracket

### Application


- Area lighting
- Industry area
- Façade

# Tango G2 LED

## Versions



BVP282 220-240 V



BVP283 220-240V

### General Information

CE mark	CE mark
Optical cover/lens type	PC-MLO
Driver included	Yes

### Mechanical and Housing

Colour	Aluminium and Grey
--------	--------------------

## Approval and Application

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
911401660504	BVP281 LED101/CW 80W 220-240V SWB	IK07	Surge protection level until 10 kV
911401660704	BVP281 LED101/CW 80W 220-240V AMB	IK07	Surge protection level until 10 kV
911401660804	BVP281 LED50/CW 40W 220-240V SWB	IK07	Surge protection level until 10 kV
911401660904	BVP281 LED101/WW 80W 220-240V SMB	IK07	Surge protection level until 10 kV
911401661004	BVP281 LED50/NW 40W 220-240V SWB	IK07	Surge protection level until 10 kV
911401661104	BVP281 LED101/WW 80W 220-240V AMB	IK07	Surge protection level until 10 kV
911401661204	BVP281 LED50/NW 40W 220-240V SMB	IK07	Surge protection level until 10 kV
911401661304	BVP281 LED50/NW 40W 220-240V AMB	IK07	Surge protection level until 10 kV
911401661404	BVP281 LED50/CW 40W 220-240V SMB	IK07	Surge protection level until 10 kV
911401661604	BVP281 LED50/CW 40W 220-240V AMB	IK07	Surge protection level until 10 kV
911401661704	BVP281 LED50/WW 40W 220-240V SMB	IK07	Surge protection level until 10 kV

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
911401661804	BVP281 LED101/CW 80W 220-240V SMB	IK07	Surge protection level until 10 kV
911401661904	BVP281 LED101/NW 80W 220-240V AMB	IK07	Surge protection level until 10 kV
911401662004	BVP281 LED151/CW 120W 220-240V AMB	IK07	Surge protection level until 10 kV
911401662104	BVP281 LED151/WW 120W 220-240V AMB	IK07	Surge protection level until 10 kV
911401662204	BVP281 LED151/NW 120W 220-240V AMB	IK07	Surge protection level until 10 kV
911401662304	BVP281 LED101/NW 80W 220-240V SWB	IK07	Surge protection level until 10 kV
911401662404	BVP281 LED151/CW 120W 220-240V SMB	IK07	Surge protection level until 10 kV
911401662504	BVP281 LED151/WW 120W 220-240V SMB	IK07	Surge protection level until 10 kV
911401662604	BVP281 LED151/CW 120W 220-240V SWB	IK07	Surge protection level until 10 kV
911401662704	BVP281 LED101/NW 80W 220-240V SMB	IK07	Surge protection level until 10 kV
911401662804	BVP281 LED151/NW 120W 220-240V SWB	IK07	Surge protection level until 10 kV

## Tango G2 LED

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
911401662904	BVP281 LED151/NW 120W 220-240V SMB	IK07	Surge protection level until 10 kV
911401663004	BVP282 LED202/WW 160W 220-240V AMB	IK07	Surge protection level until 10 kV
911401663104	BVP282 LED202/WW 160W 220-240V SWB	IK07	Surge protection level until 10 kV
911401663204	BVP282 LED202/NW 160W 220-240V SWB	IK07	Surge protection level until 10 kV
911401663304	BVP282 LED202/NW 160W 220-240V AMB	IK07	Surge protection level until 10 kV
911401663404	BVP282 LED202/CW 160W 220-240V SMB	IK07	Surge protection level until 10 kV
911401663504	BVP282 LED202/CW 160W 220-240V AMB	IK07	Surge protection level until 10 kV
911401663604	BVP282 LED202/NW 160W 220-240V SMB	IK07	Surge protection level until 10 kV
911401663704	BVP282 LED202/CW 160W 220-240V SWB	IK07	Surge protection level until 10 kV
911401663804	BVP282 LED252/WW 200W 220-240V SMB	IK07	Surge protection level until 10 kV
911401663904	BVP282 LED252/CW 200W 220-240V SWB	IK07	Surge protection level until 10 kV
911401664004	BVP282 LED252/WW 200W 220-240V SWB	IK07	Surge protection level until 10 kV
911401664104	BVP282 LED252/NW 200W 220-240V AMB	IK07	Surge protection level until 10 kV
911401664204	BVP282 LED252/WW 200W 220-240V AMB	IK07	Surge protection level until 10 kV
911401664304	BVP282 LED252/CW 200W 220-240V SMB	IK07	Surge protection level until 10 kV
911401664404	BVP282 LED252/CW 200W 220-240V AMB	IK07	Surge protection level until 10 kV
911401664504	BVP282 LED252/NW 200W 220-240V SWB	IK07	Surge protection level until 10 kV
911401664604	BVP282 LED252/NW 200W 220-240V SMB	IK07	Surge protection level until 10 kV
911401664704	BVP282 LED202/WW 160W 220-240V SMB	IK07	Surge protection level until 10 kV
911401692505	BVP283 LED262/CW 200W 220-240V AWB	IK08	-
911401692605	BVP283 LED262/CW 200W 220-240V AWBE	IK08	-
911401692705	BVP283 LED262/CW 200W 220-240V NB	IK08	-
911401692805	BVP283 LED262/CW 200W 220-240V SWB	IK08	-
911401692905	BVP283 LED262/NW 200W 220-240V AWB	IK08	-
911401693005	BVP283 LED262/NW 200W 220-240V AWBE	IK08	-

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
911401693105	BVP283 LED262/NW 200W 220-240V NB	IK08	-
911401693205	BVP283 LED262/NW 200W 220-240V SWB	IK08	-
911401693505	BVP283 LED281/WW 235W 220-240V AWB	IK08	-
911401693605	BVP283 LED281/WW 235W 220-240V AWBE	IK08	-
911401693705	BVP283 LED306/CW 235W 220-240V AWB	IK08	-
911401693805	BVP283 LED306/CW 235W 220-240V AWBE	IK08	-
911401693905	BVP283 LED306/NW 235W 220-240V AWB	IK08	-
911401694005	BVP283 LED306/NW 235W 220-240V AWBE	IK08	-
911401694105	BVP283 LED319/WW 270W 220-240V AWBE	IK08	-
911401694205	BVP283 LED319/WW 270W 220-240V NB	IK08	-
911401694305	BVP283 LED347/CW 270W 220-240V AWBE	IK08	-
911401694405	BVP283 LED347/CW 270W 220-240V NB	IK08	-
911401694505	BVP283 LED347/NW 270W 220-240V AWBE	IK08	-
911401694605	BVP283 LED347/NW 270W 220-240V NB	IK08	-
911401694905	BVP283 LED390/CW 305W 220-240V AWBE	IK08	-
911401695005	BVP283 LED390/CW 305W 220-240V NB	IK08	-
911401695105	BVP283 LED390/CW 305W 220-240V SWB	IK08	-
911401695205	BVP283 LED390/NW 305W 220-240V AWBE	IK08	-
911401695305	BVP283 LED390/NW 305W 220-240V NB	IK08	-
911401695405	BVP283 LED390/NW 305W 220-240V SWB	IK08	-
911401695505	BVP283 LED375/WW 320W 220-240V AWB	IK08	-
911401695605	BVP283 LED375/WW 320W 220-240V AWBE	IK08	-
911401695705	BVP283 LED375/WW 320W 220-240V NB	IK08	-
911401695805	BVP283 LED375/WW 320W 220-240V SWB	IK08	-
911401695905	BVP283 LED408/CW 320W 220-240V AWB	IK08	-

## Tango G2 LED

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
911401696005	BVP283 LED408/CW 320W 220-240V AWBE	IK08	-
911401696105	BVP283 LED408/CW 320W 220-240V NB	IK08	-
911401696205	BVP283 LED408/CW 320W 220-240V SWB	IK08	-
911401696305	BVP283 LED408/NW 320W 220-240V AWB	IK08	-
911401696405	BVP283 LED408/NW 320W 220-240V AWBE	IK08	-
911401696505	BVP283 LED408/NW 320W 220-240V NB	IK08	-
911401696605	BVP283 LED408/NW 320W 220-240V SWB	IK08	-
911401696905	BVP283 LED395/WW 335W 220-240V AWB	IK08	-
911401697005	BVP283 LED395/WW 335W 220-240V AWBE	IK08	-
911401697105	BVP283 LED395/WW 335W 220-240V NB	IK08	-

Order Code	Full Product Name	Mech. impact	
		protection code	Surge Protection (Common/Differential)
911401697205	BVP283 LED395/WW 335W 220-240V SWB	IK08	-
911401697305	BVP283 LED430/CW 335W 220-240V AWB	IK08	-
911401697405	BVP283 LED430/CW 335W 220-240V AWBE	IK08	-
911401697505	BVP283 LED430/CW 335W 220-240V NB	IK08	-
911401697605	BVP283 LED430/CW 335W 220-240V SWB	IK08	-
911401697705	BVP283 LED430/NW 335W 220-240V AWB	IK08	-
911401697805	BVP283 LED430/NW 335W 220-240V AWBE	IK08	-
911401697905	BVP283 LED430/NW 335W 220-240V NB	IK08	-
911401698005	BVP283 LED430/NW 335W 220-240V SWB	IK08	-
911401698105	BVP283 LED430/NW 335W AWB P7 GM	IK08	-

### Controls and Dimming

Order Code	Full Product Name	Dimmable
911401660504	BVP281 LED101/CW 80W 220-240V SWB	No
911401660704	BVP281 LED101/CW 80W 220-240V AMB	No
911401660804	BVP281 LED50/CW 40W 220-240V SWB	No
911401660904	BVP281 LED101/WW 80W 220-240V SMB	No
911401661004	BVP281 LED50/NW 40W 220-240V SWB	No
911401661104	BVP281 LED101/WW 80W 220-240V AMB	No
911401661204	BVP281 LED50/NW 40W 220-240V SMB	No
911401661304	BVP281 LED50/NW 40W 220-240V AMB	No
911401661404	BVP281 LED50/CW 40W 220-240V SMB	No
911401661604	BVP281 LED50/CW 40W 220-240V AMB	No
911401661704	BVP281 LED50/WW 40W 220-240V SMB	No
911401661804	BVP281 LED101/CW 80W 220-240V SMB	No
911401661904	BVP281 LED101/NW 80W 220-240V AMB	No
911401662004	BVP281 LED151/CW 120W 220-240V AMB	No
911401662104	BVP281 LED151/WW 120W 220-240V AMB	No
911401662204	BVP281 LED151/NW 120W 220-240V AMB	No
911401662304	BVP281 LED101/NW 80W 220-240V SWB	No
911401662404	BVP281 LED151/CW 120W 220-240V SMB	No
911401662504	BVP281 LED151/WW 120W 220-240V SMB	No
911401662604	BVP281 LED151/CW 120W 220-240V SWB	No
911401662704	BVP281 LED101/NW 80W 220-240V SMB	No
911401662804	BVP281 LED151/NW 120W 220-240V SWB	No
911401662904	BVP281 LED151/NW 120W 220-240V SMB	No
911401663004	BVP282 LED202/WW 160W 220-240V AMB	No
911401663104	BVP282 LED202/WW 160W 220-240V SWB	No
911401663204	BVP282 LED202/NW 160W 220-240V SWB	No

Order Code	Full Product Name	Dimmable
911401663304	BVP282 LED202/NW 160W 220-240V AMB	No
911401663404	BVP282 LED202/CW 160W 220-240V SMB	No
911401663504	BVP282 LED202/CW 160W 220-240V AMB	No
911401663604	BVP282 LED202/NW 160W 220-240V SMB	No
911401663704	BVP282 LED202/CW 160W 220-240V SWB	No
911401663804	BVP282 LED252/WW 200W 220-240V SMB	No
911401663904	BVP282 LED252/CW 200W 220-240V SWB	No
911401664004	BVP282 LED252/WW 200W 220-240V SWB	No
911401664104	BVP282 LED252/NW 200W 220-240V AMB	No
911401664204	BVP282 LED252/WW 200W 220-240V AMB	No
911401664304	BVP282 LED252/CW 200W 220-240V SMB	No
911401664404	BVP282 LED252/CW 200W 220-240V AMB	No
911401664504	BVP282 LED252/NW 200W 220-240V SWB	No
911401664604	BVP282 LED252/NW 200W 220-240V SMB	No
911401664704	BVP282 LED202/WW 160W 220-240V SMB	No
911401692505	BVP283 LED262/CW 200W 220-240V AWB	No
911401692605	BVP283 LED262/CW 200W 220-240V AWBE	No
911401692705	BVP283 LED262/CW 200W 220-240V NB	No
911401692805	BVP283 LED262/CW 200W 220-240V SWB	No
911401692905	BVP283 LED262/NW 200W 220-240V AWB	No
911401693005	BVP283 LED262/NW 200W 220-240V AWBE	No
911401693105	BVP283 LED262/NW 200W 220-240V NB	No
911401693205	BVP283 LED262/NW 200W 220-240V SWB	No
911401693505	BVP283 LED281/WW 235W 220-240V AWB	No
911401693605	BVP283 LED281/WW 235W 220-240V AWBE	No
911401693705	BVP283 LED306/CW 235W 220-240V AWB	No

## Tango G2 LED

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401693805	BVP283 LED306/CW 235W 220-240V AWBE	No	911401696005	BVP283 LED408/CW 320W 220-240V AWBE	No
911401693905	BVP283 LED306/NW 235W 220-240V AWB	No	911401696105	BVP283 LED408/CW 320W 220-240V NB	No
911401694005	BVP283 LED306/NW 235W 220-240V AWBE	No	911401696205	BVP283 LED408/CW 320W 220-240V SWB	No
911401694105	BVP283 LED319/WW 270W 220-240V AWBE	No	911401696305	BVP283 LED408/NW 320W 220-240V AWB	No
911401694205	BVP283 LED319/WW 270W 220-240V NB	No	911401696405	BVP283 LED408/NW 320W 220-240V AWBE	No
911401694305	BVP283 LED347/CW 270W 220-240V AWBE	No	911401696505	BVP283 LED408/NW 320W 220-240V NB	No
911401694405	BVP283 LED347/CW 270W 220-240V NB	No	911401696605	BVP283 LED408/NW 320W 220-240V SWB	No
911401694505	BVP283 LED347/NW 270W 220-240V AWBE	No	911401696905	BVP283 LED395/WW 335W 220-240V AWB	No
911401694605	BVP283 LED347/NW 270W 220-240V NB	No	911401697005	BVP283 LED395/WW 335W 220-240V AWBE	No
911401694905	BVP283 LED390/CW 305W 220-240V AWBE	No	911401697105	BVP283 LED395/WW 335W 220-240V NB	No
911401695005	BVP283 LED390/CW 305W 220-240V NB	No	911401697205	BVP283 LED395/WW 335W 220-240V SWB	No
911401695105	BVP283 LED390/CW 305W 220-240V SWB	No	911401697305	BVP283 LED430/CW 335W 220-240V AWB	No
911401695205	BVP283 LED390/NW 305W 220-240V AWBE	No	911401697405	BVP283 LED430/CW 335W 220-240V AWBE	No
911401695305	BVP283 LED390/NW 305W 220-240V NB	No	911401697505	BVP283 LED430/CW 335W 220-240V NB	No
911401695405	BVP283 LED390/NW 305W 220-240V SWB	No	911401697605	BVP283 LED430/CW 335W 220-240V SWB	No
911401695505	BVP283 LED375/WW 320W 220-240V AWB	No	911401697705	BVP283 LED430/NW 335W 220-240V AWB	No
911401695605	BVP283 LED375/WW 320W 220-240V AWBE	No	911401697805	BVP283 LED430/NW 335W 220-240V AWBE	No
911401695705	BVP283 LED375/WW 320W 220-240V NB	No	911401697905	BVP283 LED430/NW 335W 220-240V NB	No
911401695805	BVP283 LED375/WW 320W 220-240V SWB	No	911401698005	BVP283 LED430/NW 335W 220-240V SWB	No
911401695905	BVP283 LED408/CW 320W 220-240V AWB	No	911401698105	BVP283 LED430/NW 335W AWB P7 GM	Yes

### General Information

Order Code	Full Product Name	Luminaire light		Flammability mark	Lamp family code	Light source replaceable	Number of gear units	Optic type
		beam spread	Light source colour					
911401660504	BVP281 LED101/CW 80W 220-240V SWB	100°	Cool white	NO	-	Yes	-	Symmetrical wide beam
911401660704	BVP281 LED101/CW 80W 220-240V AMB	100° x 30°	Cool white	NO	-	Yes	-	Asymmetrical medium beam
911401660804	BVP281 LED50/CW 40W 220-240V SWB	100°	Cool white	NO	-	Yes	-	Symmetrical wide beam
911401660904	BVP281 LED101/WW 80W 220-240V SMB	54°	Warm white	NO	-	Yes	-	Symmetrical medium beam
911401661004	BVP281 LED50/NW 40W 220-240V SWB	100°	Neutral white	NO	-	Yes	-	Symmetrical wide beam
911401661104	BVP281 LED101/WW 80W 220-240V AMB	100° x 30°	Warm white	NO	-	Yes	-	Asymmetrical medium beam
911401661204	BVP281 LED50/NW 40W 220-240V SMB	54°	Neutral white	NO	-	Yes	-	Symmetrical medium beam
911401661304	BVP281 LED50/NW 40W 220-240V AMB	100° x 30°	Neutral white	NO	-	Yes	-	Asymmetrical medium beam
911401661404	BVP281 LED50/CW 40W 220-240V SMB	54°	Cool white	NO	-	Yes	-	Symmetrical medium beam
911401661604	BVP281 LED50/CW 40W 220-240V AMB	100° x 30°	Cool white	NO	-	Yes	-	Asymmetrical medium beam
911401661704	BVP281 LED50/WW 40W 220-240V SMB	54°	Warm white	NO	-	Yes	-	Symmetrical medium beam
911401661804	BVP281 LED101/CW 80W 220-240V SMB	54°	Cool white	NO	-	Yes	-	Symmetrical medium beam
911401661904	BVP281 LED101/NW 80W 220-240V AMB	100° x 30°	Neutral white	NO	-	Yes	-	Asymmetrical medium beam

## Tango G2 LED

Order Code	Full Product Name	Luminaire light		Flammability mark	Lamp family code	Light source replaceable	Number of gear units	Optic type
		beam spread	Light source colour					
911401662004	BVP281 LED151/CW 120W 220-240V AMB	100° x 30°	Cool white	NO	-	Yes	-	Asymmetrical medium beam
911401662104	BVP281 LED151/WW 120W 220-240V AMB	100° x 30°	Warm white	NO	-	Yes	-	Asymmetrical medium beam
911401662204	BVP281 LED151/NW 120W 220-240V AMB	100° x 30°	Neutral white	NO	-	Yes	-	Asymmetrical medium beam
911401662304	BVP281 LED101/NW 80W 220-240V SWB	100°	Neutral white	NO	-	Yes	-	Symmetrical wide beam
911401662404	BVP281 LED151/CW 120W 220-240V SMB	54°	Cool white	NO	-	Yes	-	Symmetrical medium beam
911401662504	BVP281 LED151/WW 120W 220-240V SMB	54°	Warm white	NO	-	Yes	-	Symmetrical medium beam
911401662604	BVP281 LED151/CW 120W 220-240V SWB	100°	Cool white	NO	-	Yes	-	Symmetrical wide beam
911401662704	BVP281 LED101/NW 80W 220-240V SMB	54°	Neutral white	NO	-	Yes	-	Symmetrical medium beam
911401662804	BVP281 LED151/NW 120W 220-240V SWB	100°	Neutral white	NO	-	Yes	-	Symmetrical wide beam
911401662904	BVP281 LED151/NW 120W 220-240V SMB	54°	Neutral white	NO	-	Yes	-	Symmetrical medium beam
911401663004	BVP282 LED202/WW 160W 220-240V AMB	100° x 30°	Warm white	NO	-	Yes	-	Asymmetrical medium beam
911401663104	BVP282 LED202/WW 160W 220-240V SWB	100°	Warm white	NO	-	Yes	-	Symmetrical wide beam
911401663204	BVP282 LED202/NW 160W 220-240V SWB	100°	Neutral white	NO	-	Yes	-	Symmetrical wide beam
911401663304	BVP282 LED202/NW 160W 220-240V AMB	100° x 30°	Neutral white	NO	-	Yes	-	Asymmetrical medium beam
911401663404	BVP282 LED202/CW 160W 220-240V SMB	54°	Cool white	NO	-	Yes	-	Symmetrical medium beam
911401663504	BVP282 LED202/CW 160W 220-240V AMB	100° x 30°	Cool white	NO	-	Yes	-	Asymmetrical medium beam
911401663604	BVP282 LED202/NW 160W 220-240V SMB	54°	Neutral white	NO	-	Yes	-	Symmetrical medium beam
911401663704	BVP282 LED202/CW 160W 220-240V SWB	100°	Cool white	NO	-	Yes	-	Symmetrical wide beam
911401663804	BVP282 LED252/WW 200W 220-240V SMB	54°	Warm white	NO	-	Yes	-	Symmetrical medium beam
911401663904	BVP282 LED252/CW 200W 220-240V SWB	100°	Cool white	NO	-	Yes	-	Symmetrical wide beam
911401664004	BVP282 LED252/WW 200W 220-240V SWB	100°	Warm white	NO	-	Yes	-	Symmetrical wide beam
911401664104	BVP282 LED252/NW 200W 220-240V AMB	100° x 30°	Neutral white	NO	-	Yes	-	Asymmetrical medium beam
911401664204	BVP282 LED252/WW 200W 220-240V AMB	100° x 30°	Warm white	NO	-	Yes	-	Asymmetrical medium beam
911401664304	BVP282 LED252/CW 200W 220-240V SMB	54°	Cool white	NO	-	Yes	-	Symmetrical medium beam
911401664404	BVP282 LED252/CW 200W 220-240V AMB	100° x 30°	Cool white	NO	-	Yes	-	Asymmetrical medium beam

## Tango G2 LED

Order Code	Full Product Name	Luminaire light		Flammability	Lamp family	Light source	Number of	Optic type
		beam spread	Light source colour					
911401664504	BVP282 LED252/NW 200W 220-240V SWB	100°	Neutral white	NO	-	Yes	-	Symmetrical wide beam
911401664604	BVP282 LED252/NW 200W 220-240V SMB	54°	Neutral white	NO	-	Yes	-	Symmetrical medium beam
911401664704	BVP282 LED202/WW 160W 220-240V SMB	54°	Warm white	NO	-	Yes	-	Symmetrical medium beam
911401692505	BVP283 LED262/CW 200W 220-240V AWB	-	757 cool white	-	-	-	-	-
911401692605	BVP283 LED262/CW 200W 220-240V AWBE	-	757 cool white	-	-	-	-	-
911401692705	BVP283 LED262/CW 200W 220-240V NB	-	757 cool white	-	-	-	-	-
911401692805	BVP283 LED262/CW 200W 220-240V SWB	-	757 cool white	-	-	-	-	-
911401692905	BVP283 LED262/NW 200W 220-240V AWB	-	740 neutral white	-	-	-	-	-
911401693005	BVP283 LED262/NW 200W 220-240V AWBE	-	740 neutral white	-	-	-	-	-
911401693105	BVP283 LED262/NW 200W 220-240V NB	-	740 neutral white	-	-	-	-	-
911401693205	BVP283 LED262/NW 200W 220-240V SWB	-	740 neutral white	-	-	-	-	-
911401693505	BVP283 LED281/WW 235W 220-240V AWB	-	730 warm white	-	-	-	-	-
911401693605	BVP283 LED281/WW 235W 220-240V AWBE	-	730 warm white	-	-	-	-	-
911401693705	BVP283 LED306/CW 235W 220-240V AWB	-	757 cool white	-	-	-	-	-
911401693805	BVP283 LED306/CW 235W 220-240V AWBE	-	757 cool white	-	-	-	-	-
911401693905	BVP283 LED306/NW 235W 220-240V AWB	-	740 neutral white	-	-	-	-	-
911401694005	BVP283 LED306/NW 235W 220-240V AWBE	-	740 neutral white	-	-	-	-	-
911401694105	BVP283 LED319/WW 270W 220-240V AWBE	-	730 warm white	-	-	-	-	-
911401694205	BVP283 LED319/WW 270W 220-240V NB	-	730 warm white	-	-	-	-	-
911401694305	BVP283 LED347/CW 270W 220-240V AWBE	-	757 cool white	-	-	-	-	-
911401694405	BVP283 LED347/CW 270W 220-240V NB	-	757 cool white	-	-	-	-	-
911401694505	BVP283 LED347/NW 270W 220-240V AWBE	-	740 neutral white	-	-	-	-	-
911401694605	BVP283 LED347/NW 270W 220-240V NB	-	740 neutral white	-	-	-	-	-
911401694905	BVP283 LED390/CW 305W 220-240V AWBE	-	757 cool white	-	-	-	-	-
911401695005	BVP283 LED390/CW 305W 220-240V NB	-	757 cool white	-	-	-	-	-

## Tango G2 LED

Order Code	Full Product Name	Luminaire light		Flammability mark	Lamp family code	Light source replaceable	Number of gear units	Optic type
		beam spread	Light source colour					
911401695105	BVP283 LED390/CW 305W 220-240V SWB	-	757 cool white	-	-	-	-	-
911401695205	BVP283 LED390/NW 305W 220-240V AWBE	-	740 neutral white	-	-	-	-	-
911401695305	BVP283 LED390/NW 305W 220-240V NB	-	740 neutral white	-	-	-	-	-
911401695405	BVP283 LED390/NW 305W 220-240V SWB	-	740 neutral white	-	-	-	-	-
911401695505	BVP283 LED375/WW 320W 220-240V AWB	-	730 warm white	-	-	-	-	-
911401695605	BVP283 LED375/WW 320W 220-240V AWBE	-	730 warm white	-	-	-	-	-
911401695705	BVP283 LED375/WW 320W 220-240V NB	-	730 warm white	-	-	-	-	-
911401695805	BVP283 LED375/WW 320W 220-240V SWB	-	730 warm white	-	-	-	-	-
911401695905	BVP283 LED408/CW 320W 220-240V AWB	-	757 cool white	-	-	-	-	-
911401696005	BVP283 LED408/CW 320W 220-240V AWBE	-	757 cool white	-	-	-	-	-
911401696105	BVP283 LED408/CW 320W 220-240V NB	-	757 cool white	-	-	-	-	-
911401696205	BVP283 LED408/CW 320W 220-240V SWB	-	757 cool white	-	-	-	-	-
911401696305	BVP283 LED408/NW 320W 220-240V AWB	-	740 neutral white	-	-	-	-	-
911401696405	BVP283 LED408/NW 320W 220-240V AWBE	-	740 neutral white	-	-	-	-	-
911401696505	BVP283 LED408/NW 320W 220-240V NB	-	740 neutral white	-	-	-	-	-
911401696605	BVP283 LED408/NW 320W 220-240V SWB	-	740 neutral white	-	-	-	-	-
911401696905	BVP283 LED395/WW 335W 220-240V AWB	-	730 warm white	-	-	-	-	-
911401697005	BVP283 LED395/WW 335W 220-240V AWBE	-	730 warm white	-	-	-	-	-
911401697105	BVP283 LED395/WW 335W 220-240V NB	-	730 warm white	-	-	-	-	-
911401697205	BVP283 LED395/WW 335W 220-240V SWB	-	730 warm white	-	-	-	-	-
911401697305	BVP283 LED430/CW 335W 220-240V AWB	-	757 cool white	-	-	-	-	-
911401697405	BVP283 LED430/CW 335W 220-240V AWBE	-	757 cool white	-	-	-	-	-
911401697505	BVP283 LED430/CW 335W 220-240V NB	-	757 cool white	-	-	-	-	-
911401697605	BVP283 LED430/CW 335W 220-240V SWB	-	757 cool white	-	-	-	-	-
911401697705	BVP283 LED430/NW 335W 220-240V AWB	-	740 neutral white	-	-	-	-	-



## Tango G2 LED

Order Code	Full Product Name	Luminaire light		Flammability mark	Lamp family code	Light source replaceable	Number of gear units	Optic type
		beam spread	Light source colour					
911401697805	BVP283 LED430/NW 335W 220-240V AWBE	-	740 neutral white	-	-	-	-	-
911401697905	BVP283 LED430/NW 335W 220-240V NB	-	740 neutral white	-	-	-	-	-
911401698005	BVP283 LED430/NW 335W 220-240V SWB	-	740 neutral white	-	-	-	-	-
911401698105	BVP283 LED430/NW 335W AWB P7 GM	-	740 neutral white	-	-	-	-	-

### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Colour			Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux			Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
911401660504	BVP281 LED101/CW 80W 220-240V SWB	5700 K	70	10100 lm	911401662504	BVP281 LED151/WW 120W 220-240V SMB	3000 K	70	15100 lm
911401660704	BVP281 LED101/CW 80W 220-240V AMB	5700 K	70	10100 lm	911401662604	BVP281 LED151/CW 120W 220-240V SWB	5700 K	70	15100 lm
911401660804	BVP281 LED50/CW 40W 220-240V SWB	5700 K	70	5000 lm	911401662704	BVP281 LED101/NW 80W 220-240V SMB	4000 K	70	10100 lm
911401660904	BVP281 LED101/WW 80W 220-240V SMB	3000 K	70	10100 lm	911401662804	BVP281 LED151/NW 120W 220-240V SWB	4000 K	70	15100 lm
911401661004	BVP281 LED50/NW 40W 220-240V SWB	4000 K	70	5000 lm	911401662904	BVP281 LED151/NW 120W 220-240V SMB	4000 K	70	15100 lm
911401661104	BVP281 LED101/WW 80W 220-240V AMB	3000 K	70	10100 lm	911401663004	BVP282 LED202/WW 160W 220-240V AMB	3000 K	70	20200 lm
911401661204	BVP281 LED50/NW 40W 220-240V SMB	4000 K	70	5000 lm	911401663104	BVP282 LED202/WW 160W 220-240V SWB	3000 K	70	20200 lm
911401661304	BVP281 LED50/NW 40W 220-240V AMB	4000 K	70	5000 lm	911401663204	BVP282 LED202/NW 160W 220-240V SWB	4000 K	70	20200 lm
911401661404	BVP281 LED50/CW 40W 220-240V SMB	5700 K	70	5000 lm	911401663304	BVP282 LED202/NW 160W 220-240V AMB	4000 K	70	20200 lm
911401661604	BVP281 LED50/CW 40W 220-240V AMB	5700 K	70	5000 lm	911401663404	BVP282 LED202/CW 160W 220-240V SMB	5700 K	70	20200 lm
911401661704	BVP281 LED50/WW 40W 220-240V SMB	3000 K	70	5000 lm	911401663504	BVP282 LED202/CW 160W 220-240V AMB	5700 K	70	20200 lm
911401661804	BVP281 LED101/CW 80W 220-240V SMB	5700 K	70	10100 lm	911401663604	BVP282 LED202/NW 160W 220-240V SMB	4000 K	70	20200 lm
911401661904	BVP281 LED101/NW 80W 220-240V AMB	4000 K	70	10100 lm	911401663704	BVP282 LED202/CW 160W 220-240V SWB	5700 K	70	20200 lm
911401662004	BVP281 LED151/CW 120W 220-240V AMB	5700 K	70	15100 lm	911401663804	BVP282 LED252/WW 200W 220-240V SMB	3000 K	70	25200 lm
911401662104	BVP281 LED151/WW 120W 220-240V AMB	3000 K	70	15100 lm	911401663904	BVP282 LED252/CW 200W 220-240V SWB	5700 K	70	25200 lm
911401662204	BVP281 LED151/NW 120W 220-240V AMB	4000 K	70	15100 lm	911401664004	BVP282 LED252/WW 200W 220-240V SWB	3000 K	70	25200 lm
911401662304	BVP281 LED101/NW 80W 220-240V SWB	4000 K	70	10100 lm	911401664104	BVP282 LED252/NW 200W 220-240V AMB	4000 K	70	25200 lm
911401662404	BVP281 LED151/CW 120W 220-240V SMB	5700 K	70	15100 lm	911401664204	BVP282 LED252/WW 200W 220-240V AMB	3000 K	70	25200 lm

## Tango G2 LED

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
911401664304	BVP282 LED252/CW 200W 220-240V SMB	5700 K	70	25200 lm
911401664404	BVP282 LED252/CW 200W 220-240V AMB	5700 K	70	25200 lm
911401664504	BVP282 LED252/NW 200W 220-240V SWB	4000 K	70	25200 lm
911401664604	BVP282 LED252/NW 200W 220-240V SMB	4000 K	70	25200 lm
911401664704	BVP282 LED202/WW 160W 220-240V SMB	3000 K	70	20200 lm
911401692505	BVP283 LED262/CW 200W 220-240V AWB	5700 K	>70	26200 lm
911401692605	BVP283 LED262/CW 200W 220-240V AWBE	5700 K	>70	26200 lm
911401692705	BVP283 LED262/CW 200W 220-240V NB	5700 K	>70	26200 lm
911401692805	BVP283 LED262/CW 200W 220-240V SWB	5700 K	>70	26200 lm
911401692905	BVP283 LED262/NW 200W 220-240V AWB	4000 K	>70	26200 lm
911401693005	BVP283 LED262/NW 200W 220-240V AWBE	4000 K	>70	26200 lm
911401693105	BVP283 LED262/NW 200W 220-240V NB	4000 K	>70	26200 lm
911401693205	BVP283 LED262/NW 200W 220-240V SWB	4000 K	>70	26200 lm
911401693505	BVP283 LED281/WW 235W 220-240V AWB	3000 K	>70	28100 lm
911401693605	BVP283 LED281/WW 235W 220-240V AWBE	3000 K	>70	28100 lm
911401693705	BVP283 LED306/CW 235W 220-240V AWB	5700 K	>70	30600 lm
911401693805	BVP283 LED306/CW 235W 220-240V AWBE	5700 K	>70	30600 lm
911401693905	BVP283 LED306/NW 235W 220-240V AWB	4000 K	>70	30600 lm
911401694005	BVP283 LED306/NW 235W 220-240V AWBE	4000 K	>70	30600 lm
911401694105	BVP283 LED319/WW 270W 220-240V AWBE	3000 K	>70	31900 lm
911401694205	BVP283 LED319/WW 270W 220-240V NB	3000 K	>70	31900 lm
911401694305	BVP283 LED347/CW 270W 220-240V AWBE	5700 K	>70	34700 lm
911401694405	BVP283 LED347/CW 270W 220-240V NB	5700 K	>70	34700 lm
911401694505	BVP283 LED347/NW 270W 220-240V AWBE	4000 K	>70	34700 lm

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
911401694605	BVP283 LED347/NW 270W 220-240V NB	4000 K	>70	34700 lm
911401694905	BVP283 LED390/CW 305W 220-240V AWBE	5700 K	>70	39000 lm
911401695005	BVP283 LED390/CW 305W 220-240V NB	5700 K	>70	39000 lm
911401695105	BVP283 LED390/CW 305W 220-240V SWB	5700 K	>70	39000 lm
911401695205	BVP283 LED390/NW 305W 220-240V AWBE	4000 K	>70	39000 lm
911401695305	BVP283 LED390/NW 305W 220-240V NB	4000 K	>70	39000 lm
911401695405	BVP283 LED390/NW 305W 220-240V SWB	4000 K	>70	39000 lm
911401695505	BVP283 LED375/WW 320W 220-240V AWB	3000 K	>70	37500 lm
911401695605	BVP283 LED375/WW 320W 220-240V AWBE	3000 K	>70	37500 lm
911401695705	BVP283 LED375/WW 320W 220-240V NB	3000 K	>70	37500 lm
911401695805	BVP283 LED375/WW 320W 220-240V SWB	3000 K	>70	37500 lm
911401695905	BVP283 LED408/CW 320W 220-240V AWB	5700 K	>70	40800 lm
911401696005	BVP283 LED408/CW 320W 220-240V AWBE	5700 K	>70	40800 lm
911401696105	BVP283 LED408/CW 320W 220-240V NB	5700 K	>70	40800 lm
911401696205	BVP283 LED408/CW 320W 220-240V SWB	5700 K	>70	40800 lm
911401696305	BVP283 LED408/NW 320W 220-240V AWB	4000 K	>70	40800 lm
911401696405	BVP283 LED408/NW 320W 220-240V AWBE	4000 K	>70	40800 lm
911401696505	BVP283 LED408/NW 320W 220-240V NB	4000 K	>70	40800 lm
911401696605	BVP283 LED408/NW 320W 220-240V SWB	4000 K	>70	40800 lm
911401696905	BVP283 LED395/WW 335W 220-240V AWB	3000 K	>70	39500 lm
911401697005	BVP283 LED395/WW 335W 220-240V AWBE	3000 K	>70	39500 lm
911401697105	BVP283 LED395/WW 335W 220-240V NB	3000 K	>70	39500 lm
911401697205	BVP283 LED395/WW 335W 220-240V SWB	3000 K	>70	39500 lm
911401697305	BVP283 LED430/CW 335W 220-240V AWB	5700 K	>70	43000 lm
911401697405	BVP283 LED430/CW 335W 220-240V AWBE	5700 K	>70	43000 lm

## Tango G2 LED

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour	
			Rendering Index	Initial luminous flux
911401697505	BVP283 LED430/CW 335W 220-240V NB	5700 K	>70	43000 lm
911401697605	BVP283 LED430/CW 335W 220-240V SWB	5700 K	>70	43000 lm
911401697705	BVP283 LED430/NW 335W 220-240V AWB	4000 K	>70	43000 lm
911401697805	BVP283 LED430/NW 335W 220-240V AWBE	4000 K	>70	43000 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour	
			Rendering Index	Initial luminous flux
911401697905	BVP283 LED430/NW 335W 220-240V NB	4000 K	>70	43000 lm
911401698005	BVP283 LED430/NW 335W 220-240V SWB	4000 K	>70	43000 lm
911401698105	BVP283 LED430/NW 335W AWB P7 GM	4000 K	>70	43000 lm

### Light Technical

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
911401660504	BVP281 LED101/CW 80W 220-240V SWB	-	-
911401660704	BVP281 LED101/CW 80W 220-240V AMB	-	-
911401660804	BVP281 LED50/CW 40W 220-240V SWB	-	-
911401660904	BVP281 LED101/WW 80W 220-240V SMB	-	-
911401661004	BVP281 LED50/NW 40W 220-240V SWB	-	-
911401661104	BVP281 LED101/WW 80W 220-240V AMB	-	-
911401661204	BVP281 LED50/NW 40W 220-240V SMB	-	-
911401661304	BVP281 LED50/NW 40W 220-240V AMB	-	-
911401661404	BVP281 LED50/CW 40W 220-240V SMB	-	-
911401661604	BVP281 LED50/CW 40W 220-240V AMB	-	-
911401661704	BVP281 LED50/WW 40W 220-240V SMB	-	-
911401661804	BVP281 LED101/CW 80W 220-240V SMB	-	-
911401661904	BVP281 LED101/NW 80W 220-240V AMB	-	-
911401662004	BVP281 LED151/CW 120W 220-240V AMB	-	-
911401662104	BVP281 LED151/WW 120W 220-240V AMB	-	-
911401662204	BVP281 LED151/NW 120W 220-240V AMB	-	-
911401662304	BVP281 LED101/NW 80W 220-240V SWB	-	-
911401662404	BVP281 LED151/CW 120W 220-240V SMB	-	-

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
911401662504	BVP281 LED151/WW 120W 220-240V SMB	-	-
911401662604	BVP281 LED151/CW 120W 220-240V SWB	-	-
911401662704	BVP281 LED101/NW 80W 220-240V SMB	-	-
911401662804	BVP281 LED151/NW 120W 220-240V SWB	-	-
911401662904	BVP281 LED151/NW 120W 220-240V SMB	-	-
911401663004	BVP282 LED202/WW 160W 220-240V AMB	-	-
911401663104	BVP282 LED202/WW 160W 220-240V SWB	-	-
911401663204	BVP282 LED202/NW 160W 220-240V SWB	-	-
911401663304	BVP282 LED202/NW 160W 220-240V AMB	-	-
911401663404	BVP282 LED202/CW 160W 220-240V SMB	-	-
911401663504	BVP282 LED202/CW 160W 220-240V AMB	-	-
911401663604	BVP282 LED202/NW 160W 220-240V SMB	-	-
911401663704	BVP282 LED202/CW 160W 220-240V SWB	-	-
911401663804	BVP282 LED252/WW 200W 220-240V SMB	-	-
911401663904	BVP282 LED252/CW 200W 220-240V SWB	-	-
911401664004	BVP282 LED252/WW 200W 220-240V SWB	-	-
911401664104	BVP282 LED252/NW 200W 220-240V AMB	-	-
911401664204	BVP282 LED252/WW 200W 220-240V AMB	-	-

## Tango G2 LED

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop
911401664304	BVP282 LED252/CW 200W 220-240V SMB	-	-
911401664404	BVP282 LED252/CW 200W 220-240V AMB	-	-
911401664504	BVP282 LED252/NW 200W 220-240V SWB	-	-
911401664604	BVP282 LED252/NW 200W 220-240V SMB	-	-
911401664704	BVP282 LED202/WW 160W 220-240V SMB	-	-
911401692505	BVP283 LED262/CW 200W 220-240V AWB	-	-
911401692605	BVP283 LED262/CW 200W 220-240V AWBE	-	-
911401692705	BVP283 LED262/CW 200W 220-240V NB	-	-
911401692805	BVP283 LED262/CW 200W 220-240V SWB	-	-
911401692905	BVP283 LED262/NW 200W 220-240V AWB	-	-
911401693005	BVP283 LED262/NW 200W 220-240V AWBE	-	-
911401693105	BVP283 LED262/NW 200W 220-240V NB	-	-
911401693205	BVP283 LED262/NW 200W 220-240V SWB	-	-
911401693505	BVP283 LED281/WW 235W 220-240V AWB	-	-
911401693605	BVP283 LED281/WW 235W 220-240V AWBE	-	-
911401693705	BVP283 LED306/CW 235W 220-240V AWB	-	-
911401693805	BVP283 LED306/CW 235W 220-240V AWBE	-	-
911401693905	BVP283 LED306/NW 235W 220-240V AWB	-	-
911401694005	BVP283 LED306/NW 235W 220-240V AWBE	-	-
911401694105	BVP283 LED319/WW 270W 220-240V AWBE	-	-
911401694205	BVP283 LED319/WW 270W 220-240V NB	-	-
911401694305	BVP283 LED347/CW 270W 220-240V AWBE	-	-
911401694405	BVP283 LED347/CW 270W 220-240V NB	-	-
911401694505	BVP283 LED347/NW 270W 220-240V AWBE	-	-
911401694605	BVP283 LED347/NW 270W 220-240V NB	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop
911401694905	BVP283 LED390/CW 305W 220-240V AWBE	-	-
911401695005	BVP283 LED390/CW 305W 220-240V NB	-	-
911401695105	BVP283 LED390/CW 305W 220-240V SWB	-	-
911401695205	BVP283 LED390/NW 305W 220-240V AWBE	-	-
911401695305	BVP283 LED390/NW 305W 220-240V NB	-	-
911401695405	BVP283 LED390/NW 305W 220-240V SWB	-	-
911401695505	BVP283 LED375/WW 320W 220-240V AWB	-	-
911401695605	BVP283 LED375/WW 320W 220-240V AWBE	-	-
911401695705	BVP283 LED375/WW 320W 220-240V NB	-	-
911401695805	BVP283 LED375/WW 320W 220-240V SWB	-	-
911401695905	BVP283 LED408/CW 320W 220-240V AWB	-	-
911401696005	BVP283 LED408/CW 320W 220-240V AWBE	-	-
911401696105	BVP283 LED408/CW 320W 220-240V NB	-	-
911401696205	BVP283 LED408/CW 320W 220-240V SWB	-	-
911401696305	BVP283 LED408/NW 320W 220-240V AWB	-	-
911401696405	BVP283 LED408/NW 320W 220-240V AWBE	-	-
911401696505	BVP283 LED408/NW 320W 220-240V NB	-	-
911401696605	BVP283 LED408/NW 320W 220-240V SWB	-	-
911401696905	BVP283 LED395/WW 335W 220-240V AWB	-	-
911401697005	BVP283 LED395/WW 335W 220-240V AWBE	-	-
911401697105	BVP283 LED395/WW 335W 220-240V NB	-	-
911401697205	BVP283 LED395/WW 335W 220-240V SWB	-	-
911401697305	BVP283 LED430/CW 335W 220-240V AWB	-	-
911401697405	BVP283 LED430/CW 335W 220-240V AWBE	-	-
911401697505	BVP283 LED430/CW 335W 220-240V NB	-	-

## Tango G2 LED

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
911401697605	BVP283 LED430/CW 335W 220-240V SWB	-	-
911401697705	BVP283 LED430/NW 335W 220-240V AWB	-	-
911401697805	BVP283 LED430/NW 335W 220-240V AWBE	-	-

Order Code	Full Product Name	Standard tilt	
		angle side entry	Standard tilt angle posttop
911401697905	BVP283 LED430/NW 335W 220-240V NB	-	-
911401698005	BVP283 LED430/NW 335W 220-240V SWB	-	-
911401698105	BVP283 LED430/NW 335W AWB P7 GM	-	-

