



T12 Linear fluorescent lighting

T12 Standard

Low-pressure mercury discharge lamps with a tubular 37 mm envelope

Benefits

- Provides highly reliable and high-quality lighting solution at low cost
- Standard colors with moderate color rendering

Features

- Standard colors with moderate color rendering (Ra 50 - 75)
- Low-pressure mercury discharge lamps with a tubular 37 mm envelope

Application

- Mostly used in applications where continuous light output is required and color rendering is not an important factor.