



Small and powerful energy saver gives high quality light, with compact design

GENIE

Functional non-covered Energy saving lamp, with money saving high quality light and compact design. This lamp is small enough to fit neatly wherever you need extra bright light at home, enables easy replacement of most incandescent lamp all the way.

Fördelar

- Compact energy saving lamp enables fitting neatly wherever extra brightness is needed
- Save your money with long life-time and high energy efficiency compare to incandescent lamp
- Flicker-free start & Fast run up

Funktioner

- Long-Life and Energy saving alternative to Incandescent lamps
- Fast run-up
- Recommended ambient temperature range to ensure almost constant light output (>90%): between 0 and +50° C

Användning

- Designed for incandescent lamp replacement in consumer applications where the lamp is not directly visible, especially suitable for indoor applications in functional areas.
- Enclosed fixtures required for outdoor applications
- Not suitable for use with dimmers or electronic gear

Varning och Säkerhet

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Versions





Måttskiss



Product	D (max)	C (max)	F (max)
GENIE 11W WW E27 220-240V 1PF/6	35,0 mm	115 mm	44,5 mm
GENIE 14W WW E27 220-240V 1PF/6	35,0 mm	127 mm	44,5 mm

Måttskiss



Product

GENIE 18W WW E27 220-240V 1PF/6

Genie 23W WW E27 220-240V 1PF/6

Product

GENIE 18W WW E27 220-240V 1PF/6

Genie 23W WW E27 220-240V 1PF/6

Product


GENIE 8W WW E27 220-240V 1PF/6

D (max) C (max) F (max)

35,0 mm 108 mm 44,5 mm

Product

GENIE 8W WW E14 220-240V 1PF/6



Användning och godkännande

Energieffektivitetsetikett (EEL)	A
Kviksilvernehåll (Hg) (max)	2 mg
Kviksilvernehåll (Hg) (nom)	1,5 mg

Styrenheter och dimring

Dimbar	Nej
--------	-----

Drift och elektricitet

Ingångsfrekvens	50 eller 60 Hz
Spänning (nom)	220-240 V
Tändningstid (nom)	0,3 s
Uppvärmningstid till 60 % ljus (max)	40 s
Uppvärmningstid till 60 % ljus (min)	5 s

Allmän information

Nominell livslängd (nom)	10000 h
Nominell livslängd (timmar)	10000 h
Driftcykel	10000X

Ljusteknik

Kromaticitetskoordinat X (nom)	463
Kromaticitetskoordinat Y (nom)	420
Färgkod	827
Färgbeteckning	Varmvit (WW)
Korrelerad färgtemperatur (nom)	2700 K
Färgåtergivningsindex (nom)	80
LLMF vid slutet av nominell livslängd (nom)	65 %
Bibehållet ljusflöde 2 000 tim (nom)	88 %

Mekanik och armaturhus

Lampform	Stick
----------	-------

Användning och godkännande

Order Code	Full Product Name	Energiförbrukning kWh/1 000 tim
80118010	GENIE 8W WW E27 220-240V 1PF/6	8 kWh
80119710	GENIE 11W WW E27 220-240V 1PF/6	11 kWh
80120310	GENIE 14W WW E27 220-240V 1PF/6	14 kWh
80121010	GENIE 18W WW E27 220-240V 1PF/6	18 kWh
89713501	Genie 23W WW E27 220-240V 1PF/6	23 kWh
80115910	GENIE 8W WW E14 220-240V 1PF/6	8 kWh

Drift och elektricitet

Order Code	Full Product Name	Lampström (nom)	Effekt (märkvärde) (min)
80118010	GENIE 8W WW E27 220-240V 1PF/6	60 mA	8 W
80119710	GENIE 11W WW E27 220-240V 1PF/6	80 mA	11 W
80120310	GENIE 14W WW E27 220-240V 1PF/6	100 mA	14 W

Order Code	Full Product Name	Lampström (nom)	Effekt (märkvärde) (min)
80121010	GENIE 18W WW E27 220-240V 1PF/6	130 mA	18 W
89713501	Genie 23W WW E27 220-240V 1PF/6	165 mA	23 W
80115910	GENIE 8W WW E14 220-240V 1PF/6	60 mA	8 W

Allmän information

Order Code	Full Product Name	Socket
80118010	GENIE 8W WW E27 220-240V 1PF/6	E27
80119710	GENIE 11W WW E27 220-240V 1PF/6	E27
80120310	GENIE 14W WW E27 220-240V 1PF/6	E27

Order Code	Full Product Name	Socket
80121010	GENIE 18W WW E27 220-240V 1PF/6	E27
89713501	Genie 23W WW E27 220-240V 1PF/6	E27
80115910	GENIE 8W WW E14 220-240V 1PF/6	E14

Ljusteknik

Order Code	Full Product Name	Ljusutbyte (märkvärde) (nom)	Ljusflöde (nom)	Ljusflöde (märkvärde) (nom)
80118010	GENIE 8W WW E27 220-240V 1PF/6	53 lm/W	425 lm	425 lm
80119710	GENIE 11W WW E27 220-240V 1PF/6	55 lm/W	600 lm	600 lm
80120310	GENIE 14W WW E27 220-240V 1PF/6	58 lm/W	810 lm	810 lm

Order Code	Full Product Name	Ljusutbyte (märkvärde) (nom)	Ljusflöde (nom)	Ljusflöde (märkvärde) (nom)
80121010	GENIE 18W WW E27 220-240V 1PF/6	61 lm/W	1100 lm	1100 lm
89713501	Genie 23W WW E27 220-240V 1PF/6	62 lm/W	1450 lm	1450 lm
80115910	GENIE 8W WW E14 220-240V 1PF/6	53 lm/W	425 lm	425 lm

