



# CitySoul gen2 – a versatile identity

## CitySoul poles and brackets

CitySoul gen2 is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

### Benefits

- An integrated UrbanStyling lighting toolbox designed for many different urban applications
- Luminaires, brackets and poles are designed as one integrated concept to ensure coherence
- Future-proof thanks to excellent lighting performance and product quality

### Features

- A broad range of elegant, dedicated and complete sets, including poles and brackets, a tiltable option, double post-top and catenary versions
- Various features to deliver the most efficient and comfortable lighting level
- Compatible with all Philips' standard and advanced lighting controls
- Easy maintenance on-site
- Compatible with existing CitySoul pole and bracket range Flip, Morph, Jump, Sweep

# CitySoul poles and brackets

## Application

- City centers
- Parks and plazas
- Roads and streets
- Commercial districts

## Specifications

<b>Type</b>	JRP533 (Lyre bracket)	<b>Remarks</b>	Pre-cabled possible for:
	JRP534 (Accent spigot)		Wall mounted / suspended or catenary (C2K, 1,65 m cable)
	JRP532 (Double post top spigot)		Other configurations (C8K, 6 m cable, C10K, 10 m cable, C14K, 14 m cable)
	JGP530 (East bracket)		
	JRP531 (Graphic bracket)		
	JSP532 (Right Curve bracket)		
	YHB530 (Lyre dedicated pole)		
<b>Material</b>	JRP533 (Lyre bracket): aluminum		
	JRP534 (Accent spigot): aluminum		
	JRP532 (Double post top spigot): aluminum		
	JGP530 (East bracket): aluminum		
	JRP531 (Graphic bracket): steel		
	JSP532 (Right Curve bracket): steel		
<b>Color</b>	YHB530 (Lyre dedicated pole): steel		
	Philips ultra-dark grey (close to RAL7043)		
	Satin silver grey (close to RAL9006)		
	Other RAL and AKZO Futura colors available on request		
<b>Maintenance</b>	From below by opening the housing with 1 screws (Torx T20)		
<b>Installation</b>	BPP530: post-top mounting: Ø 60-76 mm		
	BRP530: side-entry mounting: Ø 42-60 mm		
	BPP532: dedicated lyre bracket: Ø 60-76 mm		
	BPP531: post-top mounting: Ø 60-76 mm		
	BRP531: side-entry mounting: Ø 42-60 mm		
	JRP532: Ø 60 mm		
	JRP533: Ø 60 mm		
	JRP534: Ø 60-76 mm		
	JGP530: Ø 76 mm		
	JRP531: Ø 76 mm		
	JSP532: Ø 76 mm		
	Recommended mounting height: 4 up to 14 m		
	Lyre recommended mounting height : 4-5 m		
	Adjustable tilt angle: possible with specific MBA or 76PA mounting spigot		
	Operating temperature: - 20 to +35 °C		
Max SCx: t.b.d. m2			

# CitySoul poles and brackets

## Versions



Lyre bracket



Double post-top spigot



Accent spigot


## Product details



2D rendering CitySoul gen2  
Bracket - Lyre



2D rendering CitySoul gen2  
Bracket - Top



2D rendering CitySoul gen2  
Bracket - Accent

### General Information

CE mark

CE mark

## General Information

Order Code	Full Product Name	Product Family Code
61257600	JRP533 MBP-S 60 DGR	JRP533
61260600	JRP533 MBP-S 60 DGR MSP	JRP533

Order Code	Full Product Name	Product Family Code
61266800	JRP532 MBP-T 60 DGR MSP	JRP532
61269900	JRP534 MBP DGR	JRP534

## CitySoul poles and brackets

