



The affordable LEDcandle solution

CorePro LED candles and lusters

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

Benefits

- Warm white light
- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Broad compatibility with transformers

Features

- Easy retrofit
- Lifetime of 15,000 hours
- UV- and IR-free light
- Free of mercury and hazardous materials

Application

- Hotels, restaurants, bars, cafés, museums, shops
- Lobbies, reception areas , exhibitions

CorePro LED candles and lusters

Versions



E14 B35 FR





E27 P45 FR



E14 P45 FR

Dimensional drawing



D

Product	D	C
CorePro LEDcandle ND 4-25W E14 827 B35 FR	35 mm	106 mm

Product	D	C
CorePro lustre ND 5.5-40W E14 827 P45 FR	45 mm	88 mm

Product	D	C
CorePro lustre ND 4-25W E27 827 P45 FR	45 mm	87 mm

CorePro LED candles and lusters

Approval and Application

Energy Efficiency Label (EEL) A+

Controls and Dimming

Dimmable No

Operating and Electrical

Input Frequency 50 to 60 Hz

Voltage (Nom) 220-240 V

Starting Time (Nom) 0.5 s

General Information

Nominal Lifetime (Nom) 15000 h

Switching Cycle 50000X

Light Technical

Color Code 827

Correlated Color Temperature (Nom) 2700 K

Color Rendering Index (Nom) 80

Llmf At End Of Nominal Lifetime (Nom) 70 %

Mechanical and Housing

Bulb Finish Frosted

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
304386	CorePro LEDcandle ND 4-25W E14 827 B35 FR	4 kWh
304394	CorePro lustre ND 4-25W E27 827 P45 FR	4 kWh
304410	CorePro lustre ND 5.5-40W E14 827 P45 FR	6 kWh

Operating and Electrical

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
304386	CorePro LEDcandle ND 4-25W E14 827 B35 FR	25 W	4 W
304394	CorePro lustre ND 4-25W E27 827 P45 FR	25 W	4 W

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
304410	CorePro lustre ND 5.5-40W E14 827 P45 FR	40 W	5.5 W

General Information

Order Code	Full Product Name	Cap-Base
304386	CorePro LEDcandle ND 4-25W E14 827 B35 FR	E14
304394	CorePro lustre ND 4-25W E27 827 P45 FR	E27

Order Code	Full Product Name	Cap-Base
304410	CorePro lustre ND 5.5-40W E14 827 P45 FR	E14

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
304386	CorePro LEDcandle ND 4-25W E14 827 B35 FR	250 lm
304394	CorePro lustre ND 4-25W E27 827 P45 FR	250 lm

Order Code	Full Product Name	Luminous Flux (Nom)
304410	CorePro lustre ND 5.5-40W E14 827 P45 FR	470 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
304386	CorePro LEDcandle ND 4-25W E14 827 B35 FR	B35
304394	CorePro lustre ND 4-25W E27 827 P45 FR	P45

Order Code	Full Product Name	Bulb Shape
304410	CorePro lustre ND 5.5-40W E14 827 P45 FR	P45

CorePro LED candles and lusters

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
304386	CorePro LEDcandle ND 4-25W E14 827 B35 FR	75 °C
304394	CorePro lustre ND 4-25W E27 827 P45 FR	75 °C
304410	CorePro lustre ND 5.5-40W E14 827 P45 FR	85 °C

