



The affordable LED candle and luster solution

CorePro LED candles and lusters

The CorePro LEDcandles and lusters are designed for retrofit replacement of incandescent lamps, and are particularly attractive for chandeliers. They are compatible with fixtures with an E14 holder for candles and E14 or E27 holders for lusters, and are available in either warm white, white or cool daylight color temperatures. LED lamps deliver huge energy savings and minimize maintenance cost. The CorePro LED candles and lusters are perfect for your basic lighting needs. They provide the beautiful light and dependable performance you expect from LED at an affordable price.

Benefits

Features

Application

CorePro LED candles and lusters

Versions



E14 B35 CL



E14 P45 CL



E27 P45 CL



E14 B35 FR



E14 P45 FR



E27 P45 FR



E27 B35 CL



E14 B38 FR



E14 P48 FR



E27 P48 FR



E14 B35 FR



E14 P45 FR




Dimensional drawing

D C

Product	D	C
Corepro Lustre ND 5.5-40W E27 827 P45 CL	45 mm	87 mm
Corepro Lustre ND 4-25W E27 827 P45 CL	45 mm	87 mm
CorePro lustre ND 4-25W E27 827 P45 FR	45 mm	87 mm
Corepro Lustre ND 5.5-40W E27 827 P45 FR	45 mm	87 mm
CorePro lustre ND 7-60W E27 840 P48 FR	48 mm	93 mm
CorePro lustre ND 7-60W E27 827 P48 FR	48 mm	93 mm

CorePro LED candles and lusters

Dimensional drawing



Product		
Corepro Candle ND 4-25W E14 827 B35 CL		
CorePro LEDcandle ND 5.5-40W E14 865 B35 FR	35 mm	106 mm
Corepro candle ND 5.5-40W E14 840 B35 CL	35 mm	106 mm
CorePro LEDcandle ND 5.5-40W E14 840 B35 FR	35 mm	106 mm
CorePro LEDcandle ND 3.5-25W E14 840 B35 FR	35 mm	106 mm
CorePro LEDcandle ND 4-25W E14 827 B35 FR	35 mm	106 mm
Corepro candle ND 5.5-40W E14 827 B35 CL		


Product	D	C
CorePro lustre ND 5.5-40W E14 840 P45 FR	45 mm	88 mm
CorePro lustre ND 5.5-40W E14 827 P45 FR	45 mm	88 mm
Corepro lustre ND 5.5-40W E14 840 P45 CL	45 mm	88 mm
Corepro lustre ND 5.5-40W E14 827 P45 CL	45 mm	88 mm
CorePro lustre ND 3.5-25W E14 840 P45 FR	45 mm	88 mm
CorePro lustre ND 4-25W E14 827 P45 FR	45 mm	88 mm
Corepro Lustre ND 4-25W E14 827 P45 CL	45 mm	88 mm

Product	D	C
Corepro candle ND 5.5-40W E27 827 B35 CL	35 mm	104 mm

Product	D	C
CorePro LEDcandle ND 7-60W E14 865 B38 FR	38 mm	114 mm
CorePro LEDcandle ND 7-60W E14 840 B38 FR	38 mm	114 mm
CorePro LEDcandle ND 7-60W E14 827 B38 FR	38 mm	114 mm

CorePro LED candles and lusters

Dimensional drawing



Product	D	C
CorePro lustre ND 7-60W E14 865 P48 FR	48 mm	95 mm
CorePro lustre ND 5.5-40W E14 865 P45 FR	45 mm	88 mm
CorePro lustre ND 7-60W E14 840 P48 FR	48 mm	95 mm
CorePro lustre ND 7-60W E14 827 P48 FR	48 mm	95 mm

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.5 s

General Information

Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X

Light Technical

Color Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001142202	Corepro Candle ND 4-25W E14 827 B35 CL	4 kWh	A+
929001142502	Corepro candle ND 5.5-40W E14 827 B35 CL	6 kWh	A+
929001206002	Corepro candle ND 5.5-40W E14 840 B35 CL	6 kWh	A+
929001142302	Corepro Lustre ND 4-25W E14 827 P45 CL	4 kWh	A+
929001142602	Corepro lustre ND 5.5-40W E14 827 P45 CL	6 kWh	A+
929001206102	Corepro lustre ND 5.5-40W E14 840 P45 CL	6 kWh	A+
929001142402	Corepro Lustre ND 4-25W E27 827 P45 CL	4 kWh	A+
929001175302	Corepro Lustre ND 5.5-40W E27 827 P45 CL	6 kWh	A+
929001157402	CorePro LEDcandle ND 4-25W E14 827 B35 FR	4 kWh	A+
929001205602	CorePro LEDcandle ND 3.5-25W E14 840 B35 FR	4 kWh	A+
929001205802	CorePro LEDcandle ND 5.5-40W E14 840 B35 FR	6 kWh	A+
929001157502	CorePro lustre ND 4-25W E14 827 P45 FR	4 kWh	A+
929001157802	CorePro lustre ND 5.5-40W E14 827 P45 FR	6 kWh	A+
929001205702	CorePro lustre ND 3.5-25W E14 840 P45 FR	4 kWh	A+
929001205902	CorePro lustre ND 5.5-40W E14 840 P45 FR	6 kWh	A+
929001157602	CorePro lustre ND 4-25W E27 827 P45 FR	4 kWh	A+
929001175402	CorePro Lustre ND 5.5-40W E27 827 P45 FR	6 kWh	A+
929001324702	Corepro candle ND 5.5-40W E27 827 B35 CL	6 kWh	A+
929001325102	CorePro LEDcandle ND 7-60W E14 827 B38 FR	7 kWh	A++
929001325402	CorePro LEDcandle ND 7-60W E14 840 B38 FR	7 kWh	A++
929001394702	CorePro LEDcandle ND 7-60W E14 865 B38 FR	7 kWh	A++
929001325202	CorePro lustre ND 7-60W E14 827 P48 FR	7 kWh	A++
929001325502	CorePro lustre ND 7-60W E14 840 P48 FR	7 kWh	A++
929001325302	CorePro lustre ND 7-60W E27 827 P48 FR	7 kWh	A++
929001325602	CorePro lustre ND 7-60W E27 840 P48 FR	7 kWh	A++
929001394502	CorePro LEDcandle ND 5.5-40W E14 865 B35 FR	6 kWh	A+
929001394602	CorePro lustre ND 5.5-40W E14 865 P45 FR	6 kWh	A+
929001394802	CorePro lustre ND 7-60W E14 865 P48 FR	7 kWh	A++

Operating and Electrical

CorePro LED candles and lusters

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001142202	Corepro Candle ND 4-25W E14 827 B35 CL	25 W	4 W
929001142502	Corepro candle ND 5.5-40W E14 827 B35 CL	40 W	5.5 W
929001206002	Corepro candle ND 5.5-40W E14 840 B35 CL	40 W	5.5 W
929001142302	Corepro Lustre ND 4-25W E14 827 P45 CL	25 W	4 W
929001142602	Corepro lustre ND 5.5-40W E14 827 P45 CL	40 W	5.5 W
929001206102	Corepro lustre ND 5.5-40W E14 840 P45 CL	40 W	5.5 W
929001142402	Corepro Lustre ND 4-25W E27 827 P45 CL	25 W	4 W
929001175302	Corepro Lustre ND 5.5-40W E27 827 P45 CL	40 W	5.5 W
929001157402	CorePro LEDcandle ND 4-25W E14 827 B35 FR	25 W	4 W
929001205602	CorePro LEDcandle ND 3.5-25W E14 840 B35 FR	25 W	3.5 W
929001205802	CorePro LEDcandle ND 5.5-40W E14 840 B35 FR	40 W	5.5 W
929001157502	CorePro lustre ND 4-25W E14 827 P45 FR	25 W	4 W
929001157802	CorePro lustre ND 5.5-40W E14 827 P45 FR	40 W	5.5 W
929001205702	CorePro lustre ND 3.5-25W E14 840 P45 FR	25 W	3.5 W

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001205902	CorePro lustre ND 5.5-40W E14 840 P45 FR	40 W	5.5 W
929001157602	CorePro lustre ND 4-25W E27 827 P45 FR	25 W	4 W
929001175402	Corepro Lustre ND 5.5-40W E27 827 P45 FR	40 W	5.5 W
929001324702	Corepro candle ND 5.5-40W E27 827 B35 CL	40 W	5.5 W
929001325102	CorePro LEDcandle ND 7-60W E14 827 B38 FR	60 W	7 W
929001325402	CorePro LEDcandle ND 7-60W E14 840 B38 FR	60 W	7 W
929001394702	CorePro LEDcandle ND 7-60W E14 865 B38 FR	60 W	7 W
929001325202	CorePro lustre ND 7-60W E14 827 P48 FR	60 W	7 W
929001325502	CorePro lustre ND 7-60W E14 840 P48 FR	60 W	7 W
929001325302	CorePro lustre ND 7-60W E27 827 P48 FR	60 W	7 W
929001325602	CorePro lustre ND 7-60W E27 840 P48 FR	60 W	7 W
929001394502	CorePro LEDcandle ND 5.5-40W E14 865 B35 FR	40 W	5.5 W
929001394602	CorePro lustre ND 5.5-40W E14 865 P45 FR	40 W	5.5 W
929001394802	CorePro lustre ND 7-60W E14 865 P48 FR	60 W	7 W

General Information

Order Code	Full Product Name	Cap-Base
929001142202	Corepro Candle ND 4-25W E14 827 B35 CL	E14
929001142502	Corepro candle ND 5.5-40W E14 827 B35 CL	E14
929001206002	Corepro candle ND 5.5-40W E14 840 B35 CL	E14
929001142302	Corepro Lustre ND 4-25W E14 827 P45 CL	E14
929001142602	Corepro lustre ND 5.5-40W E14 827 P45 CL	E14
929001206102	Corepro lustre ND 5.5-40W E14 840 P45 CL	E14
929001142402	Corepro Lustre ND 4-25W E27 827 P45 CL	E27
929001175302	Corepro Lustre ND 5.5-40W E27 827 P45 CL	E27
929001157402	CorePro LEDcandle ND 4-25W E14 827 B35 FR	E14
929001205602	CorePro LEDcandle ND 3.5-25W E14 840 B35 FR	E14
929001205802	CorePro LEDcandle ND 5.5-40W E14 840 B35 FR	E14
929001157502	CorePro lustre ND 4-25W E14 827 P45 FR	E14
929001157802	CorePro lustre ND 5.5-40W E14 827 P45 FR	E14
929001205702	CorePro lustre ND 3.5-25W E14 840 P45 FR	E14

Order Code	Full Product Name	Cap-Base
929001205902	CorePro lustre ND 5.5-40W E14 840 P45 FR	E14
929001157602	CorePro lustre ND 4-25W E27 827 P45 FR	E27
929001175402	Corepro Lustre ND 5.5-40W E27 827 P45 FR	E27
929001324702	Corepro candle ND 5.5-40W E27 827 B35 CL	E27
929001325102	CorePro LEDcandle ND 7-60W E14 827 B38 FR	E14
929001325402	CorePro LEDcandle ND 7-60W E14 840 B38 FR	E14
929001394702	CorePro LEDcandle ND 7-60W E14 865 B38 FR	E14
929001325202	CorePro lustre ND 7-60W E14 827 P48 FR	E14
929001325502	CorePro lustre ND 7-60W E14 840 P48 FR	E14
929001325302	CorePro lustre ND 7-60W E27 827 P48 FR	E27
929001325602	CorePro lustre ND 7-60W E27 840 P48 FR	E27
929001394502	CorePro LEDcandle ND 5.5-40W E14 865 B35 FR	E14
929001394602	CorePro lustre ND 5.5-40W E14 865 P45 FR	E14
929001394802	CorePro lustre ND 7-60W E14 865 P48 FR	E14

Light Technical

CorePro LED candles and lusters

Order Code	Full Product Name	Correlated Color		
		Color Code	Temperature (Nom)	Luminous Flux (Nom)
929001142202	Corepro Candle ND 4-25W E14 827 B35 CL	827	2700 K	250 lm
929001142502	Corepro candle ND 5.5-40W E14 827 B35 CL	827	2700 K	470 lm
929001206002	Corepro candle ND 5.5-40W E14 840 B35 CL	840	4000 K	520 lm
929001142302	Corepro Lustre ND 4-25W E14 827 P45 CL	827	2700 K	250 lm
929001142602	Corepro lustre ND 5.5-40W E14 827 P45 CL	827	2700 K	470 lm
929001206102	Corepro lustre ND 5.5-40W E14 840 P45 CL	840	4000 K	520 lm
929001142402	Corepro Lustre ND 4-25W E27 827 P45 CL	827	2700 K	250 lm
929001175302	Corepro Lustre ND 5.5-40W E27 827 P45 CL	827	2700 K	470 lm
929001157402	CorePro LEDcandle ND 4-25W E14 827 B35 FR	827	2700 K	250 lm
929001205602	CorePro LEDcandle ND 3.5-25W E14 840 B35 FR	840	4000 K	290 lm
929001205802	CorePro LEDcandle ND 5.5-40W E14 840 B35 FR	840	4000 K	520 lm
929001157502	CorePro lustre ND 4-25W E14 827 P45 FR	827	2700 K	250 lm
929001157802	CorePro lustre ND 5.5-40W E14 827 P45 FR	827	2700 K	470 lm
929001205702	CorePro lustre ND 3.5-25W E14 840 P45 FR	840	4000 K	290 lm

Order Code	Full Product Name	Correlated Color		
		Color Code	Temperature (Nom)	Luminous Flux (Nom)
929001205902	CorePro lustre ND 5.5-40W E14 840 P45 FR	840	4000 K	520 lm
929001157602	CorePro lustre ND 4-25W E27 827 P45 FR	827	2700 K	250 lm
929001175402	Corepro Lustre ND 5.5-40W E27 827 P45 FR	827	2700 K	470 lm
929001324702	Corepro candle ND 5.5-40W E27 827 B35 CL	827	2700 K	470 lm
929001325102	CorePro LEDcandle ND 7-60W E14 827 B38 FR	827	2700 K	806 lm
929001325402	CorePro LEDcandle ND 7-60W E14 840 B38 FR	840	4000 K	830 lm
929001394702	CorePro LEDcandle ND 7-60W E14 865 B38 FR	865	6500 K	830 lm
929001325202	CorePro lustre ND 7-60W E14 827 P48 FR	827	2700 K	806 lm
929001325502	CorePro lustre ND 7-60W E14 840 P48 FR	840	4000 K	830 lm
929001325302	CorePro lustre ND 7-60W E27 827 P48 FR	827	2700 K	806 lm
929001325602	CorePro lustre ND 7-60W E27 840 P48 FR	840	4000 K	830 lm
929001394502	CorePro LEDcandle ND 5.5-40W E14 865 B35 FR	865	6500 K	520 lm
929001394602	CorePro lustre ND 5.5-40W E14 865 P45 FR	865	6500 K	520 lm
929001394802	CorePro lustre ND 7-60W E14 865 P48 FR	865	6500 K	830 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb	
		Bulb Finish	Shape
929001142202	Corepro Candle ND 4-25W E14 827 B35 CL	Clear	B35
929001142502	Corepro candle ND 5.5-40W E14 827 B35 CL	Clear	B35
929001206002	Corepro candle ND 5.5-40W E14 840 B35 CL	Clear	B35
929001142302	Corepro Lustre ND 4-25W E14 827 P45 CL	Clear	P45
929001142602	Corepro lustre ND 5.5-40W E14 827 P45 CL	Clear	P45
929001206102	Corepro lustre ND 5.5-40W E14 840 P45 CL	Clear	P45
929001142402	Corepro Lustre ND 4-25W E27 827 P45 CL	Clear	P45
929001175302	Corepro Lustre ND 5.5-40W E27 827 P45 CL	Clear	P45
929001157402	CorePro LEDcandle ND 4-25W E14 827 B35 FR	Frosted	B35
929001205602	CorePro LEDcandle ND 3.5-25W E14 840 B35 FR	Frosted	B35
929001205802	CorePro LEDcandle ND 5.5-40W E14 840 B35 FR	Frosted	B35
929001157502	CorePro lustre ND 4-25W E14 827 P45 FR	Frosted	P45
929001157802	CorePro lustre ND 5.5-40W E14 827 P45 FR	Frosted	P45
929001205702	CorePro lustre ND 3.5-25W E14 840 P45 FR	Frosted	P45







Order Code	Full Product Name	Bulb	
		Bulb Finish	Shape
929001205902	CorePro lustre ND 5.5-40W E14 840 P45 FR	Frosted	P45
929001157602	CorePro lustre ND 4-25W E27 827 P45 FR	Frosted	P45
929001175402	Corepro Lustre ND 5.5-40W E27 827 P45 FR	Frosted	P45
929001324702	Corepro candle ND 5.5-40W E27 827 B35 CL	Clear	B35
929001325102	CorePro LEDcandle ND 7-60W E14 827 B38 FR	Frosted	B38
929001325402	CorePro LEDcandle ND 7-60W E14 840 B38 FR	Frosted	B38
929001394702	CorePro LEDcandle ND 7-60W E14 865 B38 FR	Frosted	B38
929001325202	CorePro lustre ND 7-60W E14 827 P48 FR	Frosted	P48
929001325502	CorePro lustre ND 7-60W E14 840 P48 FR	Frosted	P48
929001325302	CorePro lustre ND 7-60W E27 827 P48 FR	Frosted	P48
929001325602	CorePro lustre ND 7-60W E27 840 P48 FR	Frosted	P48
929001394502	CorePro LEDcandle ND 5.5-40W E14 865 B35 FR	Frosted	B35
929001394602	CorePro lustre ND 5.5-40W E14 865 P45 FR	Frosted	P45

CorePro LED candles and lusters











Order Code	Full Product Name	Bulb Finish	Bulb
			Shape
929001394802	CorePro lustre ND 7-60W E14 865 P48 FR	Frosted	P48

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001142202	Corepro Candle ND 4-25W E14 827 B35 CL	75 °C
929001142502	Corepro candle ND 5.5-40W E14 827 B35 CL	85 °C
929001206002	Corepro candle ND 5.5-40W E14 840 B35 CL	85 °C
929001142302	Corepro Lustre ND 4-25W E14 827 P45 CL	75 °C
929001142602	Corepro lustre ND 5.5-40W E14 827 P45 CL	85 °C
929001206102	Corepro lustre ND 5.5-40W E14 840 P45 CL	85 °C
929001142402	Corepro Lustre ND 4-25W E27 827 P45 CL	75 °C
929001175302	Corepro Lustre ND 5.5-40W E27 827 P45 CL	85 °C
929001157402	CorePro LEDcandle ND 4-25W E14 827 B35 FR	75 °C
929001205602	CorePro LEDcandle ND 3.5-25W E14 840 B35 FR	75 °C
929001205802	CorePro LEDcandle ND 5.5-40W E14 840 B35 FR	85 °C
929001157502	CorePro lustre ND 4-25W E14 827 P45 FR	75 °C
929001157802	CorePro lustre ND 5.5-40W E14 827 P45 FR	85 °C
929001205702	CorePro lustre ND 3.5-25W E14 840 P45 FR	75 °C
929001205902	CorePro lustre ND 5.5-40W E14 840 P45 FR	85 °C
929001157602	CorePro lustre ND 4-25W E27 827 P45 FR	75 °C
929001175402	Corepro Lustre ND 5.5-40W E27 827 P45 FR	85 °C
929001324702	Corepro candle ND 5.5-40W E27 827 B35 CL	85 °C
929001325102	CorePro LEDcandle ND 7-60W E14 827 B38 FR	90 °C
929001325402	CorePro LEDcandle ND 7-60W E14 840 B38 FR	90 °C
929001394702	CorePro LEDcandle ND 7-60W E14 865 B38 FR	90 °C
929001325202	CorePro lustre ND 7-60W E14 827 P48 FR	90 °C
929001325502	CorePro lustre ND 7-60W E14 840 P48 FR	90 °C
929001325302	CorePro lustre ND 7-60W E27 827 P48 FR	90 °C
929001325602	CorePro lustre ND 7-60W E27 840 P48 FR	90 °C
929001394502	CorePro LEDcandle ND 5.5-40W E14 865 B35 FR	85 °C
929001394602	CorePro lustre ND 5.5-40W E14 865 P45 FR	85 °C
929001394802	CorePro lustre ND 7-60W E14 865 P48 FR	90 °C



CorePro LED candles and lusters



CorePro LED candles and lusters

