



The affordable LEDspot solution

CorePro LEDspot MV

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Benefits

- Warm white light
- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Broad compatibility with transformers

Features

- Easy retrofit
- Lifetime of 15,000 hours
- Compatible with an extensive range of dimmers
- UV- and IR-free light
- Free of mercury and hazardous materials

Application

- Hotels, restaurants, bars, cafés, museums, shops
- Lobbies, corridors, stairwells, washrooms, reception areas , exhibitions, display cabinets

CorePro LEDspot MV

Versions



LEDspot ESS 4W E14 R50 827-865
12D ND RCA




LEDspot ESS 7W E27 R63 827-865
12D ND RCA







LEDspot ESS 10W E27 R80
827-865 12D ND RCA

Dimensional drawing



Product	D	C
CorePro LEDspot 3-35W GU10 827 36D DIM	50 mm	54 mm
CorePro LEDspot 3-35W GU10 830 36D DIM	50 mm	54 mm
CorePro LEDspot 3-35W GU10 840 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 827 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 830 36D DIM	50 mm	54 mm
CorePro LEDspot 4-50W GU10 840 36D DIM	50 mm	54 mm
CorePro LEDspot 4.6-50W GU10 827 36D 5CT	50 mm	54 mm
Corepro LEDspot 2.7-25W GU10 827 36D	50 mm	53 mm
Corepro LEDspot 2.7-25W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 2.7-25W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 827 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 3.5-35W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 827 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 830 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 840 36D	50 mm	54 mm
Corepro LEDspot 4.6-50W GU10 865 36D	50 mm	54 mm

Dimensional drawing



Product	D	C
ESS LEDspot 6W 640lm E14 R50 827	50 mm	86 mm
ESS LEDspot 6W 640lm E14 R50 840	50 mm	86 mm
ESS LEDspot 6W 640lm E14 R50 865	50 mm	86 mm


Product	D	C
ESS LEDspot 9W 980lm E27 R63 827	63 mm	102 mm
ESS LEDspot 9W 980lm E27 R63 840	63 mm	102 mm
ESS LEDspot 9W 980lm E27 R63 865	63 mm	102 mm

Product	D	C
ESS LEDspot 10W 1150lm E27 R80 827	80 mm	115 mm
ESS LEDspot 10W 1150lm E27 R80 840	80 mm	115 mm
ESS LEDspot 10W 1150lm E27 R80 865	80 mm	115 mm

Product	D	C
CorePro LEDspot 4.9-65W GU10 830 36D ND	50 mm	54 mm
CorePro LEDspot 4.9-65W GU10 840 36D ND	50 mm	54 mm
Corepro LEDspot 550lm GU10 830 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 840 120D	50 mm	54 mm
Corepro LEDspot 550lm GU10 865 120D	50 mm	54 mm

CorePro LEDspot MV

Dimensional drawing



Product	D	C
Corepro LEDspot 670lm GU10 830 60D	50 mm	54 mm
Corepro LEDspot 730lm GU10 840 60D	50 mm	54 mm

General Information	
Switching Cycle	50,000
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	GU10	-	15,000 hour(s)
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	GU10	-	15,000 hour(s)
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	GU10	-	15,000 hour(s)
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	GU10	-	15,000 hour(s)
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	GU10	-	15,000 hour(s)
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	GU10	-	15,000 hour(s)
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	GU10	-	15,000 hour(s)
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	GU10	-	15,000 hour(s)
30875600	Corepro LEDspot 550lm GU10 830 120D	GU10	-	15,000 hour(s)
30865700	Corepro LEDspot 550lm GU10 840 120D	GU10	-	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
30867100	Corepro LEDspot 550lm GU10 865 120D	GU10	-	15,000 hour(s)
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	GU10	-	15,000 hour(s)
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	GU10	-	15,000 hour(s)
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	GU10	-	15,000 hour(s)
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	GU10	-	15,000 hour(s)
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	GU10	-	15,000 hour(s)
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	GU10	-	15,000 hour(s)
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	GU10	-	15,000 hour(s)
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	GU10	-	15,000 hour(s)
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	GU10	-	15,000 hour(s)

CorePro LEDspot MV

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	GU10	-	15,000 hour(s)
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	GU10	-	15,000 hour(s)
31192300	ESS LEDspot 6W 640lm E14 R50 827	E14	15,000 hour(s)	15,000 hour(s)
31194700	ESS LEDspot 6W 640lm E14 R50 840	E14	15,000 hour(s)	15,000 hour(s)
31196100	ESS LEDspot 6W 640lm E14 R50 865	E14	15,000 hour(s)	15,000 hour(s)
31198500	ESS LEDspot 9W 980lm E27 R63 827	E27	15,000 hour(s)	15,000 hour(s)
31200500	ESS LEDspot 9W 980lm E27 R63 840	E27	15,000 hour(s)	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Nominal lifetime
31202900	ESS LEDspot 9W 980lm E27 R63 865	E27	15,000 hour(s)	15,000 hour(s)
31204300	ESS LEDspot 10W 1150lm E27 R80 827	E27	15,000 hour(s)	15,000 hour(s)
31206700	ESS LEDspot 10W 1150lm E27 R80 840	E27	15,000 hour(s)	15,000 hour(s)
31208100	ESS LEDspot 10W 1150lm E27 R80 865	E27	15,000 hour(s)	15,000 hour(s)
81333101	Corepro LEDspot 670lm GU10 830 60D	GU10	-	25,000 hour(s)
81335501	Corepro LEDspot 730lm GU10 840 60D	GU10	-	25,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color Code	Luminous Flux	Luminous Intensity (Nom)
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	36 degree(s)	4000 K	840	240 lm	500 cd
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	36 degree(s)	3000 K	830	230 lm	500 cd
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	36 degree(s)	2700 K	827	230 lm	500 cd
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	36 degree(s)	2700 K	827	345 lm	700 cd
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	36 degree(s)	2700 K	827	355 lm	700 cd
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	36 degree(s)	2700 K	827	355 lm	700 cd
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	36 degree(s)	2700 K	827	215 lm	470 cd
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	36 degree(s)	2700 K	827	255 lm	545 cd
30875600	Corepro LEDspot 550lm GU10 830 120D	120 degree(s)	3000 K	830	550 lm	-
30865700	Corepro LEDspot 550lm GU10 840 120D	120 degree(s)	4000 K	840	550 lm	-
30867100	Corepro LEDspot 550lm GU10 865 120D	120 degree(s)	6500 K	865	550 lm	-
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	36 degree(s)	4000 K	840	350 lm	700 cd
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	36 degree(s)	3000 K	830	345 lm	700 cd
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	36 degree(s)	3000 K	830	460 lm	800 cd
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	36 degree(s)	4000 K	840	485 lm	800 cd
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	36 degree(s)	3000 K	830	225 lm	490 cd
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	36 degree(s)	4000 K	840	230 lm	500 cd
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	36 degree(s)	3000 K	830	265 lm	565 cd
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	36 degree(s)	4000 K	840	275 lm	590 cd
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	36 degree(s)	3000 K	830	370 lm	740 cd
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	36 degree(s)	4000 K	840	390 lm	770 cd
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	36 degree(s)	6500 K	865	390 lm	770 cd
31192300	ESS LEDspot 6W 640lm E14 R50 827	120 degree(s)	2700 K	827	640 lm	-
31194700	ESS LEDspot 6W 640lm E14 R50 840	120 degree(s)	4000 K	840	640 lm	-
31196100	ESS LEDspot 6W 640lm E14 R50 865	120 degree(s)	6500 K	865	640 lm	-
31198500	ESS LEDspot 9W 980lm E27 R63 827	120 degree(s)	2700 K	827	980 lm	-
31200500	ESS LEDspot 9W 980lm E27 R63 840	120 degree(s)	4000 K	840	980 lm	-
31202900	ESS LEDspot 9W 980lm E27 R63 865	120 degree(s)	6500 K	865	980 lm	-
31204300	ESS LEDspot 10W 1150lm E27 R80 827	120 degree(s)	2700 K	827	1,150 lm	-
31206700	ESS LEDspot 10W 1150lm E27 R80 840	120 degree(s)	4000 K	840	1,150 lm	-
31208100	ESS LEDspot 10W 1150lm E27 R80 865	120 degree(s)	6500 K	865	1,150 lm	-
81333101	Corepro LEDspot 670lm GU10 830 60D	60 degree(s)	3000 K	830	670 lm	750 cd

CorePro LEDspot MV

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color Code	Luminous Flux	Luminous Intensity (Nom)
81335501	Corepro LEDspot 730lm GU10 840 60D	60 degree(s)	4000 K	840	730 lm	750 cd

Operating and Electrical

		Wattage				Wattage	
Order Code	Full Product Name	Power Consumption	Equivalent	Order Code	Full Product Name	Power Consumption	Equivalent
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	3 W	35 W	72833800	Corepro LEDspot 3.5-35W GU10 830 36D	3.5 W	35 W
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	3 W	35 W	72835200	Corepro LEDspot 3.5-35W GU10 840 36D	3.5 W	35 W
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	3 W	35 W	72837600	Corepro LEDspot 4.6-50W GU10 830 36D	4.6 W	50 W
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	4 W	50 W	72839000	Corepro LEDspot 4.6-50W GU10 840 36D	4.6 W	50 W
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	4.6 W	50 W	72841300	Corepro LEDspot 4.6-50W GU10 865 36D	4.6 W	50 W
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	4.6 W	50 W	31192300	ESS LEDspot 6W 640lm E14 R50 827	6 W	50 W
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	2.7 W	25 W	31194700	ESS LEDspot 6W 640lm E14 R50 840	6 W	50 W
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	3.5 W	35 W	31196100	ESS LEDspot 6W 640lm E14 R50 865	6 W	50 W
30875600	Corepro LEDspot 550lm GU10 830 120D	4.9 W	-	31198500	ESS LEDspot 9W 980lm E27 R63 827	9 W	70 W
30865700	Corepro LEDspot 550lm GU10 840 120D	4.9 W	-	31200500	ESS LEDspot 9W 980lm E27 R63 840	9 W	70 W
30867100	Corepro LEDspot 550lm GU10 865 120D	4.9 W	-	31202900	ESS LEDspot 9W 980lm E27 R63 865	9 W	70 W
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	4 W	50 W	31204300	ESS LEDspot 10W 1150lm E27 R80 827	10 W	80 W
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	4 W	50 W	31206700	ESS LEDspot 10W 1150lm E27 R80 840	10 W	80 W
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	4.9 W	65 W	31208100	ESS LEDspot 10W 1150lm E27 R80 865	10 W	80 W
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	4.9 W	65 W	81333101	Corepro LEDspot 670lm GU10 830 60D	6.7 W	90 W
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	2.7 W	25 W	81335501	Corepro LEDspot 730lm GU10 840 60D	6.7 W	100 W
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	2.7 W	25 W				

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)	Order Code	Full Product Name	T-Case Maximum (Nom)
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	65 °C	75253100	Corepro LEDspot 3.5-35W GU10 827 36D	65 °C
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	65 °C	30875600	Corepro LEDspot 550lm GU10 830 120D	85 °C
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	65 °C	30865700	Corepro LEDspot 550lm GU10 840 120D	85 °C
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	70 °C	30867100	Corepro LEDspot 550lm GU10 865 120D	85 °C
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	72 °C	35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	70 °C
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	72 °C	35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	70 °C
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	50 °C	30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	85 °C

CorePro LEDspot MV

Order Code	Full Product Name	T-Case Maximum (Nom)
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	85 °C
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	50 °C
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	50 °C
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	65 °C
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	65 °C
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	72 °C
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	72 °C
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	72 °C
31192300	ESS LEDspot 6W 640lm E14 R50 827	70 °C
31194700	ESS LEDspot 6W 640lm E14 R50 840	70 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	Only with specific dimmers
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	Only with specific dimmers
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	Only with specific dimmers
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	Only with specific dimmers
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	No
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	No
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	No
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	No
30875600	Corepro LEDspot 550lm GU10 830 120D	No
30865700	Corepro LEDspot 550lm GU10 840 120D	No
30867100	Corepro LEDspot 550lm GU10 865 120D	No
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	Only with specific dimmers
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	Only with specific dimmers
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	No
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	No
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	No
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	-	PAR16
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	-	PAR16
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	-	PAR16
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	-	PAR16
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	-	PAR16
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	-	PAR16
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	-	PAR16
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	-	PAR16
30875600	Corepro LEDspot 550lm GU10 830 120D	-	PAR16
30865700	Corepro LEDspot 550lm GU10 840 120D	-	PAR16
30867100	Corepro LEDspot 550lm GU10 865 120D	-	PAR16
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	-	PAR16
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	-	PAR16
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	-	PAR16
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	-	PAR16
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	-	PAR16
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	-	PAR16



Order Code	Full Product Name	T-Case Maximum (Nom)
31196100	ESS LEDspot 6W 640lm E14 R50 865	70 °C
31198500	ESS LEDspot 9W 980lm E27 R63 827	80 °C
31200500	ESS LEDspot 9W 980lm E27 R63 840	80 °C
31202900	ESS LEDspot 9W 980lm E27 R63 865	80 °C
31204300	ESS LEDspot 10W 1150lm E27 R80 827	85 °C
31206700	ESS LEDspot 10W 1150lm E27 R80 840	85 °C
31208100	ESS LEDspot 10W 1150lm E27 R80 865	85 °C
81333101	Corepro LEDspot 670lm GU10 830 60D	75 °C
81335501	Corepro LEDspot 730lm GU10 840 60D	75 °C

Order Code	Full Product Name	Dimmable
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	No
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	No
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	No
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	No
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	No
31192300	ESS LEDspot 6W 640lm E14 R50 827	No
31194700	ESS LEDspot 6W 640lm E14 R50 840	No
31196100	ESS LEDspot 6W 640lm E14 R50 865	No
31198500	ESS LEDspot 9W 980lm E27 R63 827	No
31200500	ESS LEDspot 9W 980lm E27 R63 840	No
31202900	ESS LEDspot 9W 980lm E27 R63 865	No
31204300	ESS LEDspot 10W 1150lm E27 R80 827	No
31206700	ESS LEDspot 10W 1150lm E27 R80 840	No
31208100	ESS LEDspot 10W 1150lm E27 R80 865	No
81333101	Corepro LEDspot 670lm GU10 830 60D	No
81335501	Corepro LEDspot 730lm GU10 840 60D	No

Order Code	Full Product Name	Bulb Finish	Bulb Shape
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	-	PAR16
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	-	PAR16
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	-	PAR16
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	-	PAR16
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	-	PAR16
31192300	ESS LEDspot 6W 640lm E14 R50 827	Frosted	R50
31194700	ESS LEDspot 6W 640lm E14 R50 840	Frosted	R50
31196100	ESS LEDspot 6W 640lm E14 R50 865	Frosted	R50
31198500	ESS LEDspot 9W 980lm E27 R63 827	Frosted	R63
31200500	ESS LEDspot 9W 980lm E27 R63 840	Frosted	R63
31202900	ESS LEDspot 9W 980lm E27 R63 865	Frosted	R63
31204300	ESS LEDspot 10W 1150lm E27 R80 827	Frosted	R80
31206700	ESS LEDspot 10W 1150lm E27 R80 840	Frosted	R80
31208100	ESS LEDspot 10W 1150lm E27 R80 865	Frosted	R80
81333101	Corepro LEDspot 670lm GU10 830 60D	-	PAR16
81335501	Corepro LEDspot 730lm GU10 840 60D	-	PAR16


Approval and Application











Order Code	Full Product Name	Energy Consumption kWh/	
		1000 h	
73022500	CorePro LEDspot 3-35W GU10 840 36D DIM	3 kWh	
72135300	CorePro LEDspot 3-35W GU10 830 36D DIM	3 kWh	
72133900	CorePro LEDspot 3-35W GU10 827 36D DIM	3 kWh	
72137700	CorePro LEDspot 4-50W GU10 827 36D DIM	4 kWh	
75251700	Corepro LEDspot 4.6-50W GU10 827 36D	5 kWh	
70029400	CorePro LEDspot 4.6-50W GU10 827 36D 5CT	5 kWh	
75209800	Corepro LEDspot 2.7-25W GU10 827 36D	3 kWh	
75253100	Corepro LEDspot 3.5-35W GU10 827 36D	4 kWh	
30875600	Corepro LEDspot 550lm GU10 830 120D	5 kWh	
30865700	Corepro LEDspot 550lm GU10 840 120D	5 kWh	
30867100	Corepro LEDspot 550lm GU10 865 120D	5 kWh	
35885000	CorePro LEDspot 4-50W GU10 840 36D DIM	4 kWh	
35883600	CorePro LEDspot 4-50W GU10 830 36D DIM	4 kWh	
30871800	CorePro LEDspot 4.9-65W GU10 830 36D ND	5 kWh	
30861900	CorePro LEDspot 4.9-65W GU10 840 36D ND	5 kWh	
72829100	Corepro LEDspot 2.7-25W GU10 830 36D	3 kWh	
72831400	Corepro LEDspot 2.7-25W GU10 840 36D	3 kWh	
72833800	Corepro LEDspot 3.5-35W GU10 830 36D	4 kWh	
72835200	Corepro LEDspot 3.5-35W GU10 840 36D	4 kWh	
72837600	Corepro LEDspot 4.6-50W GU10 830 36D	5 kWh	
72839000	Corepro LEDspot 4.6-50W GU10 840 36D	5 kWh	
72841300	Corepro LEDspot 4.6-50W GU10 865 36D	5 kWh	
31192300	ESS LEDspot 6W 640lm E14 R50 827	6 kWh	
31194700	ESS LEDspot 6W 640lm E14 R50 840	6 kWh	
31196100	ESS LEDspot 6W 640lm E14 R50 865	6 kWh	
31198500	ESS LEDspot 9W 980lm E27 R63 827	9 kWh	
31200500	ESS LEDspot 9W 980lm E27 R63 840	9 kWh	
31202900	ESS LEDspot 9W 980lm E27 R63 865	9 kWh	
31204300	ESS LEDspot 10W 1150lm E27 R80 827	10 kWh	
31206700	ESS LEDspot 10W 1150lm E27 R80 840	10 kWh	
31208100	ESS LEDspot 10W 1150lm E27 R80 865	10 kWh	
81333101	Corepro LEDspot 670lm GU10 830 60D	7 kWh	
81335501	Corepro LEDspot 730lm GU10 840 60D	7 kWh	










90°


60°









Accent Diagrams




Accent Diagram - CorePro LEDspot 4.9-65W
GU10 830 36D ND




Accent Diagram - Corepro LEDspot 2.7-25W
GU10 827 36D




Accent Diagram - Corepro LEDspot 3.5-35W
GU10 827 36D




Accent Diagram - CorePro LEDspot 4.6-50W
GU10 827 36D 5CT




Accent Diagram - Corepro LEDspot 2.7-25W
GU10 830 36D




Accent Diagram - Corepro LEDspot 3.5-35W
GU10 830 36D



Accent Diagram - Corepro LEDspot 4.6-50W
GU10 865 36D




Accent Diagram - CorePro LEDspot 4-50W
GU10 827 36D DIM




Accent Diagram - CorePro LEDspot 4-50W
GU10 840 36D DIM


Accent Diagrams




Accent Diagram - CorePro LEDspot 4-50W
GU10 830 36D DIM




Accent Diagram - CorePro LEDspot 3-35W GU10
830 36D DIM




Accent Diagram - CorePro LEDspot 3-35W GU10
840 36D DIM




Accent Diagram - Corepro LEDspot 730lm GU10
840 60D



Accent Diagram - Corepro LEDspot 670lm GU10
830 60D




Accent Diagram - CorePro LEDspot 3-35W GU10
827 36D DIM




Accent Diagram - CorePro LEDspot 4.9-65W
GU10 840 36D ND


Beam Diagrams




Beam diagram - CorePro LEDspot 3-35W GU10 840 36D DIM




Beam diagram - CorePro LEDspot 4.9-65W GU10 840 36D ND




Beam diagram - CorePro LEDspot 2.7-25W GU10 827 36D




Beam diagram - CorePro LEDspot 3.5-35W GU10 827 36D




Beam diagram - CorePro LEDspot 4.6-50W GU10 827 36D 5CT




Beam diagram - CorePro LEDspot 2.7-25W GU10 830 36D



Beam diagram - CorePro LEDspot 3.5-35W GU10 830 36D




Beam diagram - CorePro LEDspot 4.6-50W GU10 865 36D




Beam diagram - CorePro LEDspot 4-50W GU10 830 36D DIM


Beam Diagrams




Beam diagram - CorePro LEDspot 4-50W GU10 840 36D DIM




Beam diagram - Corepro LEDspot 730lm GU10 840 60D




Beam diagram - CorePro LEDspot 3-35W GU10 830 36D DIM




Beam diagram - CorePro LEDspot 4-50W GU10 827 36D DIM



Beam diagram - CorePro LEDspot 3-35W GU10 827 36D DIM



Beam diagram - CorePro LEDspot 4.9-65W GU10 830 36D ND



Beam diagram - Corepro LEDspot 670lm GU10 830 60D

