

PHILIPS

Lighting



Philips LuxSpace, recessed – high efficiency, visual comfort and a stylish design

LuxSpace, recessed

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also user costs where they see much bigger impact on return. Therefore, LuxSpace is designed to provide the perfect combination of efficiency, visual comfort and design, without compromising on lighting performance (color rendering and light distribution). It offers a wide choice of options for creating the desired ambience to support user comfort, no matter the application is. For office applications LuxSpace supports health and wellbeing having dedicated Tunable White products and lighting controls.

Benefits

- Best-in-class efficacy with up to 160lm/W
- Creates a gentle, natural light, ensuring visual comfort
- Perfect ceiling integration with narrow rim or rimless version for plaster ceilings
- Improved glare control with office compliancy
- High color quality with CRI90 option (R9>50)
- Provides uniform lighting thanks to wide light distribution
- Supports Human Centric Lighting with Tunable White and integrated lighting controls

LuxSpace, recessed

Features

- Mini (DN560B/DN561B) and compact (DN570B/DN571B) sizes for recessed
- Square recessed (DN572B) and surface-mounted round (DN570C) versions in compact
- Choice of four optics: high-gloss, faceted, matt and white
- UGR19 and UGR22 versions with different product heights
- Selection of colors: High-gloss metalized, white (RAL9003), grey (RAL9006), black (RAL9004) as standard (any other RAL color possible upon request)
- Compliant for central emergency lighting with DC (upon request)
- Multiple additional options: PG and PGO (IP54 front face), emergency lighting (single battery 3 hours), suspended deco glasses, through-wiring, Eca and B2ca cable & connector options
- Extended useful lifetime 50,000 hours at L90

Application


- Retail
- Offices
- Hospitals and Care Centers
- Hospitality
- Airports
- Museums
- Atriums

Versions




LuxSpace recessed with faceted reflector

Dimensional drawing



Dimensional drawing



General Information	
CE mark	Yes
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Number of gear units	1 unit
Light Technical	
Optical cover type	-
Optic type	-
Operating and Electrical	
Input Voltage	220 to 240 V
Mechanical and Housing	
Housing Color	White
Approval and Application	
Protection class IEC	Safety class II
Mech. impact protection code	IK02
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Suitable for random switching	Yes

General Information (1/2)

Order Code	Full Product Name	ENEC mark	Glow-wire test	Lamp family code	Light source replaceable
910505100834	DN570B LED12S/830 PSU-E C EW WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100835	DN570B LED12S/840 PSU-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100842	DN570B LED20S/830 PSU-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100843	DN570B LED20S/840 PSU-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100850	DN570B LED20S/830 PSU-E C PG WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100851	DN570B LED20S/840 PSU-E C PG WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100868	DN570B LED24S/830 PSU-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	-	No

Order Code	Full Product Name	ENEC		Lamp	
		mark	Glow-wire test	family code	Light source replaceable
910505100869	DN570B LED24S/840 PSU-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100884	DN570B LED40S/830 PSU-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	-	No
910505100885	DN570B LED40S/840 PSU-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	-	No
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100901	DN570B LED40S/TWH PSD-E C WH	- mark	Temperature 850 °C, duration 5 s	-	No
910505100903	DN570B LED60S/830 PSU-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100904	DN570B LED60S/840 PSU-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505102295	DN570B LED24S/830 WIA-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	-	No
910505102296	DN570B LED24S/840 WIA-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	-	No
910505102299	DN570B LED40S/830 WIA-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	-	No
910505102301	DN570B LED40S/840 WIA-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	-	No
910505102304	DN570B LED24S/930H PSU-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	-	No
910505102305	DN570B LED24S/940H PSU-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	-	No
910505102652	DN570B LED20S/840UE PSU-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	20S	Yes
910505102654	DN570B LED20S/840UE PSU-E WR WH	ENEC mark	Temperature 650 °C, duration 30 s	20S	Yes
910505102656	DN570B LED24S/840UE PSU-E C WH	ENEC mark	Temperature 650 °C, duration 30 s	24S	Yes
910505100852	DN570B LED20S/830 PSU-E F WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100853	DN570B LED20S/840 PSU-E F WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100854	DN570B LED20S/830 PSU-E M WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No
910505100855	DN570B LED20S/840 PSU-E M WH	ENEC mark	Temperature 850 °C, duration 5 s	-	No

Order Code	Full Product Name	ENEC mark	Glow-wire test		Lamp family code	Light source replaceable
			Temperature	duration	850 °C,	-
910505100856	DN570B LED20S/830 PSU-E WR WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100857	DN570B LED20S/840 PSU-E WR WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100836	DN571B LED12S/830 PSU-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100837	DN571B LED12S/840 PSU-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100846	DN571B LED20S/830 PSU-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100847	DN571B LED20S/840 PSU-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100870	DN571B LED24S/830 PSU-E C WH	ENEC mark	Temperature	duration	650 °C, 30 s	- No
910505100871	DN571B LED24S/840 PSU-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100886	DN571B LED40S/830 PSU-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100887	DN571B LED40S/840 PSU-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	ENEC mark	Temperature	duration	850 °C, 5 s	- No
910505100902	DN571B LED40S/TWH PSD-E C WH	- mark	Temperature	duration	850 °C, 5 s	- No
910505102297	DN571B LED24S/830 WIA-E C WH	ENEC mark	Temperature	duration	650 °C, 30 s	- No
910505102298	DN571B LED24S/840 WIA-E C WH	ENEC mark	Temperature	duration	650 °C, 30 s	- No

Order Code	Full Product Name	ENECLamp		family code	Light source replaceable
		mark	Glow-wire test		
910505102302	DN571B LED40S/830 WIA-E C WH	ENECLamp	Temperature 650 °C, duration 30 s	-	No
910505102303	DN571B LED40S/840 WIA-E C WH	ENECLamp	Temperature 650 °C, duration 30 s	-	No
910505102306	DN571B LED24S/930H PSU-E C WH	ENECLamp	Temperature 650 °C, duration 30 s	-	No
910505102307	DN571B LED24S/940H PSU-E C WH	ENECLamp	Temperature 650 °C, duration 30 s	-	No
910505102653	DN571B LED20S/840UE PSU-E C WH	ENECLamp	Temperature 650 °C, duration 30 s	20S	Yes
910505102655	DN571B LED20S/840UE PSU-E WR WH	ENECLamp	Temperature 650 °C, duration 30 s	20S	Yes
910505102657	DN571B LED24S/840UE PSU-E C WH	ENECLamp	Temperature 650 °C, duration 30 s	24S	Yes

General Information (2/2)

Order Code	Full Product Name	Product		Order Code	Full Product Name	Product	
		family code	Service tag			family code	Service tag
910505100834	DN570B LED12S/830 PSU-E C EW WH	DN570B	Yes	910505102295	DN570B LED24S/830 WIA-E C WH	DN570B	-
910505100835	DN570B LED12S/840 PSU-E C WH	DN570B	Yes	910505102296	DN570B LED24S/840 WIA-E C WH	DN570B	-
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	DN570B	Yes	910505102299	DN570B LED40S/830 WIA-E C WH	DN570B	-
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	DN570B	Yes	910505102301	DN570B LED40S/840 WIA-E C WH	DN570B	-
910505100842	DN570B LED20S/830 PSU-E C WH	DN570B	Yes	910505102304	DN570B LED24S/930H PSU-E C WH	DN570B	-
910505100843	DN570B LED20S/840 PSU-E C WH	DN570B	Yes	910505102305	DN570B LED24S/940H PSU-E C WH	DN570B	-
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	DN570B	Yes	910505102652	DN570B LED20S/840UE PSU-E C WH	DN570B	-
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	DN570B	Yes	910505102654	DN570B LED20S/840UE PSU-E WR WH	DN570B	-
910505100850	DN570B LED20S/830 PSU-E C PG WH	DN570B	Yes	910505102656	DN570B LED24S/840UE PSU-E C WH	DN570B	-
910505100851	DN570B LED20S/840 PSU-E C PG WH	DN570B	Yes	910505100852	DN570B LED20S/830 PSU-E F WH	DN570B	Yes
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	DN570B	Yes	910505100853	DN570B LED20S/840 PSU-E F WH	DN570B	Yes
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	DN570B	Yes	910505100854	DN570B LED20S/830 PSU-E M WH	DN570B	Yes
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	DN570B	Yes	910505100855	DN570B LED20S/840 PSU-E M WH	DN570B	Yes
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	DN570B	Yes	910505100856	DN570B LED20S/830 PSU-E WR WH	DN570B	Yes
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	DN570B	Yes	910505100857	DN570B LED20S/840 PSU-E WR WH	DN570B	Yes
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	DN570B	Yes	910505100836	DN571B LED12S/830 PSU-E C WH	DN571B	Yes
910505100868	DN570B LED24S/830 PSU-E C WH	DN570B	Yes	910505100837	DN571B LED12S/840 PSU-E C WH	DN571B	Yes
910505100869	DN570B LED24S/840 PSU-E C WH	DN570B	Yes	910505100840	DN571B LED12S/830 DIA-VLC-E C WH	DN571B	Yes
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	DN570B	Yes	910505100841	DN571B LED12S/840 DIA-VLC-E C WH	DN571B	Yes
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	DN570B	Yes	910505100846	DN571B LED20S/830 PSU-E C WH	DN571B	Yes
910505100884	DN570B LED40S/830 PSU-E C WH	DN570B	Yes	910505100847	DN571B LED20S/840 PSU-E C WH	DN571B	Yes
910505100885	DN570B LED40S/840 PSU-E C WH	DN570B	Yes	910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	DN571B	Yes
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	DN570B	Yes	910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	DN571B	Yes
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	DN570B	Yes	910505100864	DN571B LED20S/830 DIA-VLC-E C WH	DN571B	Yes
910505100901	DN570B LED40S/TWH PSD-E C WH	DN570B	Yes	910505100865	DN571B LED20S/840 DIA-VLC-E C WH	DN571B	Yes
910505100903	DN570B LED60S/830 PSU-E C WH	DN570B	Yes	910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	DN571B	Yes
910505100904	DN570B LED60S/840 PSU-E C WH	DN570B	Yes				
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	DN570B	Yes				
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	DN570B	Yes				

LuxSpace, recessed

Product			
Order Code	Full Product Name	family code	Service tag
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	DN571B	Yes
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	DN571B	Yes
910505100886	DN571B LED40S/830 PSU-E C WH	DN571B	Yes
910505100887	DN571B LED40S/840 PSU-E C WH	DN571B	Yes
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	DN571B	Yes
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	DN571B	Yes
910505100902	DN571B LED40S/TWH PSD-E C WH	DN571B	Yes
910505102297	DN571B LED24S/830 WIA-E C WH	DN571B	-

Product			
Order Code	Full Product Name	family code	Service tag
910505102298	DN571B LED24S/840 WIA-E C WH	DN571B	-
910505102302	DN571B LED40S/830 WIA-E C WH	DN571B	-
910505102303	DN571B LED40S/840 WIA-E C WH	DN571B	-
910505102306	DN571B LED24S/930H PSU-E C WH	DN571B	-
910505102307	DN571B LED24S/940H PSU-E C WH	DN571B	-
910505102653	DN571B LED20S/840UE PSU-E C WH	DN571B	-
910505102655	DN571B LED20S/840UE PSU-E WR WH	DN571B	-
910505102657	DN571B LED24S/840UE PSU-E C WH	DN571B	-

Light Technical (1/2)

Order Code	Name	Beam	Correlated	Color	Luminous
		angle of light	Color	rendering	Efficacy
Full Product	source	Temperature	index	(rated)	(Nom)
910505100834	DN570B	-	3000 K	>80	131 lm/W
	LED12S/830				
	PSU-E C EW				
	WH				
910505100835	DN570B	-	4000 K	>80	141 lm/W
	LED12S/840				
	PSU-E C WH				
910505100838	DN570B	-	3000 K	>80	131 lm/W
	LED12S/830				
	DIA-VLC-E C				
	WH				
910505100839	DN570B	-	4000 K	>80	141 lm/W
	LED12S/840				
	DIA-VLC-E C				
	WH				
910505100842	DN570B	-	3000 K	>80	134 lm/W
	LED20S/830				
	PSU-E C WH				
910505100843	DN570B	-	4000 K	>80	149 lm/W
	LED20S/840				
	PSU-E C WH				
910505100844	DN570B	-	3000 K	>80	113 lm/W
	LED20S/830				
	PSU-E C ELP3				
	WH				
910505100845	DN570B	-	4000 K	>80	124 lm/W
	LED20S/840				
	PSU-E C ELP3				
	WH				
910505100850	DN570B	-	3000 K	>80	134 lm/W
	LED20S/830				
	PSU-E C PG WH				
910505100851	DN570B	-	4000 K	>80	149 lm/W
	LED20S/840				
	PSU-E C PG WH				

Order Code	Name	Beam	Correlated	Color	Luminous
		angle of light	Color	rendering	Efficacy
Full Product	source	Temperature	index	(rated)	(Nom)
910505100858	DN570B	-	3000 K	>80	134 lm/W
	LED20S/830				
	DIA-VLC-E C				
	WH				
910505100859	DN570B	-	4000 K	>80	149 lm/W
	LED20S/840				
	DIA-VLC-E C				
	WH				
910505100860	DN570B	-	3000 K	>80	113 lm/W
	LED20S/830				
	DIA-VLC-E C				
	ELP3 WH				
910505100861	DN570B	-	4000 K	>80	124 lm/W
	LED20S/840				
	DIA-VLC-E C				
	ELP3 WH				
910505100862	DN570B	-	3000 K	>80	134 lm/W
	LED20S/830				
	DIA-VLC-E C				
	PG WH				
910505100863	DN570B	-	4000 K	>80	149 lm/W
	LED20S/840				
	DIA-VLC-E C				
	PG WH				
910505100868	DN570B	-	3000 K	>80	130 lm/W
	LED24S/830				
	PSU-E C WH				
910505100869	DN570B	-	4000 K	>80	141 lm/W
	LED24S/840				
	PSU-E C WH				
910505100872	DN570B	-	3000 K	>80	130 lm/W
	LED24S/830				
	DIA-VLC-E C				
	WH				
910505100873	DN570B	-	4000 K	>80	141 lm/W
	LED24S/840				

LuxSpace, recessed

		Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering (CRI)	Luminous Efficacy (rated) (Nom)
Order Code	Full Product Name				
	DIA-VLC-E C WH				
910505100884	DN570B	-	3000 K	>80	133 lm/W
	LED40S/830 PSU-E C WH				
910505100885	DN570B	-	4000 K	>80	147 lm/W
	LED40S/840 PSU-E C WH				
910505100888	DN570B	-	3000 K	>80	133 lm/W
	LED40S/830 DIA-VLC-E C WH				
910505100889	DN570B	-	4000 K	>80	147 lm/W
	LED40S/840 DIA-VLC-E C WH				
910505100901	DN570B	-	Tunable white degree(s)	>80 2700-6500 K	100 lm/W
	LED40S/TWH PSD-E C WH				
910505100903	DN570B	-	3000 K	>80	129 lm/W
	LED60S/830 PSU-E C WH				
910505100904	DN570B	-	4000 K	>80	141 lm/W
	LED60S/840 PSU-E C WH				
910505100905	DN570B	-	3000 K	>80	129 lm/W
	LED60S/830 DIA-VLC-E C WH				
910505100906	DN570B	-	4000 K	>80	141 lm/W
	LED60S/840 DIA-VLC-E C WH				
910505102295	DN570B	-	3000 K	>80	130 lm/W
	LED24S/830 WIA-E C WH				
910505102296	DN570B	-	4000 K	>80	130 lm/W
	LED24S/840 WIA-E C WH				
910505102299	DN570B	-	3000 K	>80	133 lm/W
	LED40S/830 WIA-E C WH				
910505102301	DN570B	-	4000 K	>80	147 lm/W
	LED40S/840 WIA-E C WH				
910505102304	DN570B	-	3000 K	>90	130 lm/W
	LED24S/930H PSU-E C WH				

		Beam angle of light source	Correlated Color Temperature (Nom)	Color rendering (CRI)	Luminous Efficacy (rated) (Nom)
Order Code	Full Product Name				
910505102305	DN570B	-	4000 K	>90	133 lm/W
	LED24S/940H PSU-E C WH				
910505102652	DN570B	-	4000 K	>80	161 lm/W
	LED20S/840UE PSU-E C WH				
910505102654	DN570B	-	4000 K	>80	161 lm/W
	LED20S/840UE PSU-E WR WH				
910505102656	DN570B	-	4000 K	>80	160 lm/W
	LED24S/840UE PSU-E C WH				
910505100852	DN570B	-	3000 K	>80	134 lm/W
	LED20S/830 PSU-E F WH				
910505100853	DN570B	-	4000 K	>80	149 lm/W
	LED20S/840 PSU-E F WH				
910505100854	DN570B	-	3000 K	>80	113 lm/W
	LED20S/830 PSU-E M WH				
910505100855	DN570B	-	4000 K	>80	127 lm/W
	LED20S/840 PSU-E M WH				
910505100856	DN570B	-	3000 K	>80	134 lm/W
	LED20S/830 PSU-E WR WH				
910505100857	DN570B	-	4000 K	>80	149 lm/W
	LED20S/840 PSU-E WR WH				
910505100836	DN571B	-	3000 K	>80	131 lm/W
	LED12S/830 PSU-E C WH				
910505100837	DN571B	-	4000 K	>80	141 lm/W
	LED12S/840 PSU-E C WH				
910505100840	DN571B	-	3000 K	>80	131 lm/W
	LED12S/830 DIA-VLC-E C WH				
910505100841	DN571B	-	4000 K	>80	141 lm/W
	LED12S/840 DIA-VLC-E C WH				
910505100846	DN571B	-	3000 K	>80	134 lm/W
	LED20S/830 PSU-E C WH				

LuxSpace, recessed

		Beam angle of light	Correlated Color Temperature	Color rendering index	Luminous Efficacy (rated)
Order Code	Full Product Name	source	(Nom)	(CRI)	(Nom)
910505100847	DN571B LED20S/840 PSU-E C WH	-	4000 K	>80	149 lm/W
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	-	3000 K	>80	113 lm/W
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	-	4000 K	>80	124 lm/W
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	-	3000 K	>80	134 lm/W
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	-	4000 K	>80	149 lm/W
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	-	3000 K	>80	113 lm/W
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	-	4000 K	>80	124 lm/W
910505100870	DN571B LED24S/830 PSU-E C WH	-	3000 K	>80	130 lm/W
910505100871	DN571B LED24S/840 PSU-E C WH	-	4000 K	>80	141 lm/W
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	-	3000 K	>80	130 lm/W
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	-	4000 K	>80	141 lm/W
910505100886	DN571B LED40S/830 PSU-E C WH	-	3000 K	>80	133 lm/W

		Beam angle of light	Correlated Color Temperature	Color rendering index	Luminous Efficacy (rated)
Order Code	Full Product Name	source	(Nom)	(CRI)	(Nom)
910505100887	DN571B LED40S/840 PSU-E C WH	-	4000 K	>80	147 lm/W
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	-	3000 K	>80	133 lm/W
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	-	4000 K	>80	147 lm/W
910505100902	DN571B LED40S/TWH PSD-E C WH	degree(s)	2700-6500 K	>80	100 lm/W
910505102297	DN571B LED24S/830 WIA-E C WH	-	3000 K	>80	130 lm/W
910505102298	DN571B LED24S/840 WIA-E C WH	-	4000 K	>80	130 lm/W
910505102302	DN571B LED40S/830 WIA-E C WH	-	3000 K	>80	133 lm/W
910505102303	DN571B LED40S/840 WIA-E C WH	-	4000 K	>80	147 lm/W
910505102306	DN571B LED24S/930H PSU-E C WH	-	3000 K	>90	130 lm/W
910505102307	DN571B LED24S/940H PSU-E C WH	-	4000 K	>90	133 lm/W
910505102653	DN571B LED20S/840UE PSU-E C WH	-	4000 K	>80	161 lm/W
910505102655	DN571B LED20S/840UE PSU-E WR WH	-	4000 K	>80	161 lm/W
910505102657	DN571B LED24S/840UE PSU-E C WH	-	4000 K	>80	160 lm/W

Light Technical (2/2)

LuxSpace, recessed

Order Code	Full Product Name	Flux	Upward		
			Luminous measure (SVM)	Stroboscopic effect visibility	light output ratio
910505100834	DN570B LED12S/830 PSU-E C EW WH	1,300 lm	-	-	
910505100835	DN570B LED12S/840 PSU-E C WH	1,300 lm	-	-	
910505100838	DN570B LED12S/830 DIA- VLC-E C WH	1,300 lm	-	-	
910505100839	DN570B LED12S/840 DIA- VLC-E C WH	1,300 lm	-	-	
910505100842	DN570B LED20S/830 PSU-E C WH	2,200 lm	-	-	
910505100843	DN570B LED20S/840 PSU-E C WH	2,200 lm	-	-	
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	2,200 lm	-	-	
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	2,200 lm	-	-	
910505100850	DN570B LED20S/830 PSU-E C PG WH	2,200 lm	-	-	
910505100851	DN570B LED20S/840 PSU-E C PG WH	2,200 lm	-	-	
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	2,200 lm	-	-	
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	2,200 lm	-	-	
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	2,200 lm	-	-	
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	2,200 lm	-	-	
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	2,200 lm	-	-	
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	2,200 lm	-	-	
910505100868	DN570B LED24S/830 PSU-E C WH	2,600 lm	0.4	-	
910505100869	DN570B LED24S/840 PSU-E C WH	2,600 lm	-	-	
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	2,600 lm	-	-	
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	2,600 lm	-	-	
910505100884	DN570B LED40S/830 PSU-E C WH	4,400 lm	0.4	-	
910505100885	DN570B LED40S/840 PSU-E C WH	4,400 lm	0.4	-	
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	4,400 lm	-	-	
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	4,400 lm	-	-	

Order Code	Full Product Name	Flux	Upward		
			Luminous measure (SVM)	Stroboscopic effect visibility	light output ratio
910505100901	DN570B LED40S/TWH PSD-E C WH	3,100 lm	-	-	
910505100903	DN570B LED60S/830 PSU-E C WH	6,200 lm	-	-	
910505100904	DN570B LED60S/840 PSU-E C WH	6,200 lm	-	-	
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	6,200 lm	-	-	
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	6,200 lm	-	-	
910505102295	DN570B LED24S/830 WIA-E C WH	2,600 lm	0.5	-	
910505102296	DN570B LED24S/840 WIA-E C WH	2,600 lm	0.5	-	
910505102299	DN570B LED40S/830 WIA-E C WH	4,400 lm	0.5	-	
910505102301	DN570B LED40S/840 WIA-E C WH	4,400 lm	0.5	-	
910505102304	DN570B LED24S/930H PSU-E C WH	2,600 lm	0.4	-	
910505102305	DN570B LED24S/940H PSU-E C WH	2,600 lm	0.4	-	
910505102652	DN570B LED20S/840UE PSU-E C WH	2,100 lm	-	0	
910505102654	DN570B LED20S/840UE PSU-E WR WH	2,100 lm	-	0	
910505102656	DN570B LED24S/840UE PSU-E C WH	2,400 lm	-	0	
910505100852	DN570B LED20S/830 PSU-E F WH	2,200 lm	-	-	
910505100853	DN570B LED20S/840 PSU-E F WH	2,200 lm	-	-	
910505100854	DN570B LED20S/830 PSU-E M WH	1,860 lm	-	-	
910505100855	DN570B LED20S/840 PSU-E M WH	1,860 lm	-	-	
910505100856	DN570B LED20S/830 PSU-E WR WH	2,200 lm	-	-	
910505100857	DN570B LED20S/840 PSU-E WR WH	2,200 lm	-	-	
910505100836	DN571B LED12S/830 PSU- E C WH	1,300 lm	-	-	
910505100837	DN571B LED12S/840 PSU- E C WH	1,300 lm	-	-	
910505100840	DN571B LED12S/830 DIA- VLC-E C WH	1,300 lm	-	-	
910505100841	DN571B LED12S/840 DIA- VLC-E C WH	1,300 lm	-	-	

LuxSpace, recessed

Order Code	Full Product Name	Luminous Flux	Upward		
			Stroboscopic effect visibility measure (SVM)	light output ratio	
910505100846	DN571B LED20S/830 PSU-E C WH	2,200 lm	-	-	
910505100847	DN571B LED20S/840 PSU-E C WH	2,200 lm	-	-	
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	2,200 lm	-	-	
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	2,200 lm	-	-	
910505100864	DN571B LED20S/830 DIA- VLC-E C WH	2,200 lm	-	-	
910505100865	DN571B LED20S/840 DIA- VLC-E C WH	2,200 lm	-	-	
910505100866	DN571B LED20S/830 DIA- VLC-E C ELP3 WH	2,200 lm	-	-	
910505100867	DN571B LED20S/840 DIA- VLC-E C ELP3 WH	2,200 lm	-	-	
910505100870	DN571B LED24S/830 PSU-E C WH	2,600 lm	0.4	-	
910505100871	DN571B LED24S/840 PSU-E C WH	2,600 lm	-	-	
910505100874	DN571B LED24S/830 DIA- VLC-E C WH	2,600 lm	-	-	
910505100875	DN571B LED24S/840 DIA- VLC-E C WH	2,600 lm	-	-	
910505100886	DN571B LED40S/830 PSU-E C WH	4,400 lm	-	-	

Order Code	Full Product Name	Luminous Flux	Upward		
			Stroboscopic effect visibility measure (SVM)	light output ratio	
910505100887	DN571B LED40S/840 PSU-E C WH	4,400 lm	-	-	
910505100890	DN571B LED40S/830 DIA- VLC-E C WH	4,400 lm	-	-	
910505100891	DN571B LED40S/840 DIA- VLC-E C WH	4,400 lm	-	-	
910505100902	DN571B LED40S/TWH PSD-E C WH	3,100 lm	-	-	
910505102297	DN571B LED24S/830 WIA-E C WH	2,600 lm	0.5	-	
910505102298	DN571B LED24S/840 WIA-E C WH	2,600 lm	0.5	-	
910505102302	DN571B LED40S/830 WIA-E C WH	4,400 lm	0.5	-	
910505102303	DN571B LED40S/840 WIA-E C WH	4,400 lm	0.5	-	
910505102306	DN571B LED24S/930H PSU-E C WH	2,600 lm	0.4	-	
910505102307	DN571B LED24S/940H PSU-E C WH	2,600 lm	0.4	-	
910505102653	DN571B LED20S/840UE PSU-E C WH	2,100 lm	-	0	
910505102655	DN571B LED20S/840UE PSU-E WR WH	2,100 lm	-	0	
910505102657	DN571B LED24S/840UE PSU-E C WH	2,400 lm	-	0	

Operating and Electrical

Order Code	Full Product Name	Power		
		Line Frequency	Consumption	
910505100834	DN570B LED12S/830 PSU-E C EW WH	50 to 60 Hz	9.9 W	
910505100835	DN570B LED12S/840 PSU-E C WH	50 to 60 Hz	9.2 W	
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	50 to 60 Hz	9.9 W	
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	50 to 60 Hz	9.2 W	
910505100842	DN570B LED20S/830 PSU-E C WH	50 to 60 Hz	16.4 W	
910505100843	DN570B LED20S/840 PSU-E C WH	50 to 60 Hz	14.8 W	
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	50 to 60 Hz	19.4 W	
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	50 to 60 Hz	17.8 W	
910505100850	DN570B LED20S/830 PSU-E C PG WH	50 to 60 Hz	16.4 W	

Order Code	Full Product Name	Power		
		Line Frequency	Consumption	
910505100851	DN570B LED20S/840 PSU-E C PG WH	50 to 60 Hz	14.8 W	
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	50 to 60 Hz	16.4 W	
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	50 to 60 Hz	14.8 W	
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	50 to 60 Hz	19.4 W	
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	50 to 60 Hz	17.8 W	
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	50 to 60 Hz	16.4 W	
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	50 to 60 Hz	14.8 W	
910505100868	DN570B LED24S/830 PSU-E C WH	0/50/60 Hz	20 W	
910505100869	DN570B LED24S/840 PSU-E C WH	50 to 60 Hz	18.4 W	

LuxSpace, recessed

Power			
Order Code	Full Product Name	Line Frequency	Consumption
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	50 to 60 Hz	20 W
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	50 to 60 Hz	18.4 W
910505100884	DN570B LED40S/830 PSU-E C WH	0/50/60 Hz	33 W
910505100885	DN570B LED40S/840 PSU-E C WH	0/50/60 Hz	30 W
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	50 to 60 Hz	33 W
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	50 to 60 Hz	30 W
910505100901	DN570B LED40S/TWH PSD-E C WH	50 to 60 Hz	30 W
910505100903	DN570B LED60S/830 PSU-E C WH	50 to 60 Hz	48 W
910505100904	DN570B LED60S/840 PSU-E C WH	50 to 60 Hz	44 W
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	50 to 60 Hz	48 W
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	50 to 60 Hz	44 W
910505102295	DN570B LED24S/830 WIA-E C WH	0/50/60 Hz	20 W
910505102296	DN570B LED24S/840 WIA-E C WH	0/50/60 Hz	20 W
910505102299	DN570B LED40S/830 WIA-E C WH	0/50/60 Hz	33 W
910505102301	DN570B LED40S/840 WIA-E C WH	0/50/60 Hz	30 W
910505102304	DN570B LED24S/930H PSU-E C WH	0/50/60 Hz	20 W
910505102305	DN570B LED24S/940H PSU-E C WH	0/50/60 Hz	20 W
910505102652	DN570B LED20S/840UE PSU-E C WH	50 to 60 Hz	13 W
910505102654	DN570B LED20S/840UE PSU-E WR WH	50 to 60 Hz	13 W
910505102656	DN570B LED24S/840UE PSU-E C WH	50 to 60 Hz	15 W
910505100852	DN570B LED20S/830 PSU-E F WH	50 to 60 Hz	16.4 W
910505100853	DN570B LED20S/840 PSU-E F WH	50 to 60 Hz	14.8 W
910505100854	DN570B LED20S/830 PSU-E M WH	50 to 60 Hz	16.4 W
910505100855	DN570B LED20S/840 PSU-E M WH	50 to 60 Hz	14.8 W
910505100856	DN570B LED20S/830 PSU-E WR WH	50 to 60 Hz	16.4 W

Power			
Order Code	Full Product Name	Line Frequency	Consumption
910505100857	DN570B LED20S/840 PSU-E WR WH	50 to 60 Hz	14.8 W
910505100836	DN571B LED12S/830 PSU-E C WH	50 to 60 Hz	9.9 W
910505100837	DN571B LED12S/840 PSU-E C WH	50 to 60 Hz	9.2 W
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	50 to 60 Hz	9.9 W
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	50 to 60 Hz	9.2 W
910505100846	DN571B LED20S/830 PSU-E C WH	50 to 60 Hz	16.4 W
910505100847	DN571B LED20S/840 PSU-E C WH	50 to 60 Hz	14.8 W
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	50 to 60 Hz	19.4 W
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	50 to 60 Hz	17.8 W
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	50 to 60 Hz	16.4 W
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	50 to 60 Hz	14.8 W
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	50 to 60 Hz	19.4 W
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	50 to 60 Hz	17.8 W
910505100870	DN571B LED24S/830 PSU-E C WH	0/50/60 Hz	20 W
910505100871	DN571B LED24S/840 PSU-E C WH	50 to 60 Hz	18.4 W
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	50 to 60 Hz	20 W
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	50 to 60 Hz	18.4 W
910505100886	DN571B LED40S/830 PSU-E C WH	50 to 60 Hz	33 W
910505100887	DN571B LED40S/840 PSU-E C WH	50 to 60 Hz	30 W
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	50 to 60 Hz	33 W
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	50 to 60 Hz	30 W
910505100902	DN571B LED40S/TWH PSD-E C WH	50 to 60 Hz	30 W
910505102297	DN571B LED24S/830 WIA-E C WH	0/50/60 Hz	20 W
910505102298	DN571B LED24S/840 WIA-E C WH	0/50/60 Hz	20 W
910505102302	DN571B LED40S/830 WIA-E C WH	0/50/60 Hz	33 W

LuxSpace, recessed

Power				
Order Code	Full Product Name	Line Frequency	Consumption	
910505102303	DN571B LED40S/840 WIA-E C WH	0/50/60 Hz	30 W	
910505102306	DN571B LED24S/930H PSU-E C WH	0/50/60 Hz	20 W	
910505102307	DN571B LED24S/940H PSU-E C WH	0/50/60 Hz	20 W	

Power				
Order Code	Full Product Name	Line Frequency	Consumption	
910505102653	DN571B LED20S/840UE PSU-E C WH	50 to 60 Hz	13 W	
910505102655	DN571B LED20S/840UE PSU-E WR WH	50 to 60 Hz	13 W	
910505102657	DN571B LED24S/840UE PSU-E C WH	50 to 60 Hz	15 W	

Temperature

Order Code	Full Product Name	Ambient temperature range
910505100834	DN570B LED12S/830 PSU-E C EW WH	+10 to +25 °C
910505100835	DN570B LED12S/840 PSU-E C WH	+10 to +25 °C
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	+10 to +25 °C
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	+10 to +25 °C
910505100842	DN570B LED20S/830 PSU-E C WH	+10 to +25 °C
910505100843	DN570B LED20S/840 PSU-E C WH	+10 to +25 °C
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	+10 to +25 °C
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	+10 to +25 °C
910505100850	DN570B LED20S/830 PSU-E C PG WH	+10 to +25 °C
910505100851	DN570B LED20S/840 PSU-E C PG WH	+10 to +25 °C
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	+10 to +25 °C
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	+10 to +25 °C
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	+10 to +25 °C
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	+10 to +25 °C
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	+10 to +25 °C
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	+10 to +25 °C
910505100868	DN570B LED24S/830 PSU-E C WH	+10 to +25 °C
910505100869	DN570B LED24S/840 PSU-E C WH	+10 to +25 °C
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	+10 to +25 °C
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	+10 to +25 °C
910505100884	DN570B LED40S/830 PSU-E C WH	+10 to +25 °C
910505100885	DN570B LED40S/840 PSU-E C WH	+10 to +25 °C
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	+10 to +25 °C
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	+10 to +25 °C
910505100901	DN570B LED40S/TWH PSD-E C WH	+10 to +25 °C
910505100903	DN570B LED60S/830 PSU-E C WH	+10 to +25 °C
910505100904	DN570B LED60S/840 PSU-E C WH	+10 to +25 °C
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	+10 to +25 °C
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	+10 to +25 °C
910505102295	DN570B LED24S/830 WIA-E C WH	+10 to +25 °C
910505102296	DN570B LED24S/840 WIA-E C WH	+10 to +25 °C
910505102299	DN570B LED40S/830 WIA-E C WH	+10 to +25 °C
910505102301	DN570B LED40S/840 WIA-E C WH	+10 to +25 °C
910505102304	DN570B LED24S/930H PSU-E C WH	+10 to +25 °C
910505102305	DN570B LED24S/940H PSU-E C WH	+10 to +25 °C
910505102652	DN570B LED20S/840UE PSU-E C WH	+10 to +35 °C

Order Code	Full Product Name	Ambient temperature range
910505102654	DN570B LED20S/840UE PSU-E WR WH	+10 to +35 °C
910505102656	DN570B LED24S/840UE PSU-E C WH	+10 to +35 °C
910505100852	DN570B LED20S/830 PSU-E F WH	+10 to +25 °C
910505100853	DN570B LED20S/840 PSU-E F WH	+10 to +25 °C
910505100854	DN570B LED20S/830 PSU-E M WH	+10 to +25 °C
910505100855	DN570B LED20S/840 PSU-E M WH	+10 to +25 °C
910505100856	DN570B LED20S/830 PSU-E WR WH	+10 to +25 °C
910505100857	DN570B LED20S/840 PSU-E WR WH	+10 to +25 °C
910505100836	DN571B LED12S/830 PSU-E C WH	+10 to +25 °C
910505100837	DN571B LED12S/840 PSU-E C WH	+10 to +25 °C
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	+10 to +25 °C
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	+10 to +25 °C
910505100846	DN571B LED20S/830 PSU-E C WH	+10 to +25 °C
910505100847	DN571B LED20S/840 PSU-E C WH	+10 to +25 °C
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	+10 to +25 °C
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	+10 to +25 °C
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	+10 to +25 °C
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	+10 to +25 °C
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3	+10 to +25 °C
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	+10 to +25 °C
910505100870	DN571B LED24S/830 PSU-E C WH	+10 to +25 °C
910505100871	DN571B LED24S/840 PSU-E C WH	+10 to +25 °C
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	+10 to +25 °C
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	+10 to +25 °C
910505100886	DN571B LED40S/830 PSU-E C WH	+10 to +25 °C
910505100887	DN571B LED40S/840 PSU-E C WH	+10 to +25 °C
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	+10 to +25 °C
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	+10 to +25 °C
910505100902	DN571B LED40S/TWH PSD-E C WH	+10 to +25 °C
910505102297	DN571B LED24S/830 WIA-E C WH	+10 to +25 °C
910505102298	DN571B LED24S/840 WIA-E C WH	+10 to +25 °C
910505102302	DN571B LED40S/830 WIA-E C WH	+10 to +25 °C
910505102303	DN571B LED40S/840 WIA-E C WH	+10 to +25 °C
910505102306	DN571B LED24S/930H PSU-E C WH	+10 to +25 °C
910505102307	DN571B LED24S/940H PSU-E C WH	+10 to +25 °C
910505102653	DN571B LED20S/840UE PSU-E C WH	+10 to +35 °C
910505102655	DN571B LED20S/840UE PSU-E WR WH	+10 to +35 °C
910505102657	DN571B LED24S/840UE PSU-E C WH	+10 to +35 °C

LuxSpace, recessed

Controls and Dimming

Order Code	Full Product Name	Dimmable
910505100834	DN570B LED12S/830 PSU-E C EW WH	No
910505100835	DN570B LED12S/840 PSU-E C WH	No
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	Yes
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	Yes
910505100842	DN570B LED20S/830 PSU-E C WH	No
910505100843	DN570B LED20S/840 PSU-E C WH	No
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	No
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	No
910505100850	DN570B LED20S/830 PSU-E C PG WH	No
910505100851	DN570B LED20S/840 PSU-E C PG WH	No
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	Yes
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	Yes
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	Yes
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	Yes
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	Yes
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	Yes
910505100868	DN570B LED24S/830 PSU-E C WH	No
910505100869	DN570B LED24S/840 PSU-E C WH	No
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	Yes
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	Yes
910505100884	DN570B LED40S/830 PSU-E C WH	No
910505100885	DN570B LED40S/840 PSU-E C WH	No
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	Yes
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	Yes
910505100901	DN570B LED40S/TWH PSD-E C WH	Yes
910505100903	DN570B LED60S/830 PSU-E C WH	No
910505100904	DN570B LED60S/840 PSU-E C WH	No
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	Yes
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	Yes
910505102295	DN570B LED24S/830 WIA-E C WH	Yes
910505102296	DN570B LED24S/840 WIA-E C WH	Yes
910505102299	DN570B LED40S/830 WIA-E C WH	Yes
910505102301	DN570B LED40S/840 WIA-E C WH	Yes
910505102304	DN570B LED24S/930H PSU-E C WH	No
910505102305	DN570B LED24S/940H PSU-E C WH	No
910505102652	DN570B LED20S/840UE PSU-E C WH	No
910505102654	DN570B LED20S/840UE PSU-E WR WH	No

Order Code	Full Product Name	Dimmable
910505102656	DN570B LED24S/840UE PSU-E C WH	No
910505100852	DN570B LED20S/830 PSU-E F WH	No
910505100853	DN570B LED20S/840 PSU-E F WH	No
910505100854	DN570B LED20S/830 PSU-E M WH	No
910505100855	DN570B LED20S/840 PSU-E M WH	No
910505100856	DN570B LED20S/830 PSU-E WR WH	No
910505100857	DN570B LED20S/840 PSU-E WR WH	No
910505100836	DN571B LED12S/830 PSU-E C WH	No
910505100837	DN571B LED12S/840 PSU-E C WH	No
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	Yes
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	Yes
910505100846	DN571B LED20S/830 PSU-E C WH	No
910505100847	DN571B LED20S/840 PSU-E C WH	No
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	No
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	No
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	Yes
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	Yes
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	Yes
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	Yes
910505100870	DN571B LED24S/830 PSU-E C WH	No
910505100871	DN571B LED24S/840 PSU-E C WH	No
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	Yes
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	Yes
910505100886	DN571B LED40S/830 PSU-E C WH	No
910505100887	DN571B LED40S/840 PSU-E C WH	No
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	Yes
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	Yes
910505100902	DN571B LED40S/TWH PSD-E C WH	Yes
910505102297	DN571B LED24S/830 WIA-E C WH	Yes
910505102298	DN571B LED24S/840 WIA-E C WH	Yes
910505102302	DN571B LED40S/830 WIA-E C WH	Yes
910505102303	DN571B LED40S/840 WIA-E C WH	Yes
910505102306	DN571B LED24S/930H PSU-E C WH	No
910505102307	DN571B LED24S/940H PSU-E C WH	No
910505102653	DN571B LED20S/840UE PSU-E C WH	No
910505102655	DN571B LED20S/840UE PSU-E WR WH	No
910505102657	DN571B LED24S/840UE PSU-E C WH	No

Approval and Application

Order Code	Full Product Name	Ingress protection code
910505100834	DN570B LED12S/830 PSU-E C EW WH	IP20
910505100835	DN570B LED12S/840 PSU-E C WH	IP20
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	IP20
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	IP20
910505100842	DN570B LED20S/830 PSU-E C WH	IP20
910505100843	DN570B LED20S/840 PSU-E C WH	IP20
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	IP20
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	IP20
910505100850	DN570B LED20S/830 PSU-E C PG WH	IP20/54

Order Code	Full Product Name	Ingress protection code
910505100851	DN570B LED20S/840 PSU-E C PG WH	IP20/54
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	IP20
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	IP20
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	IP20
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	IP20
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	IP20/54
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	IP20/54
910505100868	DN570B LED24S/830 PSU-E C WH	IP20
910505100869	DN570B LED24S/840 PSU-E C WH	IP20

LuxSpace, recessed

Order Code	Full Product Name	Ingress protection code
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	IP20
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	IP20
910505100884	DN570B LED40S/830 PSU-E C WH	IP20
910505100885	DN570B LED40S/840 PSU-E C WH	IP20
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	IP20
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	IP20
910505100901	DN570B LED40S/TWH PSD-E C WH	IP20
910505100903	DN570B LED60S/830 PSU-E C WH	IP20
910505100904	DN570B LED60S/840 PSU-E C WH	IP20
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	IP20
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	IP20
910505102295	DN570B LED24S/830 WIA-E C WH	IP20
910505102296	DN570B LED24S/840 WIA-E C WH	IP20
910505102299	DN570B LED40S/830 WIA-E C WH	IP20
910505102301	DN570B LED40S/840 WIA-E C WH	IP20
910505102304	DN570B LED24S/930H PSU-E C WH	IP20
910505102305	DN570B LED24S/940H PSU-E C WH	IP20
910505102652	DN570B LED20S/840UE PSU-E C WH	IP20
910505102654	DN570B LED20S/840UE PSU-E WR WH	IP20
910505102656	DN570B LED24S/840UE PSU-E C WH	IP20
910505100852	DN570B LED20S/830 PSU-E F WH	IP20
910505100853	DN570B LED20S/840 PSU-E F WH	IP20
910505100854	DN570B LED20S/830 PSU-E M WH	IP20
910505100855	DN570B LED20S/840 PSU-E M WH	IP20
910505100856	DN570B LED20S/830 PSU-E WR WH	IP20
910505100857	DN570B LED20S/840 PSU-E WR WH	IP20
910505100836	DN571B LED12S/830 PSU-E C WH	IP20
910505100837	DN571B LED12S/840 PSU-E C WH	IP20

Order Code	Full Product Name	Ingress protection code
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	IP20
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	IP20
910505100846	DN571B LED20S/830 PSU-E C WH	IP20
910505100847	DN571B LED20S/840 PSU-E C WH	IP20
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	IP20
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	IP20
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	IP20
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	IP20
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	IP20
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	IP20
910505100870	DN571B LED24S/830 PSU-E C WH	IP20
910505100871	DN571B LED24S/840 PSU-E C WH	IP20
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	IP20
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	IP20
910505100886	DN571B LED40S/830 PSU-E C WH	IP20
910505100887	DN571B LED40S/840 PSU-E C WH	IP20
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	IP20
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	IP20
910505100902	DN571B LED40S/TWH PSD-E C WH	IP20
910505102297	DN571B LED24S/830 WIA-E C WH	IP20
910505102298	DN571B LED24S/840 WIA-E C WH	IP20
910505102302	DN571B LED40S/830 WIA-E C WH	IP20
910505102303	DN571B LED40S/840 WIA-E C WH	IP20
910505102306	DN571B LED24S/930H PSU-E C WH	IP20
910505102307	DN571B LED24S/940H PSU-E C WH	IP20
910505102653	DN571B LED20S/840UE PSU-E C WH	IP20
910505102655	DN571B LED20S/840UE PSU-E WR WH	IP20
910505102657	DN571B LED24S/840UE PSU-E C WH	IP20

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505100834	DN570B LED12S/830 PSU-E C EW WH	(0.43, 0.40) SDCM≤2
910505100835	DN570B LED12S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100842	DN570B LED20S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100843	DN570B LED20S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40) SDCM≤2
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.38) SDCM≤2
910505100850	DN570B LED20S/830 PSU-E C PG WH	(0.43, 0.40) SDCM≤2
910505100851	DN570B LED20S/840 PSU-E C PG WH	(0.38, 0.38) SDCM≤2
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	(0.43, 0.40) SDCM≤2
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	(0.38, 0.38) SDCM≤2
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	(0.43, 0.40) SDCM≤2
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	(0.38, 0.38) SDCM≤2
910505100868	DN570B LED24S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100869	DN570B LED24S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2

Order Code	Full Product Name	Initial chromaticity
910505100884	DN570B LED40S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100885	DN570B LED40S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100901	DN570B LED40S/TWH PSD-E C WH	(0.307, 0.326) SDCM≤4
910505100903	DN570B LED60S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100904	DN570B LED60S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505102295	DN570B LED24S/830 WIA-E C WH	(0.43, 0.40) SDCM≤2
910505102296	DN570B LED24S/840 WIA-E C WH	(0.38, 0.38) SDCM≤2
910505102299	DN570B LED40S/830 WIA-E C WH	(0.43, 0.40) SDCM≤2
910505102301	DN570B LED40S/840 WIA-E C WH	(0.38, 0.38) SDCM≤2
910505102304	DN570B LED24S/930H PSU-E C WH	(0.43, 0.40) SDCM≤2
910505102305	DN570B LED24S/940H PSU-E C WH	(0.38, 0.38) SDCM≤2
910505102652	DN570B LED20S/840UE PSU-E C WH	-
910505102654	DN570B LED20S/840UE PSU-E WR WH	-
910505102656	DN570B LED24S/840UE PSU-E C WH	-
910505100852	DN570B LED20S/830 PSU-E F WH	(0.43, 0.40) SDCM≤2
910505100853	DN570B LED20S/840 PSU-E F WH	(0.38, 0.38) SDCM≤2
910505100854	DN570B LED20S/830 PSU-E M WH	(0.43, 0.40) SDCM≤2
910505100855	DN570B LED20S/840 PSU-E M WH	(0.43, 0.40) SDCM≤2
910505100856	DN570B LED20S/830 PSU-E WR WH	(0.43, 0.40) SDCM≤2
910505100857	DN570B LED20S/840 PSU-E WR WH	(0.38, 0.38) SDCM≤2
910505100859	DN570B LED20S/840 PSU-E F WH	(0.43, 0.40) SDCM≤2
910505100860	DN570B LED20S/840 PSU-E F WH	(0.38, 0.38) SDCM≤2
910505100861	DN570B LED20S/840 PSU-E F WH	(0.43, 0.40) SDCM≤2
910505100862	DN570B LED20S/840 PSU-E F WH	(0.43, 0.40) SDCM≤2
910505100863	DN570B LED20S/840 PSU-E F WH	(0.43, 0.40) SDCM≤2
910505100868	DN570B LED24S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100869	DN570B LED24S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2

Order Code	Full Product Name	Initial chromaticity
910505100854	DN570B LED20S/830 PSU-E M WH	(0.43, 0.40) SDCM≤2
910505100855	DN570B LED20S/840 PSU-E M WH	(0.38, 0.38) SDCM≤2
910505100856	DN570B LED20S/830 PSU-E WR WH	(0.43, 0.40) SDCM≤2
910505100857	DN570B LED20S/840 PSU-E WR WH	(0.38, 0.38) SDCM≤2
910505100836	DN571B LED12S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100837	DN571B LED12S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100846	DN571B LED20S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100847	DN571B LED20S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	(0.43, 0.40) SDCM≤2
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	(0.38, 0.38) SDCM≤2
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	(0.43, 0.40) SDCM≤2
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	(0.38, 0.38) SDCM≤2
910505100870	DN571B LED24S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2

Order Code	Full Product Name	Initial chromaticity
910505100871	DN571B LED24S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100886	DN571B LED40S/830 PSU-E C WH	(0.43, 0.40) SDCM≤2
910505100887	DN571B LED40S/840 PSU-E C WH	(0.38, 0.38) SDCM≤2
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM≤2
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM≤2
910505100902	DN571B LED40S/TWH PSD-E C WH	(0.307, 0.326) SDCM≤4
910505102297	DN571B LED24S/830 WIA-E C WH	(0.43, 0.40) SDCM≤2
910505102298	DN571B LED24S/840 WIA-E C WH	(0.38, 0.38) SDCM≤2
910505102302	DN571B LED40S/830 WIA-E C WH	(0.43, 0.40) SDCM≤2
910505102303	DN571B LED40S/840 WIA-E C WH	(0.38, 0.38) SDCM≤2
910505102306	DN571B LED24S/930H PSU-E C WH	(0.43, 0.40) SDCM≤2
910505102307	DN571B LED24S/940H PSU-E C WH	(0.38, 0.38) SDCM≤2
910505102653	DN571B LED20S/840UE PSU-E C WH	-
910505102655	DN571B LED20S/840UE PSU-E WR WH	-
910505102657	DN571B LED24S/840UE PSU-E C WH	-

Application Conditions




Order Code	Full Product Name	Maximum dim level
910505100834	DN570B LED12S/830 PSU-E C EW WH	-
910505100835	DN570B LED12S/840 PSU-E C WH	-
910505100838	DN570B LED12S/830 DIA-VLC-E C WH	1%
910505100839	DN570B LED12S/840 DIA-VLC-E C WH	1%
910505100842	DN570B LED20S/830 PSU-E C WH	-
910505100843	DN570B LED20S/840 PSU-E C WH	-
910505100844	DN570B LED20S/830 PSU-E C ELP3 WH	-
910505100845	DN570B LED20S/840 PSU-E C ELP3 WH	-
910505100850	DN570B LED20S/830 PSU-E C PG WH	-
910505100851	DN570B LED20S/840 PSU-E C PG WH	-
910505100858	DN570B LED20S/830 DIA-VLC-E C WH	1%
910505100859	DN570B LED20S/840 DIA-VLC-E C WH	1%
910505100860	DN570B LED20S/830 DIA-VLC-E C ELP3 WH	1%
910505100861	DN570B LED20S/840 DIA-VLC-E C ELP3 WH	1%
910505100862	DN570B LED20S/830 DIA-VLC-E C PG WH	1%
910505100863	DN570B LED20S/840 DIA-VLC-E C PG WH	1%
910505100868	DN570B LED24S/830 PSU-E C WH	Not applicable
910505100869	DN570B LED24S/840 PSU-E C WH	-
910505100872	DN570B LED24S/830 DIA-VLC-E C WH	1%
910505100873	DN570B LED24S/840 DIA-VLC-E C WH	1%
910505100884	DN570B LED40S/830 PSU-E C WH	Not applicable
910505100885	DN570B LED40S/840 PSU-E C WH	Not applicable
910505100888	DN570B LED40S/830 DIA-VLC-E C WH	1%
910505100889	DN570B LED40S/840 DIA-VLC-E C WH	1%
910505100901	DN570B LED40S/TWH PSD-E C WH	1%
910505100903	DN570B LED60S/830 PSU-E C WH	-
910505100904	DN570B LED60S/840 PSU-E C WH	-
910505100905	DN570B LED60S/830 DIA-VLC-E C WH	1%
910505100906	DN570B LED60S/840 DIA-VLC-E C WH	1%
910505102295	DN570B LED24S/830 WIA-E C WH	10%
910505102296	DN570B LED24S/840 WIA-E C WH	10%

Order Code	Full Product Name	Maximum dim level
910505102299	DN570B LED40S/830 WIA-E C WH	10%
910505102301	DN570B LED40S/840 WIA-E C WH	10%
910505102304	DN570B LED24S/930H PSU-E C WH	Not applicable
910505102305	DN570B LED24S/940H PSU-E C WH	Not applicable
910505102652	DN570B LED20S/840UE PSU-E C WH	Not applicable
910505102654	DN570B LED20S/840UE PSU-E WR WH	Not applicable
910505102656	DN570B LED24S/840UE PSU-E C WH	Not applicable
910505100852	DN570B LED20S/830 PSU-E F WH	-
910505100853	DN570B LED20S/840 PSU-E F WH	-
910505100854	DN570B LED20S/830 PSU-E M WH	-
910505100855	DN570B LED20S/840 PSU-E M WH	-
910505100856	DN570B LED20S/830 PSU-E WR WH	-
910505100857	DN570B LED20S/840 PSU-E WR WH	-
910505100836	DN571B LED12S/830 PSU-E C WH	-
910505100837	DN571B LED12S/840 PSU-E C WH	-
910505100840	DN571B LED12S/830 DIA-VLC-E C WH	1%
910505100841	DN571B LED12S/840 DIA-VLC-E C WH	1%
910505100846	DN571B LED20S/830 PSU-E C WH	-
910505100847	DN571B LED20S/840 PSU-E C WH	-
910505100848	DN571B LED20S/830 PSU-E C ELP3 WH	-
910505100849	DN571B LED20S/840 PSU-E C ELP3 WH	-
910505100864	DN571B LED20S/830 DIA-VLC-E C WH	1%
910505100865	DN571B LED20S/840 DIA-VLC-E C WH	1%
910505100866	DN571B LED20S/830 DIA-VLC-E C ELP3 WH	1%
910505100867	DN571B LED20S/840 DIA-VLC-E C ELP3 WH	1%
910505100870	DN571B LED24S/830 PSU-E C WH	Not applicable
910505100871	DN571B LED24S/840 PSU-E C WH	-
910505100874	DN571B LED24S/830 DIA-VLC-E C WH	1%
910505100875	DN571B LED24S/840 DIA-VLC-E C WH	1%
910505100886	DN571B LED40S/830 PSU-E C WH	-
910505100887	DN571B LED40S/840 PSU-E C WH	-

Order Code	Full Product Name	Maximum dim level
910505100890	DN571B LED40S/830 DIA-VLC-E C WH	1%
910505100891	DN571B LED40S/840 DIA-VLC-E C WH	1%
910505100902	DN571B LED40S/TWH PSD-E C WH	1%
910505102297	DN571B LED24S/830 WIA-E C WH	10%
910505102298	DN571B LED24S/840 WIA-E C WH	10%
910505102302	DN571B LED40S/830 WIA-E C WH	10%

Order Code	Full Product Name	Maximum dim level
910505102303	DN571B LED40S/840 WIA-E C WH	10%
910505102306	DN571B LED24S/930H PSU-E C WH	Not applicable
910505102307	DN571B LED24S/940H PSU-E C WH	Not applicable
910505102653	DN571B LED20S/840UE PSU-E C WH	Not applicable
910505102655	DN571B LED20S/840UE PSU-E WR WH	Not applicable
910505102657	DN571B LED24S/840UE PSU-E C WH	Not applicable




Polar Wide Diagrams



**IFPS_DN570B PSE-E 1xLED12S/830 C-Polar
Normal (separate)**

**IFPS_DN570B PSE-E 1xLED20S/830 C-Polar
Normal (separate)**



**IFPS_DN570B PSE-E 1xLED20S/830 WR-Polar
Normal (separate)**



**IFPS_DN570B PSE-E 1xLED20S/840 F-Polar
Normal (separate)**

**IFPS_DN570B PSE-E 1xLED20S/840 WR-Polar
Normal (separate)**

**IFPS_DN570B PSE-E 1xLED24S/840 C-Polar
Normal (separate)**



**IFPS_DN571B PSE-E 1xLED12S/840 C-Polar
Normal (separate)**

**IFPS_DN571B PSE-E 1xLED24S/840 C-Polar
Normal (separate)**

