



# Energy saving upgrade without sacrifice

## Halogen A19

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar A-shape design. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

### Benefits

- A bright, energy saving alternative to standard incandescents.
- Halogen Soft White is ideal for warm colors and natural wood finishes.
- Halogen Natural Light provides light similar to natural daylight and brings out the true vibrant colors in your home.
- Halogen Twice the Life provides 2000 hours of rated average life.

### Features

- Provides 28% more energy savings
- Fully dimmable and Instant-on
- Mercury Free
- Rated average life of 1000-2000 hours
- Halogen complies with the EISA 2007 efficiency standards for 2012-2014

### Application

- Ideal for indoor table, floor lamps and other household fixtures.


# Halogen A19

## Versions



Single Contact Medium Screw A19  
(A19) Daylight Blue

## Dimensional drawing



Product	D	C (max)
Halogen 29A19/EV/CL 120V 12/2	2.375 in	4.13 in

