



Energy saving upgrade without sacrifice

Halogen A19

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar A-shape design. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

Benefits

- A bright, energy saving alternative to standard incandescents.
- Halogen Soft White is ideal for warm colors and natural wood finishes.
- Halogen Natural Light provides light similar to natural daylight and brings out the true vibrant colors in your home.
- Halogen Twice the Life provides 2000 hours of rated average life.

Features

- Provides 28% more energy savings
- Fully dimmable and Instant-on
- Mercury Free
- Rated average life of 1000-2000 hours
- Halogen complies with the EISA 2007 efficiency standards for 2012-2014

Application

- Ideal for indoor table, floor lamps and other household fixtures.

Halogen A19

Versions



E26, T60, Daylight-Blue



E26, A19, White




E26, A19, Clear



E26 A19 SWR

Dimensional drawing



Product	D	C (max)
Halogen EcoV MS 53W E26 120V A19(A60) SWR 6/4	2.36 in	4.17 in
Halogen 43A19/EV/CL 120V 12/2	2.375 in	4.13 in
Halogen 72A19/EV 120V 6/4	2.375 in	4.13 in
Halogen 72A19/EV 120V 12/2	2.375 in	4.13 in
Halogen 43A19/EV 120V 6/4	2.375 in	4.13 in
Halogen 43A19/EV 120V 12/2	2.375 in	4.13 in
Halogen 29A19/EV 120V 6/4	2.375 in	4.13 in
Halogen 72A19/EV/NTL 120V 12/2	2.375 in	4.13 in
Halogen 29A19/EV/CL 120V 12/2	2.375 in	4.13 in

Operating and Electrical

Voltage (Nom) 120 V

General Information

Cap-Base E26

Operating Position UNIVERSAL

Mechanical and Housing

Bulb Shape A-19 (A19)

Operating and Electrical

Order Code	Full Product Name	Lamp Wattage Rated@120V	Power (Rated) (Nom)
925620820601	Halogen 72A19/EV/NTL 120V 12/2	-	72 W
925701636303	Halogen 29A19/EV 120V 6/4	29 W	29 W
925701736301	Halogen 43A19/EV 120V 12/2	43 W	43 W
925701736304	Halogen 43A19/EV 120V 6/4	43 W	43 W
925701836301	Halogen 72A19/EV 120V 12/2	72 W	72 W
925701836303	Halogen 72A19/EV 120V 6/4	72 W	72 W

Order Code	Full Product Name	Lamp Wattage Rated@120V	Power (Rated) (Nom)
925702136301	Halogen 29A19/EV/CL 120V 12/2	29 W	29 W
925702236301	Halogen 43A19/EV/CL 120V 12/2	43 W	43 W
925716436302	Halogen EcoV MS 53W E26 120V A19(A60) SWR 6/4	53 W	53 W

General Information

Halogen A19

Order Code	Full Product Name	Life With		Rated Lifetime (Hours)
		3 Hour Per Day Use	Main Application	
925620820601	Halogen 72A19/EV/NTL 120V 12/2	-	General Lighting (G)	1250 h
925701636303	Halogen 29A19/EV 120V 6/4	-	General Lighting (G)	1000 h
925701736301	Halogen 43A19/EV 120V 12/2	-	General Lighting (G)	1000 h
925701736304	Halogen 43A19/EV 120V 6/4	-	General Lighting (G)	1000 h
925701836301	Halogen 72A19/EV 120V 12/2	-	General Lighting (G)	1000 h

Order Code	Full Product Name	Life With		Rated Lifetime (Hours)
		3 Hour Per Day Use	Main Application	
925701836303	Halogen 72A19/EV 120V 6/4	-	General Lighting (G)	1000 h
925702136301	Halogen 29A19/EV/CL 120V 12/2	-	General Lighting (G)	1000 h
925702236301	Halogen 43A19/EV/CL 120V 12/2	-	General Lighting (G)	1000 h
925716436302	Halogen EcoV MS 53W E26 120V A19(A60) SWR 6/4	0.9 a	Eco Vantage	1000 h

Light Technical

Order Code	Full Product Name	Correlated Color	Color Rendering Index	Luminous Flux Lamp @ 120V	Luminous Flux (Nom)
		Temperature (Nom)	(Nom)		
925620820601	Halogen 72A19/EV/NTL 120V 12/2	-	100	-	1200 lm
925701636303	Halogen 29A19/EV 120V 6/4	-	-	380 lm	-
925701736301	Halogen 43A19/EV 120V 12/2	-	-	750 lm	-
925701736304	Halogen 43A19/EV 120V 6/4	-	-	750 lm	-
925701836301	Halogen 72A19/EV 120V 12/2	-	-	1490 lm	-

Order Code	Full Product Name	Correlated Color	Color Rendering Index	Luminous Flux Lamp @ 120V	Luminous Flux (Nom)
		Temperature (Nom)	(Nom)		
925701836303	Halogen 72A19/EV 120V 6/4	-	-	1490 lm	-
925702136301	Halogen 29A19/EV/CL 120V 12/2	-	-	380 lm	-
925702236301	Halogen 43A19/EV/CL 120V 12/2	-	-	750 lm	-
925716436302	Halogen EcoV MS 53W E26 120V A19(A60) SWR 6/4	2840 K	100	850 lm	850 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Material
925620820601	Halogen 72A19/EV/NTL 120V 12/2	Daylight Blue	Soft Glass
925701636303	Halogen 29A19/EV 120V 6/4	White	Glass
925701736301	Halogen 43A19/EV 120V 12/2	White	Glass
925701736304	Halogen 43A19/EV 120V 6/4	White	Glass
925701836301	Halogen 72A19/EV 120V 12/2	White	Glass

Order Code	Full Product Name	Bulb Finish	Bulb Material
925701836303	Halogen 72A19/EV 120V 6/4	White	Glass
925702136301	Halogen 29A19/EV/CL 120V 12/2	Clear	Glass
925702236301	Halogen 43A19/EV/CL 120V 12/2	Clear	Glass
925716436302	Halogen EcoV MS 53W E26 120V A19(A60) SWR 6/4	Soft White Red	Glass

Approval and Application

Order Code	Full Product Name	Estimated Energy Cost Per Year
925620820601	Halogen 72A19/EV/NTL 120V 12/2	-
925701636303	Halogen 29A19/EV 120V 6/4	-

Order Code	Full Product Name	Estimated Energy Cost Per Year
925701736301	Halogen 43A19/EV 120V 12/2	-
925701736304	Halogen 43A19/EV 120V 6/4	-

Halogen A19

Order Code	Full Product Name	Estimated Energy Cost Per Year
925701836301	Halogen 72A19/EV 120V 12/2	-
925701836303	Halogen 72A19/EV 120V 6/4	-
925702136301	Halogen 29A19/EV/CL 120V 12/2	-

Order Code	Full Product Name	Estimated Energy Cost Per Year
925702236301	Halogen 43A19/EV/CL 120V 12/2	-
925716436302	Halogen EcoV MS 53W E26 120V A19(A60) SWR 6/4	6.38 \$

