



Energy saving upgrade without sacrifice

Halogen Deco

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar G25 & G16.5 globes, bent and blunt tip candles, and flames. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

Benefits

- A bright, energy saving alternative to standard incandescents.

Features

- Provides at least 28% energy savings
- Fully dimmable and Instant-on
- Mercury Free
- Rated average life of 1000-2500 hours
- Halogen complies with the EISA 2007 efficiency standards for 2012-2014

Application

- Halogen globes are great for lighting vanity mirrors and decorative fixtures.
- Halogen candles are ideal for wall sconces, chandeliers and other decorative fixtures.

Halogen Deco

Versions




40 W E26 G-25 CL



E26 G25 WH

Dimensional drawing



Product	D (max)	C (max)
Halogen 40G25/EV/W 120V 12/1 TP	80 mm	115 mm
Halogen 40G25/EV/CL 120V 12/1 TP	80 mm	115 mm

Halogen Deco

Approval and Application

Energy Efficiency Label (EEL) D

Controls and Dimming

Dimmable Yes

Operating and Electrical

Lamp Current (Nom) 0.33 A

Voltage (Nom) 120 V

Power (Rated) (Nom) 40 W

Starting Time (Nom) 0.0 s

Warm Up Time To 60% Light (Nom) instant full light

General Information

Cap-Base E26

Nominal Lifetime (Nom) 2500 h

Operating Position Universal

Rated Lifetime (Hours) 2500 h

Switching Cycle 8000X

Light Technical

Correlated Color Temperature (Nom) 2800 K

Color Rendering Index (Nom) 95

Mechanical and Housing

Bulb Shape G25

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
420844	Halogen 40G25/EV/CL 120V 12/1 TP	550 lm	550 lm
420851	Halogen 40G25/EV/W 120V 12/1 TP	500 lm	500 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Order Code	Full Product Name	Bulb Finish
420844	Halogen 40G25/EV/CL 120V 12/1 TP	Clear (CL)	420851	Halogen 40G25/EV/W 120V 12/1 TP	White (WH)

