



Energy saving upgrade without sacrifice

Halogen Deco

Halogen bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar G25 & G16.5 globes, bent and blunt tip candles, and flames. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

Benefits

- A bright, energy saving alternative to standard incandescents.

Features

- Provides at least 28% energy savings
- Fully dimmable and Instant-on
- Mercury Free
- Rated average life of 1000-2500 hours
- Halogen complies with the EISA 2007 efficiency standards for 2012-2014

Application

- Halogen globes are great for lighting vanity mirrors and decorative fixtures.
- Halogen candles are ideal for wall sconces, chandeliers and other decorative fixtures.

Halogen Deco

Versions



E12 G16.5 WH



40 W E26 G-25 CL






E26 G25 WH



25 W, 40 W E26 BA11 CL

Dimensional drawing



Product	D (max)	C (max)
Halogen 40G25/EV/CL 120V 12/1 TP	80 mm	115 mm
Halogen 40G25/EV/W 120V 12/1 TP	80 mm	115 mm

Product	D (max)	C (max)
Halogen BC40BA11/E26/EV/CL 120V 6/2 TP	36 mm	95.5 mm

Product	D (max)	C (max)
Halogen BC25G16-1/2C/EV/W 120V 6/2 TP	51 mm	76 mm

Halogen Deco

Approval and Application

Energy Efficiency Label (EEL)	D
-------------------------------	---

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Voltage (Nom)	120 V
---------------	-------

Starting Time (Nom)	0.0 s
---------------------	-------

General Information

Nominal Lifetime (Nom)	2500 h
------------------------	--------

Operating Position	UNIVERSAL
--------------------	-----------

Rated Lifetime (Hours)	2500 h
------------------------	--------

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)	Warm Up Time To 60% Light (Nom)
925707636302	Halogen BC25G16-1/2C/EV/W 120V 6/2 TP	0.21 A	25 W	instant full light
925707936301	Halogen 40G25/EV/CL 120V 12/1 TP	0.33 A	40 W	instant full light

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)	Warm Up Time To 60% Light (Nom)
925708036301	Halogen 40G25/EV/W 120V 12/1 TP	0.33 A	40 W	instant full light
925708936301	Halogen BC40BA11/E26/EV/CL 120V 6/2 TP	0.33 A	40 W	-

General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle
925707636302	Halogen BC25G16-1/2C/EV/W 120V 6/2 TP	E12	8000X
925707936301	Halogen 40G25/EV/CL 120V 12/1 TP	E26	8000X
925708036301	Halogen 40G25/EV/W 120V 12/1 TP	E26	8000X

Order Code	Full Product Name	Cap-Base	Switching Cycle
925708936301	Halogen BC40BA11/E26/EV/CL 120V 6/2 TP	E26	-

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
925707636302	Halogen BC25G16-1/2C/EV/W 120V 6/2 TP	2700 K	95	252 lm	252 lm
925707936301	Halogen 40G25/EV/CL 120V 12/1 TP	2800 K	95	550 lm	550 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
925708036301	Halogen 40G25/EV/W 120V 12/1 TP	2800 K	95	500 lm	500 lm
925708936301	Halogen BC40BA11/E26/EV/CL 120V 6/2 TP	2800 K	-	540 lm	540 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
925707636302	Halogen BC25G16-1/2C/EV/W 120V 6/2 TP	White	G16.5
925707936301	Halogen 40G25/EV/CL 120V 12/1 TP	Clear	G-25 (G25)

Order Code	Full Product Name	Bulb Finish	Bulb Shape
925708036301	Halogen 40G25/EV/W 120V 12/1 TP	White	G-25 (G25)
925708936301	Halogen BC40BA11/E26/EV/CL 120V 6/2 TP	Clear	BA11

