



# Energy saving upgrade without sacrifice

## Halogen PAR

Halogen PAR lamps reduce energy consumption without sacrificing the qualities of a traditional PAR lamp. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar PAR20, PAR30S, PAR30L, and PAR38 shapes. Use them in existing fixtures just as you would standard halogen PAR lamps.

### Benefits

### Features

### Application

### Versions



E26/50x39, PAR38



E26, PAR30L, Clear







E26, PAR20, Spot



E26, PAR30S, Flood

# Halogen PAR

## Dimensional drawing



### Product

Halogen 72PAR38/EVP/FL25 120V 12/1

Halogen 53PAR38/EVP/FL25 120V 12/1

### Product

Halogen 53PAR30S/EVP/WFL40 120V 15/1

Halogen 53PAR30S/EVP/FL25 120V 15/1

Halogen 39PAR30S/EVP/FL25 120V 15/1

### Product

Halogen 39PAR20/EVP/SP10 120V 15/1

### Product

Halogen 39PAR30L/EVP/FL25 120V 15/1

Halogen 53PAR30L/EVP/WFL40 120V 15/1

Halogen 53PAR30L/EV/FL25 120V 16/2 TP

Halogen 53PAR30L/EVP/FL25 120V 15/1

# Halogen PAR

Operating and Electrical	
Voltage (Nom)	120 V
General Information	
Operating Position	UNIVERSAL
Rated Lifetime (Hours)	1100 h
Light Technical	
Color Rendering Index (Nom)	100
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Reflector Finish	Aluminized

## Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
925706336302	Halogen 53PAR38/EVP/FL25 120V 12/1	53 W
925706536306	Halogen 72PAR38/EVP/FL25 120V 12/1	72 W
925706936304	Halogen 53PAR30L/EVP/FL25 120V 15/1	53 W
925706936305	Halogen 53PAR30L/EV/FL25 120V 16/2 TP	53 W
925707036302	Halogen 53PAR30L/EVP/WFL40 120V 15/1	53 W

Order Code	Full Product Name	Power (Rated) (Nom)
925707136303	Halogen 39PAR30L/EVP/FL25 120V 15/1	39 W
925707436302	Halogen 39PAR20/EVP/SP10 120V 15/1	39 W
925709736302	Halogen 39PAR30S/EVP/FL25 120V 15/1	39 W
925710036302	Halogen 53PAR30S/EVP/FL25 120V 15/1	53 W
925714136301	Halogen 53PAR30S/EVP/WFL40 120V 15/1	53 W

## General Information

Order Code	Full Product Name	Cap-Base	Life With 3 Hour Per Day		Main Application
			Use		
925706336302	Halogen 53PAR38/EVP/ FL25 120V 12/1	E26/50X39	-		Outdoor (OD)
925706536306	Halogen 72PAR38/EVP/ FL25 120V 12/1	E26/50X39	-		Outdoor (OD)
925706936304	Halogen 53PAR30L/EVP/ FL25 120V 15/1	E26	-		Indoor Reflector
925706936305	Halogen 53PAR30L/EV/ FL25 120V 16/2 TP	E26	-		Indoor Reflector
925707036302	Halogen 53PAR30L/EVP/ WFL40 120V 15/1	E26	2.7 a		Indoor Reflector
925707136303	Halogen 39PAR30L/EVP/ FL25 120V 15/1	E26	-		Track, Downlighting & Outdoor

Order Code	Full Product Name	Cap-Base	Life With 3 Hour Per Day		Main Application
			Use		
925707436302	Halogen 39PAR20/EVP/ SP10 120V 15/1	E26	-		Track, Downlighting & Outdoor
925709736302	Halogen 39PAR30S/EVP/ FL25 120V 15/1	E26	2.7 a		Track, Downlighting & Outdoor
925710036302	Halogen 53PAR30S/EVP/ FL25 120V 15/1	E26	-		Indoor Reflector
925714136301	Halogen 53PAR30S/EVP/ WFL40 120V 15/1	E26	-		Indoor Reflector

## Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Beam Description	Correlated Color Temperature (Nom)	Luminous Flux	Luminous Flux	Luminous Intensity
					Lamp @ 120V	(Nom)	(Nom)
925706336302	Halogen 53PAR38/EVP/FL25 120V 12/1	25 °	Flood	2900 K	-	920 lm	2000 cd
925706536306	Halogen 72PAR38/EVP/FL25 120V 12/1	25 °	Flood	2900 K	-	1350 lm	2000 cd
925706936304	Halogen 53PAR30L/EVP/FL25 120V 15/1	25 °	Flood	2900 K	920 lm	920 lm	3100 cd

## Halogen PAR

Order Code	Full Product Name	Beam Angle (Nom)	Beam Description	Correlated Color Temperature (Nom)	Luminous Flux Lamp @ 120V	Luminous Flux (Nom)	Luminous Intensity (Nom)
925706936305	Halogen 53PAR30L/EV/FL25 120V 16/2 TP	25 °	Flood	2900 K	920 lm	920 lm	3100 cd
925707036302	Halogen 53PAR30L/EVP/WFL40 120V 15/1	40 °	Wide Flood	-	-	920 lm	950 cd
925707136303	Halogen 39PAR30L/EVP/FL25 120V 15/1	25 °	Flood	2900 K	-	520 lm	2350 cd
925707436302	Halogen 39PAR20/EVP/SP10 120V 15/1	10 °	Spot	2900 K	-	500 lm	4150 cd
925709736302	Halogen 39PAR30S/EVP/FL25 120V 15/1	25 °	Flood	-	-	530 lm	2250 cd
925710036302	Halogen 53PAR30S/EVP/FL25 120V 15/1	25 °	Flood	2900 K	920 lm	920 lm	-
925714136301	Halogen 53PAR30S/EVP/WFL40 120V 15/1	40 °	Wide Flood	2900 K	920 lm	920 lm	-

### Mechanical and Housing

Order Code	Full Product Name	Bulb Shape	Order Code	Full Product Name	Bulb Shape
925706336302	Halogen 53PAR38/EVP/FL25 120V 12/1	PAR38	925707136303	Halogen 39PAR30L/EVP/FL25 120V 15/1	PAR30L
925706536306	Halogen 72PAR38/EVP/FL25 120V 12/1	PAR38	925707436302	Halogen 39PAR20/EVP/SP10 120V 15/1	PAR20
925706936304	Halogen 53PAR30L/EVP/FL25 120V 15/1	PAR30L	925709736302	Halogen 39PAR30S/EVP/FL25 120V 15/1	PAR30S
925706936305	Halogen 53PAR30L/EV/FL25 120V 16/2 TP	PAR30L	925710036302	Halogen 53PAR30S/EVP/FL25 120V 15/1	PAR30S
925707036302	Halogen 53PAR30L/EVP/WFL40 120V 15/1	PAR30L	925714136301	Halogen 53PAR30S/EVP/WFL40 120V 15/1	PAR30S

### Approval and Application

Order Code	Full Product Name	Estimated Energy Cost Per Year	Order Code	Full Product Name	Estimated Energy Cost Per Year
925706336302	Halogen 53PAR38/EVP/FL25 120V 12/1	-	925707136303	Halogen 39PAR30L/EVP/FL25 120V 15/1	-
925706536306	Halogen 72PAR38/EVP/FL25 120V 12/1	-	925707436302	Halogen 39PAR20/EVP/SP10 120V 15/1	6.02 \$
925706936304	Halogen 53PAR30L/EVP/FL25 120V 15/1	-	925709736302	Halogen 39PAR30S/EVP/FL25 120V 15/1	6.02 \$
925706936305	Halogen 53PAR30L/EV/FL25 120V 16/2 TP	-	925710036302	Halogen 53PAR30S/EVP/FL25 120V 15/1	-
925707036302	Halogen 53PAR30L/EVP/WFL40 120V 15/1	6.02 \$	925714136301	Halogen 53PAR30S/EVP/WFL40 120V 15/1	-

