



The affordable LEDbulbs solution

CorePro Plastic LEDbulbs

The CorePro LED bulb is the perfect bulb for your basic lighting needs. It provides beautiful light and dependable performance you expect from LED at an affordable price. CorePro LEDbulbs are compatible with existing fixtures with an E27 or B22 holder and are designed for retrofit replacement of incandescent bulbs. They deliver huge energy savings of 80% and provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Benefits

- This bulb is the perfect replacement for your matted incandescent bulbs
- Up to 80% energy saving
- Lower maintenance costs

Features

- Easy retrofit with existing lamp holders
- Long lifetime
- Instant full light on upon switching on
- UV- and IR-free light
- Free of mercury and hazardous materials – RoHS Compliant

Application

- Hospitality
- Residential
- Walkways

CorePro Plastic LEDbulbs

Versions



LEDbulb ND 10 75W A60 E27 827
6CT



LEDbulb ND 8 60W A60 E27 827
6CT



LEDbulb A65 E27 FR P1



LEDbulb CorePro B22 A60 5W



SPPR_LED Bulb_0029-Product
photo



SPPR LEDbulb 0031



LEDbulb CorePro 9.5-68W E27
Stick Frost 830 24D ND






LEDbulb Core EU5 combine 2



LEDbulb Core EU5 combine 1

CorePro Plastic LEDbulbs

Dimensional drawing



Product	D	C
CorePro LEDbulb ND 10-75W A60 E27 840	60 mm	110 mm
CorePro LEDbulb ND 10-75W A60 E27 865	60 mm	110 mm
CorePro LEDbulb ND 10.5-75W A60 E27 830	60 mm	110 mm
CorePro LEDbulb ND 11-75W A60 E27 827	60 mm	110 mm
CorePro LEDbulb ND 13-100W A60 E27 827	60 mm	110 mm
CorePro LEDbulb ND 13-100W A60 E27 830	60 mm	110 mm


Product	D	C
CorePro LEDbulb ND 10.5-75W A60 B22 930	60 mm	107 mm
CorePro LEDbulb ND 10.5-75W A60B22 930UK	60 mm	107 mm
CorePro LEDbulb ND 11-75W A60 B22 927 UK	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 B22 930	60 mm	105 mm
CorePro LEDbulb ND 4.9-40W A60 B22 930UK	60 mm	105 mm
CorePro LEDbulb ND 7.5-60W A60 B22 930	60 mm	105 mm
CorePro LEDbulb ND 8-60W A60 B22 927 UK	60 mm	105 mm
CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	60 mm	105 mm
CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	60 mm	105 mm

Product	D	C
CorePro LEDbulb ND 10-75W A60 E27 827	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 830	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 865	60 mm	108 mm
CorePro LEDbulb ND 10-75W A60 E27 940	60 mm	109 mm
CorePro LEDbulb ND 10-75W A60 E27 940UK	60 mm	109 mm
CorePro LEDbulb ND 10.5-75W A60 E27 930	60 mm	109 mm
CorePro LEDbulb ND 10.5-75W A60E27 930UK	60 mm	109 mm
CorePro LEDbulb ND 11-75W A60 E27 927	60 mm	109 mm
CorePro LEDbulb ND 11-75W A60 E27 927 UK	60 mm	109 mm
LEDbulb ND 10-75W A60 E27 827 2CT	60 mm	108 mm
LEDbulb ND 10-75W A60 E27 827 6CT	60 mm	108 mm
LEDbulb ND 10-75W A60 E27 840 2CT	60 mm	108 mm

Product	D	C
CorePro LEDbulb ND 13-100W A60 B22 930	60 mm	110 mm
CoreProLEDbulb ND 13-100W A60 B22 927 UK	60 mm	118 mm
CoreProLEDbulb ND 13-100W A60 B22 930 UK	60 mm	110 mm

CorePro Plastic LEDbulbs

Dimensional drawing



Product	D	C
CorePro LEDbulb ND 13-100W A60 E27 827	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 830	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 840	60 mm	120 mm
CorePro LEDbulb ND 13-100W A60 E27 865	60 mm	120 mm
LEDbulb ND 13-100W A67 E27 827 2CT	60 mm	120 mm
LEDbulb ND 13-100W A67 E27 840 2CT	60 mm	120 mm


Product	D	C
CorePro LEDbulb ND 5.5-40W A60 B22 827	60 mm	110 mm
CorePro LEDbulb ND 8-60W A60 B22 827	60 mm	110 mm

Product	D	C
CorePro LED bulb ND 7.5-60W A60 E27 865	60 mm	110 mm
CorePro LEDbulb ND 5-40W A60 E27 830	60 mm	110 mm
CorePro LEDbulb ND 5-40W A60 E27 840	60 mm	110 mm
CorePro LEDbulb ND 5.5-40W A60 E27 827	60 mm	110 mm
CorePro LEDbulb ND 7.5-60W A60 E27 830	60 mm	110 mm
CorePro LEDbulb ND 7.5-60W A60 E27 840	60 mm	110 mm
CorePro LEDbulb ND 8-60W A60 E27 827 SKT	60 mm	110 mm
CorePro LEDbulbND 8-60W A60E27 827 3CT/8	60 mm	110 mm


Product	D	C
CorePro LEDbulb ND 11-75W A60 B22 827	60 mm	110 mm
CorePro LEDbulb ND 13-100W A60 B22 827	60 mm	110 mm

CorePro Plastic LEDbulbs


Dimensional drawing



Product	D	C
CorePro LEDbulb ND 12.5-100W A60 E27 940	60 mm	110 mm
CorePro LEDbulb ND 13-100W A60 E27 930	60 mm	110 mm
CoreProLEDbulb ND 13-100W A60 E27 927	60 mm	120 mm
CoreProLEDbulb ND 13-100W A60 E27 927 UK	60 mm	120 mm
CoreProLEDbulb ND 13-100W A60 E27 930 UK	60 mm	110 mm



Product	D	C
CorePro LEDbulb ND 12.5-100W A60 E27 865	60 mm	110 mm




Product	D	C
CorePro LEDbulb ND 4.9-40W A60 B22 827	60 mm	110 mm

Product	D	C
CorePro LEDbulb ND 4.9-40W A60 E27 827	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 827	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 830	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 830	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 4.9-40W A60 E27 840	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 865	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 865	60 mm	110 mm
CorePro LEDbulb ND 4.9-40W A60 E27 930	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 930UK	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 940	60 mm	107 mm
CorePro LEDbulb ND 4.9-40W A60 E27 940UK	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 930	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 930UK	60 mm	107 mm
CorePro LEDbulb ND 7.5-60W A60 E27 940	60 mm	107 mm

CorePro Plastic LEDbulbs

Dimensional drawing

Product	D	C
CorePro LEDbulb ND 7.5-60W A60 E27 940UK	60 mm	107 mm
CorePro LEDbulb ND 8-60W A60 E27 827	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 827 SKT	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 830	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 840	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 865	60 mm	108 mm
CorePro LEDbulb ND 8-60W A60 E27 927	60 mm	107 mm
CorePro LEDbulb ND 8-60W A60 E27 927 UK	60 mm	107 mm
CoreProLEDbulb ND 4.9-40W A60 E27 927	60 mm	107 mm
CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	60 mm	107 mm
LEDbulb ND 4.9-40W A60 E27 827 2CT	60 mm	107 mm
LEDbulb ND 4.9-40W A60 E27 840 2CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 827 2CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 827 6CT	60 mm	108 mm
LEDbulb ND 8-60W A60 E27 840 2CT	60 mm	108 mm



Product	D	C
CorePro LED Stick 7.5-57W E27 3CT 830	37.2 mm	114.3 mm
CorePro LED Stick 7.5-60W E27 3CT 840	37.2 mm	114.3 mm

General Information	
Switching Cycle	50,000
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	E27	15,000 hour(s)

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	E27	15,000 hour(s)
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	E27	15,000 hour(s)
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	E27	15,000 hour(s)
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	E27	15,000 hour(s)
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	E27	15,000 hour(s)
929001233802	CorePro LEDbulb ND 5.5-40W A60 B22 827	B22	15,000 hour(s)
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	B22	15,000 hour(s)
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	B22	15,000 hour(s)
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	B22	15,000 hour(s)
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	B22	15,000 hour(s)
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	B22	15,000 hour(s)
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	B22	15,000 hour(s)
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	B22	15,000 hour(s)
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	E27	15,000 hour(s)
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	E27	15,000 hour(s)
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	E27	15,000 hour(s)
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	E27	15,000 hour(s)
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	E27	15,000 hour(s)
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	E27	15,000 hour(s)
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	E27	15,000 hour(s)
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	E27	15,000 hour(s)
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	E27	15,000 hour(s)
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	E27	15,000 hour(s)
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	E27	15,000 hour(s)
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	E27	15,000 hour(s)
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	E27	15,000 hour(s)
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	E27	15,000 hour(s)
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	E27	15,000 hour(s)
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	E27	15,000 hour(s)
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	E27	15,000 hour(s)
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	E27	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	E27	15,000 hour(s)
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	B22	15,000 hour(s)
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	B22	15,000 hour(s)
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	B22	15,000 hour(s)
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	B22	15,000 hour(s)
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	B22	15,000 hour(s)
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	B22	15,000 hour(s)
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	B22	15,000 hour(s)
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	E27	15,000 hour(s)
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	E27	15,000 hour(s)
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	E27	15,000 hour(s)
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	E27	15,000 hour(s)
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	E27	15,000 hour(s)
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	E27	15,000 hour(s)
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	E27	15,000 hour(s)
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	E27	15,000 hour(s)
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	E27	15,000 hour(s)
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	E27	15,000 hour(s)
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	E27	15,000 hour(s)
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	E27	15,000 hour(s)
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	E27	15,000 hour(s)
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	E27	15,000 hour(s)
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	E27	15,000 hour(s)
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	E27	15,000 hour(s)
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	E27	15,000 hour(s)
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	E27	15,000 hour(s)
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	E27	15,000 hour(s)
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	E27	10,000 hour(s)
929003564102	LEDbulb ND 4.9-40W A60 E27 840 2CT	E27	15,000 hour(s)
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	E27	15,000 hour(s)

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929003604208	CorePro LEDbulb ND 4.9-40W A60 E27 865	E27	15,000 hour(s)
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	E27	15,000 hour(s)
929001162332	CorePro LEDbulb ND 10.5-75W A60 E27 830	E27	15,000 hour(s)
929001163832	CorePro LEDbulb ND 10-75W A60 E27 865	E27	15,000 hour(s)
929001234402	CorePro LEDbulb ND 11-75W A60 E27 827	E27	15,000 hour(s)
929001234502	CorePro LEDbulb ND 13-100W A60 E27 827	E27	15,000 hour(s)
929001234802	CorePro LEDbulb ND 10-75W A60 E27 840	E27	15,000 hour(s)
929001235002	CorePro LEDbulb ND 13-100W A60 E27 830	E27	15,000 hour(s)
929001312502	CorePro LEDbulb ND 12.5-100W A60 E27 865	E27	15,000 hour(s)
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	B22	15,000 hour(s)
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	B22	15,000 hour(s)
929001234202	CorePro LEDbulb ND 5.5-40W A60 E27 827	E27	15,000 hour(s)
929001234602	CorePro LEDbulb ND 5-40W A60 E27 840	E27	15,000 hour(s)
929001234702	CorePro LEDbulb ND 7.5-60W A60 E27 840	E27	15,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929001304532	CorePro LEDbulb ND 5-40W A60 E27 830	E27	15,000 hour(s)
929001304732	CorePro LEDbulb ND 7.5-60W A60 E27 830	E27	15,000 hour(s)
929001304832	CorePro LED bulb ND 7.5-60W A60 E27 865	E27	15,000 hour(s)
929001901102	CorePro LED Stick 7.5-57W E27 3CT 830	E27	15,000 hour(s)
929001901202	CorePro LED Stick 7.5-60W E27 3CT 840	E27	15,000 hour(s)
929001234350	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	E27	15,000 hour(s)
929001234332	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	E27	15,000 hour(s)
929003603202	CorePro LEDbulb ND 4.9-40W A60 E27 827	E27	15,000 hour(s)
929003603302	CorePro LEDbulb ND 4.9-40W A60 E27 840	E27	15,000 hour(s)
929003603432	CorePro LEDbulb ND 4.9-40W A60 E27 830	E27	15,000 hour(s)
929003603532	CorePro LEDbulb ND 4.9-40W A60 E27 865	E27	15,000 hour(s)
929002306274	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	E27	15,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		
				(CRI)	Color Code	Luminous Flux
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	180 degree(s)	2700 K	80	827	1,055 lm
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	180 degree(s)	2700 K	90	927	1,521 lm
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	180 degree(s)	2700 K	90	927	1,521 lm
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	200 degree(s)	3000 K	90	930	1,521 lm
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	200 degree(s)	3000 K	90	930	1,521 lm
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	200 degree(s)	4000 K	90	940	1,521 lm
929001233802	CorePro LEDbulb ND 5.5-40W A60 B22 827	200 degree(s)	2700 K	80	827	470 lm
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	200 degree(s)	2700 K	80	827	806 lm
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	180 degree(s)	2700 K	90	927	1,521 lm
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	200 degree(s)	3000 K	90	930	1,521 lm
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	200 degree(s)	3000 K	90	930	1,521 lm
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	180 degree(s)	2700 K	90	927	1,055 lm
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	180 degree(s)	3000 K	90	930	1,055 lm
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	180 degree(s)	3000 K	90	930	1,055 lm
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	180 degree(s)	2700 K	80	827	806 lm
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	180 degree(s)	2700 K	80	827	1,521 lm
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	180 degree(s)	2700 K	80	827	1,521 lm
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	180 degree(s)	4000 K	80	840	1,521 lm
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	180 degree(s)	4000 K	80	840	1,521 lm
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	180 degree(s)	6500 K	80	865	1,521 lm
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	180 degree(s)	3000 K	80	830	1,521 lm
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	180 degree(s)	2700 K	80	827	1,055 lm
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	180 degree(s)	2700 K	80	827	1,055 lm
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	180 degree(s)	4000 K	80	840	1,055 lm

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		Luminous Flux
				(CRI)	Color Code	
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	180 degree(s)	4000 K	80	840	1,055 lm
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	180 degree(s)	6500 K	80	865	1,055 lm
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	180 degree(s)	2700 K	90	927	1,055 lm
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	180 degree(s)	2700 K	90	927	1,055 lm
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	180 degree(s)	3000 K	90	930	1,055 lm
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	180 degree(s)	3000 K	90	930	1,055 lm
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	180 degree(s)	4000 K	90	940	1,055 lm
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	180 degree(s)	4000 K	90	940	1,055 lm
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	180 degree(s)	3000 K	80	830	1,055 lm
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	180 degree(s)	2700 K	90	927	470 lm
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	180 degree(s)	3000 K	90	930	470 lm
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	180 degree(s)	3000 K	90	930	470 lm
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	180 degree(s)	2700 K	90	927	806 lm
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	180 degree(s)	3000 K	90	930	806 lm
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	180 degree(s)	3000 K	90	930	806 lm
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	200 degree(s)	2700 K	80	827	470 lm
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	180 degree(s)	2700 K	80	827	806 lm
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	180 degree(s)	2700 K	80	827	806 lm
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	180 degree(s)	4000 K	80	840	806 lm
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	180 degree(s)	4000 K	80	840	806 lm
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	180 degree(s)	6500 K	80	865	806 lm
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	180 degree(s)	2700 K	80	827	470 lm
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	180 degree(s)	2700 K	80	827	470 lm
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	180 degree(s)	2700 K	90	927	470 lm
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	180 degree(s)	2700 K	90	927	470 lm
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	180 degree(s)	3000 K	90	930	470 lm
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	180 degree(s)	3000 K	90	930	470 lm
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	180 degree(s)	4000 K	90	940	470 lm
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	180 degree(s)	4000 K	90	940	470 lm
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	180 degree(s)	2700 K	90	927	806 lm
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	180 degree(s)	2700 K	90	927	806 lm
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	180 degree(s)	3000 K	90	930	806 lm
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	180 degree(s)	3000 K	90	930	806 lm
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	180 degree(s)	4000 K	90	940	806 lm
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	180 degree(s)	4000 K	90	940	806 lm
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	180 degree(s)	3000 K	80	830	470 lm
929003564102	LEDbulb ND 4.9-40W A60 E27 840 2CT	180 degree(s)	4000 K	80	840	470 lm
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	180 degree(s)	4000 K	80	840	470 lm
929003604208	CorePro LEDbulb ND 4.9-40W A60 E27 865	180 degree(s)	6500 K	80	865	470 lm
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	180 degree(s)	3000 K	80	830	806 lm
929001162332	CorePro LEDbulb ND 10.5-75W A60 E27 830	200 degree(s)	3000 K	80	830	1,055 lm
929001163832	CorePro LEDbulb ND 10-75W A60 E27 865	200 degree(s)	6500 K	80	865	1,055 lm
929001234402	CorePro LEDbulb ND 11-75W A60 E27 827	200 degree(s)	2700 K	80	827	1,055 lm
929001234502	CorePro LEDbulb ND 13-100W A60 E27 827	200 degree(s)	2700 K	80	827	1,521 lm
929001234802	CorePro LEDbulb ND 10-75W A60 E27 840	200 degree(s)	4000 K	80	840	1,055 lm
929001235002	CorePro LEDbulb ND 13-100W A60 E27 830	200 degree(s)	3000 K	80	830	1,521 lm
929001312502	CorePro LEDbulb ND 12.5-100W A60 E27 865	200 degree(s)	6500 K	80	865	1,521 lm
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	200 degree(s)	2700 K	80	827	1,055 lm
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	200 degree(s)	2700 K	80	827	1,521 lm
929001234202	CorePro LEDbulb ND 5.5-40W A60 E27 827	200 degree(s)	2700 K	80	827	470 lm
929001234602	CorePro LEDbulb ND 5-40W A60 E27 840	200 degree(s)	4000 K	80	840	470 lm

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color rendering index		Color Code	Luminous Flux
				(CRI)			
929001234702	CorePro LEDbulb ND 7.5-60W A60 E27 840	200 degree(s)	4000 K	80		840	806 lm
929001304532	CorePro LEDbulb ND 5-40W A60 E27 830	200 degree(s)	3000 K	80		830	470 lm
929001304732	CorePro LEDbulb ND 7.5-60W A60 E27 830	200 degree(s)	3000 K	80		830	806 lm
929001304832	CorePro LED bulb ND 7.5-60W A60 E27 865	200 degree(s)	6500 K	80		865	806 lm
929001901102	CorePro LED Stick 7.5-57W E27 3CT 830	200 degree(s)	3000 K	80		830	750 lm
929001901202	CorePro LED Stick 7.5-60W E27 3CT 840	200 degree(s)	4000 K	80		840	806 lm
929001234350	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	200 degree(s)	2700 K	80		827	806 lm
929001234332	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	200 degree(s)	2700 K	80		827	806 lm
929003603202	CorePro LEDbulb ND 4.9-40W A60 E27 827	200 degree(s)	2700 K	80		827	470 lm
929003603302	CorePro LEDbulb ND 4.9-40W A60 E27 840	200 degree(s)	4000 K	80		840	470 lm
929003603432	CorePro LEDbulb ND 4.9-40W A60 E27 830	200 degree(s)	3000 K	80		830	470 lm
929003603532	CorePro LEDbulb ND 4.9-40W A60 E27 865	200 degree(s)	6500 K	80		865	470 lm
929002306274	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	180 degree(s)	2700 K	80		827	806 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	50 Hz	50 Hz	13 W	100 W
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	50 Hz	50 Hz	13 W	100 W
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	50 to 60 Hz	50 to 60 Hz	12.5 W	100 W
929001233802	CorePro LEDbulb ND 5.5-40W A60 B22 827	50 to 60 Hz	50 to 60 Hz	5.5 W	40 W
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	50 Hz	50 Hz	13 W	100 W
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	50 to 60 Hz	50 to 60 Hz	13 W	100 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	50 Hz	50 Hz	11 W	75 W
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	50 Hz	50 Hz	10.5 W	75 W
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	50 Hz	50 Hz	10.5 W	75 W
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	50 to 60 Hz	50 to 60 Hz	10 W	75 W

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	50 Hz	50 Hz	11 W	75 W
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	50 Hz	50 Hz	11 W	75 W
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	50 Hz	50 Hz	10.5 W	75 W
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	50 Hz	50 Hz	10.5 W	75 W
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	50 Hz	50 Hz	10 W	75 W
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	50 Hz	50 Hz	10 W	75 W
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	50 Hz	50 Hz	4.9 W	40 W
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	50 Hz	50 Hz	4.9 W	40 W
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	50 Hz	50 Hz	4.9 W	40 W
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	50 Hz	50 Hz	8 W	60 W
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	50 Hz	50 Hz	7.5 W	60 W
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	50 Hz	50 Hz	7.5 W	60 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	50 Hz	50 Hz	4.9 W	40 W
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	50 Hz	50 Hz	4.9 W	40 W
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	50 Hz	50 Hz	4.9 W	40 W
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	50 Hz	50 Hz	4.9 W	40 W
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	50 Hz	50 Hz	4.9 W	40 W
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	50 Hz	50 Hz	4.9 W	40 W
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	50 Hz	50 Hz	8 W	60 W
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	50 Hz	50 Hz	8 W	60 W
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	50 Hz	50 Hz	7.5 W	60 W

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	50 Hz	50 Hz	7.5 W	60 W
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	50 Hz	50 Hz	7.5 W	60 W
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	50 Hz	50 Hz	7.5 W	60 W
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003564102	LEDbulb ND 4.9-40W A60 E27 840 2CT	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003604208	CorePro LEDbulb ND 4.9-40W A60 E27 865	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929001162332	CorePro LEDbulb ND 10.5-75W A60 E27 830	50 to 60 Hz	50 to 60 Hz	10.5 W	75 W
929001163832	CorePro LEDbulb ND 10-75W A60 E27 865	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929001234402	CorePro LEDbulb ND 11-75W A60 E27 827	50 to 60 Hz	50 to 60 Hz	11 W	75 W
929001234502	CorePro LEDbulb ND 13-100W A60 E27 827	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929001234802	CorePro LEDbulb ND 10-75W A60 E27 840	50 to 60 Hz	50 to 60 Hz	10 W	75 W
929001235002	CorePro LEDbulb ND 13-100W A60 E27 830	50 to 60 Hz	50 to 60 Hz	13 W	100 W
929001312502	CorePro LEDbulb ND 12.5-100W A60 E27 865	50 to 60 Hz	50 to 60 Hz	12.5 W	100 W
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	50 to 60 Hz	50 to 60 Hz	11 W	75 W
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	50 to 60 Hz	50 to 60 Hz	13 W	100 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929001234202	CorePro LEDbulb ND 5.5-40W A60 E27 827	50 to 60 Hz	50 to 60 Hz	5.5 W	40 W
929001234602	CorePro LEDbulb ND 5-40W A60 E27 840	50 to 60 Hz	50 to 60 Hz	5 W	40 W
929001234702	CorePro LEDbulb ND 7.5-60W A60 E27 840	50 to 60 Hz	50 to 60 Hz	7.5 W	60 W
929001304532	CorePro LEDbulb ND 5-40W A60 E27 830	50 to 60 Hz	50 to 60 Hz	5 W	40 W
929001304732	CorePro LEDbulb ND 7.5-60W A60 E27 830	50 to 60 Hz	50 to 60 Hz	7.5 W	60 W
929001304832	CorePro LED bulb ND 7.5-60W A60 E27 865	50 to 60 Hz	50 to 60 Hz	7.5 W	60 W
929001901102	CorePro LED Stick 7.5-57W E27 3CT 830	50 to 60 Hz	50 to 60 Hz	7.5 W	57 W
929001901202	CorePro LED Stick 7.5-60W E27 3CT 840	50 to 60 Hz	50 to 60 Hz	7.5 W	60 W
929001234350	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929001234332	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	50 to 60 Hz	50 to 60 Hz	8 W	60 W
929003603202	CorePro LEDbulb ND 4.9-40W A60 E27 827	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003603302	CorePro LEDbulb ND 4.9-40W A60 E27 840	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003603432	CorePro LEDbulb ND 4.9-40W A60 E27 830	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929003603532	CorePro LEDbulb ND 4.9-40W A60 E27 865	50 to 60 Hz	50 to 60 Hz	4.9 W	40 W
929002306274	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	50 to 60 Hz	50 to 60 Hz	8 W	60 W

CorePro Plastic LEDbulbs

Temperature

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	-	95 °C
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	-20 °C to 45 °C	105 °C
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	-20 °C to 45 °C	105 °C
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	-	95 °C
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	-	95 °C
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	-	95 °C
929001233802	CorePro LEDbulb ND 5.5-40W A60 B22 827	-	75 °C
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	-	85 °C
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	-20 °C to 45 °C	105 °C
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	-	95 °C
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	-	95 °C
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	-20 °C to 45 °C	105 °C
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	-20 °C to 45 °C	105 °C
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	-20 °C to 45 °C	105 °C
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	-	95 °C
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	-20 °C to 45 °C	95 °C
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	-20 °C to 45 °C	95 °C
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	-20 °C to 45 °C	95 °C
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	-20 °C to 45 °C	95 °C
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	-20 °C to 45 °C	95 °C
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	-20 °C to 45 °C	95 °C
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	-20 °C to 45 °C	85 °C
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	-20 °C to 45 °C	95 °C
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	-20 °C to 45 °C	85 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	-20 °C to 45 °C	95 °C
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	-20 °C to 45 °C	85 °C
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	-20 °C to 45 °C	105 °C
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	-20 °C to 45 °C	105 °C
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	-20 °C to 45 °C	105 °C
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	-20 °C to 45 °C	105 °C
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	-20 °C to 45 °C	105 °C
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	-20 °C to 45 °C	105 °C
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	-20 °C to 45 °C	85 °C
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	-20 °C to 45 °C	80 °C
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	-20 °C to 45 °C	80 °C
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	-20 °C to 45 °C	80 °C
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	-20 °C to 45 °C	95 °C
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	-20 °C to 45 °C	95 °C
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	-20 °C to 45 °C	95 °C
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	-20 °C to 45 °C	80 °C
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	-20 °C to 45 °C	75 °C
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	-20 °C to 45 °C	95 °C
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	-20 °C to 45 °C	75 °C
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	-20 °C to 45 °C	95 °C
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	-20 °C to 45 °C	75 °C
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	-20 °C to 45 °C	75 °C
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	-20 °C to 45 °C	75 °C
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	-20 °C to 45 °C	80 °C

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929003542599	CoreProLEDbulb ND 4.9–40W A60 E27 927 UK	–20 °C to 45 °C	80 °C
929003542602	CorePro LEDbulb ND 4.9–40W A60 E27 930	–20 °C to 45 °C	80 °C
929003542699	CorePro LEDbulb ND 4.9–40W A60 E27 930UK	–20 °C to 45 °C	80 °C
929003542702	CorePro LEDbulb ND 4.9–40W A60 E27 940	–20 °C to 45 °C	80 °C
929003542799	CorePro LEDbulb ND 4.9–40W A60 E27 940UK	–20 °C to 45 °C	80 °C
929003543302	CorePro LEDbulb ND 8–60W A60 E27 927	–20 °C to 45 °C	95 °C
929003543385	CorePro LEDbulb ND 8–60W A60 E27 927 UK	–20 °C to 45 °C	95 °C
929003543402	CorePro LEDbulb ND 7.5–60W A60 E27 930	–20 °C to 45 °C	95 °C
929003543499	CorePro LEDbulb ND 7.5–60W A60 E27 930UK	–20 °C to 45 °C	95 °C
929003543502	CorePro LEDbulb ND 7.5–60W A60 E27 940	–20 °C to 45 °C	95 °C
929003543599	CorePro LEDbulb ND 7.5–60W A60 E27 940UK	–20 °C to 45 °C	95 °C
929003560908	CorePro LEDbulb ND 4.9–40W A60 E27 830	–20 °C to 45 °C	75 °C
929003564102	LEDbulb ND 4.9–40W A60 E27 840 2CT	–20 °C to 45 °C	–
929003564108	CorePro LEDbulb ND 4.9–40W A60 E27 840	–20 °C to 45 °C	75 °C
929003604208	CorePro LEDbulb ND 4.9–40W A60 E27 865	–20 °C to 45 °C	75 °C
929003607408	CorePro LEDbulb ND 8–60W A60 E27 830	–20 °C to 45 °C	75 °C
929001162332	CorePro LEDbulb ND 10.5–75W A60 E27 830	–	80 °C
929001163832	CorePro LEDbulb ND 10–75W A60 E27 865	–	80 °C
929001234402	CorePro LEDbulb ND 11–75W A60 E27 827	–	80 °C
929001234502	CorePro LEDbulb ND 13–100W A60 E27 827	–	85 °C

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929002306502	LEDbulb ND 10–75W A60 E27 827 6CT	A60
929003003702	CoreProLEDbulb ND 13–100W A60 E27 927	A60
929003003799	CoreProLEDbulb ND 13–100W A60 E27 927 UK	A60
929003003902	CorePro LEDbulb ND 13–100W A60 E27 930	A60
929003003999	CoreProLEDbulb ND 13–100W A60 E27 930 UK	A60
929003004102	CorePro LEDbulb ND 12.5–100W A60 E27 940	A60

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929001234802	CorePro LEDbulb ND 10–75W A60 E27 840	–	80 °C
929001235002	CorePro LEDbulb ND 13–100W A60 E27 830	–	85 °C
929001312502	CorePro LEDbulb ND 12.5–100W A60 E27 865	–	85 °C
929001234002	CorePro LEDbulb ND 11–75W A60 B22 827	–	80 °C
929001234102	CorePro LEDbulb ND 13–100W A60 B22 827	–	85 °C
929001234202	CorePro LEDbulb ND 5.5–40W A60 E27 827	–	75 °C
929001234602	CorePro LEDbulb ND 5–40W A60 E27 840	–	75 °C
929001234702	CorePro LEDbulb ND 7.5–60W A60 E27 840	–	85 °C
929001304532	CorePro LEDbulb ND 5–40W A60 E27 830	–	75 °C
929001304732	CorePro LEDbulb ND 7.5–60W A60 E27 830	–	85 °C
929001304832	CorePro LED bulb ND 7.5–60W A60 E27 865	–	85 °C
929001901102	CorePro LED Stick 7.5–57W E27 3CT 830	–20 °C to 45 °C	85 °C
929001901202	CorePro LED Stick 7.5–60W E27 3CT 840	–20 °C to 45 °C	85 °C
929001234350	CorePro LEDbulb ND 8–60W A60 E27 827 SKT	–	85 °C
929001234332	CorePro LEDbulbND 8–60W A60E27 827 3CT/8	–	85 °C
929003603202	CorePro LEDbulb ND 4.9–40W A60 E27 827	–20 °C to 45 °C	80 °C
929003603302	CorePro LEDbulb ND 4.9–40W A60 E27 840	–20 °C to 45 °C	80 °C
929003603432	CorePro LEDbulb ND 4.9–40W A60 E27 830	–20 °C to 45 °C	80 °C
929003603532	CorePro LEDbulb ND 4.9–40W A60 E27 865	–20 °C to 45 °C	80 °C
929002306274	CorePro LEDbulb ND 8–60W A60 E27 827 SKT	–20 °C to 45 °C	75 °C

Order Code	Full Product Name	Bulb Shape
929001233802	CorePro LEDbulb ND 5.5–40W A60 B22 827	A60
929001233902	CorePro LEDbulb ND 8–60W A60 B22 827	A60
929003003899	CoreProLEDbulb ND 13–100W A60 B22 927 UK	A60
929003004002	CorePro LEDbulb ND 13–100W A60 B22 930	A60
929003004099	CoreProLEDbulb ND 13–100W A60 B22 930 UK	A60
929003544599	CorePro LEDbulb ND 11–75W A60 B22 927 UK	A60

CorePro Plastic LEDbulbs

Order Code	Full Product Name	Bulb Shape
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	A60
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	A60
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	A60
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	A60
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	A67
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	A60
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	A67
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	A60
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	A60
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	A60
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	A60
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	A60
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	A60
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	A60
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	A60
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	A60
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	A60
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	A60
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	A60
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	A60
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	A60
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	A60
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	A60
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	A60
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	A60
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	A60
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	A60
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	A60
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	A60
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	A60
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	A60
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	A60
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	A60
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	A60
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	A60
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	A60
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	A60
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	A60

Order Code	Full Product Name	Bulb Shape
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	A60
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	A60
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	A60
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	A60
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	A60
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	A60
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	A60
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	A60
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	A60
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	A60
929003564102	LEDbulb ND 4.9-40W A60 E27 840 2CT	A60
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	A60
929003604208	CorePro LEDbulb ND 4.9-40W A60 E27 865	A60
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	A60
929001162332	CorePro LEDbulb ND 10.5-75W A60 E27 830	A60
929001163832	CorePro LEDbulb ND 10-75W A60 E27 865	A60
929001234402	CorePro LEDbulb ND 11-75W A60 E27 827	A60
929001234502	CorePro LEDbulb ND 13-100W A60 E27 827	A60
929001234802	CorePro LEDbulb ND 10-75W A60 E27 840	A60
929001235002	CorePro LEDbulb ND 13-100W A60 E27 830	A60
929001312502	CorePro LEDbulb ND 12.5-100W A60 E27 865	A60
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	A60
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	A60
929001234202	CorePro LEDbulb ND 5.5-40W A60 E27 827	A60
929001234602	CorePro LEDbulb ND 5-40W A60 E27 840	A60
929001234702	CorePro LEDbulb ND 7.5-60W A60 E27 840	A60
929001304532	CorePro LEDbulb ND 5-40W A60 E27 830	A60
929001304732	CorePro LEDbulb ND 7.5-60W A60 E27 830	A60
929001304832	CorePro LED bulb ND 7.5-60W A60 E27 865	A60
929001901102	CorePro LED Stick 7.5-57W E27 3CT 830	Stick
929001901202	CorePro LED Stick 7.5-60W E27 3CT 840	Stick
929001234350	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	A60
929001234332	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	A60
929003603202	CorePro LEDbulb ND 4.9-40W A60 E27 827	A60
929003603302	CorePro LEDbulb ND 4.9-40W A60 E27 840	A60
929003603432	CorePro LEDbulb ND 4.9-40W A60 E27 830	A60
929003603532	CorePro LEDbulb ND 4.9-40W A60 E27 865	A60
929002306274	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	A60

Approval and Application


Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002306502	LEDbulb ND 10-75W A60 E27 827 6CT	10 kWh
929003003702	CoreProLEDbulb ND 13-100W A60 E27 927	13 kWh
929003003799	CoreProLEDbulb ND 13-100W A60 E27 927 UK	13 kWh
929003003902	CorePro LEDbulb ND 13-100W A60 E27 930	13 kWh
929003003999	CoreProLEDbulb ND 13-100W A60 E27 930 UK	13 kWh
929003004102	CorePro LEDbulb ND 12.5-100W A60 E27 940	13 kWh
929001233802	CorePro LEDbulb ND 5.5-40W A60 B22 827	6 kWh
929001233902	CorePro LEDbulb ND 8-60W A60 B22 827	8 kWh
929003003899	CoreProLEDbulb ND 13-100W A60 B22 927 UK	13 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003004002	CorePro LEDbulb ND 13-100W A60 B22 930	13 kWh
929003004099	CoreProLEDbulb ND 13-100W A60 B22 930 UK	13 kWh
929003544599	CorePro LEDbulb ND 11-75W A60 B22 927 UK	11 kWh
929003544602	CorePro LEDbulb ND 10.5-75W A60 B22 930	11 kWh
929003544699	CorePro LEDbulb ND 10.5-75W A60B22 930UK	11 kWh
929002306202	LEDbulb ND 8-60W A60 E27 827 6CT	8 kWh
929002306808	CorePro LEDbulb ND 13-100W A60 E27 827	13 kWh











CorePro Plastic LEDbulbs

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002306862	LEDbulb ND 13-100W A67 E27 827 2CT	13 kWh
929002306908	CorePro LEDbulb ND 13-100W A60 E27 840	13 kWh
929002306962	LEDbulb ND 13-100W A67 E27 840 2CT	13 kWh
929002307008	CorePro LEDbulb ND 13-100W A60 E27 865	13 kWh
929003607608	CorePro LEDbulb ND 13-100W A60 E27 830	13 kWh
929002306508	CorePro LEDbulb ND 10-75W A60 E27 827	10 kWh
929002306562	LEDbulb ND 10-75W A60 E27 827 2CT	10 kWh
929002306608	CorePro LEDbulb ND 10-75W A60 E27 840	10 kWh
929002306662	LEDbulb ND 10-75W A60 E27 840 2CT	10 kWh
929002306708	CorePro LEDbulb ND 10-75W A60 E27 865	10 kWh
929003544102	CorePro LEDbulb ND 11-75W A60 E27 927	11 kWh
929003544199	CorePro LEDbulb ND 11-75W A60 E27 927 UK	11 kWh
929003544202	CorePro LEDbulb ND 10.5-75W A60 E27 930	11 kWh
929003544299	CorePro LEDbulb ND 10.5-75W A60E27 930UK	11 kWh
929003544302	CorePro LEDbulb ND 10-75W A60 E27 940	10 kWh
929003544399	CorePro LEDbulb ND 10-75W A60 E27 940UK	10 kWh
929003607508	CorePro LEDbulb ND 10-75W A60 E27 830	10 kWh
929003542999	CoreProLEDbulb ND 4.9-40W A60 B22 927 UK	5 kWh
929003543002	CorePro LEDbulb ND 4.9-40W A60 B22 930	5 kWh
929003543099	CorePro LEDbulb ND 4.9-40W A60 B22 930UK	5 kWh
929003543799	CorePro LEDbulb ND 8-60W A60 B22 927 UK	8 kWh
929003543802	CorePro LEDbulb ND 7.5-60W A60 B22 930	8 kWh
929003543899	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	8 kWh
929003603102	CorePro LEDbulb ND 4.9-40W A60 B22 827	5 kWh
929002306208	CorePro LEDbulb ND 8-60W A60 E27 827	8 kWh
929002306262	LEDbulb ND 8-60W A60 E27 827 2CT	8 kWh
929002306308	CorePro LEDbulb ND 8-60W A60 E27 840	8 kWh
929002306362	LEDbulb ND 8-60W A60 E27 840 2CT	8 kWh
929002306408	CorePro LEDbulb ND 8-60W A60 E27 865	8 kWh
929003540202	LEDbulb ND 4.9-40W A60 E27 827 2CT	5 kWh
929003540208	CorePro LEDbulb ND 4.9-40W A60 E27 827	5 kWh
929003542502	CoreProLEDbulb ND 4.9-40W A60 E27 927	5 kWh
929003542599	CoreProLEDbulb ND 4.9-40W A60 E27 927 UK	5 kWh
929003542602	CorePro LEDbulb ND 4.9-40W A60 E27 930	5 kWh
929003542699	CorePro LEDbulb ND 4.9-40W A60 E27 930UK	5 kWh
929003542702	CorePro LEDbulb ND 4.9-40W A60 E27 940	5 kWh
929003542799	CorePro LEDbulb ND 4.9-40W A60 E27 940UK	5 kWh
929003543302	CorePro LEDbulb ND 8-60W A60 E27 927	8 kWh
929003543385	CorePro LEDbulb ND 8-60W A60 E27 927 UK	8 kWh
929003543402	CorePro LEDbulb ND 7.5-60W A60 E27 930	8 kWh
929003543499	CorePro LEDbulb ND 7.5-60W A60 E27 930UK	8 kWh
929003543502	CorePro LEDbulb ND 7.5-60W A60 E27 940	8 kWh
929003543599	CorePro LEDbulb ND 7.5-60W A60 E27 940UK	8 kWh
929003560908	CorePro LEDbulb ND 4.9-40W A60 E27 830	5 kWh
929003564102	LEDbulb ND 4.9-40W A60 E27 840 2CT	5 kWh
929003564108	CorePro LEDbulb ND 4.9-40W A60 E27 840	5 kWh
929003604208	CorePro LEDbulb ND 4.9-40W A60 E27 865	5 kWh











Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003607408	CorePro LEDbulb ND 8-60W A60 E27 830	8 kWh
929001162332	CorePro LEDbulb ND 10.5-75W A60 E27 830	11 kWh
929001163832	CorePro LEDbulb ND 10-75W A60 E27 865	10 kWh
929001234402	CorePro LEDbulb ND 11-75W A60 E27 827	11 kWh
929001234502	CorePro LEDbulb ND 13-100W A60 E27 827	13 kWh
929001234802	CorePro LEDbulb ND 10-75W A60 E27 840	10 kWh
929001235002	CorePro LEDbulb ND 13-100W A60 E27 830	13 kWh
929001312502	CorePro LEDbulb ND 12.5-100W A60 E27 865	13 kWh
929001234002	CorePro LEDbulb ND 11-75W A60 B22 827	11 kWh
929001234102	CorePro LEDbulb ND 13-100W A60 B22 827	13 kWh
929001234202	CorePro LEDbulb ND 5.5-40W A60 E27 827	6 kWh
929001234602	CorePro LEDbulb ND 5-40W A60 E27 840	5 kWh
929001234702	CorePro LEDbulb ND 7.5-60W A60 E27 840	8 kWh
929001304532	CorePro LEDbulb ND 5-40W A60 E27 830	5 kWh
929001304732	CorePro LEDbulb ND 7.5-60W A60 E27 830	8 kWh
929001304832	CorePro LED bulb ND 7.5-60W A60 E27 865	8 kWh
929001901102	CorePro LED Stick 7.5-57W E27 3CT 830	8 kWh
929001901202	CorePro LED Stick 7.5-60W E27 3CT 840	8 kWh
929001234350	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	8 kWh
929001234332	CorePro LEDbulbND 8-60W A60E27 827 3CT/8	8 kWh
929003603202	CorePro LEDbulb ND 4.9-40W A60 E27 827	5 kWh
929003603302	CorePro LEDbulb ND 4.9-40W A60 E27 840	5 kWh
929003603432	CorePro LEDbulb ND 4.9-40W A60 E27 830	5 kWh
929003603532	CorePro LEDbulb ND 4.9-40W A60 E27 865	5 kWh
929002306274	CorePro LEDbulb ND 8-60W A60 E27 827 SKT	8 kWh





CorePro Plastic LEDbulbs













CorePro Plastic LEDbulbs



CorePro Plastic LEDbulbs



CorePro Plastic LEDbulbs



CorePro Plastic LEDbulbs

