



A flexible and affordable retail toolbox

GreenSpace Accent Fixed

With the GreenSpace Accent family, retailers and building operators can now make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Fixed's regular cut-out and specific lumen packages make retrofit installation quick and easy. Completing the ideal lighting plan for your store, GreenSpace Accent Fixed offers flexible general lighting supported by a choice of beams and special light flavors and LED recipes that enable you to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to find out more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

Benefits

- High lumen output from very compact, low-height luminaire
- Low glare thanks to slightly recessed reflector
- Wide application coverage

Features

- Excellent quality of light enabled by Philips PerfectAccent optics
- High energy efficiency
- Clean and robust design
- One-to-one CDM replacement

Application

- Retail stores, especially food and fashion stores


Specifications

GreenSpace Accent Fixed

| | |
|---|---|
| Type | RS340B |
| Ceiling type | Exposed- and symmetrical concealed T-bar ceiling and plaster (board) ceiling |
| Light source | Non-replaceable LED module |
| Power | 1700 lm - 15 W, 2700 lm - 27 W, 3900 lm - 34.5 W at 3000 K 1900 lm - 26 W; 2600 lm - 39 W at Fresh Food Meat (FMT) |
| Beam angle | MB (24°) WB (36°) VWB (60°) |
| Luminous flux | 2800, 4000 lm at 3000 K 1900, 2600 lm at FMT 2700 lm at Fresh Food Champagne (CH) |
| Correlated Color | 2500 K (for CH) |
| Temperature | 2700, 3000 K (for 830, PremiumWhite PW9, CrispWhite CRW, FMT) 4000 K |
| Color Rendering Index | 80 for 827, 830, 840, FMT, CH 90 for PW9 >95 for CRW |
| Lumen maintenance at median useful life* | L80 |
| 50000 h | |

| | |
|--|--|
| Control gear failure rate at median useful life | 5% |
| 50000 h | |
| Performance Ambient | +25 °C |
| Temperature Tq | |
| Operating temperature range | +10 to +40 °C |
| Driver | Separate |
| Mains voltage | 230 or 240 V / 50 - 60 Hz |
| Dimming | Non-dimmable (PSU-E) DALI-dimmable (PSD-E) |
| Material | Housing: die-cast aluminum |
| Color | White (WH, RAL9003), Black (BK, RAL 9004), Silver (SI, RAL9006) |
| Optical cover | PMMA, clear Push-in connector with pull relief (PIP), 3-pole Wieland/Adels plug (CW3), 3-pole Wieland/Adels plug with lock (CW-L) |
| Installation | Fixation by means of spring fasteners Through-wiring is possible |

Versions




GreenSpace Accent Fixed




GreenSpace Accent elbow RS342B downlight

Product details



GreenSpace_Accent_Fixed-RS340B-DP01.tif




GreenSpace_Accent_Fixed-RS340B-DP02.tif

GreenSpace Accent Fixed


Product details




GreenSpace_Accent_Fixed-RS340B-DPO3.tif



IPDP_RS340Bi_0001-Detail photo



IPDP_RS340Bi_0007-Detail photo



IPDP_RS340Bi_0017-Detail photo

GreenSpace Accent Fixed

Application Conditions

| | |
|-------------------------------|-----|
| Suitable for random switching | Yes |
|-------------------------------|-----|

Approval and Application

| | |
|------------------------------|------|
| Mech. impact protection code | IK02 |
| Ingress protection code | IP20 |

General Information

| | |
|----------------------------|---|
| Beam angle of light source | 120 ° |
| CE mark | CE mark |
| Protection class IEC | Safety class II |
| Driver included | Yes |
| ENEC mark | ENEC mark |
| Flammability mark | For mounting on normally flammable surfaces |
| Glow-wire test | Temperature 650 °C, duration 30 s |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Service tag | Yes |

Initial Performance (IEC Compliant)

| | |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

Mechanical and Housing

| | |
|-------|-------|
| Color | White |
|-------|-------|

Application Conditions

| Order Code | Full Product Name | Ambient temperature range | Maximum dim level |
|--------------|--|---------------------------|-------------------|
| 910500459720 | RS340B LED19S/FMT PSU-E WB WH | +10 to +25 °C | - |
| 910500459721 | RS340B LED27S/FMT PSU-E MB WH | +10 to +25 °C | - |
| 910500459722 | RS340B LED27S/830 PSU-E WB WH | +10 to +25 °C | - |
| 910500459723 | RS340B LED27S/840 PSU-E WB WH | +10 to +25 °C | - |
| 910500459727 | RS340B LED27S/PW930 PSU-E WB WH | +10 to +25 °C | - |
| 910500459728 | RS340B LED27S/PW930 PSU-E MB WH CW-L | +10 to +25 °C | - |
| 910500459729 | RS340B LED27S/PW930 PSD-VLC-E MB WH CW-L | +10 to +25 °C | 1% |
| 910500459730 | RS340B LED27S/827 PSD-VLC-E MB WH CW-L | +10 to +25 °C | 1% |
| 910500459731 | RS340B LED27S/830 PSD-VLC-E MB WH CW-L | +10 to +25 °C | 1% |
| 910500459733 | RS340B LED27S/PW930 PSU-E WB WH CW-L | +10 to +25 °C | - |
| 910500459734 | RS340B LED27S/830 PSU-E VWB WH | +10 to +25 °C | - |
| 910500459735 | RS340B LED27S/830 PSD-VLC-E VWB WH | +10 to +25 °C | 1% |
| 910500459736 | RS340B LED39S/830 PSU-E WB WH | +10 to +25 °C | - |
| 910500459737 | RS340B LED39S/827 PSU-E WB WH | +10 to +25 °C | - |
| 910500459738 | RS340B LED39S/840 PSU-E WB WH | +10 to +25 °C | - |
| 910500459739 | RS340B LED39S/840 PSD-VLC-E WB WH | +10 to +25 °C | 1% |
| 910500459740 | RS340B LED39S/PW930 PSU-E WB WH | +10 to +25 °C | - |
| 910500459741 | RS340B LED39S/PW930 PSU-E WB WH CW-L | +10 to +25 °C | - |
| 910500459742 | RS340B LED39S/PW930 PSD-VLC-E WB WH CW-L | +10 to +25 °C | 1% |
| 910500459743 | RS340B LED39S/830 PSU-E WB WH CW-L | +10 to +25 °C | - |
| 910500459744 | RS340B LED39S/830 PSU-E VWB WH | +10 to +25 °C | - |
| 910500459745 | RS340B LED39S/830 PSD-VLC-E VWB WH | +10 to +25 °C | 1% |
| 910500465313 | RS340B LED27S/CH PSU-E WB WH | +10 to +25 °C | - |
| 910500465314 | RS342B LED27S/CH PSU-E WB WH | +10 to +40 °C | - |

Controls and Dimming

| Order Code | Full Product Name | Dimmable | Order Code | Full Product Name | Dimmable |
|--------------|--|----------|--------------|--|----------|
| 910500459720 | RS340B LED19S/FMT PSU-E WB WH | No | 910500459736 | RS340B LED39S/830 PSU-E WB WH | No |
| 910500459721 | RS340B LED27S/FMT PSU-E MB WH | No | 910500459737 | RS340B LED39S/827 PSU-E WB WH | No |
| 910500459722 | RS340B LED27S/830 PSU-E WB WH | No | 910500459738 | RS340B LED39S/840 PSU-E WB WH | No |
| 910500459723 | RS340B LED27S/840 PSU-E WB WH | No | 910500459739 | RS340B LED39S/840 PSD-VLC-E WB WH | Yes |
| 910500459727 | RS340B LED27S/PW930 PSU-E WB WH | No | 910500459740 | RS340B LED39S/PW930 PSU-E WB WH | No |
| 910500459728 | RS340B LED27S/PW930 PSU-E MB WH CW-L | No | 910500459741 | RS340B LED39S/PW930 PSU-E WB WH CW-L | No |
| 910500459729 | RS340B LED27S/PW930 PSD-VLC-E MB WH CW-L | Yes | 910500459742 | RS340B LED39S/PW930 PSD-VLC-E WB WH CW-L | Yes |
| 910500459730 | RS340B LED27S/827 PSD-VLC-E MB WH CW-L | Yes | 910500459743 | RS340B LED39S/830 PSU-E WB WH CW-L | No |
| 910500459731 | RS340B LED27S/830 PSD-VLC-E MB WH CW-L | Yes | 910500459744 | RS340B LED39S/830 PSU-E VWB WH | No |
| 910500459733 | RS340B LED27S/PW930 PSU-E WB WH CW-L | No | 910500459745 | RS340B LED39S/830 PSD-VLC-E VWB WH | Yes |
| 910500459734 | RS340B LED27S/830 PSU-E VWB WH | No | 910500465313 | RS340B LED27S/CH PSU-E WB WH | No |
| 910500459735 | RS340B LED27S/830 PSD-VLC-E VWB WH | Yes | 910500465314 | RS342B LED27S/CH PSU-E WB WH | No |

Operating and Electrical

| Order Code | Full Product Name | Input Voltage | Order Code | Full Product Name | Input Voltage |
|--------------|-------------------------------|---------------|--------------|--------------------------------------|---------------|
| 910500459720 | RS340B LED19S/FMT PSU-E WB WH | 220 to 240 V | 910500459723 | RS340B LED27S/840 PSU-E WB WH | 220 to 240 V |
| 910500459721 | RS340B LED27S/FMT PSU-E MB WH | 220 to 240 V | 910500459727 | RS340B LED27S/PW930 PSU-E WB WH | 220 to 240 V |
| 910500459722 | RS340B LED27S/830 PSU-E WB WH | 220 to 240 V | 910500459728 | RS340B LED27S/PW930 PSU-E MB WH CW-L | 220 to 240 V |

GreenSpace Accent Fixed

| Order Code | Full Product Name | Input Voltage |
|--------------|--|---------------|
| 910500459729 | RS340B LED27S/PW930 PSD-VLC-E MB WH CW-L | 220 to 240 V |
| 910500459730 | RS340B LED27S/827 PSD-VLC-E MB WH CW-L | 220 to 240 V |
| 910500459731 | RS340B LED27S/830 PSD-VLC-E MB WH CW-L | 220 to 240 V |
| 910500459733 | RS340B LED27S/PW930 PSU-E WB WH CW-L | 220 to 240 V |
| 910500459734 | RS340B LED27S/830 PSU-E VWB WH | 220 to 240 V |
| 910500459735 | RS340B LED27S/830 PSD-VLC-E VWB WH | 220 to 240 V |
| 910500459736 | RS340B LED39S/830 PSU-E WB WH | 220 to 240 V |
| 910500459737 | RS340B LED39S/827 PSU-E WB WH | 220 to 240 V |
| 910500459738 | RS340B LED39S/840 PSU-E WB WH | 220 to 240 V |

| Order Code | Full Product Name | Input Voltage |
|--------------|--|---------------|
| 910500459739 | RS340B LED39S/840 PSD-VLC-E WB WH | 220 to 240 V |
| 910500459740 | RS340B LED39S/PW930 PSU-E WB WH | 220 to 240 V |
| 910500459741 | RS340B LED39S/PW930 PSU-E WB WH CW-L | 220 to 240 V |
| 910500459742 | RS340B LED39S/PW930 PSD-VLC-E WB WH CW-L | 220 to 240 V |
| 910500459743 | RS340B LED39S/830 PSU-E WB WH CW-L | 220 to 240 V |
| 910500459744 | RS340B LED39S/830 PSU-E VWB WH | 220 to 240 V |
| 910500459745 | RS340B LED39S/830 PSD-VLC-E VWB WH | 220 to 240 V |
| 910500465313 | RS340B LED27S/CH PSU-E WB WH | 220-240 V |
| 910500465314 | RS342B LED27S/CH PSU-E WB WH | 220-240 V |

General Information (1/2)

| Order Code | Full Product Name | Cap-Base | Optical cover/lens | | Lamp family | |
|--------------|--|----------|--------------------|------|-------------|---|
| | | | type | Gear | code | |
| 910500459720 | RS340B LED19S/FMT PSU-E WB WH | - | - | - | - | - |
| 910500459721 | RS340B LED27S/FMT PSU-E MB WH | - | - | - | - | - |
| 910500459722 | RS340B LED27S/830 PSU-E WB WH | - | - | - | - | - |
| 910500459723 | RS340B LED27S/840 PSU-E WB WH | - | - | - | - | - |
| 910500459727 | RS340B LED27S/PW930 PSU-E WB WH | - | - | - | - | - |
| 910500459728 | RS340B LED27S/PW930 PSU-E MB WH CW-L | - | - | - | - | - |
| 910500459729 | RS340B LED27S/PW930 PSD-VLC-E MB WH CW-L | - | - | - | - | - |
| 910500459730 | RS340B LED27S/827 PSD-VLC-E MB WH CW-L | - | - | - | - | - |
| 910500459731 | RS340B LED27S/830 PSD-VLC-E MB WH CW-L | - | - | - | - | - |
| 910500459733 | RS340B LED27S/PW930 PSU-E WB WH CW-L | - | - | - | - | - |
| 910500459734 | RS340B LED27S/830 PSU-E VWB WH | - | - | - | - | - |
| 910500459735 | RS340B LED27S/830 PSD-VLC-E VWB WH | - | - | - | - | - |
| 910500459736 | RS340B LED39S/830 PSU-E WB WH | - | - | - | - | - |

| Order Code | Full Product Name | Cap-Base | Optical cover/lens | | Lamp family | |
|--------------|--|----------|------------------------------|------|-------------|---|
| | | | type | Gear | code | |
| 910500459737 | RS340B LED39S/827 PSU-E WB WH | - | - | - | - | - |
| 910500459738 | RS340B LED39S/840 PSU-E WB WH | - | - | - | - | - |
| 910500459739 | RS340B LED39S/840 PSD-VLC-E WB WH | - | - | - | - | - |
| 910500459740 | RS340B LED39S/PW930 PSU-E WB WH | - | - | - | - | - |
| 910500459741 | RS340B LED39S/PW930 PSU-E WB WH CW-L | - | - | - | - | - |
| 910500459742 | RS340B LED39S/PW930 PSD-VLC-E WB WH CW-L | - | - | - | - | - |
| 910500459743 | RS340B LED39S/830 PSU-E WB WH CW-L | - | - | - | - | - |
| 910500459744 | RS340B LED39S/830 PSU-E VWB WH | - | - | - | - | - |
| 910500459745 | RS340B LED39S/830 PSD-VLC-E VWB WH | - | - | - | - | - |
| 910500465313 | RS340B LED27S/CH PSU-E WB WH | - | - | - | - | - |
| 910500465314 | RS342B LED27S/CH PSU-E WB WH | - | Acrylic bowl/ cover clear | - | LED27S | - |

General Information (2/2)

| Order Code | Full Product Name | Number of light sources | Optic type | Product Family | |
|--------------|-------------------------------|-------------------------|-------------|----------------|---------|
| | | | | Code | UL mark |
| 910500459720 | RS340B LED19S/FMT PSU-E WB WH | - | Wide beam | RS340B | - |
| 910500459721 | RS340B LED27S/FMT PSU-E MB WH | - | Medium beam | RS340B | - |

| Order Code | Full Product Name | Number of light sources | Optic type | Product Family | |
|--------------|-------------------------------|-------------------------|------------|----------------|---------|
| | | | | Code | UL mark |
| 910500459722 | RS340B LED27S/830 PSU-E WB WH | - | Wide beam | RS340B | - |
| 910500459723 | RS340B LED27S/840 PSU-E WB WH | - | Wide beam | RS340B | - |

GreenSpace Accent Fixed

| Order Code | Full Product Name | Number of light | | Product Family UL | |
|--------------|--|-----------------|----------------|-------------------|------|
| | | sources | Optic type | Code | mark |
| 910500459727 | RS340B LED27S/PW930 PSU-E WB WH | - | Wide beam | RS340B | - |
| 910500459728 | RS340B LED27S/PW930 PSU-E MB WH CW-L | - | Medium beam | RS340B | - |
| 910500459729 | RS340B LED27S/PW930 PSD-VLC-E MB WH CW-L | - | Medium beam | RS340B | - |
| 910500459730 | RS340B LED27S/827 PSD-VLC-E MB WH CW-L | - | Medium beam | RS340B | - |
| 910500459731 | RS340B LED27S/830 PSD-VLC-E MB WH CW-L | - | Medium beam | RS340B | - |
| 910500459733 | RS340B LED27S/PW930 PSU-E WB WH CW-L | - | Wide beam | RS340B | - |
| 910500459734 | RS340B LED27S/830 PSU-E VWB WH | - | Very wide beam | RS340B | - |
| 910500459735 | RS340B LED27S/830 PSD-VLC-E VWB WH | - | Very wide beam | RS340B | - |
| 910500459736 | RS340B LED39S/830 PSU-E WB WH | - | Wide beam | RS340B | - |
| 910500459737 | RS340B LED39S/827 PSU-E WB WH | - | Wide beam | RS340B | - |

| Order Code | Full Product Name | Number of light | | Product Family UL | |
|--------------|--|-----------------|----------------|-------------------|------|
| | | sources | Optic type | Code | mark |
| 910500459738 | RS340B LED39S/840 PSU-E WB WH | - | Wide beam | RS340B | - |
| 910500459739 | RS340B LED39S/840 PSD-VLC-E WB WH | - | Wide beam | RS340B | - |
| 910500459740 | RS340B LED39S/PW930 PSU-E WB WH | - | Wide beam | RS340B | - |
| 910500459741 | RS340B LED39S/PW930 PSU-E WB WH CW-L | - | Wide beam | RS340B | - |
| 910500459742 | RS340B LED39S/PW930 PSD-VLC-E WB WH CW-L | - | Wide beam | RS340B | - |
| 910500459743 | RS340B LED39S/830 PSU-E WB WH CW-L | - | Wide beam | RS340B | - |
| 910500459744 | RS340B LED39S/830 PSU-E VWB WH | - | Very wide beam | RS340B | - |
| 910500459745 | RS340B LED39S/830 PSD-VLC-E VWB WH | - | Very wide beam | RS340B | - |
| 910500465313 | RS340B LED27S/CH PSU-E WB WH | - | Wide beam | RS340B | - |
| 910500465314 | RS342B LED27S/CH PSU-E WB WH | 1 pc | Wide beam | RS342B | - |

Initial Performance (IEC Compliant) (1/2)

| Order Code | Full Product Name | Init. Corr. Color Temperature | Init. Color Rendering Initial LED luminaire efficacy | | |
|--------------|-------------------------------|-------------------------------|--|--------------------|--------------------------------|
| | | | Initial chromaticity | Index | Initial LED luminaire efficacy |
| 910500459720 | RS340B LED19S/FMT PSU-E WB WH | (0.40, 0.33) 3000 K | ≥80 | 70.37037037037037 | lm/W |
| 910500459721 | RS340B LED27S/FMT PSU-E MB WH | (0.40, 0.33) 3000 K | ≥80 | 68.35443037974683 | lm/W |
| 910500459722 | RS340B LED27S/830 PSU-E WB WH | (0.43, 0.40) 3000 K | ≥80 | 114.8936170212766 | lm/W |
| 910500459723 | RS340B LED27S/840 PSU-E WB WH | (0.38, 0.38) 4000 K | ≥80 | 119.14893617021276 | lm/W |

| Order Code | Full Product Name | Init. Corr. Color Temperature | Init. Color Rendering Initial LED luminaire efficacy | | |
|--------------|--|-------------------------------|--|--------------------|--------------------------------|
| | | | Initial chromaticity | Index | Initial LED luminaire efficacy |
| 910500459727 | RS340B LED27S/PW930 PSU-E WB WH | (0.42, 0.39) 3000 K | ≥90 | 105.88235294117646 | lm/W |
| 910500459728 | RS340B LED27S/PW930 PSU-E MB WH | (0.42, 0.39) 3000 K | ≥90 | 105.88235294117646 | lm/W |
| 910500459729 | RS340B LED27S/PW930 PSD-VLC-E MB WH CW-L | (0.42, 0.39) 3000 K | ≥90 | 105.88235294117646 | lm/W |
| 910500459730 | RS340B LED27S/827 | (0.46, 0.41) 2700 K | ≥80 | 110.63829787234043 | lm/W |

GreenSpace Accent Fixed

| Order Code | Full Product | | Init. Corr. | Init. Color | |
|--------------|--|------------------------|-------------------|-----------------|--------------------------------|
| | Name | Initial chromaticity | Color Temperature | Rendering Index | Initial LED luminaire efficacy |
| | PSD- VLC-E MB WH CW-L | | | | |
| 910500459731 | RS340B LED27S/ 830 | (0.43, 0.40) | 3000 K | ≥80 | 114.8936170212766 lm/W |
| | PSD- VLC-E MB WH CW-L | SDCM<3 | | | |
| 910500459733 | RS340B LED27S/ PW930 PSU-E WB WH CW-L | (0.42, 0.39) | 3000 K | ≥90 | 105.88235294117646 lm/W |
| | PSD- VLC-E WB WH CW-L | SDCM<3 | | | |
| 910500459734 | RS340B LED27S/ 830 PSU-E VWB WH | (0.43, 0.40) | 3000 K | ≥80 | 114.8936170212766 lm/W |
| | PSD- VLC-E VWB WH | SDCM<3 | | | |
| 910500459735 | RS340B LED27S/ 830 PSD- VLC-E VWB WH | (0.43, 0.40) | 3000 K | ≥80 | 114.8936170212766 lm/W |
| | PSD- VLC-E VWB WH | SDCM<3 | | | |
| 910500459736 | RS340B LED39S/ 830 PSU-E WB WH | (0.43, 0.40) | 3000 K | ≥80 | 123.80952380952381 lm/W |
| | PSD- VLC-E VWB WH | SDCM<3 | | | |
| 910500459737 | RS340B LED39S/ 827 PSU-E WB WH | (0.46, 0.41) SDCM<3 | 2700 K | ≥80 | 119.04761904761905 lm/W |
| | PSD- VLC-E VWB WH | | | | |
| 910500459738 | RS340B LED39S/ 840 PSU-E WB WH | (0.38, 0.38) SDCM<3 | 4000 K | ≥80 | 120.63492063492063 lm/W |
| | PSD- VLC-E VWB WH | | | | |
| 910500459739 | RS340B LED39S/ 840 PSD- | (0.38, 0.38) SDCM<3 | 4000 K | ≥80 | 120.63492063492063 lm/W |

| Order Code | Full Product | | Init. Corr. | Init. Color | |
|--------------|--|----------------------|-------------------|-----------------|--------------------------------|
| | Name | Initial chromaticity | Color Temperature | Rendering Index | Initial LED luminaire efficacy |
| | VLC-E WB WH | | | | |
| 910500459740 | RS340B LED39S/ PW930 PSU-E WB WH | (0.42, 0.39) | 3000 K | ≥90 | 101.2987012987013 lm/W |
| | PSD- VLC-E WB WH CW-L | SDCM<3 | | | |
| 910500459741 | RS340B LED39S/ PW930 PSU-E WB WH CW-L | (0.42, 0.39) | 3000 K | ≥90 | 101.2987012987013 lm/W |
| | PSD- VLC-E WB WH CW-L | SDCM<3 | | | |
| 910500459742 | RS340B LED39S/ PW930 PSD- VLC-E WB WH CW-L | (0.42, 0.39) | 3000 K | ≥90 | 101.2987012987013 lm/W |
| | PSD- VLC-E WB WH CW-L | SDCM<3 | | | |
| 910500459743 | RS340B LED39S/ 830 PSU-E WB WH CW-L | (0.43, 0.40) | 3000 K | ≥80 | 123.80952380952381 lm/W |
| | PSD- VLC-E WB WH CW-L | SDCM<3 | | | |
| 910500459744 | RS340B LED39S/ 830 PSU-E VWB WH | (0.43, 0.40) | 3000 K | ≥80 | 123.80952380952381 lm/W |
| | PSD- VLC-E VWB WH | SDCM<3 | | | |
| 910500459745 | RS340B LED39S/ 830 PSD- VLC-E VWB WH | (0.43, 0.40) | 3000 K | ≥80 | 123.80952380952381 lm/W |
| | PSD- VLC-E VWB WH | SDCM<3 | | | |
| 910500465313 | RS340B LED27S/ CH PSU- E WB WH | (0.46, 0.39) | 2700 K | ≥80 | 110.63829787234043 lm/W |
| | PSD- VLC-E VWB WH | SDCM<3 | | | |
| 910500465314 | RS342B LED27S/ CH PSU- E WB WH | (0.46, 0.39) | 2700 K | ≥80 | 110.63829787234043 lm/W |

Initial Performance (IEC Compliant) (2/2)

GreenSpace Accent Fixed

| Order Code | Full Product Name | Initial luminous flux | Initial input power |
|--------------|--|-----------------------|---------------------|
| 910500459720 | RS340B LED19S/FMT PSU-E WB WH | 1900 lm | 27 W |
| 910500459721 | RS340B LED27S/FMT PSU-E MB WH | 2700 lm | 39.5 W |
| 910500459722 | RS340B LED27S/830 PSU-E WB WH | 2700 lm | 23.5 W |
| 910500459723 | RS340B LED27S/840 PSU-E WB WH | 2800 lm | 23.5 W |
| 910500459727 | RS340B LED27S/PW930 PSU-E WB WH | 2700 lm | 25.5 W |
| 910500459728 | RS340B LED27S/PW930 PSU-E MB WH CW-L | 2700 lm | 25.5 W |
| 910500459729 | RS340B LED27S/PW930 PSD-VLC-E MB WH CW-L | 2700 lm | 25.5 W |
| 910500459730 | RS340B LED27S/827 PSD-VLC-E MB WH CW-L | 2600 lm | 23.5 W |
| 910500459731 | RS340B LED27S/830 PSD-VLC-E MB WH CW-L | 2700 lm | 23.5 W |
| 910500459733 | RS340B LED27S/PW930 PSU-E WB WH CW-L | 2700 lm | 25.5 W |
| 910500459734 | RS340B LED27S/830 PSU-E VWB WH | 2700 lm | 23.5 W |
| 910500459735 | RS340B LED27S/830 PSD-VLC-E VWB WH | 2700 lm | 23.5 W |

| Order Code | Full Product Name | Initial luminous flux | Initial input power |
|--------------|--|-----------------------|---------------------|
| 910500459736 | RS340B LED39S/830 PSU-E WB WH | 3900 lm | 31.5 W |
| 910500459737 | RS340B LED39S/827 PSU-E WB WH | 3750 lm | 31.5 W |
| 910500459738 | RS340B LED39S/840 PSU-E WB WH | 3800 lm | 31.5 W |
| 910500459739 | RS340B LED39S/840 PSD-VLC-E WB WH | 3800 lm | 31.5 W |
| 910500459740 | RS340B LED39S/PW930 PSU-E WB WH | 3900 lm | 38.5 W |
| 910500459741 | RS340B LED39S/PW930 PSU-E WB WH CW-L | 3900 lm | 38.5 W |
| 910500459742 | RS340B LED39S/PW930 PSD-VLC-E WB WH CW-L | 3900 lm | 38.5 W |
| 910500459743 | RS340B LED39S/830 PSU-E WB WH CW-L | 3900 lm | 31.5 W |
| 910500459744 | RS340B LED39S/830 PSU-E VWB WH | 3900 lm | 31.5 W |
| 910500459745 | RS340B LED39S/830 PSD-VLC-E VWB WH | 3900 lm | 31.5 W |
| 910500465313 | RS340B LED27S/CH PSU-E WB WH | 2600 lm | 23.5 W |
| 910500465314 | RS342B LED27S/CH PSU-E WB WH | 2600 lm | 23.5 W |

