



For top performance and sustainability

MASTER LEDtube InstantFit HF T5

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T5 lighting tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime make these T5 LED tubes the choice for every demanding application.

Benefits

- Absolute performance that provides a solution for every application
- Unparalleled savings with low energy consumption and long lifetime
- Robust and reliable: stands up to everyday conditions

Features

- Retrofit existing T5 lamps with HF ballast
- Compatible with a wide range of ballasts
- > 50% energy savings compared to fluorescent tubes with up to 155lm/W
- Extra-long life up to 60,000 hours
- Ultra output up to 5600lm
- No mercury

Application

- Office
- Schools
- Retail

MASTER LEDtube InstantFit HF T5


Versions



MAS LEDtube HF 1500mm 26W G5 T5 HO

LEDtube 1200mm 17W G5

Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube HF 1200mm HE 16.5W 830 T5	15.5 mm	18.8 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube HF 1200mm HE 16.5W 840 T5	15.5 mm	18.8 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube HF 1200mm HE 16.5W 865 T5	15.5 mm	18.8 mm	1,149 mm	1,156.1 mm	1,163.2 mm
MAS LEDtube HF 1200mm HO 26W 840 T5 OE	15.5 mm	19 mm	1,149 mm	1,156 mm	1,163 mm
MAS LEDtube HF 1500mm HE 20W 830 T5	15.5 mm	18.8 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube HF 1500mm HE 20W 840 T5	15.5 mm	18.8 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube HF 1500mm HE 20W 865 T5	15.5 mm	18.8 mm	1,449 mm	1,456.1 mm	1,463.2 mm
MAS LEDtube HF 1500mm HO 26W 830 T5 OE	15.5 mm	19 mm	1,449 mm	1,456 mm	1,463 mm
MAS LEDtube HF 1500mm HO 26W 840 T5 OE	15.5 mm	19 mm	1,449 mm	1,456 mm	1,463 mm
MAS LEDtube HF 1500mm HO 26W 865 T5 OE	15.5 mm	19 mm	1,449 mm	1,456 mm	1,463 mm
MAS LEDtube HF 1500mm UO 36W 840 T5	15.5 mm	19 mm	1,449 mm	1,456 mm	1,463 mm
MAS LEDtube HF 600mm HE 8W 830 T5	15.5 mm	18.8 mm	549 mm	556.1 mm	563.2 mm
MAS LEDtube HF 600mm HE 8W 840 T5	15.5 mm	18.8 mm	549 mm	556.1 mm	563.2 mm

MASTER LEDtube InstantFit HF T5

General Information	
Cap-Base	G5
Switching Cycle	50,000
Nominal lifetime	60,000 hour(s)
Light Technical	
Beam Angle (Nom)	200 degree(s)
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s
Temperature	
Ambient temperature range	-20 °C to 45 °C
Controls and Dimming	
Dimmable	Yes - Check ballast compatibility
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	T5

Light Technical

Order Code	Full Product Name	Correlated Color		Luminous Flux
		Temperature (Nom)	Color Code	
74953800	Master LEDtube HF 1200mm HO 26W 840 T5 OE	4000 K	840	3,900 lm
74957600	Master LEDtube HF 1500mm HO 26W 830 T5 OE	3000 K	830	3,700 lm
74959000	Master LEDtube HF 1500mm HO 26W 840 T5 OE	4000 K	840	3,900 lm
74961300	Master LEDtube HF 1500mm HO 26W 865 T5 OE	6500 K	865	3,900 lm
41907000	Master LEDtube HF 1500mm UO 36W 840 T5	4000 K	840	5,600 lm
74323200	Master LEDtube HF 600mm HE 8W 830 T5	3000 K	830	1,000 lm
74325600	Master LEDtube HF 600mm HE 8W 840 T5	4000 K	840	1,050 lm
74329400	Master LEDtube HF 1200mm HE 16.5W 830 T5	3000 K	830	2,300 lm
74331700	Master LEDtube HF 1200mm HE 16.5W 840 T5	4000 K	840	2,500 lm
74333100	Master LEDtube HF 1200mm HE 16.5W 865 T5	6500 K	865	2,500 lm
74335500	Master LEDtube HF 1500mm HE 20W 830 T5	3000 K	830	2,800 lm
74337900	Master LEDtube HF 1500mm HE 20W 840 T5	4000 K	840	3,000 lm
74339300	Master LEDtube HF 1500mm HE 20W 865 T5	6500 K	865	3,000 lm

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power
				Consumption
74953800	Master LEDtube HF 1200mm HO 26W 840 T5 OE	30K to 60K Hz	30K to 60K Hz	26 W
74957600	Master LEDtube HF 1500mm HO 26W 830 T5 OE	20K to 140K Hz	20K to 140K Hz	26 W
74959000	Master LEDtube HF 1500mm HO 26W 840 T5 OE	20K to 140K Hz	20K to 140K Hz	26 W
74961300	Master LEDtube HF 1500mm HO 26W 865 T5 OE	20K to 140K Hz	20K to 140K Hz	26 W
41907000	Master LEDtube HF 1500mm UO 36W 840 T5	30K to 100K Hz	30K to 100K Hz	36 W
74323200	Master LEDtube HF 600mm HE 8W 830 T5	30K to 100K Hz	30K to 100K Hz	8 W
74325600	Master LEDtube HF 600mm HE 8W 840 T5	30K to 100K Hz	30K to 100K Hz	8 W

Order Code	Full Product Name	Input Frequency	Line Frequency	Power
				Consumption
74329400	Master LEDtube HF 1200mm HE 16.5W 830 T5	30K to 100K Hz	30K to 100K Hz	16.5 W
74331700	Master LEDtube HF 1200mm HE 16.5W 840 T5	30K to 100K Hz	30K to 100K Hz	16.5 W
74333100	Master LEDtube HF 1200mm HE 16.5W 865 T5	30K to 100K Hz	30K to 100K Hz	16.5 W
74335500	Master LEDtube HF 1500mm HE 20W 830 T5	30K to 100K Hz	30K to 100K Hz	20 W
74337900	Master LEDtube HF 1500mm HE 20W 840 T5	30K to 100K Hz	30K to 100K Hz	20 W
74339300	Master LEDtube HF 1500mm HE 20W 865 T5	30K to 100K Hz	30K to 100K Hz	20 W

Temperature

MASTER LEDtube InstantFit HF T5

Order Code	Full Product Name	T-Case Maximum (Nom)
74953800	Master LEDtube HF 1200mm HO 26W 840 T5 OE	55 °C
74957600	Master LEDtube HF 1500mm HO 26W 830 T5 OE	50 °C
74959000	Master LEDtube HF 1500mm HO 26W 840 T5 OE	50 °C
74961300	Master LEDtube HF 1500mm HO 26W 865 T5 OE	50 °C
41907000	Master LEDtube HF 1500mm UO 36W 840 T5	75 °C
74323200	Master LEDtube HF 600mm HE 8W 830 T5	65 °C
74325600	Master LEDtube HF 600mm HE 8W 840 T5	65 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
74329400	Master LEDtube HF 1200mm HE 16.5W 830 T5	65 °C
74331700	Master LEDtube HF 1200mm HE 16.5W 840 T5	65 °C
74333100	Master LEDtube HF 1200mm HE 16.5W 865 T5	65 °C
74335500	Master LEDtube HF 1500mm HE 20W 830 T5	65 °C
74337900	Master LEDtube HF 1500mm HE 20W 840 T5	65 °C
74339300	Master LEDtube HF 1500mm HE 20W 865 T5	65 °C

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
74953800	Master LEDtube HF 1200mm HO 26W 840 T5 OE	26 kWh
74957600	Master LEDtube HF 1500mm HO 26W 830 T5 OE	26 kWh
74959000	Master LEDtube HF 1500mm HO 26W 840 T5 OE	26 kWh
74961300	Master LEDtube HF 1500mm HO 26W 865 T5 OE	26 kWh
41907000	Master LEDtube HF 1500mm UO 36W 840 T5	36 kWh
74323200	Master LEDtube HF 600mm HE 8W 830 T5	8 kWh
74325600	Master LEDtube HF 600mm HE 8W 840 T5	8 kWh
74329400	Master LEDtube HF 1200mm HE 16.5W 830 T5	17 kWh
74331700	Master LEDtube HF 1200mm HE 16.5W 840 T5	17 kWh
74333100	Master LEDtube HF 1200mm HE 16.5W 865 T5	17 kWh
74335500	Master LEDtube HF 1500mm HE 20W 830 T5	20 kWh
74337900	Master LEDtube HF 1500mm HE 20W 840 T5	20 kWh
74339300	Master LEDtube HF 1500mm HE 20W 865 T5	20 kWh

