



For top performance and sustainability

MASTER LEDtube InstantFit HF T5

The Philips MASTER LEDtube integrates an LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescents. These T5 lighting tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings, thanks to low energy consumption and an exceptionally long lifetime, make these T5 LED tubes the choice for every demanding applications.

Benefits

- Absolute performance that provides a solution for every application
- Unparalleled savings with low energy consumption and long lifetime
- Robust and reliable: stands up to everyday conditions

Features

- Retrofit existing T5 lamps with HF ballast
- Compatible with a wide range of ballasts
- > 50% energy savings compared to fluorescent tubes with up to 155 lm/W
- Extra-long life up to 60,000 hours
- Ultra output up to 5,600 lm
- No mercury

Application


- Office
- Schools
- Retail

MASTER LEDtube InstantFit HF T5

Versions



Dimensional drawing



Product	D1	D2	A1	A2	A3
Master LEDtube HF 1500mm UO 36W 840 T5	15.2 mm	21 mm	1447.8 mm	1454.9 mm	1462 mm
Master LEDtube HF 1500mm UO 36W 865 T5	15.2 mm	21 mm	1447.8 mm	1454.9 mm	1462 mm

MASTER LEDtube InstantFit HF T5

Approval and application

Energy Consumption kWh/1000 h 36 kWh

Controls and dimming

Dimmable No

Operating and electrical

Input Frequency 40000-75000 Hz

Voltage (Nom) 65-75 V

Power (Nom) 36 W

Starting Time (Nom) 0.5 s

General information

Cap-Base G5

Nominal Lifetime (Nom) 60000 h

Switching Cycle 50000

Light technical

Beam Angle (Nom) 160 °

Colour Rendering Index (Nom) 80

Llmf At End Of Nominal Lifetime (Nom) 70 %

Luminous Flux (Nom) 5600 lm

Mechanical and housing

Bulb Finish Frosted

Bulb Shape Tube, double-ended

Temperature

T-Ambient (Max) 45 °C

T-Ambient (Min) -20 °C


T-Case Maximum (Nom) 75 °C

T-Storage (Max) 65 °C

T-Storage (Min) -40 °C

Light technical

Order Code	Full Product Name	Correlated Colour Temperature	
		Colour Code (Nom)	
929001346202	Master LEDtube HF 1500mm UO 36W 840 T5	840	4000 K
929001346302	Master LEDtube HF 1500mm UO 36W 865 T5	865	6500 K



MASTER LEDtube InstantFit HF T5

