



新一代節能 T5 燈管

MASTER LEDtube InstantFit HF T5

飛利浦 MASTER LEDtube InstantFit T5 結合 LED 光源與傳統日光燈的規格。獨特出眾的設計，打造完美均一的視覺效果，幾乎與傳統日光燈無異。對於有更高光源輸出需求，並且希望發揮超值使用效益的客戶而言，飛利浦 MASTER LEDtube InstantFit T5 是非常理想的選擇。Full energy savings & longer lifetime result in attractive payback times and TCO benefits.

优点

- 耗電量降低而減少了營運成本
- 使用壽命比傳統日光燈管延長 2~3 倍，維護成本更低
- Fastest and easiest way to upgrade existing luminaire to LED technology, with a 100%- safe installation process

特点



- 適用現有 HF 安定器裝設的 T5 燈管之改裝更換
- HF compatibility: no wires to replace, no hassle changing drivers; our InstantFit solution works with High Frequency electronic ballasts, making it easy and safe for all installation methods
- Electronic Pin safety: with Philips products you can safely touch the other end-cap when installing the tube. The integrated driver is also safely isolated from touchable parts. Philips LED tubes adhere to all UL and IEC pin safety requirements

应用

- 專為高照明需求用途進一步節省能源設計，適用於辦公室照明、學校照明、商店照明

MASTER LEDtube InstantFit HF T5

二维绘图



Product	D1	D2	A1	A2	A3
Master LEDtube HF 1200mm HE 16.5W 865 T5	15.5 mm	18.8 mm	1149 mm	1156.1 mm	1163.2 mm
Master LEDtube HF 1200mm HE 16.5W 840 T5	15.5 mm	18.8 mm	1149 mm	1156.1 mm	1163.2 mm
Master LEDtube HF 1200mm HE 16.5W 830 T5	15.5 mm	18.8 mm	1149 mm	1156.1 mm	1163.2 mm

