



RoadFlair Sleek and superior Beyond anticipation

RoadFlair

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

Benefits

- High lumen efficacy 120 to 140 lumen per watt – much higher than currently available solutions
- Unique functional design Sleek, light-weight and well-designed luminaire
- Control and dimming ready Supports CityTouch connect application, 7-Pin Nema socket and standard outdoor dimming protocols
- Value for money Most competitive product in its segment Perfect for renovation, upgrading projects
- Best-in-class LED lighting technology at an unmatched, competitive price
- Equipped with Service tag, a QR-based identification system that makes each luminaire uniquely identifiable and provides maintenance, installation and spare part information

Features

- Excellent thermal management operating Temperature -40 to 50C
- Exposed Optic Transparent and weather resistant grade polycarbonate optics
- Multiple optic Options to meet all road and street lighting application requirements
- Lightweight housing design
- Available in 3000K, 4000K, 5000K and 5700K CCT options

Application

- Pedestrian Road
- Highway Road
- Residential Road
- Interchange

Versions



BRP392/393 LED 220-240V DM



BRP394 LED 220-240V DM



BRP391 LED 220-240V DM

Product details



RoadFlair BRP392 BRP393 Back

Approval and Application

Mech. impact protection code IK08

General Information

CE mark CE mark

Driver included Yes

Light source replaceable No

Initial Performance (IEC Compliant)

Init. Color Rendering Index >70

Mechanical and Housing

Color Gray

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401611404	BRP393 LED271/WW 240W 220-240V DM GM	Not applicable
911401622403	BRP392 LED144/NW 120W 220-240V DM MP1	-
911401622503	BRP392 LED192/NW 160W 220-240V DM MP1	-
911401622903	BRP392 LED180/NW 150W 220-240V DM MP1	-
911401623303	BRP392 LED120/NW 100W 220-240V DM MP1	-
911401623403	BRP392 LED84/NW 70W 220-240V DM MP1	-
911401623503	BRP392 LED96/NW 80W 220-240V DM MP1	-
911401623703	BRP392 LED108/NW 90W 220-240V DM MP1	-
911401624003	BRP392 LED90/WW 80W 220-240V DM MP1	-
911401624303	BRP392 LED135/WW 120W 220-240V DM MP1	-
911401624503	BRP392 LED79/WW 70W 220-240V DM MP1	-
911401624603	BRP392 LED102/WW 90W 220-240V DM MP1	-
911401624903	BRP392 LED113/WW 100W 220-240V DM MP1	-
911401625403	BRP392 LED169/WW 150W 220-240V DM MP1	-
911401625703	BRP392 LED180/WW 160W 220-240V DM MP1	-
911401673303	BRP393 LED236/WW 210W 220-240V DM MP1 GC	-
911401673403	BRP393 LED203/WW 180W 220-240V DM MP1 GC	-
911401673503	BRP393 LED248/WW 220W 220-240V DM MP1 GC	-
911401673603	BRP393 LED271/WW 240W 220-240V DM MP1 GC	-
911401673703	BRP393 LED288/NW 240W 220-240V DM MP1 GC	-
911401673803	BRP393 LED259/WW 230W 220-240V DM MP1 GC	-
911401673903	BRP393 LED276/NW 230W 220-240V DM MP1 GC	-
911401674003	BRP393 LED214/WW 190W 220-240V DM MP1 GC	-
911401674103	BRP393 LED226/WW 200W 220-240V DM MP1 GC	-
911401674203	BRP393 LED192/WW 170W 220-240V DM MP1 GC	-
911401674303	BRP393 LED252/NW 210W 220-240V DM MP1 GC	-
911401674403	BRP393 LED204/NW 170W 220-240V DM MP1 GC	-
911401674503	BRP393 LED264/NW 220W 220-240V DM MP1 GC	-
911401674603	BRP393 LED216/NW 180W 220-240V DM MP1 GC	-
911401674703	BRP393 LED240/NW 200W 220-240V DM MP1 GC	-
911401674803	BRP393 LED228/NW 190W 220-240V DM MP1 GC	-
911401699903	BRP392 LED120/NW 100W DM MP1 ILT	-
911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	10%
911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	10%
911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	10%

Order Code	Full Product Name	Maximum dim level
911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	10%
911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	10%
911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	10%
911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	10%
911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	10%
911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	10%
911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	10%
911401863498	BRP393 LED311/NW 217W 220-240V DM PSR	10%
911401863598	BRP393 LED298/NW 208W 220-240V DM PSR	10%
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	10%
911401863798	BRP393 LED273/NW 192W 220-240V DM PSR	10%
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	10%
911401863998	BRP393 LED248/NW 174W 220-240V DM PSR	10%
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	10%
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	10%
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	10%
911401866498	BRP392 LED186/WW 138W 220-240V DM PSR	10%
911401866598	BRP392 LED175/WW 130W 220-240V DM PSR	10%
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	10%
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	10%
911401866898	BRP392 LED140/WW 104W 220-240V DM PSR	10%
911401866998	BRP392 LED128/WW 96W 220-240V DM PSR	10%
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	10%
911401867198	BRP393 LED303/WW 225W 220-240V DM PSR	10%
911401867298	BRP393 LED291/WW 217W 220-240V DM PSR	10%
911401867398	BRP393 LED280/WW 208W 220-240V DM PSR	10%
911401867498	BRP393 LED268/WW 200W 220-240V DM PSR	10%
911401867598	BRP393 LED256/WW 192W 220-240V DM PSR	10%
911401867698	BRP393 LED245/WW 183W 220-240V DM PSR	10%
911401867798	BRP393 LED233/WW 174W 220-240V DM PSR	10%
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	10%
911401622603	BRP394 LED216/NW 180W 220-240V DM MP1	-
911401622703	BRP394 LED288/NW 240W 220-240V DM MP1	-
911401622803	BRP394 LED300/NW 250W 220-240V DM MP1	-
911401623003	BRP394 LED264/NW 220W 220-240V DM MP1	-

Order Code	Full Product Name	Maximum dim level
911401623103	BRP394 LED240/NW 200W 220-240V DM MP1	-
911401623203	BRP394 LED336/NW 280W 220-240V DM MP1	-
911401624103	BRP394 LED384/NW 320W 220-240V DM MP1	-
911401624203	BRP394 LED360/NW 300W 220-240V DM MP1	-
911401625003	BRP394 LED361/WW 320W 220-240V DM MP1	-
911401625103	BRP394 LED338/WW 300W 220-240V DM MP1	-
911401625203	BRP394 LED203/WW 180W 220-240V DM MP1	-
911401625303	BRP394 LED271/WW 240W 220-240V DM MP1	-
911401625503	BRP394 LED248/WW 220W 220-240V DM MP1	-
911401625603	BRP394 LED282/WW 250W 220-240V DM MP1	-
911401625803	BRP394 LED316/WW 280W 220-240V DM MP1	-
911401625903	BRP394 LED226/WW 200W 220-240V DM MP1	-
911401699703	BRP394 LED193/NW 160W DM MP1 ILT	-
911401699803	BRP394 LED215/NW 180W DM MP1 ILT	-
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	10%
911401864298	BRP394 LED437/NW 308W 220-240V DM PSR	10%
911401864398	BRP394 LED424/NW 300W 220-240V DM PSR	10%
911401864498	BRP394 LED412/NW 285W 220-240V DM PSR	10%
911401864598	BRP394 LED398/NW 276W 220-240V DM PSR	10%
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	10%
911401864798	BRP394 LED373/NW 259W 220-240V DM PSR	10%
911401864898	BRP394 LED360/NW 251W 220-240V DM PSR	10%
911401864998	BRP394 LED348/NW 242W 220-240V DM PSR	10%
911401865098	BRP394 LED336/NW 234W 220-240V DM PSR	10%
911401867998	BRP394 LED421/WW 316W 220-240V DM PSR	10%
911401868098	BRP394 LED410/WW 308W 220-240V DM PSR	10%
911401868198	BRP394 LED400/WW 300W 220-240V DM PSR	10%
911401868298	BRP394 LED386/WW 285W 220-240V DM PSR	10%
911401868398	BRP394 LED373/WW 276W 220-240V DM PSR	10%
911401868498	BRP394 LED361/WW 268W 220-240V DM PSR	10%
911401868598	BRP394 LED350/WW 259W 220-240V DM PSR	10%

Order Code	Full Product Name	Maximum dim level
911401868698	BRP394 LED338/WW 251W 220-240V DM PSR	10%
911401868798	BRP394 LED326/WW 242W 220-240V DM PSR	10%
911401868898	BRP394 LED315/WW 234W 220-240V DM PSR	10%
911401623603	BRP391 LED96/NW 80W 220-240V DM MP1	-
911401623803	BRP391 LED84/NW 70W 220-240V DM MP1	-
911401624403	BRP391 LED90/WW 80W 220-240V DM MP1	-
911401624703	BRP391 LED56/WW 50W 220-240V DM MP1	-
911401624803	BRP391 LED79/WW 70W 220-240V DM MP1	-
911401699603	BRP391 LED60/NW 50W DM MP1 ILT	-
911401861398	BRP390 LED81/NW 57W 220-240V DM	-
911401861498	BRP390 LED74/NW 52W 220-240V DM	-
911401861598	BRP390 LED68/NW 48W 220-240V DM	-
911401861698	BRP390 LED62/NW 46W 220-240V DM	-
911401861798	BRP390 LED56/NW 41W 220-240V DM	-
911401861898	BRP390 LED50/NW 36W 220-240V DM	-
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	10%
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	10%
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	10%
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	10%
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	10%
911401865198	BRP390 LED76/WW 57W 220-240V DM	-
911401865298	BRP390 LED70/WW 52W 220-240V DM	-
911401865398	BRP390 LED64/WW 48W 220-240V DM	-
911401865498	BRP390 LED58/WW 46W 220-240V DM	-
911401865598	BRP390 LED52/WW 41W 220-240V DM	-
911401865698	BRP390 LED46/WW 36W 220-240V DM	-
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	10%
911401865898	BRP391 LED100/WW 75W 220-240V DM PSR	10%
911401865998	BRP391 LED93/WW 70W 220-240V DM PSR	10%
911401866098	BRP391 LED87/WW 67W 220-240V DM PSR	10%
911401866198	BRP391 LED81/WW 63W 220-240V DM PSR	10%

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401611404	BRP393 LED271/WW 240W 220-240V DM GM	No
911401622403	BRP392 LED144/NW 120W 220-240V DM MP1	No
911401622503	BRP392 LED192/NW 160W 220-240V DM MP1	No
911401622903	BRP392 LED180/NW 150W 220-240V DM MP1	No
911401623303	BRP392 LED120/NW 100W 220-240V DM MP1	No
911401623403	BRP392 LED84/NW 70W 220-240V DM MP1	No
911401623503	BRP392 LED96/NW 80W 220-240V DM MP1	No
911401623703	BRP392 LED108/NW 90W 220-240V DM MP1	No
911401624003	BRP392 LED90/WW 80W 220-240V DM MP1	No
911401624303	BRP392 LED135/WW 120W 220-240V DM MP1	No
911401624503	BRP392 LED79/WW 70W 220-240V DM MP1	No
911401624603	BRP392 LED102/WW 90W 220-240V DM MP1	No
911401624903	BRP392 LED113/WW 100W 220-240V DM MP1	No
911401625403	BRP392 LED169/WW 150W 220-240V DM MP1	No
911401625703	BRP392 LED180/WW 160W 220-240V DM MP1	No
911401673303	BRP393 LED236/WW 210W 220-240V DM MP1 GC	No

Order Code	Full Product Name	Dimmable
911401673403	BRP393 LED203/WW 180W 220-240V DM MP1 GC	No
911401673503	BRP393 LED248/WW 220W 220-240V DM MP1 GC	No
911401673603	BRP393 LED271/WW 240W 220-240V DM MP1 GC	No
911401673703	BRP393 LED288/NW 240W 220-240V DM MP1 GC	No
911401673803	BRP393 LED259/WW 230W 220-240V DM MP1 GC	No
911401673903	BRP393 LED276/NW 230W 220-240V DM MP1 GC	No
911401674003	BRP393 LED214/WW 190W 220-240V DM MP1 GC	No
911401674103	BRP393 LED226/WW 200W 220-240V DM MP1 GC	No
911401674203	BRP393 LED192/WW 170W 220-240V DM MP1 GC	No
911401674303	BRP393 LED252/NW 210W 220-240V DM MP1 GC	No
911401674403	BRP393 LED204/NW 170W 220-240V DM MP1 GC	No
911401674503	BRP393 LED264/NW 220W 220-240V DM MP1 GC	No
911401674603	BRP393 LED216/NW 180W 220-240V DM MP1 GC	No
911401674703	BRP393 LED240/NW 200W 220-240V DM MP1 GC	No
911401674803	BRP393 LED228/NW 190W 220-240V DM MP1 GC	No
911401699903	BRP392 LED120/NW 100W DM MP1 ILT	No

Order Code	Full Product Name	Dimmable
911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	Yes
911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	Yes
911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	Yes
911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	Yes
911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	Yes
911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	Yes
911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	Yes
911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	Yes
911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	Yes
911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	Yes
911401863498	BRP393 LED311/NW 217W 220-240V DM PSR	Yes
911401863598	BRP393 LED298/NW 208W 220-240V DM PSR	Yes
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	Yes
911401863798	BRP393 LED273/NW 192W 220-240V DM PSR	Yes
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	Yes
911401863998	BRP393 LED248/NW 174W 220-240V DM PSR	Yes
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	Yes
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	Yes
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	Yes
911401866498	BRP392 LED186/WW 138W 220-240V DM PSR	Yes
911401866598	BRP392 LED175/WW 130W 220-240V DM PSR	Yes
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	Yes
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	Yes
911401866898	BRP392 LED140/WW 104W 220-240V DM PSR	Yes
911401866998	BRP392 LED128/WW 96W 220-240V DM PSR	Yes
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	Yes
911401867198	BRP393 LED303/WW 225W 220-240V DM PSR	Yes
911401867298	BRP393 LED291/WW 217W 220-240V DM PSR	Yes
911401867398	BRP393 LED280/WW 208W 220-240V DM PSR	Yes
911401867498	BRP393 LED268/WW 200W 220-240V DM PSR	Yes
911401867598	BRP393 LED256/WW 192W 220-240V DM PSR	Yes
911401867698	BRP393 LED245/WW 183W 220-240V DM PSR	Yes
911401867798	BRP393 LED233/WW 174W 220-240V DM PSR	Yes
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	Yes
911401622603	BRP394 LED216/NW 180W 220-240V DM MP1	No
911401622703	BRP394 LED288/NW 240W 220-240V DM MP1	No
911401622803	BRP394 LED300/NW 250W 220-240V DM MP1	No
911401623003	BRP394 LED264/NW 220W 220-240V DM MP1	No
911401623103	BRP394 LED240/NW 200W 220-240V DM MP1	No
911401623203	BRP394 LED336/NW 280W 220-240V DM MP1	No
911401624103	BRP394 LED384/NW 320W 220-240V DM MP1	No
911401624203	BRP394 LED360/NW 300W 220-240V DM MP1	No
911401625003	BRP394 LED361/WW 320W 220-240V DM MP1	No
911401625103	BRP394 LED338/WW 300W 220-240V DM MP1	No
911401625203	BRP394 LED203/WW 180W 220-240V DM MP1	No
911401625303	BRP394 LED271/WW 240W 220-240V DM MP1	No
911401625503	BRP394 LED248/WW 220W 220-240V DM MP1	No
911401625603	BRP394 LED282/WW 250W 220-240V DM MP1	No
911401625803	BRP394 LED316/WW 280W 220-240V DM MP1	No
911401625903	BRP394 LED226/WW 200W 220-240V DM MP1	No

Order Code	Full Product Name	Dimmable
911401699703	BRP394 LED193/NW 160W DM MP1 ILT	No
911401699803	BRP394 LED215/NW 180W DM MP1 ILT	No
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	Yes
911401864298	BRP394 LED437/NW 308W 220-240V DM PSR	Yes
911401864398	BRP394 LED424/NW 300W 220-240V DM PSR	Yes
911401864498	BRP394 LED412/NW 285W 220-240V DM PSR	Yes
911401864598	BRP394 LED398/NW 276W 220-240V DM PSR	Yes
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	Yes
911401864798	BRP394 LED373/NW 259W 220-240V DM PSR	Yes
911401864898	BRP394 LED360/NW 251W 220-240V DM PSR	Yes
911401864998	BRP394 LED348/NW 242W 220-240V DM PSR	Yes
911401865098	BRP394 LED336/NW 234W 220-240V DM PSR	Yes
911401867998	BRP394 LED421/WW 316W 220-240V DM PSR	Yes
911401868098	BRP394 LED410/WW 308W 220-240V DM PSR	Yes
911401868198	BRP394 LED400/WW 300W 220-240V DM PSR	Yes
911401868298	BRP394 LED386/WW 285W 220-240V DM PSR	Yes
911401868398	BRP394 LED373/WW 276W 220-240V DM PSR	Yes
911401868498	BRP394 LED361/WW 268W 220-240V DM PSR	Yes
911401868598	BRP394 LED350/WW 259W 220-240V DM PSR	Yes
911401868698	BRP394 LED338/WW 251W 220-240V DM PSR	Yes
911401868798	BRP394 LED326/WW 242W 220-240V DM PSR	Yes
911401868898	BRP394 LED315/WW 234W 220-240V DM PSR	Yes
911401623603	BRP391 LED96/NW 80W 220-240V DM MP1	No
911401623803	BRP391 LED84/NW 70W 220-240V DM MP1	No
911401624403	BRP391 LED90/WW 80W 220-240V DM MP1	No
911401624703	BRP391 LED56/WW 50W 220-240V DM MP1	No
911401624803	BRP391 LED79/WW 70W 220-240V DM MP1	No
911401699603	BRP391 LED60/NW 50W DM MP1 ILT	No
911401861398	BRP390 LED81/NW 57W 220-240V DM	No
911401861498	BRP390 LED74/NW 52W 220-240V DM	No
911401861598	BRP390 LED68/NW 48W 220-240V DM	No
911401861698	BRP390 LED62/NW 46W 220-240V DM	No
911401861798	BRP390 LED56/NW 41W 220-240V DM	No
911401861898	BRP390 LED50/NW 36W 220-240V DM	No
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	Yes
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	Yes
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	Yes
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	Yes
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	Yes
911401865198	BRP390 LED76/WW 57W 220-240V DM	No
911401865298	BRP390 LED70/WW 52W 220-240V DM	No
911401865398	BRP390 LED64/WW 48W 220-240V DM	No
911401865498	BRP390 LED58/WW 46W 220-240V DM	No
911401865598	BRP390 LED52/WW 41W 220-240V DM	No
911401865698	BRP390 LED46/WW 36W 220-240V DM	No
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	Yes
911401865898	BRP391 LED100/WW 75W 220-240V DM PSR	Yes
911401865998	BRP391 LED93/WW 70W 220-240V DM PSR	Yes
911401866098	BRP391 LED87/WW 67W 220-240V DM PSR	Yes
911401866198	BRP391 LED81/WW 63W 220-240V DM PSR	Yes

General Information

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark	Lamp family code	Number of gear units	Optic type	Service tag
911401611404	BRP393 LED271/WW 240W 220-240V DM GM	730 warm white	-	-	-	2 units	-	-
911401622403	BRP392 LED144/NW 120W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401622503	BRP392 LED192/NW 160W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	Yes
911401622903	BRP392 LED180/NW 150W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401623303	BRP392 LED120/NW 100W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401623403	BRP392 LED84/NW 70W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401623503	BRP392 LED96/NW 80W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401623703	BRP392 LED108/NW 90W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401624003	BRP392 LED90/WW 80W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401624303	BRP392 LED135/WW 120W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401624503	BRP392 LED79/WW 70W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401624603	BRP392 LED102/WW 90W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401624903	BRP392 LED113/WW 100W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401625403	BRP392 LED169/WW 150W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401625703	BRP392 LED180/WW 160W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401673303	BRP393 LED236/WW 210W 220-240V DM MP1 GC	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401673403	BRP393 LED203/WW 180W 220-240V DM MP1 GC	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401673503	BRP393 LED248/WW 220W 220-240V DM MP1 GC	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401673603	BRP393 LED271/WW 240W 220-240V DM MP1 GC	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401673703	BRP393 LED288/NW 240W 220-240V DM MP1 GC	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401673803	BRP393 LED259/WW 230W 220-240V DM MP1 GC	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401673903	BRP393 LED276/NW 230W 220-240V DM MP1 GC	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401674003	BRP393 LED214/WW 190W 220-240V DM MP1 GC	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401674103	BRP393 LED226/WW 200W 220-240V DM MP1 GC	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401674203	BRP393 LED192/WW 170W 220-240V DM MP1 GC	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark	Lamp family code	Number of gear units	Optic type	Service tag
911401674303	BRP393 LED252/NW 210W 220-240V DM MP1 GC	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401674403	BRP393 LED204/NW 170W 220-240V DM MP1 GC	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401674503	BRP393 LED264/NW 220W 220-240V DM MP1 GC	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401674603	BRP393 LED216/NW 180W 220-240V DM MP1 GC	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401674703	BRP393 LED240/NW 200W 220-240V DM MP1 GC	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401674803	BRP393 LED228/NW 190W 220-240V DM MP1 GC	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401699903	BRP392 LED120/NW 100W DM MP1 ILT	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401863498	BRP393 LED311/NW 217W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401863598	BRP393 LED298/NW 208W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401863798	BRP393 LED273/NW 192W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401863998	BRP393 LED248/NW 174W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark	Lamp family code	Number of gear units	Optic type	Service tag
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401866498	BRP392 LED186/WW 138W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401866598	BRP392 LED175/WW 130W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401866898	BRP392 LED140/WW 104W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401866998	BRP392 LED128/WW 96W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401867198	BRP393 LED303/WW 225W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401867298	BRP393 LED291/WW 217W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401867398	BRP393 LED280/WW 208W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401867498	BRP393 LED268/WW 200W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401867598	BRP393 LED256/WW 192W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401867698	BRP393 LED245/WW 183W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401867798	BRP393 LED233/WW 174W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401622603	BRP394 LED216/NW 180W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401622703	BRP394 LED288/NW 240W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401622803	BRP394 LED300/NW 250W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401623003	BRP394 LED264/NW 220W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401623103	BRP394 LED240/NW 200W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401623203	BRP394 LED336/NW 280W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401624103	BRP394 LED384/NW 320W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401624203	BRP394 LED360/NW 300W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401625003	BRP394 LED361/WW 320W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark	Lamp family code	Number of gear units	Optic type	Service tag
911401625103	BRP394 LED338/WW 300W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401625203	BRP394 LED203/WW 180W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401625303	BRP394 LED271/WW 240W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401625503	BRP394 LED248/WW 220W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401625603	BRP394 LED282/WW 250W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401625803	BRP394 LED316/WW 280W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401625903	BRP394 LED226/WW 200W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401699703	BRP394 LED193/NW 160W DM MP1 ILT	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401699803	BRP394 LED215/NW 180W DM MP1 ILT	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401864298	BRP394 LED437/NW 308W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401864398	BRP394 LED424/NW 300W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401864498	BRP394 LED412/NW 285W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401864598	BRP394 LED398/NW 276W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401864798	BRP394 LED373/NW 259W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401864898	BRP394 LED360/NW 251W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401864998	BRP394 LED348/NW 242W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401865098	BRP394 LED336/NW 234W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401867998	BRP394 LED421/WW 316W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401868098	BRP394 LED410/WW 308W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401868198	BRP394 LED400/WW 300W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401868298	BRP394 LED386/WW 285W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401868398	BRP394 LED373/WW 276W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401868498	BRP394 LED361/WW 268W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401868598	BRP394 LED350/WW 259W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark	Lamp family code	Number of gear units	Optic type	Service tag
911401868698	BRP394 LED338/WW 251W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401868798	BRP394 LED326/WW 242W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401868898	BRP394 LED315/WW 234W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401623603	BRP391 LED96/NW 80W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401623803	BRP391 LED84/NW 70W 220-240V DM MP1	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401624403	BRP391 LED90/WW 80W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401624703	BRP391 LED56/WW 50W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401624803	BRP391 LED79/WW 70W 220-240V DM MP1	730 warm white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401699603	BRP391 LED60/NW 50W DM MP1 ILT	740 neutral white	Polycarbonate micro lens optic	-	-	-	Medium beam	-
911401861398	BRP390 LED81/NW 57W 220-240V DM	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401861498	BRP390 LED74/NW 52W 220-240V DM	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401861598	BRP390 LED68/NW 48W 220-240V DM	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401861698	BRP390 LED62/NW 46W 220-240V DM	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401861798	BRP390 LED56/NW 41W 220-240V DM	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401861898	BRP390 LED50/NW 36W 220-240V DM	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	740 neutral white	Polycarbonate micro lens optic	-	-	-	-	-
911401865198	BRP390 LED76/WW 57W 220-240V DM	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401865298	BRP390 LED70/WW 52W 220-240V DM	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401865398	BRP390 LED64/WW 48W 220-240V DM	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401865498	BRP390 LED58/WW 46W 220-240V DM	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401865598	BRP390 LED52/WW 41W 220-240V DM	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401865698	BRP390 LED46/WW 36W 220-240V DM	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401865898	BRP391 LED100/WW 75W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401865998	BRP391 LED93/WW 70W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-
911401866098	BRP391 LED87/WW 67W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-

Order Code	Full Product Name	Light source color	Optical cover/lens type	Flammability mark	Lamp family code	Number of gear units	Optic type	Service tag
911401866198	BRP391 LED81/WW 63W 220-240V DM PSR	730 warm white	Polycarbonate micro lens optic	-	-	-	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux	Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401611404	BRP393 LED271/WW 240W 220-240V DM GM	3000 K	27072 lm	911401673903	BRP393 LED276/NW 230W 220-240V DM MP1 GC	4000 K	27600 lm
911401622403	BRP392 LED144/NW 120W 220-240V DM MP1	4000 K	14400 lm	911401674003	BRP393 LED214/WW 190W 220-240V DM MP1 GC	3000 K	21400 lm
911401622503	BRP392 LED192/NW 160W 220-240V DM MP1	4000 K	19200 lm	911401674103	BRP393 LED226/WW 200W 220-240V DM MP1 GC	3000 K	22600 lm
911401622903	BRP392 LED180/NW 150W 220-240V DM MP1	4000 K	18000 lm	911401674203	BRP393 LED192/WW 170W 220-240V DM MP1 GC	3000 K	19200 lm
911401623303	BRP392 LED120/NW 100W 220-240V DM MP1	4000 K	12000 lm	911401674303	BRP393 LED252/NW 210W 220-240V DM MP1 GC	4000 K	25200 lm
911401623403	BRP392 LED84/NW 70W 220-240V DM MP1	4000 K	8400 lm	911401674403	BRP393 LED204/NW 170W 220-240V DM MP1 GC	4000 K	20400 lm
911401623503	BRP392 LED96/NW 80W 220-240V DM MP1	4000 K	9600 lm	911401674503	BRP393 LED264/NW 220W 220-240V DM MP1 GC	4000 K	26400 lm
911401623703	BRP392 LED108/NW 90W 220-240V DM MP1	4000 K	10800 lm	911401674603	BRP393 LED216/NW 180W 220-240V DM MP1 GC	4000 K	21600 lm
911401624003	BRP392 LED90/WW 80W 220-240V DM MP1	3000 K	9000 lm	911401674703	BRP393 LED240/NW 200W 220-240V DM MP1 GC	4000 K	24000 lm
911401624303	BRP392 LED135/WW 120W 220-240V DM MP1	3000 K	13500 lm	911401674803	BRP393 LED228/NW 190W 220-240V DM MP1 GC	4000 K	22800 lm
911401624503	BRP392 LED79/WW 70W 220-240V DM MP1	3000 K	7900 lm	911401699903	BRP392 LED120/NW 100W DM MP1 ILT	4000 K	12000 lm
911401624603	BRP392 LED102/WW 90W 220-240V DM MP1	3000 K	10200 lm	911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	4000 K	22495 lm
911401624903	BRP392 LED113/WW 100W 220-240V DM MP1	3000 K	11300 lm	911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	4000 K	21246 lm
911401625403	BRP392 LED169/WW 150W 220-240V DM MP1	3000 K	16900 lm	911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	4000 K	19914 lm
911401625703	BRP392 LED180/WW 160W 220-240V DM MP1	3000 K	18000 lm	911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	4000 K	18669 lm
911401673303	BRP393 LED236/WW 210W 220-240V DM MP1 GC	3000 K	23600 lm	911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	4000 K	17425 lm
911401673403	BRP393 LED203/WW 180W 220-240V DM MP1 GC	3000 K	20300 lm	911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	4000 K	16179 lm
911401673503	BRP393 LED248/WW 220W 220-240V DM MP1 GC	3000 K	24800 lm	911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	4000 K	14935 lm
911401673603	BRP393 LED271/WW 240W 220-240V DM MP1 GC	3000 K	27100 lm	911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	4000 K	13690 lm
911401673703	BRP393 LED288/NW 240W 220-240V DM MP1 GC	4000 K	28800 lm	911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	4000 K	12446 lm
911401673803	BRP393 LED259/WW 230W 220-240V DM MP1 GC	3000 K	25900 lm	911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	4000 K	32360 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401863498	BRP393 LED311/NW 217W 220-240V DM PSR	4000 K	31115 lm
911401863598	BRP393 LED298/NW 208W 220-240V DM PSR	4000 K	29871 lm
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	4000 K	28626 lm
911401863798	BRP393 LED273/NW 192W 220-240V DM PSR	4000 K	27382 lm
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	4000 K	26136 lm
911401863998	BRP393 LED248/NW 174W 220-240V DM PSR	4000 K	24892 lm
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	4000 K	23647 lm
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	3000 K	21089 lm
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	3000 K	19918 lm
911401866498	BRP392 LED186/WW 138W 220-240V DM PSR	3000 K	18669 lm
911401866598	BRP392 LED175/WW 130W 220-240V DM PSR	3000 K	17502 lm
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	3000 K	16336 lm
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	3000 K	15168 lm
911401866898	BRP392 LED140/WW 104W 220-240V DM PSR	3000 K	14002 lm
911401866998	BRP392 LED128/WW 96W 220-240V DM PSR	3000 K	12835 lm
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	3000 K	11668 lm
911401867198	BRP393 LED303/WW 225W 220-240V DM PSR	3000 K	30338 lm
911401867298	BRP393 LED291/WW 217W 220-240V DM PSR	3000 K	29170 lm
911401867398	BRP393 LED280/WW 208W 220-240V DM PSR	3000 K	28004 lm
911401867498	BRP393 LED268/WW 200W 220-240V DM PSR	3000 K	26837 lm
911401867598	BRP393 LED256/WW 192W 220-240V DM PSR	3000 K	25670 lm
911401867698	BRP393 LED245/WW 183W 220-240V DM PSR	3000 K	24503 lm
911401867798	BRP393 LED233/WW 174W 220-240V DM PSR	3000 K	23337 lm
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	3000 K	22169 lm
911401622603	BRP394 LED216/NW 180W 220-240V DM MP1	4000 K	21600 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401622703	BRP394 LED288/NW 240W 220-240V DM MP1	4000 K	28800 lm
911401622803	BRP394 LED300/NW 250W 220-240V DM MP1	4000 K	30000 lm
911401623003	BRP394 LED264/NW 220W 220-240V DM MP1	4000 K	26400 lm
911401623103	BRP394 LED240/NW 200W 220-240V DM MP1	4000 K	24000 lm
911401623203	BRP394 LED336/NW 280W 220-240V DM MP1	4000 K	33600 lm
911401624103	BRP394 LED384/NW 320W 220-240V DM MP1	4000 K	38400 lm
911401624203	BRP394 LED360/NW 300W 220-240V DM MP1	4000 K	36000 lm
911401625003	BRP394 LED361/WW 320W 220-240V DM MP1	3000 K	36100 lm
911401625103	BRP394 LED338/WW 300W 220-240V DM MP1	3000 K	33800 lm
911401625203	BRP394 LED203/WW 180W 220-240V DM MP1	3000 K	20300 lm
911401625303	BRP394 LED271/WW 240W 220-240V DM MP1	3000 K	27100 lm
911401625503	BRP394 LED248/WW 220W 220-240V DM MP1	3000 K	24800 lm
911401625603	BRP394 LED282/WW 250W 220-240V DM MP1	3000 K	28200 lm
911401625803	BRP394 LED316/WW 280W 220-240V DM MP1	3000 K	31600 lm
911401625903	BRP394 LED226/WW 200W 220-240V DM MP1	3000 K	22600 lm
911401699703	BRP394 LED193/NW 160W DM MP1 ILT	4000 K	19300 lm
911401699803	BRP394 LED215/NW 180W DM MP1 ILT	4000 K	21500 lm
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	4000 K	44991 lm
911401864298	BRP394 LED437/NW 308W 220-240V DM PSR	4000 K	43742 lm
911401864398	BRP394 LED424/NW 300W 220-240V DM PSR	4000 K	42492 lm
911401864498	BRP394 LED412/NW 285W 220-240V DM PSR	4000 K	41243 lm
911401864598	BRP394 LED398/NW 276W 220-240V DM PSR	4000 K	39828 lm
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	4000 K	38583 lm
911401864798	BRP394 LED373/NW 259W 220-240V DM PSR	4000 K	37338 lm
911401864898	BRP394 LED360/NW 251W 220-240V DM PSR	4000 K	36093 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401864998	BRP394 LED348/NW 242W 220-240V DM PSR	4000 K	34849 lm
911401865098	BRP394 LED336/NW 234W 220-240V DM PSR	4000 K	33604 lm
911401867998	BRP394 LED421/WW 316W 220-240V DM PSR	3000 K	42179 lm
911401868098	BRP394 LED410/WW 308W 220-240V DM PSR	3000 K	41008 lm
911401868198	BRP394 LED400/WW 300W 220-240V DM PSR	3000 K	39837 lm
911401868298	BRP394 LED386/WW 285W 220-240V DM PSR	3000 K	38665 lm
911401868398	BRP394 LED373/WW 276W 220-240V DM PSR	3000 K	37338 lm
911401868498	BRP394 LED361/WW 268W 220-240V DM PSR	3000 K	36171 lm
911401868598	BRP394 LED350/WW 259W 220-240V DM PSR	3000 K	35005 lm
911401868698	BRP394 LED338/WW 251W 220-240V DM PSR	3000 K	33838 lm
911401868798	BRP394 LED326/WW 242W 220-240V DM PSR	3000 K	32671 lm
911401868898	BRP394 LED315/WW 234W 220-240V DM PSR	3000 K	31504 lm
911401623603	BRP391 LED96/NW 80W 220-240V DM MP1	4000 K	9600 lm
911401623803	BRP391 LED84/NW 70W 220-240V DM MP1	4000 K	8400 lm
911401624403	BRP391 LED90/WW 80W 220-240V DM MP1	3000 K	9000 lm
911401624703	BRP391 LED56/WW 50W 220-240V DM MP1	3000 K	5600 lm
911401624803	BRP391 LED79/WW 70W 220-240V DM MP1	3000 K	7900 lm
911401699603	BRP391 LED60/NW 50W DM MP1 ILT	4000 K	6000 lm
911401861398	BRP390 LED81/NW 57W 220-240V DM	4000 K	8123 lm
911401861498	BRP390 LED74/NW 52W 220-240V DM	4000 K	7498 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux
911401861598	BRP390 LED68/NW 48W 220-240V DM	4000 K	6874 lm
911401861698	BRP390 LED62/NW 46W 220-240V DM	4000 K	6249 lm
911401861798	BRP390 LED56/NW 41W 220-240V DM	4000 K	5624 lm
911401861898	BRP390 LED50/NW 36W 220-240V DM	4000 K	4999 lm
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	4000 K	11201 lm
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	4000 K	10579 lm
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	4000 K	9957 lm
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	4000 K	9334 lm
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	4000 K	8712 lm
911401865198	BRP390 LED76/WW 57W 220-240V DM	3000 K	7615 lm
911401865298	BRP390 LED70/WW 52W 220-240V DM	3000 K	7030 lm
911401865398	BRP390 LED64/WW 48W 220-240V DM	3000 K	6444 lm
911401865498	BRP390 LED58/WW 46W 220-240V DM	3000 K	5859 lm
911401865598	BRP390 LED52/WW 41W 220-240V DM	3000 K	5272 lm
911401865698	BRP390 LED46/WW 36W 220-240V DM	3000 K	4687 lm
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	3000 K	10501 lm
911401865898	BRP391 LED100/WW 75W 220-240V DM PSR	3000 K	9918 lm
911401865998	BRP391 LED93/WW 70W 220-240V DM PSR	3000 K	9335 lm
911401866098	BRP391 LED87/WW 67W 220-240V DM PSR	3000 K	8751 lm
911401866198	BRP391 LED81/WW 63W 220-240V DM PSR	3000 K	8167 lm

Light Technical

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401611404	BRP393 LED271/WW 240W 220-240V DM GM	0°	-	0
911401622403	BRP392 LED144/NW 120W 220-240V DM MP1	5°	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401622503	BRP392 LED192/NW 160W 220-240V DM MP1	5°	-	-
911401622903	BRP392 LED180/NW 150W 220-240V DM MP1	5°	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401623303	BRP392 LED120/NW 100W 220-240V DM MP1	5°	-	-
911401623403	BRP392 LED84/NW 70W 220-240V DM MP1	5°	-	-
911401623503	BRP392 LED96/NW 80W 220-240V DM MP1	5°	-	-
911401623703	BRP392 LED108/NW 90W 220-240V DM MP1	5°	-	-
911401624003	BRP392 LED90/WW 80W 220-240V DM MP1	5°	-	-
911401624303	BRP392 LED135/WW 120W 220-240V DM MP1	5°	-	-
911401624503	BRP392 LED79/WW 70W 220-240V DM MP1	5°	-	-
911401624603	BRP392 LED102/WW 90W 220-240V DM MP1	5°	-	-
911401624903	BRP392 LED113/WW 100W 220-240V DM MP1	5°	-	-
911401625403	BRP392 LED169/WW 150W 220-240V DM MP1	5°	-	-
911401625703	BRP392 LED180/WW 160W 220-240V DM MP1	5°	-	-
911401673303	BRP393 LED236/WW 210W 220-240V DM MP1 GC	5°	-	-
911401673403	BRP393 LED203/WW 180W 220-240V DM MP1 GC	5°	-	-
911401673503	BRP393 LED248/WW 220W 220-240V DM MP1 GC	5°	-	-
911401673603	BRP393 LED271/WW 240W 220-240V DM MP1 GC	5°	-	-
911401673703	BRP393 LED288/NW 240W 220-240V DM MP1 GC	5°	-	-
911401673803	BRP393 LED259/WW 230W 220-240V DM MP1 GC	5°	-	-
911401673903	BRP393 LED276/NW 230W 220-240V DM MP1 GC	5°	-	-
911401674003	BRP393 LED214/WW 190W 220-240V DM MP1 GC	5°	-	-
911401674103	BRP393 LED226/WW 200W 220-240V DM MP1 GC	5°	-	-
911401674203	BRP393 LED192/WW 170W 220-240V DM MP1 GC	5°	-	-
911401674303	BRP393 LED252/NW 210W 220-240V DM MP1 GC	5°	-	-
911401674403	BRP393 LED204/NW 170W 220-240V DM MP1 GC	5°	-	-
911401674503	BRP393 LED264/NW 220W 220-240V DM MP1 GC	5°	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401674603	BRP393 LED216/NW 180W 220-240V DM MP1 GC	5°	-	-
911401674703	BRP393 LED240/NW 200W 220-240V DM MP1 GC	5°	-	-
911401674803	BRP393 LED228/NW 190W 220-240V DM MP1 GC	5°	-	-
911401699903	BRP392 LED120/NW 100W DM MP1 ILT	5°	-	-
911401862498	BRP392 LED224/NW 158W 220-240V DM PSR	-	-	-
911401862598	BRP392 LED212/NW 150W 220-240V DM PSR	-	-	-
911401862698	BRP392 LED200/NW 138W 220-240V DM PSR	-	-	-
911401862798	BRP392 LED186/NW 130W 220-240V DM PSR	-	-	-
911401862898	BRP392 LED174/NW 121W 220-240V DM PSR	-	-	-
911401862998	BRP392 LED161/NW 113W 220-240V DM PSR	-	-	-
911401863098	BRP392 LED150/NW 104W 220-240V DM PSR	-	-	-
911401863198	BRP392 LED136/NW 96W 220-240V DM PSR	-	-	-
911401863298	BRP392 LED124/NW 88W 220-240V DM PSR	-	-	-
911401863398	BRP393 LED323/NW 225W 220-240V DM PSR	-	-	-
911401863498	BRP393 LED311/NW 217W 220-240V DM PSR	-	-	-
911401863598	BRP393 LED298/NW 208W 220-240V DM PSR	-	-	-
911401863698	BRP393 LED286/NW 200W 220-240V DM PSR	-	-	-
911401863798	BRP393 LED273/NW 192W 220-240V DM PSR	-	-	-
911401863898	BRP393 LED261/NW 183W 220-240V DM PSR	-	-	-
911401863998	BRP393 LED248/NW 174W 220-240V DM PSR	-	-	-
911401864098	BRP393 LED236/NW 166W 220-240V DM PSR	-	-	-
911401866298	BRP392 LED210/WW 158W 220-240V DM PSR	-	-	-
911401866398	BRP392 LED200/WW 150W 220-240V DM PSR	-	-	-
911401866498	BRP392 LED186/WW 138W 220-240V DM PSR	-	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401866598	BRP392 LED175/WW 130W 220-240V DM PSR	-	-	-
911401866698	BRP392 LED163/WW 121W 220-240V DM PSR	-	-	-
911401866798	BRP392 LED151/WW 113W 220-240V DM PSR	-	-	-
911401866898	BRP392 LED140/WW 104W 220-240V DM PSR	-	-	-
911401866998	BRP392 LED128/WW 96W 220-240V DM PSR	-	-	-
911401867098	BRP392 LED116/WW 88W 220-240V DM PSR	-	-	-
911401867198	BRP393 LED303/WW 225W 220-240V DM PSR	-	-	-
911401867298	BRP393 LED291/WW 217W 220-240V DM PSR	-	-	-
911401867398	BRP393 LED280/WW 208W 220-240V DM PSR	-	-	-
911401867498	BRP393 LED268/WW 200W 220-240V DM PSR	-	-	-
911401867598	BRP393 LED256/WW 192W 220-240V DM PSR	-	-	-
911401867698	BRP393 LED245/WW 183W 220-240V DM PSR	-	-	-
911401867798	BRP393 LED233/WW 174W 220-240V DM PSR	-	-	-
911401867898	BRP393 LED221/WW 166W 220-240V DM PSR	-	-	-
911401622603	BRP394 LED216/NW 180W 220-240V DM MP1	5°	-	-
911401622703	BRP394 LED288/NW 240W 220-240V DM MP1	5°	-	-
911401622803	BRP394 LED300/NW 250W 220-240V DM MP1	5°	-	-
911401623003	BRP394 LED264/NW 220W 220-240V DM MP1	5°	-	-
911401623103	BRP394 LED240/NW 200W 220-240V DM MP1	5°	-	-
911401623203	BRP394 LED336/NW 280W 220-240V DM MP1	5°	-	-
911401624103	BRP394 LED384/NW 320W 220-240V DM MP1	5°	-	-
911401624203	BRP394 LED360/NW 300W 220-240V DM MP1	5°	-	-
911401625003	BRP394 LED361/WW 320W 220-240V DM MP1	5°	-	-
911401625103	BRP394 LED338/WW 300W 220-240V DM MP1	5°	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401625203	BRP394 LED203/WW 180W 220-240V DM MP1	5°	-	-
911401625303	BRP394 LED271/WW 240W 220-240V DM MP1	5°	-	-
911401625503	BRP394 LED248/WW 220W 220-240V DM MP1	5°	-	-
911401625603	BRP394 LED282/WW 250W 220-240V DM MP1	5°	-	-
911401625803	BRP394 LED316/WW 280W 220-240V DM MP1	5°	-	-
911401625903	BRP394 LED226/WW 200W 220-240V DM MP1	5°	-	-
911401699703	BRP394 LED193/NW 160W DM MP1 ILT	5°	-	-
911401699803	BRP394 LED215/NW 180W DM MP1 ILT	5°	-	-
911401864198	BRP394 LED449/NW 316W 220-240V DM PSR	-	-	-
911401864298	BRP394 LED437/NW 308W 220-240V DM PSR	-	-	-
911401864398	BRP394 LED424/NW 300W 220-240V DM PSR	-	-	-
911401864498	BRP394 LED412/NW 285W 220-240V DM PSR	-	-	-
911401864598	BRP394 LED398/NW 276W 220-240V DM PSR	-	-	-
911401864698	BRP394 LED385/NW 268W 220-240V DM PSR	-	-	-
911401864798	BRP394 LED373/NW 259W 220-240V DM PSR	-	-	-
911401864898	BRP394 LED360/NW 251W 220-240V DM PSR	-	-	-
911401864998	BRP394 LED348/NW 242W 220-240V DM PSR	-	-	-
911401865098	BRP394 LED336/NW 234W 220-240V DM PSR	-	-	-
911401867998	BRP394 LED421/WW 316W 220-240V DM PSR	-	-	-
911401868098	BRP394 LED410/WW 308W 220-240V DM PSR	-	-	-
911401868198	BRP394 LED400/WW 300W 220-240V DM PSR	-	-	-
911401868298	BRP394 LED386/WW 285W 220-240V DM PSR	-	-	-
911401868398	BRP394 LED373/WW 276W 220-240V DM PSR	-	-	-
911401868498	BRP394 LED361/WW 268W 220-240V DM PSR	-	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401868598	BRP394 LED350/WW 259W 220-240V DM PSR	-	-	-
911401868698	BRP394 LED338/WW 251W 220-240V DM PSR	-	-	-
911401868798	BRP394 LED326/WW 242W 220-240V DM PSR	-	-	-
911401868898	BRP394 LED315/WW 234W 220-240V DM PSR	-	-	-
911401623603	BRP391 LED96/NW 80W 220-240V DM MP1	5°	-	-
911401623803	BRP391 LED84/NW 70W 220-240V DM MP1	5°	-	-
911401624403	BRP391 LED90/WW 80W 220-240V DM MP1	5°	-	-
911401624703	BRP391 LED56/WW 50W 220-240V DM MP1	5°	-	-
911401624803	BRP391 LED79/WW 70W 220-240V DM MP1	5°	-	-
911401699603	BRP391 LED60/NW 50W DM MP1 ILT	5°	-	-
911401861398	BRP390 LED81/NW 57W 220-240V DM	-	-	-
911401861498	BRP390 LED74/NW 52W 220-240V DM	-	-	-
911401861598	BRP390 LED68/NW 48W 220-240V DM	-	-	-
911401861698	BRP390 LED62/NW 46W 220-240V DM	-	-	-
911401861798	BRP390 LED56/NW 41W 220-240V DM	-	-	-
911401861898	BRP390 LED50/NW 36W 220-240V DM	-	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop	Upward light output ratio
911401861998	BRP391 LED112/NW 80W 220-240V DM PSR	-	-	-
911401862098	BRP391 LED105/NW 75W 220-240V DM PSR	-	-	-
911401862198	BRP391 LED100/NW 70W 220-240V DM PSR	-	-	-
911401862298	BRP391 LED93/NW 67W 220-240V DM PSR	-	-	-
911401862398	BRP391 LED87/NW 63W 220-240V DM PSR	-	-	-
911401865198	BRP390 LED76/WW 57W 220-240V DM	-	-	-
911401865298	BRP390 LED70/WW 52W 220-240V DM	-	-	-
911401865398	BRP390 LED64/WW 48W 220-240V DM	-	-	-
911401865498	BRP390 LED58/WW 46W 220-240V DM	-	-	-
911401865598	BRP390 LED52/WW 41W 220-240V DM	-	-	-
911401865698	BRP390 LED46/WW 36W 220-240V DM	-	-	-
911401865798	BRP391 LED105/WW 80W 220-240V DM PSR	-	-	-
911401865898	BRP391 LED100/WW 75W 220-240V DM PSR	-	-	-
911401865998	BRP391 LED93/WW 70W 220-240V DM PSR	-	-	-
911401866098	BRP391 LED87/WW 67W 220-240V DM PSR	-	-	-
911401866198	BRP391 LED81/WW 63W 220-240V DM PSR	-	-	-

