



# Philips Ledinaire recessed: simply great LED

## Ledinaire recessed

Philips Ledinaire recessed (RC060B) is a range of popular off-the-shelf LED luminaires that come with Philips high-quality levels at a competitive price. Reliable, energy-efficient and affordable, Ledinaire LED recessed lights are available in a range of dimensions from 600 x 600 mm to 300 x 1,200 mm. This makes Ledinaire Recessed LED lighting panels perfect for a wide range of applications from classrooms to corridors – just what you need.

### Benefits

- Philips quality and reliability
- Energy saving
- Diffuse, comfortable light

### Features

- Recessed and surface-mounted versions
- Modern, unobtrusive design
- Easy connector for faster installation
- Energy-efficient up to 100 lm/W
- Long lifetime of 50,000 hours @L70
- Non-office compliant (NOC) versions available

### Application

- Offices
- Healthcare
- Education


# Ledinaire recessed

## Versions



Ledinaire Recessed-RC060B W60L60

## Dimensional drawing



## Product details



Philips Ledinaire recessed panel  
DT01



Philips Ledinaire recessed panel  
Back DT01



Philips Ledinaire recessed panel  
Back DT03



Philips Ledinaire recessed panel  
Back DT02

## Ledinaire recessed

