



LED Driver Transformer 12W 12V. The ideal complement for LED 12V systems, up to 12W.

LED transformer

The new LED transformer 12W 12V operates with 12Vdc LED loads from 6W to 12W, with high performance inside. The mains voltage range of 110 to 240V. The output voltage is a stable and safe 12Vdc, and it has long lifetime (30,000 hours). It's compact size and light weight allows to use it in several different types of installation.

Benefits

- Operation with 12Vdc LED loads from 6W to 12W
- Compact design for easy installation
- Ideal for the application with low power 12Vdc LED strips and LED boards

Features

- Multi-voltage
- 30,000 hours lifetime
- Silent operation
- 2 years warranty

Application

- Lamps LED (6W-12W)

LED transformer


Versions



ET-E 10 LED

LED Transformer 17 W

Dimensional drawing



Product	D1	C1	A2	B2	A1
LED TRANSFORMER (127V 17W DIMMABLE)	4.4 mm	24.5 mm	72 in	34 in	76 mm

Product	A1	A2	B1	C1	D1
ET-E 10 W LED 220-240V	80 mm	70 mm	40 mm	22 mm	4.4 mm

Operating and electrical

Input Frequency 50 to 60 Hz

Operating and electrical

Order Code	Full Product Name	Input Voltage
913712911566	ET-E 10 W LED 220-240V	220 to 240 V

Order Code	Full Product Name	Input Voltage
929000719013	LED TRANSFORMER (127V 17W DIMMABLE)	127 V

General information

LED transformer

Order Code	Full Product Name	Number Of Products On MCB (16A Type B) (Nom)
913712911566	ET-E 10 W LED 220-240V	-
929000719013	LED TRANSFORMER (127V 17W DIMMABLE)	90

System characteristics

Order Code	Full Product Name	Rated Ballast-Lamp Power
913712911566	ET-E 10 W LED 220-240V	10 W

Order Code	Full Product Name	Rated Ballast-Lamp Power
929000719013	LED TRANSFORMER (127V 17W DIMMABLE)	2-17 W

