



LuxSpace Accent Fresh Food – Bring your food produce to life

LuxSpace Accent Fresh Food

Retailers are increasingly having to contend with rising energy prices. At the same time, they need to retain high-quality lighting to catch the customer's eye, as well as flexibility in architectural integration. Food retailers generally want superior light sources that illuminate their fresh food counters in the freshest way possible, making food appealing while keeping the light ambiance attractive and welcoming. When a warm light ambiance is preferred, Fresh Food Champagne is the perfect LED solution to light fruit, vegetables, cheese, bread and pastries. Fresh Food Rose is a perfect warm-light solution for meat counters, enhancing the redness of meat but also slowing down the discoloration of sliced meat. When a brighter or more natural light ambiance is preferred, Fresh Food Authentic White is recommended for fruits, vegetables, cheeses, bread and pastries. Fresh Food Meat creates the best light setting for meat enhancement in a cooler ambiance.

Benefits

- Fresh Food Champagne offers a nice warm ambiance while enhancing the color of fruit, vegetables, cheese and bread
- Fresh Food Meat offers a cooler natural light setting while enhancing the redness of meat
- Fresh Food Rose creates a warm ambiance while enhancing the redness of meat & slowing down sliced meat discoloration

LuxSpace Accent Fresh Food

Features

- High color rendering
- Special spectrums tailored to the specific requirements of fresh food counters
- DALI dimming to adjust the light exactly to the desired level

Application

- Butcher's shops and meat counters in supermarkets
- Bakeries and bread counters in supermarkets
- Fruit and vegetable stores and supermarket counters

Specifications

Type	RS740B (compact, fixed version), light source colour Fresh Food Meat (FMT) or Fresh Food Champagne (CH)
	RS741B (compact, adjustable version), light source colour Fresh Food Meat (FMT) or Fresh Food Champagne (CH)
	RS750B (performance, fixed version), light source colour Fresh Food Meat (FMT), Fresh Food Champagne (CH) or Fresh Food Rose (ROSE)
	RS751B (performance, adjustable version), light source colour Fresh Food Meat (FMT), Fresh Food Champagne (CH) or Fresh Food Rose (ROSE)
	RS752B (performance, elbow version), light source colour Fresh Food Rose (ROSE)
Ceiling type	Plaster (board) ceiling
Light source	Non-replaceable LED module
Power	Compact versions: 31 W (LED17S, light colour CH), 36 W (LED19S, light colour FMT)
	Performance versions: 31 W (LED19S, light colour ROSE), 47 W (LED26S, light colour FMT), 48 W (LED26S, light colour ROSE), 49 W (LED27S, light colour CH)
Beam angle	Compact versions: MB (25°), WB (35°)
	Performance versions: MB (25°), WB (35°), VWB (60°)
Luminous flux	Compact versions: 1,700 lm (LED17S, light colour CH), 1,900 lm (LED19S, light colour FMT)
	Performance versions: 1,900 lm (LED19S, light colour ROSE), 2,600 lm (LED26S, light colour FMT), 2,700 lm (LED27S, light colour CH)

Specifications

Driver	Built-in
Mains voltage	230 or 240 V/50-60 Hz
Dimming	Non-dimmable (PSU)
	DALI-dimmable (PSD)
Material	Rings: metal
	Heatsink: die-cast aluminium
	Front cover: acrylic
	Optic: plastic, metalised

Correlated Colour	2,200 K (light colour ROSE)
Temperature	2,500 K (light colour CH)
	3,000 K (light colour FMT)
Colour Rendering Index	>80 (light colour ROSE)
	87 (light colour FMT)
	90 (light colour CH)
Standard deviation	3
colour matching	
Lumen maintenance at median useful life*	L80
50,000 h	
Control gear failure rate at median useful life	5%
50,000 h	
Performance Ambient	+25 °C
Temperature Tq	
Driver failure rate	1% per 5,000 hours
Operating temperature range	+10 to +35 °C

Colour	Black (BK, RAL9004)
	White (WH, RAL9003)
	Silver (SI, RAL 9006 metalised grey)
	Compact fixed versions only: aluminium brushed (ALU)
	Compact adjustable and performance versions only: aluminium brushed – black or aluminium brushed – white (ALU-BK or ALU-WH, outer rim: brushed aluminium; inner front housing: black or white)
	Other RAL colours available on request
Optical cover	Acrylic cover (AC)
	Linear-lens array, oval shape (LIN)

LuxSpace Accent Fresh Food

Installation	Push-in connector or with pull relief (default option) Wieland/Adels compatible connector available as an option (CW3) for fixed versions with DALI driver
Installation	Fixed with spring fasteners
Remarks	Fresh Food Champagne (CH) is the dedicated light recipe for bread and pastries, fruits and vegetables areas. It brings a warm traditional ambience. Fresh Food Meat (FMT) and Fresh Food Rose (ROSE) are both dedicated light recipes for meat counters. You can choose between a natural cool light setting or a warm traditional light setting for your meat counter.

Versions



LuxSpace Accent Performance G3
- LED Module, system flux 2700 lm

