



Philips CorePro LED lineales R7S

CorePro LED lineales R7S

Lámpara LED que reemplaza a la lámpara. halógena lineal de doble terminal. Bajo consumo de energía. Larga duración en comparación con las lámparas. halógenas. La solución perfecta para adaptación de luminarias decorativas en aplicaciones comerciales y de hostelería

Beneficios

- Hasta un 90 % de ahorro energético en comparación con las lámparas halógenas estándar
- Menores costes de mantenimiento

Características

- Sustitución sencilla
- Funciona a 220-240 V CA y su formato está diseñado como intercambio directo para todos los portalámparas de doble terminación.
- Vida útil de 15 000 horas (B50L70)
- Luz libre de UV e IR
- Sin mercurio ni otros materiales peligrosos – conformes con la directiva RoHS

Aplicaciones

- Salas de estar, pasillos, luminarias de exterior (iluminación de seguridad), luminarias de pie para interior, iluminación de construcción

Versions



LED Lamps, CorePro 118 mm R7S



LED Lamps, CorePro 118 mm R7S

CorePro LED lineales R7S

Versions



CorePro LEDlinear MV 120W R7S
830 Linear



LEDlinear CorePro 7,2W R7S




LEDspot R7S 230V




LEDlinear CorePro 7,2W R7S 1

Plano de dimensiones




Product	D	C
CorePro LEDlinear ND 7.5-60W R7S 78mm830	29 mm	78 mm
CorePro LEDlinear ND 7.5-60W R7S 78mm840	29 mm	78 mm



Product	D	C
CorePro LED linear D 14-120W R7S 118 830	29 mm	118 mm
CorePro LED linear D 14-120W R7S 118 840	29 mm	118 mm
CorePro R7S 118mm 14-100W 830 D	29 mm	118 mm
CorePro R7S 118mm 14-100W 840 D	29 mm	118 mm
CoreProLED linearD 17.5-150W R7S 118 830	42 mm	118 mm
CoreProLED linearD 17.5-150W R7S 118 840	42 mm	118 mm

CorePro LED lineales R7S

Plano de dimensiones



Product	D	C
CorePro R7S 118mm 7.2-60W 830	15 mm	118 mm
CorePro R7S 118mm 7.2-60W 840	15 mm	118 mm

Información general	
Vida útil nominal	15.000 hora(s)
Datos técnicos de la luz	
Índice de reproducción cromática (IRC)	80
LLMF al fin de vida útil nominal (nom.)	70 %
Operativos y eléctricos	
Frecuencia de entrada	50 a 60 Hz
Line Frequency	50 to 60 Hz
Hora de inicio (nom.)	0,5 s

Información general

Order Code	Full Product Name	Base del casquillo	Ciclo de encendido/apagado
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	R7s	50.000
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	R7s	50.000
71400300	CorePro LED linear D 14-120W R7S 118 830	R7S	50.000
71406500	CorePro LED linear D 14-120W R7S 118 840	R7S	50.000
71394500	CorePro LEDlinear ND 7.5-60W R7S 78mm830	R7s	50.000

Order Code	Full Product Name	Base del casquillo	Ciclo de encendido/apagado
71396900	CorePro LEDlinear ND 7.5-60W R7S 78mm840	R7S	50.000
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	R7s	8.000
64673800	CoreProLED linearD 17.5-150W R7S 118 830	R7s	50.000
64675200	CoreProLED linearD 17.5-150W R7S 118 840	R7s	50.000
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	R7S	8.000

Datos técnicos de la luz

Order Code	Full Product Name	Temperatura de color correlacionada (Nom)	Código de color	Flujo luminoso
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	3000 K	830	1.600 lm
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	4000 K	840	1.800 lm

Order Code	Full Product Name	Temperatura de color correlacionada (Nom)	Código de color	Flujo luminoso
71400300	CorePro LED linear D 14-120W R7S 118 830	3000 K	830	2.000 lm
71406500	CorePro LED linear D 14-120W R7S 118 840	4000 K	840	2.000 lm

CorePro LED lineales R7S

Order Code	Full Product Name	Temperatura de color		
		correlacionada (Nom)	Código de color	Flujo luminoso
71394500	CorePro LEDlinear ND 7.5-60W R7S 78mm830	3000 K	830	950 lm
71396900	CorePro LEDlinear ND 7.5-60W R7S 78mm840	4000 K	840	1.000 lm
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	3000 K	830	810 lm

Order Code	Full Product Name	Temperatura de color		
		correlacionada (Nom)	Código de color	Flujo luminoso
64673800	CoreProLED linearD 17.5-150W R7S 118 830	3000 K	830	2.460 lm
64675200	CoreProLED linearD 17.5-150W R7S 118 840	4000 K	840	2.460 lm
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	4000 K	840	850 lm

Operativos y eléctricos

Order Code	Full Product Name	Consumo de energía	Equivalente de potencia
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	14 W	100 W
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	14 W	100 W
71400300	CorePro LED linear D 14-120W R7S 118 830	14 W	120 W
71406500	CorePro LED linear D 14-120W R7S 118 840	14 W	120 W
71394500	CorePro LEDlinear ND 7.5-60W R7S 78mm830	7,5 W	60 W

Order Code	Full Product Name	Consumo de energía	Equivalente de potencia
71396900	CorePro LEDlinear ND 7.5-60W R7S 78mm840	7,5 W	60 W
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	7,2 W	60 W
64673800	CoreProLED linearD 17.5-150W R7S 118 830	17,5 W	150 W
64675200	CoreProLED linearD 17.5-150W R7S 118 840	17,5 W	150 W
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	7,2 W	60 W

Temperatura

Order Code	Full Product Name	Temperatura máxima (nom.)
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	90 °C
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	90 °C
71400300	CorePro LED linear D 14-120W R7S 118 830	100 °C
71406500	CorePro LED linear D 14-120W R7S 118 840	100 °C
71394500	CorePro LEDlinear ND 7.5-60W R7S 78mm830	104 °C

Order Code	Full Product Name	Temperatura máxima (nom.)
71396900	CorePro LEDlinear ND 7.5-60W R7S 78mm840	104 °C
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	110 °C
64673800	CoreProLED linearD 17.5-150W R7S 118 830	102 °C
64675200	CoreProLED linearD 17.5-150W R7S 118 840	102 °C
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	110 °C

Controles y regulación

Order Code	Full Product Name	Regulable
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	Solo con reguladores específicos
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	Solo con reguladores específicos
71400300	CorePro LED linear D 14-120W R7S 118 830	Sí
71406500	CorePro LED linear D 14-120W R7S 118 840	Sí
71394500	CorePro LEDlinear ND 7.5-60W R7S 78mm830	No

Order Code	Full Product Name	Regulable
71396900	CorePro LEDlinear ND 7.5-60W R7S 78mm840	No
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	No
64673800	CoreProLED linearD 17.5-150W R7S 118 830	Solo con reguladores específicos
64675200	CoreProLED linearD 17.5-150W R7S 118 840	Solo con reguladores específicos
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	No

Mecánicos y de carcasa



CorePro LED lineales R7S

Order Code	Full Product Name	Acabado de la bombilla	Forma de la bombilla
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	-	Lineal
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	-	Lineal
71400300	CorePro LED linear D 14-120W R7S 118 830	-	Lineal
71406500	CorePro LED linear D 14-120W R7S 118 840	-	Lineal
71394500	CorePro LEDlinear ND 7.5-60W R7S 78mm830	-	Otros



Order Code	Full Product Name	Acabado de la bombilla	Forma de la bombilla
71396900	CorePro LEDlinear ND 7.5-60W R7S 78mm840	-	Otros
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	Transparente	Lineal
64673800	CoreProLED linearD 17.5-150W R7S 118 830	-	Lineal
64675200	CoreProLED linearD 17.5-150W R7S 118 840	-	Lineal
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	Transparente	Lineal

Aprobación y aplicación



Order Code	Full Product Name	Consumo energético kWh/ 1000 h
57879700	CorePro LED linear R7S 118mm 14-100W 830 D	14 kWh
57881000	CorePro LED linear R7S 118mm 14-100W 840 D	14 kWh
71400300	CorePro LED linear D 14-120W R7S 118 830	14 kWh
71406500	CorePro LED linear D 14-120W R7S 118 840	14 kWh
71394500	CorePro LEDlinear ND 7.5-60W R7S 78mm830	8 kWh
71396900	CorePro LEDlinear ND 7.5-60W R7S 78mm840	8 kWh
30397300	CorePro LED linear R7S 118mm 7.2-60W 830	8 kWh
64673800	CoreProLED linearD 17.5-150W R7S 118 830	18 kWh
64675200	CoreProLED linearD 17.5-150W R7S 118 840	18 kWh
30399700	CorePro LED linear R7S 118mm 7.2-60W 840	8 kWh



CorePro LED lineales R7S





Accent Diagrams



Accent Diagram - CorePro LEDlineal ND
7.5-60W R7S 78mm830

Accent Diagram - CorePro LEDlineal ND
7.5-60W R7S 78mm840

Beam Diagrams



Beam diagram - CorePro LEDlineal ND 7.5-60W
R7S 78mm830

Beam diagram - CorePro LEDlineal ND 7.5-60W
R7S 78mm840

CorePro LED lineales R7S

