PHILIPS

Lighting



Guaranteed performance, thinking ahead

Maxos fusion

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

Benefits

- Freedom of (re-)positioning enables you to direct the light where needed
- Family of fixtures to create the desired atmosphere; wide variety of beam shapes to suit diversity of applications
- With up to 13-wire track, emergency lighting and third-party hardware can be integrated to declutter ceilings

Features

- Track system inside the trunk with up to 13 wires
- High uniformity and artefact-free light distributions
- Linear fixtures, non-linear fixtures and spots can be easily installed onto the trunk
- Eight optics, including (double) asymmetric distributions and a frosted cover
- IP54 optional, silicone-free
- StoreWise, Indoor Positioning and GreenWarehouse-ready

Maxos fusion

Application


- (Food) retail
- Industrial halls/areas
- Warehouses/distribution centers


Versions



Maxos Fusion Panel-LL612X


Dimensional drawing






Maxos fusion

Dimensional drawing





Product details

Maxos_Fusion_Panel-LL512X_PCO_WH-DP.tif



Maxos_Fusion_Panel-LL512X_PCO_WH-DP03.tif



Maxos_Fusion_Panel-LL512X_WB_WH-DP02.tif



Maxos_Fusion_Panel-LL512X_WB_WH-DP03.tif



Product details

Maxos_Fusion_Panel-LL512X_WH-DP01.tif



Maxos_Fusion_Panel-LL512X_WH-DP06.tif



Maxos_Fusion_Panel-LL512X_WH-DP07.tif



Maxos_Fusion_Panel-LL612_LL623X-1DPP.tif



Maxos_Fusion_Panel-LL612_LL623X-2DPP.tif



Maxos_Fusion_Panel-LL612X-DPP.tif



Maxos_Fusion_Panel-LL623X-DPP.tif



General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Explosion hazard class	-
Glow-wire test	Temperature 850 °C, duration 30 s
Embedded control	-
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Beam angle of light source	120 degree(s)
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Operating and Electrical	
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	-20 to +35 °C
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK02
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Application Conditions	
Maximum dim level	1%

General Information

Order Code	Full Product Name	Flammability mark	Lamp family code	Product family code
910925864293	LL512X LED31S/840 PSD PCO 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864294	LL512X LED50S/840 PSD PCO 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864295	LL512X LED61S/840 PSD PCO 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864296	LL523X LED62S/840 PSD PCO 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864297	LL523X LED100S/840 PSD PCO 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864298	LL523X LED123S/840 PSD PCO 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925867821	LL512X LED61S/840 PSD PCO 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL512X
910925867822	LL523X LED123S/840 PSD PCO 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867840	LL512X LED61S/840 PSD PCO 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL512X
910925867841	LL523X LED123S/840 PSD PCO 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925868118	LL523X LED123S/840 PSD PCO 13 ELP3 WH	For mounting on normally flammable surfaces	-	LL523X
910925868120	LL523X LED62S/840 PSD PCO 13 ELP3 WH	For mounting on normally flammable surfaces	-	LL523X
910925868975	LL523X LED123S/840 SIA PCO 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868976	LL523X LED100S/840 SIA PCO 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868977	LL523X LED62S/840 SIA PCO 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925864354	LL512X LED31S/840 PSD WB 7 BK	For mounting on normally flammable surfaces	-	LL512X
910925864355	LL512X LED50S/840 PSD WB 7 BK	For mounting on normally flammable surfaces	-	LL512X
910925864356	LL512X LED61S/840 PSD WB 7 BK	For mounting on normally flammable surfaces	-	LL512X
910925864357	LL523X LED62S/840 PSD WB 7 BK	For mounting on normally flammable surfaces	-	LL523X
910925864358	LL523X LED100S/840 PSD WB 7 BK	For mounting on normally flammable surfaces	-	LL523X
910925864359	LL523X LED123S/840 PSD WB 7 BK	For mounting on normally flammable surfaces	-	LL523X
910925868122	LL512X LED31S/940 PSED WB-OC 13 BK	For mounting on normally flammable surfaces	-	LL512X
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	For mounting on normally flammable surfaces	-	LL512X
910925868126	LL523X LED62S/940 PSED WB-OC 13 BK	For mounting on normally flammable surfaces	-	LL523X

Order Code	Full Product Name	Flammability mark	Lamp family code	Product family code
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	For mounting on normally flammable surfaces	-	LL523X
910925864348	LL512X LED31S/840 PSD WB 7 SI	For mounting on normally flammable surfaces	-	LL512X
910925864349	LL512X LED50S/840 PSD WB 7 SI	For mounting on normally flammable surfaces	-	LL512X
910925864350	LL512X LED61S/840 PSD WB 7 SI	For mounting on normally flammable surfaces	-	LL512X
910925864352	LL523X LED100S/840 PSD WB 7 SI	For mounting on normally flammable surfaces	-	LL523X
910925864303	LL512X LED31S/840 PSD WB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864304	LL512X LED50S/840 PSD WB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864305	LL512X LED61S/840 PSD WB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864309	LL512X LED31S/840 PSED WB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864310	LL512X LED50S/840 PSED WB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864311	LL512X LED61S/840 PSED WB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864312	LL512X LED31S/840 PSD MB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864313	LL512X LED50S/840 PSD MB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864314	LL512X LED61S/840 PSD MB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864320	LL512X LED61S/840 PSD NB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	For mounting on normally flammable surfaces	LED31S	LL512X
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925864344	LL512X LED61S/840 PSD A20 7 WH	For mounting on normally flammable surfaces	-	LL512X

Order Code	Full Product Name	Flammability mark	Lamp family code	Product family code
910925864624	LL512X LED50S/835 PSD WB 7 WH	For mounting on normally flammable surfaces	-	LL512X
910925868121	LL512X LED31S/940 PSED WB-OC 13 WH	For mounting on normally flammable surfaces	-	LL512X
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	For mounting on normally flammable surfaces	-	LL512X
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	For mounting on normally flammable surfaces	-	LL512X
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	-	LL512X
910925864306	LL523X LED62S/840 PSD WB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864307	LL523X LED100S/840 PSD WB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864308	LL523X LED123S/840 PSD WB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864315	LL523X LED62S/840 PSD MB 7 WH	For mounting on normally flammable surfaces	-	LL523X

Order Code	Full Product Name	Flammability mark	Lamp family code	Product family code
910925864316	LL523X LED100S/840 PSD MB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864317	LL523X LED123S/840 PSD MB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864321	LL523X LED62S/840 PSD NB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864322	LL523X LED100S/840 PSD NB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864323	LL523X LED123S/840 PSD NB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864346	LL523X LED100S/840 PSD A20 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864347	LL523X LED123S/840 PSD A20 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925864351	LL523X LED62S/840 PSD WB 7 SI	For mounting on normally flammable surfaces	-	LL523X
910925864353	LL523X LED123S/840 PSD WB 7 SI	For mounting on normally flammable surfaces	-	LL523X
910925864625	LL523X LED100S/835 PSD WB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925865537	LL523X LED160S/840 PSD MB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925865538	LL523X LED160S/840 PSD NB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925865539	LL523X LED160S/840 PSD XNB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925865540	LL523X LED160S/830 PSD MB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925865541	LL523X LED160S/830 PSD NB 7 WH	For mounting on normally flammable surfaces	-	LL523X
910925865542	LL523X LED160S/830 PSD XNB 7 WH	For mounting on normally flammable surfaces	-	LL523X

Order Code	Full Product Name	Flammability mark	Lamp family code	Product family code
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867817	LL523X LED100S/840 PSD MB 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867823	LL523X LED100S/840 PSED MB 13 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867824	LL523X LED100S/840 PSED WB 13 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867836	LL523X LED100S/840 PSD MB 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867842	LL523X LED100S/840 PSED MB 13 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867843	LL523X LED100S/840 PSED WB 13 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867853	LL523X LED100S/840 PSD WB 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	For mounting on normally flammable surfaces	-	LL523X

Order Code	Full Product Name	Flammability mark	Lamp family code	Product family code
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925868111	LL523X LED62S/840 PSED WB 13 WH	For mounting on normally flammable surfaces	-	LL523X
910925868119	LL523X LED62S/840 PSD WB 13 ELP3 WH	For mounting on normally flammable surfaces	-	LL523X
910925868125	LL523X LED62S/940 PSED WB-OC 13 WH	For mounting on normally flammable surfaces	-	LL523X
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925868129	LL523X LED62S/940 PSD WB-OC 13 ELP3 WH	For mounting on normally flammable surfaces	-	LL523X
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	For mounting on normally flammable surfaces	-	LL523X
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	For mounting on normally flammable surfaces	-	LL523X
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X

Order Code	Full Product Name	Flammability mark	Lamp family code	Product family code
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	For mounting on normally flammable surfaces	-	LL523X
910925864377	LL612X LED61S/840 PSD WB 7 WH	For mounting on easily flammable surfaces	-	LL612X
910925864378	LL612X LED61S/840 PSD MB 7 WH	For mounting on easily flammable surfaces	-	LL612X
910925864379	LL612X LED61S/840 PSD NB 7 WH	For mounting on easily flammable surfaces	-	LL612X
910925864380	LL623X LED123S/840 PSD WB 7 WH	For mounting on easily flammable surfaces	-	LL623X
910925864381	LL623X LED123S/840 PSD MB 7 WH	For mounting on easily flammable surfaces	-	LL623X
910925864382	LL623X LED123S/840 PSD NB 7 WH	For mounting on easily flammable surfaces	-	LL623X
910925868648	LL515X 61S/840 PSD WB 7 HE WH	For mounting on normally flammable surfaces	-	LL515X
910925868649	LL515X 80S/840 PSD WB 7 HE WH	For mounting on normally flammable surfaces	-	LL515X
910925868650	LL515X 61S/840 PSD MB 7 HE WH	For mounting on normally flammable surfaces	-	LL515X
910925868651	LL515X 80S/840 PSD MB 7 HE WH	For mounting on normally flammable surfaces	-	LL515X
910925868652	LL515X 61S/840 PSD NB 7 HE WH	For mounting on normally flammable surfaces	-	LL515X
910925868653	LL515X 80S/840 PSD NB 7 HE WH	For mounting on normally flammable surfaces	-	LL515X

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925864293	LL512X LED31S/840 PSD PCO 7 WH	4000 K	>80	128 lm/W	2,700 lm
910925864294	LL512X LED50S/840 PSD PCO 7 WH	4000 K	>80	119 lm/W	4,300 lm
910925864295	LL512X LED61S/840 PSD PCO 7 WH	4000 K	>80	117 lm/W	5,300 lm
910925864296	LL523X LED62S/840 PSD PCO 7 WH	4000 K	>80	129 lm/W	5,300 lm
910925864297	LL523X LED100S/840 PSD PCO 7 WH	4000 K	>80	121 lm/W	8,600 lm
910925864298	LL523X LED123S/840 PSD PCO 7 WH	4000 K	>80	119 lm/W	10,600 lm
910925867821	LL512X LED61S/840 PSD PCO 7 VLC WH XA	4000 K	>80	150 lm/W	6,100 lm
910925867822	LL523X LED123S/840 PSD PCO 7 VLC WH XA	4000 K	>80	154.4 lm/W	12,300 lm
910925867840	LL512X LED61S/840 PSD PCO 7 VLC WH XA	4000 K	>80	150 lm/W	6,100 lm
910925867841	LL523X LED123S/840	4000 K	>80	154.4 lm/W	12,300 lm

Maxos fusion

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSD PCO 7 VLC WH XA				
910925868118	LL523X LED123S/840 PSD PCO 13 ELP3 WH	4000 K	>80	119 lm/W	10,600 lm
910925868120	LL523X LED62S/840 PSD PCO 13 ELP3 WH	4000 K	>80	129 lm/W	5,300 lm
910925868975	LL523X LED123S/840 SIA PCO 7 WH HE	4000 K	>80	146 lm/W	10,500 lm
910925868976	LL523X LED100S/840 SIA PCO 7 WH HE	4000 K	>80	151 lm/W	8,600 lm
910925868977	LL523X LED62S/840 SIA PCO 7 WH HE	4000 K	>80	154 lm/W	5,300 lm
910925864354	LL512X LED31S/840 PSD WB 7 BK	4000 K	>80	147 lm/W	3,100 lm
910925864355	LL512X LED50S/840 PSD WB 7 BK	4000 K	>80	138 lm/W	5,000 lm
910925864356	LL512X LED61S/840 PSD WB 7 BK	4000 K	>80	135 lm/W	6,100 lm
910925864357	LL523X LED62S/840 PSD WB 7 BK	4000 K	>80	151 lm/W	6,200 lm
910925864358	LL523X LED100S/840 PSD WB 7 BK	4000 K	>80	140 lm/W	10,100 lm
910925864359	LL523X LED123S/840 PSD WB 7 BK	4000 K	>80	138 lm/W	12,300 lm
910925868122	LL512X LED31S/940 PSED WB-OC 13 BK	4000 K	>90	147 lm/W	3,100 lm
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	4000 K	>80	175 lm/W	3,150 lm
910925868126	LL523X LED62S/940 PSED WB-OC 13 BK	4000 K	>90	151 lm/W	6,200 lm
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	4000 K	>80	185 lm/W	6,200 lm
910925864348	LL512X LED31S/840 PSD WB 7 SI	4000 K	>80	147 lm/W	3,100 lm
910925864349	LL512X LED50S/840 PSD WB 7 SI	4000 K	>80	138 lm/W	5,000 lm
910925864350	LL512X LED61S/840 PSD WB 7 SI	4000 K	>80	135 lm/W	6,100 lm
910925864352	LL523X LED100S/840 PSD WB 7 SI	4000 K	>80	140 lm/W	10,100 lm
910925864303	LL512X LED31S/840 PSD WB 7 WH	4000 K	>80	147 lm/W	3,100 lm
910925864304	LL512X LED50S/840 PSD WB 7 WH	4000 K	>80	138 lm/W	5,000 lm
910925864305	LL512X LED61S/840 PSD WB 7 WH	4000 K	>80	135 lm/W	6,100 lm
910925864309	LL512X LED31S/840 PSED WB 7 WH	4000 K	>80	147 lm/W	3,100 lm
910925864310	LL512X LED50S/840 PSED WB 7 WH	4000 K	>80	138 lm/W	5,000 lm
910925864311	LL512X LED61S/840 PSED WB 7 WH	4000 K	>80	135 lm/W	6,100 lm
910925864312	LL512X LED31S/840 PSD MB 7 WH	4000 K	>80	147 lm/W	3,100 lm
910925864313	LL512X LED50S/840 PSD MB 7 WH	4000 K	>80	138 lm/W	5,000 lm
910925864314	LL512X LED61S/840 PSD MB 7 WH	4000 K	>80	135 lm/W	6,100 lm

Maxos fusion

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925864320	LL512X LED61S/840 PSD NB 7 WH	4000 K	>80	135 lm/W	6,100 lm
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	4000 K	>80	147 lm/W	3,100 lm
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	4000 K	>80	138 lm/W	5,000 lm
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	4000 K	>80	135 lm/W	6,100 lm
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	4000 K	>80	147 lm/W	3,100 lm
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	4000 K	>80	138 lm/W	5,000 lm
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	4000 K	>80	135 lm/W	6,100 lm
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	4000 K	>80	147 lm/W	3,100 lm
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	4000 K	>80	138 lm/W	5,000 lm
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	4000 K	>80	135 lm/W	6,100 lm
910925864344	LL512X LED61S/840 PSD A20 7 WH	4000 K	>80	135 lm/W	6,100 lm
910925864624	LL512X LED50S/835 PSD WB 7 WH	3500 K	>80	139 lm/W	5,000 lm
910925868121	LL512X LED31S/940 PSED WB-OC 13 WH	4000 K	>90	147 lm/W	3,100 lm
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	4000 K	>80	175 lm/W	3,150 lm
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	4000 K	>80	175 lm/W	3,100 lm
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	4000 K	>80	175 lm/W	3,150 lm
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	4000 K	>80	175 lm/W	3,150 lm
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	4000 K	>80	172 lm/W	5,000 lm
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	4000 K	>80	172 lm/W	5,000 lm
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	4000 K	>80	172 lm/W	5,000 lm

Maxos fusion

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	4000 K	>80	165 lm/W	6,100 lm
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	4000 K	>80	175 lm/W	3,150 lm
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	4000 K	>80	160 lm/W	8,000 lm
910925864306	LL523X LED62S/840 PSD WB 7 WH	4000 K	>80	151 lm/W	6,200 lm
910925864307	LL523X LED100S/840 PSD WB 7 WH	4000 K	>80	140 lm/W	10,100 lm
910925864308	LL523X LED123S/840 PSD WB 7 WH	4000 K	>80	138 lm/W	12,300 lm
910925864315	LL523X LED62S/840 PSD MB 7 WH	4000 K	>80	151 lm/W	6,200 lm
910925864316	LL523X LED100S/840 PSD MB 7 WH	4000 K	>80	140 lm/W	10,100 lm
910925864317	LL523X LED123S/840 PSD MB 7 WH	4000 K	>80	138 lm/W	12,300 lm
910925864321	LL523X LED62S/840 PSD NB 7 WH	4000 K	>80	151 lm/W	6,200 lm
910925864322	LL523X LED100S/840 PSD NB 7 WH	4000 K	>80	140 lm/W	10,100 lm
910925864323	LL523X LED123S/840 PSD NB 7 WH	4000 K	>80	138 lm/W	12,300 lm
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	4000 K	>80	151 lm/W	6,200 lm
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	4000 K	>80	140 lm/W	10,100 lm
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	4000 K	>80	138 lm/W	12,300 lm
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	4000 K	>80	151 lm/W	6,200 lm
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	4000 K	>80	140 lm/W	10,100 lm
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	4000 K	>80	138 lm/W	12,300 lm
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	4000 K	>80	151 lm/W	6,200 lm
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	4000 K	>80	140 lm/W	10,100 lm
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	4000 K	>80	138 lm/W	12,300 lm
910925864346	LL523X LED100S/840 PSD A20 7 WH	4000 K	>80	140 lm/W	10,100 lm
910925864347	LL523X LED123S/840 PSD A20 7 WH	4000 K	>80	138 lm/W	12,300 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910925864351	LL523X LED62S/840 PSD WB 7 SI	4000 K	>80	151 lm/W	6,200 lm
910925864353	LL523X LED123S/840 PSD WB 7 SI	4000 K	>80	138 lm/W	12,300 lm
910925864625	LL523X LED100S/835 PSD WB 7 WH	3500 K	>80	141 lm/W	10,000 lm
910925865537	LL523X LED160S/840 PSD MB 7 WH	4000 K	>80	128 lm/W	16,000 lm
910925865538	LL523X LED160S/840 PSD NB 7 WH	4000 K	>80	128 lm/W	16,000 lm
910925865539	LL523X LED160S/840 PSD XNB 7 WH	4000 K	>80	128 lm/W	16,000 lm
910925865540	LL523X LED160S/830 PSD MB 7 WH	3000 K	>80	128 lm/W	16,000 lm
910925865541	LL523X LED160S/830 PSD NB 7 WH	3000 K	>80	128 lm/W	16,000 lm
910925865542	LL523X LED160S/830 PSD XNB 7 WH	3000 K	>80	128 lm/W	16,000 lm
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	3000 K	>80	172.1 lm/W	12,300 lm
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	3000 K	>80	167 lm/W	16,000 lm
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	3000 K	>80	172.1 lm/W	12,300 lm
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	3000 K	>80	167 lm/W	16,000 lm
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	3000 K	>80	167 lm/W	16,000 lm
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867817	LL523X LED100S/840 PSD MB 7 VLC WH XA	4000 K	>80	183.6 lm/W	10,000 lm
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	4000 K	>80	175.8 lm/W	16,000 lm
910925867823	LL523X LED100S/840 PSED MB 13 VLC WH XA	4000 K	>80	183.6 lm/W	10,000 lm
910925867824	LL523X LED100S/840 PSED WB 13 VLC WH XA	4000 K	>80	183.6 lm/W	10,000 lm
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	4000 K	>80	175.8 lm/W	16,000 lm
910925867836	LL523X LED100S/840	4000 K	>80	183.6 lm/W	10,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSD MB 7 VLC WH XA				
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	4000 K	>80	175.8 lm/W	16,000 lm
910925867842	LL523X LED100S/840 PSED MB 13 VLC WH XA	4000 K	>80	183.6 lm/W	10,000 lm
910925867843	LL523X LED100S/840 PSED WB 13 VLC WH XA	4000 K	>80	183.6 lm/W	10,000 lm
910925867853	LL523X LED100S/840 PSD WB 7 VLC WH XA	4000 K	>80	183.6 lm/W	10,000 lm
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	4000 K	>80	180.9 lm/W	12,300 lm
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	4000 K	>80	175.8 lm/W	16,000 lm
910925868111	LL523X LED62S/840 PSED WB 13 WH	4000 K	>80	151 lm/W	6,200 lm
910925868119	LL523X LED62S/840 PSD WB 13 ELP3 WH	4000 K	>80	151 lm/W	6,200 lm
910925868125	LL523X LED62S/940 PSED WB-OC 13 WH	4000 K	>90	151 lm/W	6,200 lm
910925868127	LL523X LED62S/840	4000 K	>80	185 lm/W	6,200 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSED WB-OC 13 WH XA				
910925868129	LL523X LED62S/940 PSD WB-OC 13 ELP3 WH	4000 K	>90	151 lm/W	6,200 lm
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	4000 K	>80	185 lm/W	6,200 lm
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	4000 K	>80	185 lm/W	6,200 lm
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	4000 K	>80	180 lm/W	6,200 lm
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	4000 K	>80	180 lm/W	6,200 lm
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	4000 K	>80	177 lm/W	10,100 lm
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	4000 K	>80	177 lm/W	10,100 lm
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	4000 K	>80	165 lm/W	16,000 lm
910925868957	LL523X LED160S/840	4000 K	>80	165 lm/W	16,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSD MB 7 WH HE				
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	4000 K	>80	177 lm/W	10,100 lm
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	4000 K	>80	177 lm/W	10,100 lm
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	4000 K	>80	171 lm/W	12,300 lm
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	4000 K	>80	165 lm/W	16,000 lm
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	4000 K	>80	165 lm/W	16,000 lm
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	4000 K	>80	180 lm/W	6,200 lm
910925869742	LL523X LED160S/840	4000 K	>80	165 lm/W	16,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSD WB 7 WH HE				
910925864377	LL612X LED61S/840 PSD WB 7 WH	4000 K	>80	137 lm/W	6,150 lm
910925864378	LL612X LED61S/840 PSD MB 7 WH	4000 K	>80	137 lm/W	6,150 lm
910925864379	LL612X LED61S/840 PSD NB 7 WH	4000 K	>80	137 lm/W	6,150 lm
910925864380	LL623X LED123S/840 PSD WB 7 WH	4000 K	>80	138 lm/W	12,300 lm
910925864381	LL623X LED123S/840 PSD MB 7 WH	4000 K	>80	138 lm/W	12,300 lm
910925864382	LL623X LED123S/840 PSD NB 7 WH	4000 K	>80	138 lm/W	12,300 lm
910925868648	LL515X 61S/840 PSD WB 7 HE WH	4000 K	>80	165 lm/W	6,100 lm
910925868649	LL515X 80S/840 PSD WB 7 HE WH	4000 K	>80	160 lm/W	8,000 lm
910925868650	LL515X 61S/840 PSD MB 7 HE WH	4000 K	>80	165 lm/W	6,100 lm
910925868651	LL515X 80S/840 PSD MB 7 HE WH	4000 K	>80	160 lm/W	8,000 lm
910925868652	LL515X 61S/840 PSD NB 7 HE WH	4000 K	>80	165 lm/W	6,100 lm
910925868653	LL515X 80S/840 PSD NB 7 HE WH	4000 K	>80	160 lm/W	8,000 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Optic type
910925864293	LL512X LED31S/840 PSD PCO 7 WH	-	Opal
910925864294	LL512X LED50S/840 PSD PCO 7 WH	-	Opal

Order Code	Full Product Name	Number of light sources	Optic type
910925864295	LL512X LED61S/840 PSD PCO 7 WH	-	Opal
910925864296	LL523X LED62S/840 PSD PCO 7 WH	-	Opal

Maxos fusion

Order Code	Full Product Name	Number of light sources	Optic type
910925864297	LL523X LED100S/840 PSD PCO 7 WH	-	Opal
910925864298	LL523X LED123S/840 PSD PCO 7 WH	-	Opal
910925867821	LL512X LED61S/840 PSD PCO 7 VLC WH XA	-	Opal
910925867822	LL523X LED123S/840 PSD PCO 7 VLC WH XA	-	Opal
910925867840	LL512X LED61S/840 PSD PCO 7 VLC WH XA	-	Opal
910925867841	LL523X LED123S/840 PSD PCO 7 VLC WH XA	-	Opal
910925868118	LL523X LED123S/840 PSD PCO 13 ELP3 WH	-	Opal
910925868120	LL523X LED62S/840 PSD PCO 13 ELP3 WH	-	Opal
910925868975	LL523X LED123S/840 SIA PCO 7 WH HE	-	Opal
910925868976	LL523X LED100S/840 SIA PCO 7 WH HE	-	Opal
910925868977	LL523X LED62S/840 SIA PCO 7 WH HE	-	Opal
910925864354	LL512X LED31S/840 PSD WB 7 BK	-	Wide beam
910925864355	LL512X LED50S/840 PSD WB 7 BK	-	Wide beam
910925864356	LL512X LED61S/840 PSD WB 7 BK	-	Wide beam
910925864357	LL523X LED62S/840 PSD WB 7 BK	-	Wide beam
910925864358	LL523X LED100S/840 PSD WB 7 BK	-	Wide beam
910925864359	LL523X LED123S/840 PSD WB 7 BK	-	Wide beam
910925868122	LL512X LED31S/940 PSED WB-OC 13 BK	-	Wide beam
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	-	Wide beam
910925868126	LL523X LED62S/940 PSED WB-OC 13 BK	-	Wide beam
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	-	Wide beam
910925864348	LL512X LED31S/840 PSD WB 7 SI	-	Wide beam
910925864349	LL512X LED50S/840 PSD WB 7 SI	-	Wide beam
910925864350	LL512X LED61S/840 PSD WB 7 SI	-	Wide beam
910925864352	LL523X LED100S/840 PSD WB 7 SI	-	Wide beam
910925864303	LL512X LED31S/840 PSD WB 7 WH	-	Wide beam
910925864304	LL512X LED50S/840 PSD WB 7 WH	-	Wide beam
910925864305	LL512X LED61S/840 PSD WB 7 WH	-	Wide beam
910925864309	LL512X LED31S/840 PSED WB 7 WH	-	Wide beam
910925864310	LL512X LED50S/840 PSED WB 7 WH	-	Wide beam

Order Code	Full Product Name	Number of light sources	Optic type
910925864311	LL512X LED61S/840 PSED WB 7 WH	-	Wide beam
910925864312	LL512X LED31S/840 PSD MB 7 WH	-	Medium beam
910925864313	LL512X LED50S/840 PSD MB 7 WH	-	Medium beam
910925864314	LL512X LED61S/840 PSD MB 7 WH	-	Medium beam
910925864320	LL512X LED61S/840 PSD NB 7 WH	-	Narrow beam
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	-	Double asymmetric optic 35° wide beam
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	-	Double asymmetric optic 35° wide beam
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	-	Double asymmetric optic 35° wide beam
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	-	Double asymmetric optic wide beam
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	-	Double asymmetric optic wide beam
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	-	Double asymmetric optic wide beam
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	1	Double asymmetric optic narrow beam
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	-	Double asymmetric optic narrow beam
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	-	Double asymmetric optic narrow beam
910925864344	LL512X LED61S/840 PSD A20 7 WH	-	Asymmetrical mirror
910925864624	LL512X LED50S/835 PSD WB 7 WH	-	Wide beam
910925868121	LL512X LED31S/940 PSED WB-OC 13 WH	-	Wide beam
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	-	Wide beam
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	-	Wide beam
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	-	Medium beam
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	-	Wide beam
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	-	Medium beam
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	-	Wide beam
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	-	Narrow beam
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	-	Medium beam
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	-	Wide beam
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	-	Narrow beam

Maxos fusion

Order Code	Full Product Name	Number of light sources	Optic type
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	-	Medium beam
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	-	Wide beam
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	-	Narrow beam
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	-	Medium beam
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	-	Wide beam
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	-	Narrow beam
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	-	Medium beam
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	-	Wide beam
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	-	Wide beam
910925864306	LL523X LED62S/840 PSD WB 7 WH	-	Wide beam
910925864307	LL523X LED100S/840 PSD WB 7 WH	-	Wide beam
910925864308	LL523X LED123S/840 PSD WB 7 WH	-	Wide beam
910925864315	LL523X LED62S/840 PSD MB 7 WH	-	Medium beam
910925864316	LL523X LED100S/840 PSD MB 7 WH	-	Medium beam
910925864317	LL523X LED123S/840 PSD MB 7 WH	-	Medium beam
910925864321	LL523X LED62S/840 PSD NB 7 WH	-	Narrow beam
910925864322	LL523X LED100S/840 PSD NB 7 WH	-	Narrow beam
910925864323	LL523X LED123S/840 PSD NB 7 WH	-	Narrow beam
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	-	Double asymmetric optic 35° wide beam
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	-	Double asymmetric optic 35° wide beam
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	-	Double asymmetric optic 35° wide beam
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	-	Double asymmetric optic wide beam
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	-	Double asymmetric optic wide beam
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	-	Double asymmetric optic wide beam
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	-	Double asymmetric optic narrow beam
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	-	Double asymmetric optic narrow beam
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	-	Double asymmetric optic narrow beam
910925864346	LL523X LED100S/840 PSD A20 7 WH	-	Asymmetrical mirror
910925864347	LL523X LED123S/840 PSD A20 7 WH	-	Asymmetrical mirror
910925864351	LL523X LED62S/840 PSD WB 7 SI	-	Wide beam
910925864353	LL523X LED123S/840 PSD WB 7 SI	-	Wide beam
910925864625	LL523X LED100S/835 PSD WB 7 WH	-	Wide beam
910925865537	LL523X LED160S/840 PSD MB 7 WH	-	Medium beam
910925865538	LL523X LED160S/840 PSD NB 7 WH	-	Narrow beam
910925865539	LL523X LED160S/840 PSD XNB 7 WH	-	Extra narrow beam
910925865540	LL523X LED160S/830 PSD MB 7 WH	-	Medium beam
910925865541	LL523X LED160S/830 PSD NB 7 WH	-	Narrow beam
910925865542	LL523X LED160S/830 PSD XNB 7 WH	-	Extra narrow beam
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	-	Wide beam
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	-	Medium beam
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	-	Double asymmetric optic 35° wide beam
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	-	Double asymmetric optic 35° wide beam
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	-	Wide beam
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	-	Narrow beam
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	-	Wide beam
910925867817	LL523X LED100S/840 PSD MB 7 VLC WH XA	-	Medium beam
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	-	Medium beam
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	-	Wide beam
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	-	Medium beam
910925867823	LL523X LED100S/840 PSED MB 13 VLC WH XA	-	Medium beam
910925867824	LL523X LED100S/840 PSED WB 13 VLC WH XA	-	Wide beam

Order Code	Full Product Name	Number of light sources	Optic type
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	-	Narrow beam
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	-	Medium beam
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	-	Wide beam
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	-	Narrow beam
910925867836	LL523X LED100S/840 PSD MB 7 VLC WH XA	-	Medium beam
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	-	Medium beam
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	-	Wide beam
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	-	Medium beam
910925867842	LL523X LED100S/840 PSED MB 13 VLC WH XA	-	Medium beam
910925867843	LL523X LED100S/840 PSED WB 13 VLC WH XA	-	Wide beam
910925867853	LL523X LED100S/840 PSD WB 7 VLC WH XA	-	Wide beam
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	-	Narrow beam
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	-	Narrow beam
910925868111	LL523X LED62S/840 PSED WB 13 WH	-	Wide beam
910925868119	LL523X LED62S/840 PSD WB 13 ELP3 WH	-	Wide beam
910925868125	LL523X LED62S/940 PSED WB-OC 13 WH	-	Wide beam
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	-	Wide beam
910925868129	LL523X LED62S/940 PSD WB-OC 13 ELP3 WH	-	Wide beam
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	-	Wide beam
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	-	Wide beam
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	-	Medium beam
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	-	Wide beam
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	-	Medium beam
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	-	Wide beam
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	-	Narrow beam
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	-	Medium beam
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	-	Wide beam
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	-	Narrow beam
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	-	Medium beam
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	-	Medium beam
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	-	Wide beam
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	-	Narrow beam
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	-	Medium beam
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	-	Wide beam
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	-	Narrow beam
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	-	Medium beam
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	-	Wide beam
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	-	Wide beam
910925864377	LL612X LED61S/840 PSD WB 7 WH	-	Wide beam
910925864378	LL612X LED61S/840 PSD MB 7 WH	-	Medium beam
910925864379	LL612X LED61S/840 PSD NB 7 WH	-	Narrow beam
910925864380	LL623X LED123S/840 PSD WB 7 WH	-	Wide beam
910925864381	LL623X LED123S/840 PSD MB 7 WH	-	Medium beam
910925864382	LL623X LED123S/840 PSD NB 7 WH	-	Narrow beam
910925868648	LL515X 61S/840 PSD WB 7 HE WH	-	Wide beam
910925868649	LL515X 80S/840 PSD WB 7 HE WH	-	Wide beam
910925868650	LL515X 61S/840 PSD MB 7 HE WH	-	Medium beam
910925868651	LL515X 80S/840 PSD MB 7 HE WH	-	Medium beam
910925868652	LL515X 61S/840 PSD NB 7 HE WH	-	Narrow beam
910925868653	LL515X 80S/840 PSD NB 7 HE WH	-	Narrow beam

Operating and Electrical

Maxos fusion

Order Code	Full Product Name	Input Voltage	Power Consumption
910925864293	LL512X LED31S/840 PSD PCO 7 WH	220-240 V	21 W
910925864294	LL512X LED50S/840 PSD PCO 7 WH	220-240 V	36 W
910925864295	LL512X LED61S/840 PSD PCO 7 WH	220-240 V	45 W
910925864296	LL523X LED62S/840 PSD PCO 7 WH	220-240 V	41 W
910925864297	LL523X LED100S/840 PSD PCO 7 WH	220-240 V	71 W
910925864298	LL523X LED123S/840 PSD PCO 7 WH	220-240 V	89 W
910925867821	LL512X LED61S/840 PSD PCO 7 VLC WH XA	220-240 V	35 W
910925867822	LL523X LED123S/840 PSD PCO 7 VLC WH XA	220-240 V	68 W
910925867840	LL512X LED61S/840 PSD PCO 7 VLC WH XA	220-240 V	35 W
910925867841	LL523X LED123S/840 PSD PCO 7 VLC WH XA	220-240 V	68 W
910925868118	LL523X LED123S/840 PSD PCO 13 ELP3 WH	220-240 V	89 W
910925868120	LL523X LED62S/840 PSD PCO 13 ELP3 WH	220-240 V	41 W
910925868975	LL523X LED123S/840 SIA PCO 7 WH HE	220-240 V	72 W
910925868976	LL523X LED100S/840 SIA PCO 7 WH HE	220-240 V	57 W
910925868977	LL523X LED62S/840 SIA PCO 7 WH HE	220-240 V	34.5 W
910925864354	LL512X LED31S/840 PSD WB 7 BK	220-240 V	21 W
910925864355	LL512X LED50S/840 PSD WB 7 BK	220-240 V	36 W
910925864356	LL512X LED61S/840 PSD WB 7 BK	220-240 V	45 W
910925864357	LL523X LED62S/840 PSD WB 7 BK	220-240 V	41 W
910925864358	LL523X LED100S/840 PSD WB 7 BK	220-240 V	71 W
910925864359	LL523X LED123S/840 PSD WB 7 BK	220-240 V	89 W
910925868122	LL512X LED31S/940 PSED WB-OC 13 BK	220-240 V	21 W
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	220-240 V	18 W
910925868126	LL523X LED62S/940 PSED WB-OC 13 BK	220-240 V	41 W
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	220-240 V	33.5 W
910925864348	LL512X LED31S/840 PSD WB 7 SI	220-240 V	21 W
910925864349	LL512X LED50S/840 PSD WB 7 SI	220-240 V	36 W
910925864350	LL512X LED61S/840 PSD WB 7 SI	220-240 V	45 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910925864352	LL523X LED100S/840 PSD WB 7 SI	220-240 V	71 W
910925864303	LL512X LED31S/840 PSD WB 7 WH	220-240 V	21 W
910925864304	LL512X LED50S/840 PSD WB 7 WH	220-240 V	36 W
910925864305	LL512X LED61S/840 PSD WB 7 WH	220-240 V	45 W
910925864309	LL512X LED31S/840 PSED WB 7 WH	220-240 V	21 W
910925864310	LL512X LED50S/840 PSED WB 7 WH	220-240 V	36 W
910925864311	LL512X LED61S/840 PSED WB 7 WH	220-240 V	45 W
910925864312	LL512X LED31S/840 PSD MB 7 WH	220-240 V	21 W
910925864313	LL512X LED50S/840 PSD MB 7 WH	220-240 V	36 W
910925864314	LL512X LED61S/840 PSD MB 7 WH	220-240 V	45 W
910925864320	LL512X LED61S/840 PSD NB 7 WH	220-240 V	45 W
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	220-240 V	21 W
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	220-240 V	36 W
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	220-240 V	45 W
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	220-240 V	21 W
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	220-240 V	36 W
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	220-240 V	45 W
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	220-240 V	21 W
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	220-240 V	36 W
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	220-240 V	45 W
910925864344	LL512X LED61S/840 PSD A20 7 WH	220-240 V	45 W
910925864624	LL512X LED50S/835 PSD WB 7 WH	220-240 V	36 W
910925868121	LL512X LED31S/940 PSED WB-OC 13 WH	220-240 V	21 W
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	220-240 V	18 W
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	220-240 V	18 W
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	220-240 V	18 W
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	220-240 V	18 W

Maxos fusion

Order Code	Full Product Name	Input Voltage	Power Consumption
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	220-240 V	29 W
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	220-240 V	29 W
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	220-240 V	37 W
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	220-240 V	37 W
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	220-240 V	37 W
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	220-240 V	50 W
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	220-240 V	50 W
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	220-240 V	29 W
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	220-240 V	37 W
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	220-240 V	37 W
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	220-240 V	37 W
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	220-240 V	50 W
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	220-240 V	50 W
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	220-240 V	18 W
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	220-240 V	50 W
910925864306	LL523X LED62S/840 PSD WB 7 WH	220-240 V	41 W
910925864307	LL523X LED100S/840 PSD WB 7 WH	220-240 V	71 W
910925864308	LL523X LED123S/840 PSD WB 7 WH	220-240 V	89 W
910925864315	LL523X LED62S/840 PSD MB 7 WH	220-240 V	41 W
910925864316	LL523X LED100S/840 PSD MB 7 WH	220-240 V	71 W
910925864317	LL523X LED123S/840 PSD MB 7 WH	220-240 V	89 W
910925864321	LL523X LED62S/840 PSD NB 7 WH	220-240 V	41 W
910925864322	LL523X LED100S/840 PSD NB 7 WH	220-240 V	71 W
910925864323	LL523X LED123S/840 PSD NB 7 WH	220-240 V	89 W
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	220-240 V	41 W
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	220-240 V	71 W
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	220-240 V	89 W
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	220-240 V	41 W
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	220-240 V	71 W
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	220-240 V	89 W
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	220-240 V	41 W
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	220-240 V	71 W
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	220-240 V	89 W
910925864346	LL523X LED100S/840 PSD A20 7 WH	220-240 V	71 W
910925864347	LL523X LED123S/840 PSD A20 7 WH	220-240 V	89 W
910925864351	LL523X LED62S/840 PSD WB 7 SI	220-240 V	41 W
910925864353	LL523X LED123S/840 PSD WB 7 SI	220-240 V	89 W
910925864625	LL523X LED100S/835 PSD WB 7 WH	220-240 V	71 W
910925865537	LL523X LED160S/840 PSD MB 7 WH	220-240 V	127 W
910925865538	LL523X LED160S/840 PSD NB 7 WH	220-240 V	127 W
910925865539	LL523X LED160S/840 PSD XNB 7 WH	220-240 V	127 W
910925865540	LL523X LED160S/830 PSD MB 7 WH	220-240 V	125 W
910925865541	LL523X LED160S/830 PSD NB 7 WH	220-240 V	125 W
910925865542	LL523X LED160S/830 PSD XNB 7 WH	220-240 V	125 W
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	220-240 V	68 W
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	220-240 V	91 W
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	220-240 V	68 W
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	220-240 V	68 W
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	220-240 V	91 W
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	220-240 V	91 W
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	220-240 V	68 W

Maxos fusion

Order Code	Full Product Name	Input Voltage	Power Consumption
910925867817	LL523X LED100S/840 PSD MB 7 VLC WH XA	220-240 V	55 W
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	220-240 V	68 W
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	220-240 V	68 W
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	220-240 V	91 W
910925867823	LL523X LED100S/840 PSED MB 13 VLC WH XA	220-240 V	55 W
910925867824	LL523X LED100S/840 PSED WB 13 VLC WH XA	220-240 V	55 W
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	220-240 V	68 W
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	220-240 V	68 W
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	220-240 V	68 W
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	220-240 V	91 W
910925867836	LL523X LED100S/840 PSD MB 7 VLC WH XA	220-240 V	55 W
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	220-240 V	68 W
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	220-240 V	68 W
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	220-240 V	91 W
910925867842	LL523X LED100S/840 PSED MB 13 VLC WH XA	220-240 V	55 W
910925867843	LL523X LED100S/840 PSED WB 13 VLC WH XA	220-240 V	55 W
910925867853	LL523X LED100S/840 PSD WB 7 VLC WH XA	220-240 V	55 W
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	220-240 V	68 W
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	220-240 V	91 W
910925868111	LL523X LED62S/840 PSED WB 13 WH	220-240 V	41 W
910925868119	LL523X LED62S/840 PSD WB 13 ELP3 WH	220-240 V	41 W
910925868125	LL523X LED62S/940 PSED WB-OC 13 WH	220-240 V	41 W
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	220-240 V	33.5 W
910925868129	LL523X LED62S/940 PSD WB-OC 13 ELP3 WH	220-240 V	35 W
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	220-240 V	35 W
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	220-240 V	35 W
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	220-240 V	34.5 W
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	220-240 V	34.5 W
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	220-240 V	57 W
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	220-240 V	57 W
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	220-240 V	72 W
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	220-240 V	72 W
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	220-240 V	72 W
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	220-240 V	97 W
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	220-240 V	97 W
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	220-240 V	57 W
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	220-240 V	57 W
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	220-240 V	72 W
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	220-240 V	72 W
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	220-240 V	72 W
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	220-240 V	97 W
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	220-240 V	97 W
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	220-240 V	34.5 W
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	220-240 V	97 W
910925864377	LL612X LED61S/840 PSD WB 7 WH	220 to 240 V	45 W
910925864378	LL612X LED61S/840 PSD MB 7 WH	220 to 240 V	45 W
910925864379	LL612X LED61S/840 PSD NB 7 WH	220 to 240 V	45 W
910925864380	LL623X LED123S/840 PSD WB 7 WH	220 to 240 V	89 W
910925864381	LL623X LED123S/840 PSD MB 7 WH	220 to 240 V	89 W
910925864382	LL623X LED123S/840 PSD NB 7 WH	220 to 240 V	89 W
910925868648	LL515X 61S/840 PSD WB 7 HE WH	220-240 V	37 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910925868649	LL515X 80S/840 PSD WB 7 HE WH	220-240 V	50 W
910925868650	LL515X 61S/840 PSD MB 7 HE WH	220-240 V	37 W
910925868651	LL515X 80S/840 PSD MB 7 HE WH	220-240 V	50 W
910925868652	LL515X 61S/840 PSD NB 7 HE WH	220-240 V	37 W
910925868653	LL515X 80S/840 PSD NB 7 HE WH	220-240 V	50 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
910925864293	LL512X LED31S/840 PSD PCO 7 WH	Yes
910925864294	LL512X LED50S/840 PSD PCO 7 WH	Yes
910925864295	LL512X LED61S/840 PSD PCO 7 WH	Yes
910925864296	LL523X LED62S/840 PSD PCO 7 WH	Yes
910925864297	LL523X LED100S/840 PSD PCO 7 WH	Yes
910925864298	LL523X LED123S/840 PSD PCO 7 WH	Yes
910925867821	LL512X LED61S/840 PSD PCO 7 VLC WH XA	Yes
910925867822	LL523X LED123S/840 PSD PCO 7 VLC WH XA	Yes
910925867840	LL512X LED61S/840 PSD PCO 7 VLC WH XA	Yes
910925867841	LL523X LED123S/840 PSD PCO 7 VLC WH XA	Yes
910925868118	LL523X LED123S/840 PSD PCO 13 ELP3 WH	Yes
910925868120	LL523X LED62S/840 PSD PCO 13 ELP3 WH	Yes
910925868975	LL523X LED123S/840 SIA PCO 7 WH HE	Yes
910925868976	LL523X LED100S/840 SIA PCO 7 WH HE	Yes
910925868977	LL523X LED62S/840 SIA PCO 7 WH HE	Yes
910925864354	LL512X LED31S/840 PSD WB 7 BK	Yes
910925864355	LL512X LED50S/840 PSD WB 7 BK	Yes
910925864356	LL512X LED61S/840 PSD WB 7 BK	Yes
910925864357	LL523X LED62S/840 PSD WB 7 BK	Yes
910925864358	LL523X LED100S/840 PSD WB 7 BK	Yes
910925864359	LL523X LED123S/840 PSD WB 7 BK	Yes
910925868122	LL512X LED31S/940 PSED WB-OC 13 BK	Yes
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	Yes
910925868126	LL523X LED62S/940 PSED WB-OC 13 BK	Yes
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	Yes
910925864348	LL512X LED31S/840 PSD WB 7 SI	Yes
910925864349	LL512X LED50S/840 PSD WB 7 SI	Yes
910925864350	LL512X LED61S/840 PSD WB 7 SI	Yes
910925864352	LL523X LED100S/840 PSD WB 7 SI	Yes
910925864303	LL512X LED31S/840 PSD WB 7 WH	Yes
910925864304	LL512X LED50S/840 PSD WB 7 WH	Yes
910925864305	LL512X LED61S/840 PSD WB 7 WH	Yes
910925864309	LL512X LED31S/840 PSED WB 7 WH	Yes
910925864310	LL512X LED50S/840 PSED WB 7 WH	Yes
910925864311	LL512X LED61S/840 PSED WB 7 WH	Yes
910925864312	LL512X LED31S/840 PSD MB 7 WH	Yes
910925864313	LL512X LED50S/840 PSD MB 7 WH	Yes
910925864314	LL512X LED61S/840 PSD MB 7 WH	Yes
910925864320	LL512X LED61S/840 PSD NB 7 WH	Yes
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	Yes
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	Yes
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	Yes
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	Yes
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	Yes
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	Yes
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	Yes
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	Yes
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	Yes
910925864344	LL512X LED61S/840 PSD A20 7 WH	Yes
910925864624	LL512X LED50S/835 PSD WB 7 WH	Yes
910925868121	LL512X LED31S/940 PSED WB-OC 13 WH	Yes
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	Yes
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	Yes
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	Yes
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	Yes
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	Yes
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	Yes
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	Yes
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	Yes
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	Yes
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	Yes
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	Yes
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	Yes
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	Yes
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	Yes
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	Yes
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	Yes
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	Yes
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	Yes
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	Yes
910925864306	LL523X LED62S/840 PSD WB 7 WH	Yes
910925864307	LL523X LED100S/840 PSD WB 7 WH	Yes
910925864308	LL523X LED123S/840 PSD WB 7 WH	Yes
910925864315	LL523X LED62S/840 PSD MB 7 WH	Yes
910925864316	LL523X LED100S/840 PSD MB 7 WH	Yes
910925864317	LL523X LED123S/840 PSD MB 7 WH	Yes
910925864321	LL523X LED62S/840 PSD NB 7 WH	Yes
910925864322	LL523X LED100S/840 PSD NB 7 WH	Yes
910925864323	LL523X LED123S/840 PSD NB 7 WH	Yes
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	Yes
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	Yes
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	Yes
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	Yes
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	Yes

Order Code	Full Product Name	Dimmable
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	Yes
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	Yes
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	Yes
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	Yes
910925864346	LL523X LED100S/840 PSD A20 7 WH	Yes
910925864347	LL523X LED123S/840 PSD A20 7 WH	Yes
910925864351	LL523X LED62S/840 PSD WB 7 SI	Yes
910925864353	LL523X LED123S/840 PSD WB 7 SI	Yes
910925864625	LL523X LED100S/835 PSD WB 7 WH	Yes
910925865537	LL523X LED160S/840 PSD MB 7 WH	Yes
910925865538	LL523X LED160S/840 PSD NB 7 WH	Yes
910925865539	LL523X LED160S/840 PSD XNB 7 WH	Yes
910925865540	LL523X LED160S/830 PSD MB 7 WH	Yes
910925865541	LL523X LED160S/830 PSD NB 7 WH	Yes
910925865542	LL523X LED160S/830 PSD XNB 7 WH	Yes
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	Yes
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	Yes
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	Yes
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	Yes
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	Yes
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	Yes
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	Yes
910925867817	LL523X LED100S/840 PSD MB 7 VLC WH XA	Yes
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	Yes
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	Yes
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	Yes
910925867823	LL523X LED100S/840 PSED MB 13 VLC WH XA	Yes
910925867824	LL523X LED100S/840 PSED WB 13 VLC WH XA	Yes
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	Yes
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	Yes
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	Yes
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	Yes
910925867836	LL523X LED100S/840 PSD MB 7 VLC WH XA	Yes
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	Yes
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	Yes
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	Yes
910925867842	LL523X LED100S/840 PSED MB 13 VLC WH XA	Yes
910925867843	LL523X LED100S/840 PSED WB 13 VLC WH XA	Yes
910925867853	LL523X LED100S/840 PSD WB 7 VLC WH XA	Yes

Order Code	Full Product Name	Dimmable
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	Yes
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	Yes
910925868111	LL523X LED62S/840 PSED WB 13 WH	Yes
910925868119	LL523X LED62S/840 PSD WB 13 ELP3 WH	Yes
910925868125	LL523X LED62S/940 PSED WB-OC 13 WH	Yes
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	Yes
910925868129	LL523X LED62S/940 PSD WB-OC 13 ELP3 WH	Yes
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	Yes
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	Yes
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	Yes
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	Yes
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	Yes
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	Yes
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	Yes
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	Yes
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	Yes
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	Yes
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	Yes
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	Yes
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	Yes
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	Yes
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	Yes
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	Yes
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	Yes
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	Yes
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	Yes
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	Yes
910925864377	LL612X LED61S/840 PSD WB 7 WH	DALI
910925864378	LL612X LED61S/840 PSD MB 7 WH	DALI
910925864379	LL612X LED61S/840 PSD NB 7 WH	DALI
910925864380	LL623X LED123S/840 PSD WB 7 WH	DALI
910925864381	LL623X LED123S/840 PSD MB 7 WH	DALI
910925864382	LL623X LED123S/840 PSD NB 7 WH	DALI
910925868648	LL515X 61S/840 PSD WB 7 HE WH	Yes
910925868649	LL515X 80S/840 PSD WB 7 HE WH	Yes
910925868650	LL515X 61S/840 PSD MB 7 HE WH	Yes
910925868651	LL515X 80S/840 PSD MB 7 HE WH	Yes
910925868652	LL515X 61S/840 PSD NB 7 HE WH	Yes
910925868653	LL515X 80S/840 PSD NB 7 HE WH	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
910925864293	LL512X LED31S/840 PSD PCO 7 WH	White
910925864294	LL512X LED50S/840 PSD PCO 7 WH	White
910925864295	LL512X LED61S/840 PSD PCO 7 WH	White
910925864296	LL523X LED62S/840 PSD PCO 7 WH	White
910925864297	LL523X LED100S/840 PSD PCO 7 WH	White
910925864298	LL523X LED123S/840 PSD PCO 7 WH	White
910925867821	LL512X LED61S/840 PSD PCO 7 VLC WH XA	White
910925867822	LL523X LED123S/840 PSD PCO 7 VLC WH XA	White
910925867840	LL512X LED61S/840 PSD PCO 7 VLC WH XA	White

Order Code	Full Product Name	Housing Color
910925867841	LL523X LED123S/840 PSD PCO 7 VLC WH XA	White
910925868118	LL523X LED123S/840 PSD PCO 13 ELP3 WH	White
910925868120	LL523X LED62S/840 PSD PCO 13 ELP3 WH	White
910925868975	LL523X LED123S/840 SIA PCO 7 WH HE	White
910925868976	LL523X LED100S/840 SIA PCO 7 WH HE	White
910925868977	LL523X LED62S/840 SIA PCO 7 WH HE	White
910925864354	LL512X LED31S/840 PSD WB 7 BK	Black
910925864355	LL512X LED50S/840 PSD WB 7 BK	Black
910925864356	LL512X LED61S/840 PSD WB 7 BK	Black

Order Code	Full Product Name	Housing Color
910925864357	LL523X LED62S/840 PSD WB 7 BK	Black
910925864358	LL523X LED100S/840 PSD WB 7 BK	Black
910925864359	LL523X LED123S/840 PSD WB 7 BK	Black
910925868122	LL512X LED31S/940 PSED WB-OC 13 BK	Black
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	Black
910925868126	LL523X LED62S/940 PSED WB-OC 13 BK	Black
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	Black
910925864348	LL512X LED31S/840 PSD WB 7 SI	Silver
910925864349	LL512X LED50S/840 PSD WB 7 SI	Silver
910925864350	LL512X LED61S/840 PSD WB 7 SI	Silver
910925864352	LL523X LED100S/840 PSD WB 7 SI	Silver
910925864303	LL512X LED31S/840 PSD WB 7 WH	White
910925864304	LL512X LED50S/840 PSD WB 7 WH	White
910925864305	LL512X LED61S/840 PSD WB 7 WH	White
910925864309	LL512X LED31S/840 PSED WB 7 WH	White
910925864310	LL512X LED50S/840 PSED WB 7 WH	White
910925864311	LL512X LED61S/840 PSED WB 7 WH	White
910925864312	LL512X LED31S/840 PSD MB 7 WH	White
910925864313	LL512X LED50S/840 PSD MB 7 WH	White
910925864314	LL512X LED61S/840 PSD MB 7 WH	White
910925864320	LL512X LED61S/840 PSD NB 7 WH	White
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	White
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	White
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	White
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	White
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	White
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	White
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	White
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	White
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	White
910925864344	LL512X LED61S/840 PSD A20 7 WH	White
910925864624	LL512X LED50S/835 PSD WB 7 WH	White
910925868121	LL512X LED31S/940 PSED WB-OC 13 WH	White
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	White
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	White
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	White
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	White
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	White
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	White
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	White
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	White
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	White
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	White
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	White
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	White
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	White
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	White
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	White
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	White
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	White
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	White
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	White

Order Code	Full Product Name	Housing Color
910925864306	LL523X LED62S/840 PSD WB 7 WH	White
910925864307	LL523X LED100S/840 PSD WB 7 WH	White
910925864308	LL523X LED123S/840 PSD WB 7 WH	White
910925864315	LL523X LED62S/840 PSD MB 7 WH	White
910925864316	LL523X LED100S/840 PSD MB 7 WH	White
910925864317	LL523X LED123S/840 PSD MB 7 WH	White
910925864321	LL523X LED62S/840 PSD NB 7 WH	White
910925864322	LL523X LED100S/840 PSD NB 7 WH	White
910925864323	LL523X LED123S/840 PSD NB 7 WH	White
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	White
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	White
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	White
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	White
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	White
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	White
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	White
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	White
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	White
910925864346	LL523X LED100S/840 PSD A20 7 WH	White
910925864347	LL523X LED123S/840 PSD A20 7 WH	White
910925864351	LL523X LED62S/840 PSD WB 7 SI	Silver
910925864353	LL523X LED123S/840 PSD WB 7 SI	Silver
910925864625	LL523X LED100S/835 PSD WB 7 WH	White
910925865537	LL523X LED160S/840 PSD MB 7 WH	White
910925865538	LL523X LED160S/840 PSD NB 7 WH	White
910925865539	LL523X LED160S/840 PSD XNB 7 WH	White
910925865540	LL523X LED160S/830 PSD MB 7 WH	White
910925865541	LL523X LED160S/830 PSD NB 7 WH	White
910925865542	LL523X LED160S/830 PSD XNB 7 WH	White
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	White
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	White
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	White
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	White
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	White
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	White
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	White
910925867817	LL523X LED100S/840 PSD MB 7 VLC WH XA	White
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	White
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	White
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	White
910925867823	LL523X LED100S/840 PSED MB 13 VLC WH XA	White
910925867824	LL523X LED100S/840 PSED WB 13 VLC WH XA	White
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	White
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	White
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	White
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	White
910925867836	LL523X LED100S/840 PSD MB 7 VLC WH XA	White
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	White
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	White
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	White
910925867842	LL523X LED100S/840 PSED MB 13 VLC WH XA	White
910925867843	LL523X LED100S/840 PSED WB 13 VLC WH XA	White

Order Code	Full Product Name	Housing Color
910925867853	LL523X LED100S/840 PSD WB 7 VLC WH XA	White
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	White
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	White
910925868111	LL523X LED62S/840 PSED WB 13 WH	White
910925868119	LL523X LED62S/840 PSD WB 13 ELP3 WH	White
910925868125	LL523X LED62S/940 PSED WB-OC 13 WH	White
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	White
910925868129	LL523X LED62S/940 PSD WB-OC 13 ELP3 WH	White
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	White
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	White
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	White
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	White
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	White
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	White
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	White
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	White
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	White
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	White
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	White
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	White

Order Code	Full Product Name	Housing Color
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	White
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	White
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	White
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	White
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	White
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	White
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	White
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	White
910925864377	LL612X LED61S/840 PSD WB 7 WH	White
910925864378	LL612X LED61S/840 PSD MB 7 WH	White
910925864379	LL612X LED61S/840 PSD NB 7 WH	White
910925864380	LL623X LED123S/840 PSD WB 7 WH	White
910925864381	LL623X LED123S/840 PSD MB 7 WH	White
910925864382	LL623X LED123S/840 PSD NB 7 WH	White
910925868648	LL515X 61S/840 PSD WB 7 HE WH	White
910925868649	LL515X 80S/840 PSD WB 7 HE WH	White
910925868650	LL515X 61S/840 PSD MB 7 HE WH	White
910925868651	LL515X 80S/840 PSD MB 7 HE WH	White
910925868652	LL515X 61S/840 PSD NB 7 HE WH	White
910925868653	LL515X 80S/840 PSD NB 7 HE WH	White

Approval and Application

Order Code	Full Product Name	Ingress protection code
910925864293	LL512X LED31S/840 PSD PCO 7 WH	IP20
910925864294	LL512X LED50S/840 PSD PCO 7 WH	IP20
910925864295	LL512X LED61S/840 PSD PCO 7 WH	IP20
910925864296	LL523X LED62S/840 PSD PCO 7 WH	IP20
910925864297	LL523X LED100S/840 PSD PCO 7 WH	IP20
910925864298	LL523X LED123S/840 PSD PCO 7 WH	IP20
910925867821	LL512X LED61S/840 PSD PCO 7 VLC WH XA	IP20
910925867822	LL523X LED123S/840 PSD PCO 7 VLC WH XA	IP20
910925867840	LL512X LED61S/840 PSD PCO 7 VLC WH XA	IP20
910925867841	LL523X LED123S/840 PSD PCO 7 VLC WH XA	IP20
910925868118	LL523X LED123S/840 PSD PCO 13 ELP3 WH	IP20
910925868120	LL523X LED62S/840 PSD PCO 13 ELP3 WH	IP20
910925868975	LL523X LED123S/840 SIA PCO 7 WH HE	IP20
910925868976	LL523X LED100S/840 SIA PCO 7 WH HE	IP20
910925868977	LL523X LED62S/840 SIA PCO 7 WH HE	IP20
910925864354	LL512X LED31S/840 PSD WB 7 BK	IP20
910925864355	LL512X LED50S/840 PSD WB 7 BK	IP20
910925864356	LL512X LED61S/840 PSD WB 7 BK	IP20
910925864357	LL523X LED62S/840 PSD WB 7 BK	IP20
910925864358	LL523X LED100S/840 PSD WB 7 BK	IP20
910925864359	LL523X LED123S/840 PSD WB 7 BK	IP20
910925868122	LL512X LED31S/940 PSED WB-OC 13 BK	IP20
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	IP20
910925868126	LL523X LED62S/940 PSED WB-OC 13 BK	IP20
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	IP20
910925864348	LL512X LED31S/840 PSD WB 7 SI	IP20
910925864349	LL512X LED50S/840 PSD WB 7 SI	IP20
910925864350	LL512X LED61S/840 PSD WB 7 SI	IP20

Order Code	Full Product Name	Ingress protection code
910925864352	LL523X LED100S/840 PSD WB 7 SI	IP20
910925864303	LL512X LED31S/840 PSD WB 7 WH	IP20
910925864304	LL512X LED50S/840 PSD WB 7 WH	IP20
910925864305	LL512X LED61S/840 PSD WB 7 WH	IP20
910925864309	LL512X LED31S/840 PSED WB 7 WH	IP20
910925864310	LL512X LED50S/840 PSED WB 7 WH	IP20
910925864311	LL512X LED61S/840 PSED WB 7 WH	IP20
910925864312	LL512X LED31S/840 PSD MB 7 WH	IP20
910925864313	LL512X LED50S/840 PSD MB 7 WH	IP20
910925864314	LL512X LED61S/840 PSD MB 7 WH	IP20
910925864320	LL512X LED61S/840 PSD NB 7 WH	IP20
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	IP20
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	IP20
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	IP20
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	IP20
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	IP20
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	IP20
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	IP20
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	IP20
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	IP20
910925864344	LL512X LED61S/840 PSD A20 7 WH	IP20
910925864624	LL512X LED50S/835 PSD WB 7 WH	IP20
910925868121	LL512X LED31S/940 PSED WB-OC 13 WH	IP20
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	IP20
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	IP20
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	IP20
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	IP20
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	IP20

Order Code	Full Product Name	Ingress protection code
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	IP20
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	IP20
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	IP20
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	IP20
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	IP20
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	IP20
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	IP20
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	IP20
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	IP20
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	IP20
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	IP20
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	IP20
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	IP20
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	IP20
910925864306	LL523X LED62S/840 PSD WB 7 WH	IP20
910925864307	LL523X LED100S/840 PSD WB 7 WH	IP20
910925864308	LL523X LED123S/840 PSD WB 7 WH	IP20
910925864315	LL523X LED62S/840 PSD MB 7 WH	IP20
910925864316	LL523X LED100S/840 PSD MB 7 WH	IP20
910925864317	LL523X LED123S/840 PSD MB 7 WH	IP20
910925864321	LL523X LED62S/840 PSD NB 7 WH	IP20
910925864322	LL523X LED100S/840 PSD NB 7 WH	IP20
910925864323	LL523X LED123S/840 PSD NB 7 WH	IP20
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	IP20
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	IP20
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	IP20
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	IP20
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	IP20
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	IP20
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	IP20
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	IP20
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	IP20
910925864346	LL523X LED100S/840 PSD A20 7 WH	IP20
910925864347	LL523X LED123S/840 PSD A20 7 WH	IP20
910925864351	LL523X LED62S/840 PSD WB 7 SI	IP20
910925864353	LL523X LED123S/840 PSD WB 7 SI	IP20
910925864625	LL523X LED100S/835 PSD WB 7 WH	IP20
910925865537	LL523X LED160S/840 PSD MB 7 WH	IP20
910925865538	LL523X LED160S/840 PSD NB 7 WH	IP20
910925865539	LL523X LED160S/840 PSD XNB 7 WH	IP20
910925865540	LL523X LED160S/830 PSD MB 7 WH	IP20
910925865541	LL523X LED160S/830 PSD NB 7 WH	IP20
910925865542	LL523X LED160S/830 PSD XNB 7 WH	IP20
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	IP20
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	IP20
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	IP20
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	IP20
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	IP20
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	IP20
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	IP20
910925867817	LL523X LED100S/840 PSD MB 7 VLC WH XA	IP20
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	IP20

Order Code	Full Product Name	Ingress protection code
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	IP20
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	IP20
910925867823	LL523X LED100S/840 PSED MB 13 VLC WH XA	IP20
910925867824	LL523X LED100S/840 PSED WB 13 VLC WH XA	IP20
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	IP20
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	IP20
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	IP20
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	IP20
910925867836	LL523X LED100S/840 PSD MB 7 VLC WH XA	IP20
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	IP20
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	IP20
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	IP20
910925867842	LL523X LED100S/840 PSED MB 13 VLC WH XA	IP20
910925867843	LL523X LED100S/840 PSED WB 13 VLC WH XA	IP20
910925867853	LL523X LED100S/840 PSD WB 7 VLC WH XA	IP20
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	IP20
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	IP20
910925868111	LL523X LED62S/840 PSED WB 13 WH	IP20
910925868119	LL523X LED62S/840 PSD WB 13 ELP3 WH	IP20
910925868125	LL523X LED62S/940 PSED WB-OC 13 WH	IP20
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	IP20
910925868129	LL523X LED62S/940 PSD WB-OC 13 ELP3 WH	IP20
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	IP20
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	IP20
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	IP20
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	IP20
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	IP20
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	IP20
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	IP20
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	IP20
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	IP20
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	IP20
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	IP20
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	IP20
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	IP20
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	IP20
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	IP20
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	IP20
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	IP20
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	IP20
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	IP20
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	IP20
910925864377	LL612X LED61S/840 PSD WB 7 WH	IP54

Order Code	Full Product Name	Ingress protection code
910925864378	LL612X LED61S/840 PSD MB 7 WH	IP54
910925864379	LL612X LED61S/840 PSD NB 7 WH	IP54
910925864380	LL623X LED123S/840 PSD WB 7 WH	IP54
910925864381	LL623X LED123S/840 PSD MB 7 WH	IP54
910925864382	LL623X LED123S/840 PSD NB 7 WH	IP54
910925868648	LL515X 61S/840 PSD WB 7 HE WH	IP20

Order Code	Full Product Name	Ingress protection code
910925868649	LL515X 80S/840 PSD WB 7 HE WH	IP20
910925868650	LL515X 61S/840 PSD MB 7 HE WH	IP20
910925868651	LL515X 80S/840 PSD MB 7 HE WH	IP20
910925868652	LL515X 61S/840 PSD NB 7 HE WH	IP20
910925868653	LL515X 80S/840 PSD NB 7 HE WH	IP20

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910925864293	LL512X LED31S/840 PSD PCO 7 WH	(0.34. 0.35) SDCM <3
910925864294	LL512X LED50S/840 PSD PCO 7 WH	(0.34. 0.35) SDCM <3
910925864295	LL512X LED61S/840 PSD PCO 7 WH	(0.34. 0.35) SDCM <3
910925864296	LL523X LED62S/840 PSD PCO 7 WH	(0.34. 0.35) SDCM <3
910925864297	LL523X LED100S/840 PSD PCO 7 WH	(0.34. 0.35) SDCM <3
910925864298	LL523X LED123S/840 PSD PCO 7 WH	(0.34. 0.35) SDCM <3
910925867821	LL512X LED61S/840 PSD PCO 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867822	LL523X LED123S/840 PSD PCO 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867840	LL512X LED61S/840 PSD PCO 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867841	LL523X LED123S/840 PSD PCO 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925868118	LL523X LED123S/840 PSD PCO 13 ELP3 WH	(0.34. 0.35) SDCM <3
910925868120	LL523X LED62S/840 PSD PCO 13 ELP3 WH	(0.34. 0.35) SDCM <3
910925868975	LL523X LED123S/840 SIA PCO 7 WH HE	(0.34. 0.35) SDCM <3
910925868976	LL523X LED100S/840 SIA PCO 7 WH HE	(0.34. 0.35) SDCM <3
910925868977	LL523X LED62S/840 SIA PCO 7 WH HE	(0.34. 0.35) SDCM <3
910925864354	LL512X LED31S/840 PSD WB 7 BK	(0.34. 0.35) SDCM <3
910925864355	LL512X LED50S/840 PSD WB 7 BK	(0.34. 0.35) SDCM <3
910925864356	LL512X LED61S/840 PSD WB 7 BK	(0.34. 0.35) SDCM <3
910925864357	LL523X LED62S/840 PSD WB 7 BK	(0.34. 0.35) SDCM <3
910925864358	LL523X LED100S/840 PSD WB 7 BK	(0.34. 0.35) SDCM <3
910925864359	LL523X LED123S/840 PSD WB 7 BK	(0.34. 0.35) SDCM <3
910925868122	LL512X LED31S/940 PSED WB-OC 13 BK	(0.34. 0.35) SDCM <3
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	(0.34. 0.35) SDCM <3
910925868126	LL523X LED62S/940 PSED WB-OC 13 BK	(0.34. 0.35) SDCM <3
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	(0.34. 0.35) SDCM <3
910925864348	LL512X LED31S/840 PSD WB 7 SI	(0.34. 0.35) SDCM <3
910925864349	LL512X LED50S/840 PSD WB 7 SI	(0.34. 0.35) SDCM <3
910925864350	LL512X LED61S/840 PSD WB 7 SI	(0.34. 0.35) SDCM <3
910925864352	LL523X LED100S/840 PSD WB 7 SI	(0.34. 0.35) SDCM <3
910925864303	LL512X LED31S/840 PSD WB 7 WH	(0.34. 0.35) SDCM <3
910925864304	LL512X LED50S/840 PSD WB 7 WH	(0.34. 0.35) SDCM <3
910925864305	LL512X LED61S/840 PSD WB 7 WH	(0.34. 0.35) SDCM <3
910925864309	LL512X LED31S/840 PSED WB 7 WH	(0.34. 0.35) SDCM <3
910925864310	LL512X LED50S/840 PSED WB 7 WH	(0.34. 0.35) SDCM <3
910925864311	LL512X LED61S/840 PSED WB 7 WH	(0.34. 0.35) SDCM <3
910925864312	LL512X LED31S/840 PSD MB 7 WH	(0.34. 0.35) SDCM <3
910925864313	LL512X LED50S/840 PSD MB 7 WH	(0.34. 0.35) SDCM <3
910925864314	LL512X LED61S/840 PSD MB 7 WH	(0.34. 0.35) SDCM <3
910925864320	LL512X LED61S/840 PSD NB 7 WH	(0.34. 0.35) SDCM <3
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	(0.34. 0.35) SDCM <3
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	(0.34. 0.35) SDCM <3
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	(0.34. 0.35) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	(0.34. 0.35) SDCM <3
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	(0.34. 0.35) SDCM <3
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	(0.34. 0.35) SDCM <3
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	(0.34. 0.35) SDCM <3
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	(0.34. 0.35) SDCM <3
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	(0.34. 0.35) SDCM <3
910925864344	LL512X LED61S/840 PSD A20 7 WH	(0.34. 0.35) SDCM <3
910925864624	LL512X LED50S/835 PSD WB 7 WH	(0.34. 0.35) SDCM <3
910925868121	LL512X LED31S/940 PSED WB-OC 13 WH	(0.34. 0.35) SDCM <3
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	(0.34. 0.35) SDCM <3
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	(0.34. 0.35) SDCM <3
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	(0.34. 0.35) SDCM <3
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	(0.34. 0.35) SDCM <3
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	(0.34. 0.35) SDCM <3
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	(0.34. 0.35) SDCM <3
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	(0.34. 0.35) SDCM <3
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	(0.34. 0.35) SDCM <3
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	(0.34. 0.35) SDCM <3
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	(0.34. 0.35) SDCM <3
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	(0.34. 0.35) SDCM <3
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	(0.34. 0.35) SDCM <3
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	(0.34. 0.35) SDCM <3
910925864306	LL523X LED62S/840 PSD WB 7 WH	(0.34. 0.35) SDCM <3
910925864307	LL523X LED100S/840 PSD WB 7 WH	(0.34. 0.35) SDCM <3
910925864308	LL523X LED123S/840 PSD WB 7 WH	(0.34. 0.35) SDCM <3
910925864315	LL523X LED62S/840 PSD MB 7 WH	(0.34. 0.35) SDCM <3
910925864316	LL523X LED100S/840 PSD MB 7 WH	(0.34. 0.35) SDCM <3
910925864317	LL523X LED123S/840 PSD MB 7 WH	(0.34. 0.35) SDCM <3
910925864321	LL523X LED62S/840 PSD NB 7 WH	(0.34. 0.35) SDCM <3
910925864322	LL523X LED100S/840 PSD NB 7 WH	(0.34. 0.35) SDCM <3
910925864323	LL523X LED123S/840 PSD NB 7 WH	(0.34. 0.35) SDCM <3
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	(0.34. 0.35) SDCM <3
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	(0.34. 0.35) SDCM <3
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	(0.34. 0.35) SDCM <3
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	(0.34. 0.35) SDCM <3
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	(0.34. 0.35) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	(0.34. 0.35) SDCM <3
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	(0.34. 0.35) SDCM <3
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	(0.34. 0.35) SDCM <3
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	(0.34. 0.35) SDCM <3
910925864346	LL523X LED100S/840 PSD A20 7 WH	(0.34. 0.35) SDCM <3
910925864347	LL523X LED123S/840 PSD A20 7 WH	(0.34. 0.35) SDCM <3
910925864351	LL523X LED62S/840 PSD WB 7 SI	(0.34. 0.35) SDCM <3
910925864353	LL523X LED123S/840 PSD WB 7 SI	(0.34. 0.35) SDCM <3
910925864625	LL523X LED100S/835 PSD WB 7 WH	(0.34. 0.35) SDCM <3
910925865537	LL523X LED160S/840 PSD MB 7 WH	(0.34. 0.35) SDCM <3
910925865538	LL523X LED160S/840 PSD NB 7 WH	(0.34. 0.35) SDCM <3
910925865539	LL523X LED160S/840 PSD XNB 7 WH	(0.34. 0.35) SDCM <3
910925865540	LL523X LED160S/830 PSD MB 7 WH	(0.4314.0.4000) SDCM
910925865541	LL523X LED160S/830 PSD NB 7 WH	(0.4314.0.4000) SDCM
910925865542	LL523X LED160S/830 PSD XNB 7 WH	(0.4314.0.4000) SDCM
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	(0.34. 0.35) SDCM <3
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	(0.34. 0.35) SDCM <3
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	(0.34. 0.35) SDCM <3
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	(0.34. 0.35) SDCM <3
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	(0.34. 0.35) SDCM <3
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	(0.34. 0.35) SDCM <3
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	(0.34. 0.35) SDCM <3
910925867817	LL523X LED100S/840 PSD MB 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	(0.34. 0.35) SDCM <3
910925867823	LL523X LED100S/840 PSED MB 13 VLC WH XA	(0.34. 0.35) SDCM <3
910925867824	LL523X LED100S/840 PSED WB 13 VLC WH XA	(0.34. 0.35) SDCM <3
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	(0.34. 0.35) SDCM <3
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	(0.34. 0.35) SDCM <3
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	(0.34. 0.35) SDCM <3
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	(0.34. 0.35) SDCM <3
910925867836	LL523X LED100S/840 PSD MB 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	(0.34. 0.35) SDCM <3
910925867842	LL523X LED100S/840 PSED MB 13 VLC WH XA	(0.34. 0.35) SDCM <3
910925867843	LL523X LED100S/840 PSED WB 13 VLC WH XA	(0.34. 0.35) SDCM <3

Order Code	Full Product Name	Initial chromaticity
910925867853	LL523X LED100S/840 PSD WB 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	(0.34. 0.35) SDCM <3
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	(0.34. 0.35) SDCM <3
910925868111	LL523X LED62S/840 PSED WB 13 WH	(0.34. 0.35) SDCM <3
910925868119	LL523X LED62S/840 PSD WB 13 ELP3 WH	(0.34. 0.35) SDCM <3
910925868125	LL523X LED62S/940 PSED WB-OC 13 WH	(0.34. 0.35) SDCM <3
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	(0.34. 0.35) SDCM <3
910925868129	LL523X LED62S/940 PSD WB-OC 13 ELP3 WH	(0.34. 0.35) SDCM <3
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	(0.34. 0.35) SDCM <3
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	(0.34. 0.35) SDCM <3
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	(0.34. 0.35) SDCM <3
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	(0.34. 0.35) SDCM <3
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	(0.34. 0.35) SDCM <3
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	(0.34. 0.35) SDCM <3
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	(0.34. 0.35) SDCM <3
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	(0.34. 0.35) SDCM <3
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	(0.34. 0.35) SDCM <3
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	(0.34. 0.35) SDCM <3
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	(0.34. 0.35) SDCM <3
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	(0.34. 0.35) SDCM <3
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	(0.34. 0.35) SDCM <3
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	(0.34. 0.35) SDCM <3
910925864377	LL612X LED61S/840 PSD WB 7 WH	(0.34. 0.35) SDCM <3
910925864378	LL612X LED61S/840 PSD MB 7 WH	(0.34. 0.35) SDCM <3
910925864379	LL612X LED61S/840 PSD NB 7 WH	(0.34. 0.35) SDCM <3
910925864380	LL623X LED123S/840 PSD WB 7 WH	(0.34. 0.35) SDCM <3
910925864381	LL623X LED123S/840 PSD MB 7 WH	(0.34. 0.35) SDCM <3
910925864382	LL623X LED123S/840 PSD NB 7 WH	(0.34. 0.35) SDCM <3
910925868648	LL515X 61S/840 PSD WB 7 HE WH	(0.34. 0.35) SDCM <3
910925868649	LL515X 80S/840 PSD WB 7 HE WH	(0.34. 0.35) SDCM <3
910925868650	LL515X 61S/840 PSD MB 7 HE WH	(0.34. 0.35) SDCM <3
910925868651	LL515X 80S/840 PSD MB 7 HE WH	(0.34. 0.35) SDCM <3
910925868652	LL515X 61S/840 PSD NB 7 HE WH	(0.34. 0.35) SDCM <3
910925868653	LL515X 80S/840 PSD NB 7 HE WH	(0.34. 0.35) SDCM <3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
910925864293	LL512X LED31S/840 PSD PCO 7 WH	-
910925864294	LL512X LED50S/840 PSD PCO 7 WH	-
910925864295	LL512X LED61S/840 PSD PCO 7 WH	-
910925864296	LL523X LED62S/840 PSD PCO 7 WH	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925864297	LL523X LED100S/840 PSD PCO 7 WH	-
910925864298	LL523X LED123S/840 PSD PCO 7 WH	-
910925867821	LL512X LED61S/840 PSD PCO 7 VLC WH XA	-
910925867822	LL523X LED123S/840 PSD PCO 7 VLC WH XA	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867840	LL512X LED61S/840 PSD PCO 7 VLC WH XA	-
910925867841	LL523X LED123S/840 PSD PCO 7 VLC WH XA	-
910925868118	LL523X LED123S/840 PSD PCO 13 ELP3 WH	-
910925868120	LL523X LED62S/840 PSD PCO 13 ELP3 WH	-
910925868975	LL523X LED123S/840 SIA PCO 7 WH HE	-
910925868976	LL523X LED100S/840 SIA PCO 7 WH HE	-
910925868977	LL523X LED62S/840 SIA PCO 7 WH HE	-
910925864354	LL512X LED31S/840 PSD WB 7 BK	-
910925864355	LL512X LED50S/840 PSD WB 7 BK	-
910925864356	LL512X LED61S/840 PSD WB 7 BK	-
910925864357	LL523X LED62S/840 PSD WB 7 BK	-
910925864358	LL523X LED100S/840 PSD WB 7 BK	-
910925864359	LL523X LED123S/840 PSD WB 7 BK	-
910925868122	LL512X LED31S/940 PSED WB-OC 13 BK	-
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	-
910925868126	LL523X LED62S/940 PSED WB-OC 13 BK	-
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	-
910925864348	LL512X LED31S/840 PSD WB 7 SI	-
910925864349	LL512X LED50S/840 PSD WB 7 SI	-
910925864350	LL512X LED61S/840 PSD WB 7 SI	-
910925864352	LL523X LED100S/840 PSD WB 7 SI	-
910925864303	LL512X LED31S/840 PSD WB 7 WH	-
910925864304	LL512X LED50S/840 PSD WB 7 WH	-
910925864305	LL512X LED61S/840 PSD WB 7 WH	-
910925864309	LL512X LED31S/840 PSED WB 7 WH	-
910925864310	LL512X LED50S/840 PSED WB 7 WH	-
910925864311	LL512X LED61S/840 PSED WB 7 WH	-
910925864312	LL512X LED31S/840 PSD MB 7 WH	-
910925864313	LL512X LED50S/840 PSD MB 7 WH	-
910925864314	LL512X LED61S/840 PSD MB 7 WH	-
910925864320	LL512X LED61S/840 PSD NB 7 WH	-
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	-
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	-
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	-
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	-
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	-
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	-
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	-
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	-
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	-
910925864344	LL512X LED61S/840 PSD A20 7 WH	-
910925864624	LL512X LED50S/835 PSD WB 7 WH	-
910925868121	LL512X LED31S/940 PSED WB-OC 13 WH	-
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	-
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	-
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	-
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	-
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	-
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	-
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	-
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	-
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	-
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	-
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	-
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	-
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	-
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	-
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	-
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	-
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	-
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	-
910925864306	LL523X LED62S/840 PSD WB 7 WH	-
910925864307	LL523X LED100S/840 PSD WB 7 WH	-
910925864308	LL523X LED123S/840 PSD WB 7 WH	-
910925864315	LL523X LED62S/840 PSD MB 7 WH	-
910925864316	LL523X LED100S/840 PSD MB 7 WH	-
910925864317	LL523X LED123S/840 PSD MB 7 WH	-
910925864321	LL523X LED62S/840 PSD NB 7 WH	-
910925864322	LL523X LED100S/840 PSD NB 7 WH	-
910925864323	LL523X LED123S/840 PSD NB 7 WH	-
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	-
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	-
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	-
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	-
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	-
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	-
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	-
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	-
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	-
910925864346	LL523X LED100S/840 PSD A20 7 WH	-
910925864347	LL523X LED123S/840 PSD A20 7 WH	-
910925864351	LL523X LED62S/840 PSD WB 7 SI	-
910925864353	LL523X LED123S/840 PSD WB 7 SI	-
910925864625	LL523X LED100S/835 PSD WB 7 WH	-
910925865537	LL523X LED160S/840 PSD MB 7 WH	0.50 %
910925865538	LL523X LED160S/840 PSD NB 7 WH	0.50 %
910925865539	LL523X LED160S/840 PSD XNB 7 WH	0.50 %
910925865540	LL523X LED160S/830 PSD MB 7 WH	0.50 %
910925865541	LL523X LED160S/830 PSD NB 7 WH	0.50 %
910925865542	LL523X LED160S/830 PSD XNB 7 WH	0.50 %
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	-
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	-
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	-
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	-
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	-
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	-
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	-
910925867817	LL523X LED100S/840 PSD MB 7 VLC WH XA	-
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	-
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	-
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925867823	LL523X LED100S/840 PSED MB 13 VLC WH XA	-
910925867824	LL523X LED100S/840 PSED WB 13 VLC WH XA	-
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	-
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	-
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	-
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	-
910925867836	LL523X LED100S/840 PSD MB 7 VLC WH XA	-
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	-
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	-
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	-
910925867842	LL523X LED100S/840 PSED MB 13 VLC WH XA	-
910925867843	LL523X LED100S/840 PSED WB 13 VLC WH XA	-
910925867853	LL523X LED100S/840 PSD WB 7 VLC WH XA	-
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	-
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	-
910925868111	LL523X LED62S/840 PSED WB 13 WH	-
910925868119	LL523X LED62S/840 PSD WB 13 ELP3 WH	-
910925868125	LL523X LED62S/940 PSED WB-OC 13 WH	-
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	-
910925868129	LL523X LED62S/940 PSD WB-OC 13 ELP3 WH	-
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	-

Order Code	Full Product Name	Driver failure rate at 5000 h
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	-
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	-
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	-
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	-
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	-
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	-
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	-
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	-
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	-
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	-
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	-
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	-
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	-
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	-
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	-
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	-
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	-
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	-
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	-
910925864377	LL612X LED61S/840 PSD WB 7 WH	-
910925864378	LL612X LED61S/840 PSD MB 7 WH	-
910925864379	LL612X LED61S/840 PSD NB 7 WH	-
910925864380	LL623X LED123S/840 PSD WB 7 WH	-
910925864381	LL623X LED123S/840 PSD MB 7 WH	-
910925864382	LL623X LED123S/840 PSD NB 7 WH	-
910925868648	LL515X 61S/840 PSD WB 7 HE WH	-
910925868649	LL515X 80S/840 PSD WB 7 HE WH	-
910925868650	LL515X 61S/840 PSD MB 7 HE WH	-
910925868651	LL515X 80S/840 PSD MB 7 HE WH	-
910925868652	LL515X 61S/840 PSD NB 7 HE WH	-
910925868653	LL515X 80S/840 PSD NB 7 HE WH	-

Application Conditions

Order Code	Full Product Name	Suitable for random switching
910925864293	LL512X LED31S/840 PSD PCO 7 WH	Not applicable
910925864294	LL512X LED50S/840 PSD PCO 7 WH	Not applicable
910925864295	LL512X LED61S/840 PSD PCO 7 WH	Not applicable
910925864296	LL523X LED62S/840 PSD PCO 7 WH	Not applicable
910925864297	LL523X LED100S/840 PSD PCO 7 WH	Not applicable
910925864298	LL523X LED123S/840 PSD PCO 7 WH	Not applicable
910925867821	LL512X LED61S/840 PSD PCO 7 VLC WH XA	Not applicable
910925867822	LL523X LED123S/840 PSD PCO 7 VLC WH XA	Not applicable
910925867840	LL512X LED61S/840 PSD PCO 7 VLC WH XA	Not applicable
910925867841	LL523X LED123S/840 PSD PCO 7 VLC WH XA	Not applicable
910925868118	LL523X LED123S/840 PSD PCO 13 ELP3 WH	Not applicable
910925868120	LL523X LED62S/840 PSD PCO 13 ELP3 WH	Not applicable
910925868975	LL523X LED123S/840 SIA PCO 7 WH HE	Not applicable
910925868976	LL523X LED100S/840 SIA PCO 7 WH HE	Not applicable
910925868977	LL523X LED62S/840 SIA PCO 7 WH HE	Not applicable

Order Code	Full Product Name	Suitable for random switching
910925864354	LL512X LED31S/840 PSD WB 7 BK	Not applicable
910925864355	LL512X LED50S/840 PSD WB 7 BK	Not applicable
910925864356	LL512X LED61S/840 PSD WB 7 BK	Not applicable
910925864357	LL523X LED62S/840 PSD WB 7 BK	Not applicable
910925864358	LL523X LED100S/840 PSD WB 7 BK	Not applicable
910925864359	LL523X LED123S/840 PSD WB 7 BK	Not applicable
910925868122	LL512X LED31S/940 PSED WB-OC 13 BK	Not applicable
910925868124	LL512X LED31S/840 PSED WB-OC 13 BK XA	Not applicable
910925868126	LL523X LED62S/940 PSED WB-OC 13 BK	Not applicable
910925868128	LL523X LED62S/840 PSED WB-OC 13 BK XA	Not applicable
910925864348	LL512X LED31S/840 PSD WB 7 SI	Not applicable
910925864349	LL512X LED50S/840 PSD WB 7 SI	Not applicable
910925864350	LL512X LED61S/840 PSD WB 7 SI	Not applicable
910925864352	LL523X LED100S/840 PSD WB 7 SI	Not applicable
910925864303	LL512X LED31S/840 PSD WB 7 WH	Not applicable

Order Code	Full Product Name	Suitable for random switching
910925864304	LL512X LED50S/840 PSD WB 7 WH	Not applicable
910925864305	LL512X LED61S/840 PSD WB 7 WH	Not applicable
910925864309	LL512X LED31S/840 PSED WB 7 WH	Not applicable
910925864310	LL512X LED50S/840 PSED WB 7 WH	Not applicable
910925864311	LL512X LED61S/840 PSED WB 7 WH	Not applicable
910925864312	LL512X LED31S/840 PSD MB 7 WH	Not applicable
910925864313	LL512X LED50S/840 PSD MB 7 WH	Not applicable
910925864314	LL512X LED61S/840 PSD MB 7 WH	Not applicable
910925864320	LL512X LED61S/840 PSD NB 7 WH	Not applicable
910925864324	LL512X LED31S/840 PSD DA35W 7 WH	Not applicable
910925864325	LL512X LED50S/840 PSD DA35W 7 WH	Not applicable
910925864326	LL512X LED61S/840 PSD DA35W 7 WH	Not applicable
910925864330	LL512X LED31S/840 PSD DA25W 7 WH	Not applicable
910925864331	LL512X LED50S/840 PSD DA25W 7 WH	Not applicable
910925864332	LL512X LED61S/840 PSD DA25W 7 WH	Not applicable
910925864336	LL512X LED31S/840 PSD DA25N 7 WH	Not applicable
910925864337	LL512X LED50S/840 PSD DA25N 7 WH	Not applicable
910925864338	LL512X LED61S/840 PSD DA25N 7 WH	Not applicable
910925864344	LL512X LED61S/840 PSD A20 7 WH	Not applicable
910925864624	LL512X LED50S/835 PSD WB 7 WH	Not applicable
910925868121	LL512X LED31S/940 PSED WB-OC 13 WH	Not applicable
910925868123	LL512X LED31S/840 PSED WB-OC 13 WH XA	Not applicable
910925868139	LL512X LED31S/840 PSD WB-OC 7 WH XA	Not applicable
910925868958	LL512X LED31S/840 PSD MB 7 WH HE	Not applicable
910925868959	LL512X LED31S/840 PSD WB 7 WH HE	Not applicable
910925868960	LL512X LED50S/840 PSD MB 7 WH HE	Not applicable
910925868961	LL512X LED50S/840 PSD WB 7 WH HE	Not applicable
910925868962	LL512X LED61S/840 PSD NB 7 WH HE	Not applicable
910925868963	LL512X LED61S/840 PSD MB 7 WH HE	Not applicable
910925868964	LL512X LED61S/840 PSD WB 7 WH HE	Not applicable
910925868965	LL512X LED80S/840 PSD NB 7 WH HE	Not applicable
910925868966	LL512X LED80S/840 PSD MB 7 WH HE	Not applicable
910925868979	LL512X LED50S/840 SIA WB 7 WH HE	Not applicable
910925868980	LL512X LED61S/840 SIA NB 7 WH HE	Not applicable
910925868981	LL512X LED61S/840 SIA MB 7 WH HE	Not applicable
910925868982	LL512X LED61S/840 SIA WB 7 WH HE	Not applicable
910925868983	LL512X LED80S/840 SIA NB 7 WH HE	Not applicable
910925868984	LL512X LED80S/840 SIA MB 7 WH HE	Not applicable
910925868986	LL512X LED31S/840 SIA WB 7 WH HE	Not applicable
910925869743	LL512X LED80S/840 PSD WB 7 WH HE	Not applicable
910925864306	LL523X LED62S/840 PSD WB 7 WH	Not applicable
910925864307	LL523X LED100S/840 PSD WB 7 WH	Not applicable
910925864308	LL523X LED123S/840 PSD WB 7 WH	Not applicable
910925864315	LL523X LED62S/840 PSD MB 7 WH	Not applicable
910925864316	LL523X LED100S/840 PSD MB 7 WH	Not applicable
910925864317	LL523X LED123S/840 PSD MB 7 WH	Not applicable
910925864321	LL523X LED62S/840 PSD NB 7 WH	Not applicable
910925864322	LL523X LED100S/840 PSD NB 7 WH	Not applicable
910925864323	LL523X LED123S/840 PSD NB 7 WH	Not applicable
910925864327	LL523X LED62S/840 PSD DA35W 7 WH	Not applicable
910925864328	LL523X LED100S/840 PSD DA35W 7 WH	Not applicable

Order Code	Full Product Name	Suitable for random switching
910925864329	LL523X LED123S/840 PSD DA35W 7 WH	Not applicable
910925864333	LL523X LED62S/840 PSD DA25W 7 WH	Not applicable
910925864334	LL523X LED100S/840 PSD DA25W 7 WH	Not applicable
910925864335	LL523X LED123S/840 PSD DA25W 7 WH	Not applicable
910925864339	LL523X LED62S/840 PSD DA25N 7 WH	Not applicable
910925864340	LL523X LED100S/840 PSD DA25N 7 WH	Not applicable
910925864341	LL523X LED123S/840 PSD DA25N 7 WH	Not applicable
910925864346	LL523X LED100S/840 PSD A20 7 WH	Not applicable
910925864347	LL523X LED123S/840 PSD A20 7 WH	Not applicable
910925864351	LL523X LED62S/840 PSD WB 7 SI	Not applicable
910925864353	LL523X LED123S/840 PSD WB 7 SI	Not applicable
910925864625	LL523X LED100S/835 PSD WB 7 WH	Not applicable
910925865537	LL523X LED160S/840 PSD MB 7 WH	Not applicable
910925865538	LL523X LED160S/840 PSD NB 7 WH	Not applicable
910925865539	LL523X LED160S/840 PSD XNB 7 WH	Not applicable
910925865540	LL523X LED160S/830 PSD MB 7 WH	Not applicable
910925865541	LL523X LED160S/830 PSD NB 7 WH	Not applicable
910925865542	LL523X LED160S/830 PSD XNB 7 WH	Not applicable
910925867810	LL523X LED123S/830 PSD WB 7 WH XA	Not applicable
910925867811	LL523X LED160S/830 PSD MB 7 WH XA	Not applicable
910925867812	LL523X LED123S/830 PSD DA45W 7 WH XA	Not applicable
910925867813	LL523X LED123S/840 PSD DA45W 7 WH XA	Not applicable
910925867814	LL523X LED160S/830 PSD WB 7 WH XA	Not applicable
910925867815	LL523X LED160S/830 PSD NB 7 WH XA	Not applicable
910925867816	LL523X LED123S/840 PSD WB 7 WH XA	Not applicable
910925867817	LL523X LED100S/840 PSD MB 7 VLC WH XA	Not applicable
910925867818	LL523X LED123S/840 PSD MB 7 VLC WH XA	Not applicable
910925867819	LL523X LED123S/840 PSD WB 7 VLC WH XA	Not applicable
910925867820	LL523X LED160S/840 PSD MB 7 WH XA	Not applicable
910925867823	LL523X LED100S/840 PSED MB 13 VLC WH XA	Not applicable
910925867824	LL523X LED100S/840 PSED WB 13 VLC WH XA	Not applicable
910925867825	LL523X LED123S/840 PSED NB 13 VLC WH XA	Not applicable
910925867826	LL523X LED123S/840 PSED MB 13 VLC WH XA	Not applicable
910925867827	LL523X LED123S/840 PSED WB 13 VLC WH XA	Not applicable
910925867828	LL523X LED160S/840 PSED NB 13 WH XA	Not applicable
910925867836	LL523X LED100S/840 PSD MB 7 VLC WH XA	Not applicable
910925867837	LL523X LED123S/840 PSD MB 7 VLC WH XA	Not applicable
910925867838	LL523X LED123S/840 PSD WB 7 VLC WH XA	Not applicable
910925867839	LL523X LED160S/840 PSD MB 7 WH XA	Not applicable
910925867842	LL523X LED100S/840 PSED MB 13 VLC WH XA	Not applicable
910925867843	LL523X LED100S/840 PSED WB 13 VLC WH XA	Not applicable
910925867853	LL523X LED100S/840 PSD WB 7 VLC WH XA	Not applicable
910925867854	LL523X LED123S/840 PSD NB 7 VLC WH XA	Not applicable
910925867855	LL523X LED160S/840 PSD NB 7 WH XA	Not applicable

Maxos fusion

Order Code	Full Product Name	Suitable for random switching
910925868111	LL523X LED62S/840 PSED WB 13 WH	Not applicable
910925868119	LL523X LED62S/840 PSD WB 13 ELP3 WH	Not applicable
910925868125	LL523X LED62S/940 PSED WB-OC 13 WH	Not applicable
910925868127	LL523X LED62S/840 PSED WB-OC 13 WH XA	Not applicable
910925868129	LL523X LED62S/940 PSD WB-OC 13 ELP3 WH	Not applicable
910925868130	LL523X LED62S/840 PSD WB-OC 13 ELP3 WH X	Not applicable
910925868138	LL523X LED62S/840 PSD WB-OC 7 WH XA	Not applicable
910925868949	LL523X LED62S/840 PSD MB 7 WH HE	Not applicable
910925868950	LL523X LED62S/840 PSD WB 7 WH HE	Not applicable
910925868951	LL523X LED100S/840 PSD MB 7 WH HE	Not applicable
910925868952	LL523X LED100S/840 PSD WB 7 WH HE	Not applicable
910925868953	LL523X LED123S/840 PSD NB 7 WH HE	Not applicable
910925868954	LL523X LED123S/840 PSD MB 7 WH HE	Not applicable
910925868955	LL523X LED123S/840 PSD WB 7 WH HE	Not applicable
910925868956	LL523X LED160S/840 PSD NB 7 WH HE	Not applicable
910925868957	LL523X LED160S/840 PSD MB 7 WH HE	Not applicable
910925868967	LL523X LED100S/840 SIA MB 7 WH HE	Not applicable

Order Code	Full Product Name	Suitable for random switching
910925868968	LL523X LED100S/840 SIA WB 7 WH HE	Not applicable
910925868969	LL523X LED123S/840 SIA NB 7 WH HE	Not applicable
910925868970	LL523X LED123S/840 SIA MB 7 WH HE	Not applicable
910925868971	LL523X LED123S/840 SIA WB 7 WH HE	Not applicable
910925868972	LL523X LED160S/840 SIA NB 7 WH HE	Not applicable
910925868973	LL523X LED160S/840 SIA MB 7 WH HE	Not applicable
910925868974	LL523X LED62S/840 SIA WB 7 WH HE	Not applicable
910925869742	LL523X LED160S/840 PSD WB 7 WH HE	Not applicable
910925864377	LL612X LED61S/840 PSD WB 7 WH	Yes
910925864378	LL612X LED61S/840 PSD MB 7 WH	Yes
910925864379	LL612X LED61S/840 PSD NB 7 WH	Yes
910925864380	LL623X LED123S/840 PSD WB 7 WH	Yes
910925864381	LL623X LED123S/840 PSD MB 7 WH	Yes
910925864382	LL623X LED123S/840 PSD NB 7 WH	Yes
910925868648	LL515X 61S/840 PSD WB 7 HE WH	Not applicable
910925868649	LL515X 80S/840 PSD WB 7 HE WH	Not applicable
910925868650	LL515X 61S/840 PSD MB 7 HE WH	Not applicable
910925868651	LL515X 80S/840 PSD MB 7 HE WH	Not applicable
910925868652	LL515X 61S/840 PSD NB 7 HE WH	Not applicable
910925868653	LL515X 80S/840 PSD NB 7 HE WH	Not applicable

© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.