



Product Description

TORNADO

The Helix range is a twist-shape compact fluorescent lamp, with optimal light distribution. It is available in 11W, 15W, 20W and 23W (25W), with lumen equivalence of 60W, 75W, 100W and 125W incandescent light bulb. It is also available in two color temperatures: warm white (2700K) and cool daylight (6500K). It is available in both 220-240V and 120-127V and able to operate under a wide voltage range (Power supply fluctuation). It consumes up to 80% less energy than the incandescent light bulb and lasts for 3 years.

Benefits

Features

Application

Warnings and Safety

Versions



20W, E27



23W, E26, E27



15W, B22



20W, B22



TORNADO

Versions



23W, B22

Dimensional drawing




Product	D (max)	C (max)	F (max)
TORNADO 15W WW E27 220-240V 1PF/6	51.5 mm	107.5 mm	42.5 mm
TORNADO 15W CDL E27 220-240V 1PF/6	51.5 mm	107.5 mm	42.5 mm

Product	D (max)	C (max)	F (max)
TORNADO 24W CDL B22 220-240V 1PF/6	61.5 mm	117 mm	50.5 mm
TORNADO 24W WW B22 220-240V 1PF/6	61.5 mm	117 mm	50.5 mm

Product	D (max)	C (max)	F (max)
TORNADO 20W CDL B22 220-240V 1PF/6	56.5 mm	110.0 mm	47 mm
TORNADO 20W WW B22 220-240V 1PF/6	56.5 mm	110.0 mm	47 mm

TORNADO

Dimensional drawing



Product	D (max)	C (max)	F (max)
TORNADO 15W CDL B22 220-240V 1PF/6	51.5 mm	106.0 mm	42.5 mm
TORNADO 15W WW B22 220-240V 1PF/6	51.5 mm	106.0 mm	42.5 mm

Product	D (max)	C (max)	F (max)
TORNADO 24W CDL E27 220-240V 1PF/6	61.5 mm	118.5 mm	50.5 mm
TORNADO 24W WW E27 220-240V 1PF/6	61.5 mm	118.5 mm	50.5 mm

Product	D (max)	C (max)	F (max)
TORNADO 20W CDL E27 220-240V 1CT/12	56.5 mm	111.5 mm	47 mm
TORNADO 20W CDL E27 220-240V 1PF/6	56.5 mm	111.5 mm	47 mm
TORNADO 20W WW E27 220-240V 1PF/6	56.5 mm	111.5 mm	47 mm

Approval and Application

Energy Efficiency Label (EEL)	A
-------------------------------	---

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Frequency	50 or 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.3 s
Warm Up Time To 60% Light (Max)	60 s
Warm Up Time To 60% Light (Min)	5 s

General Information

Nominal Lifetime (Nom)	8000 h
Rated Lifetime (Hours)	8000 h
Switching Cycle	5000X

Light Technical

Llmf At End Of Nominal Lifetime (Nom)	70 %
Lumen Maintenance 2000 h (Nom)	85 %
Lumen Maintenance 5000 h (Nom)	75 %

Mechanical and Housing

Bulb Shape	Spiral
------------	--------

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h	Mercury (Hg) Content (Nom)
929689848105	TORNADO 15W WW E27 220-240V 1PF/6	15 kWh	-
929689848205	TORNADO 15W CDL E27 220-240V 1PF/6	15 kWh	-
929689848306	TORNADO 20W WW E27 220-240V 1PF/6	20 kWh	1.5 mg
929689848405	TORNADO 20W CDL E27 220-240V 1PF/6	20 kWh	1.5 mg
929689848499	TORNADO 20W CDL E27 220-240V 1CT/12	20 kWh	1.5 mg
929689848506	TORNADO 24W WW E27 220-240V 1PF/6	23 kWh	2 mg
929689848605	TORNADO 24W CDL E27 220-240V 1PF/6	23 kWh	2 mg
929689858102	TORNADO 15W WW B22 220-240V 1PF/6	15 kWh	1.5 mg
929689858202	TORNADO 15W CDL B22 220-240V 1PF/6	15 kWh	1.5 mg
929689858302	TORNADO 20W WW B22 220-240V 1PF/6	20 kWh	1.5 mg
929689858402	TORNADO 20W CDL B22 220-240V 1PF/6	20 kWh	1.5 mg
929689858502	TORNADO 24W WW B22 220-240V 1PF/6	23 kWh	2 mg
929689858602	TORNADO 24W CDL B22 220-240V 1PF/6	23 kWh	2 mg

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
929689848105	TORNADO 15W WW E27 220-240V 1PF/6	110 mA	15 W
929689848205	TORNADO 15W CDL E27 220-240V 1PF/6	110 mA	15 W
929689848306	TORNADO 20W WW E27 220-240V 1PF/6	150 mA	20 W
929689848405	TORNADO 20W CDL E27 220-240V 1PF/6	150 mA	20 W
929689848499	TORNADO 20W CDL E27 220-240V 1CT/12	150 mA	20 W
929689848506	TORNADO 24W WW E27 220-240V 1PF/6	170 mA	23 W
929689848605	TORNADO 24W CDL E27 220-240V 1PF/6	170 mA	23 W

Order Code	Full Product Name	Lamp Current (Nom)	Power (Rated) (Nom)
929689858102	TORNADO 15W WW B22 220-240V 1PF/6	110 mA	15 W
929689858202	TORNADO 15W CDL B22 220-240V 1PF/6	110 mA	15 W
929689858302	TORNADO 20W WW B22 220-240V 1PF/6	150 mA	20 W
929689858402	TORNADO 20W CDL B22 220-240V 1PF/6	150 mA	20 W
929689858502	TORNADO 24W WW B22 220-240V 1PF/6	170 mA	23 W
929689858602	TORNADO 24W CDL B22 220-240V 1PF/6	170 mA	23 W

General Information

Order Code	Full Product Name	Cap-Base
929689848105	TORNADO 15W WW E27 220-240V 1PF/6	E27
929689848205	TORNADO 15W CDL E27 220-240V 1PF/6	E27
929689848306	TORNADO 20W WW E27 220-240V 1PF/6	E27

Order Code	Full Product Name	Cap-Base
929689848405	TORNADO 20W CDL E27 220-240V 1PF/6	E27
929689848499	TORNADO 20W CDL E27 220-240V 1CT/12	E27
929689848506	TORNADO 24W WW E27 220-240V 1PF/6	E27

TORNADO

Order Code	Full Product Name	Cap-Base
929689848605	TORNADO 24W CDL E27 220-240V 1PF/6	E27
929689858102	TORNADO 15W WW B22 220-240V 1PF/6	B22
929689858202	TORNADO 15W CDL B22 220-240V 1PF/6	B22
929689858302	TORNADO 20W WW B22 220-240V 1PF/6	B22

Order Code	Full Product Name	Cap-Base
929689858402	TORNADO 20W CDL B22 220-240V 1PF/6	B22
929689858502	TORNADO 24W WW B22 220-240V 1PF/6	B22
929689858602	TORNADO 24W CDL B22 220-240V 1PF/6	B22

Light Technical (1/2)

Order Code	Full Product Name	Chromaticity		Color	
		Coordinate X (Nom)	Coordinate Y (Nom)	Code	Color Designation
929689848105	TORNADO 15W WW E27 220-240V 1PF/6	463	420	827	Warm White (WW)
929689848205	TORNADO 15W CDL E27 220-240V 1PF/6	313	337	865	Cool Daylight
929689848306	TORNADO 20W WW E27 220-240V 1PF/6	463	420	827	Warm White (WW)
929689848405	TORNADO 20W CDL E27 220-240V 1PF/6	313	337	865	Cool Daylight
929689848499	TORNADO 20W CDL E27 220-240V 1CT/12	313	337	865	Cool Daylight
929689848506	TORNADO 24W WW E27 220-240V 1PF/6	463	420	827	Warm White (WW)
929689848605	TORNADO 24W CDL E27 220-240V 1PF/6	313	337	865	Cool Daylight

Order Code	Full Product Name	Chromaticity		Color	
		Coordinate X (Nom)	Coordinate Y (Nom)	Code	Color Designation
	220-240V 1PF/6				
929689858102	TORNADO 15W WW B22 220-240V 1PF/6	463	420	827	Warm White (WW)
929689858202	TORNADO 15W CDL B22 220-240V 1PF/6	313	337	865	Cool Daylight
929689858302	TORNADO 20W WW B22 220-240V 1PF/6	463	420	827	Warm White (WW)
929689858402	TORNADO 20W CDL B22 220-240V 1PF/6	313	337	865	Cool Daylight
929689858502	TORNADO 24W WW B22 220-240V 1PF/6	463	420	827	Warm White (WW)
929689858602	TORNADO 24W CDL B22 220-240V 1PF/6	313	337	865	Cool Daylight

Light Technical (2/2)

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
		929689848105	TORNADO 15W WW E27 220-240V 1PF/6	2700 K	82	65 lm/W
929689848205	TORNADO 15W CDL E27	6500 K	80	61 lm/W	900 lm	900 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
			220-240V 1PF/6			
929689848306	TORNADO 20W WW E27 220-240V 1PF/6	2700 K	82	65 lm/W	1250 lm	1250 lm

TORNADO

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
929689848405	TORNADO 20W CDL E27 220-240V 1PF/6	6500 K	80	61 lm/W	1200 lm	1200 lm
929689848499	TORNADO 20W CDL E27 220-240V 1CT/12	6500 K	80	61 lm/W	1200 lm	1200 lm
929689848506	TORNADO 24W WW E27 220-240V 1PF/6	2700 K	82	67 lm/W	1550 lm	1550 lm
929689848605	TORNADO 24W CDL E27 220-240V 1PF/6	6500 K	80	63 lm/W	1450 lm	1450 lm
929689858102	TORNADO 15W WW B22 220-240V 1PF/6	2700 K	82	65 lm/W	950 lm	950 lm
929689858202	TORNADO 15W CDL	6500 K	80	61 lm/W	900 lm	900 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
	B22 220-240V 1PF/6					
929689858302	TORNADO 20W WW B22 220-240V 1PF/6	2700 K	82	65 lm/W	1250 lm	1250 lm
929689858402	TORNADO 20W CDL B22 220-240V 1PF/6	6500 K	80	61 lm/W	1200 lm	1200 lm
929689858502	TORNADO 24W WW B22 220-240V 1PF/6	2700 K	82	67 lm/W	1550 lm	1550 lm
929689858602	TORNADO 24W CDL B22 220-240V 1PF/6	6500 K	80	63 lm/W	1450 lm	1450 lm

