



Product Description

CLASSICTONE Standard

Conventional pear-shaped incandescent lamps

Benefits

- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect
- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect

Features

- · Vacuum-filled (15W) or gas-filled (25W and above)
- · Vacuum-filled (15W) or gas-filled (25W and above)
- · Choice of clear or frosted lamp types
- \cdot Choice of clear or frosted lamp types
- Universal burning position
- · Universal burning position

Application

- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare
- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare
- Frosted lamps give low glare and diffused lighting for universal applicability
- · Frosted lamps give low glare and diffused lighting for universal applicability


CLASSICTONE Standard

Versions



LPPR ISTDAE E27 A55 CL

Dimensional drawing



Product	D (max)	D	C (max)
CLAS 75W E27 220-240V A55 CL 1CT/10X10F	56 mm	55 mm	97 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.