

Classic look & feel and LED filament for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Benefits

- Around 90% energy saving
- Long lifetime reduces need for replacement
- Environmentally friendly: contains no mercury or other hazardous substances

Features


- Heritage design with classic shape
- Long LED Filament

Application

- Home: living room, bedroom
- Hospitality: restaurants and hotels

Classic filament LEDbulbs

Versions



LEDbulb E27 ST6 5.5W



LEDclassic A60 E27 smoky POS2



Bulb G95 230V 5W-25W 250lm
2000K E27 D




LEDclassic ST64 E27 smoky POS2



LEDbulb G93 E27 smoky





Dimensional drawing



Product	D	C
LEDclassic 11W A60 E27 smoky ND RFSRT4	60 mm	106 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LED classic 25W G93 E27 GOLD SP D SRT4	96 mm	143 mm

Product	D	C
LED classic 11W G93 E27 smoky ND RF 1PF	95 mm	142 mm

Product	D	C
LEDclassic 11W ST64 E27 smoky ND RFSRT4	64 mm	143 mm

Product	D	C
LED classic 25W ST64 E27GOLD SP D RFSRT4	65 mm	143 mm

Classic filament LEDbulbs

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	1800 K
Color rendering index (CRI)	80
Color Code	818
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Luminous Flux
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	330 degree(s)	250 lm
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	-	100 lm
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	330 degree(s)	250 lm
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	-	100 lm
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	-	100 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	4 W	25 W
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	2.3 W	11 W
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	4 W	25 W

Order Code	Full Product Name	Power Consumption	Wattage Equivalent
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	2.3 W	11 W
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	2 W	11 W

Temperature

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	-20 to +45 °C	35 °C
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	-20 to +40 °C	40 °C
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	-20 to +45 °C	35 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	-20 to +40 °C	40 °C
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	-20 to +40 °C	40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	Only with specific dimmers
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	No
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	Only with specific dimmers

Order Code	Full Product Name	Dimmable
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	No
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	Amber	ST64

Order Code	Full Product Name	Bulb Finish	Bulb Shape
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	smoky	A60

Classic filament LEDbulbs

Order Code	Full Product Name	Bulb Finish	Bulb Shape
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	Amber	G93
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	smoky	ST64

Order Code	Full Product Name	Bulb Finish	Bulb Shape
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	smoky	G93

Approval and Application

		Energy Consumption kWh/
Order Code	Full Product Name	1000 h
31545700	LED classic 25W ST64 E27GOLD SP D RFSRT4	4 kWh
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	3 kWh
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	4 kWh
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	3 kWh
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	2 kWh

