



Classic LEDbulbs lamps for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features


- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI> 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LEDbulbs

Versions





LEDbulb E27 ST6 5.5W



Bulb G95 230V 5W-25W 250lm
2000K E27 D

Dimensional drawing



Product	D	C
LED classic 25W G93 E27 GOLD SP D SRT4	96 mm	143 mm



Product	D	C
LED classic 25W ST64 E27GOLD SP D RFSRT4	65 mm	143 mm

Classic filament LEDbulbs

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Beam Angle (Nom)	330 degree(s)
Correlated Color Temperature (Nom)	1800 K
Color rendering index (CRI)	80
Color Code	818
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	250 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Power Consumption	4 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	25 W
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	35 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Amber
Approval and Application	
Energy Consumption kWh/1000 h	4 kWh

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	ST64
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	G93



Classic filament LEDbulbs

