

# Classic LEDbulbs lamps for decorative lighting

## Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

### Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI > 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

### Application



- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

# Classic filament LEDbulbs

## Versions



## Dimensional drawing





Product	D	C
LEDClassic 7-60W G120 E27 2000K GOLD APR	125 mm	188 mm

Product	D	C
LEDClassic 4.5-50W B35 E14 WW CL D APR	35 mm	118 mm

# Classic filament LEDbulbs

## Dimensional drawing



D

Product	D	C
LEDClassic 4-35W ST64 E27 825 CL_G NDAPR	64 mm	142 mm

Product	D	C
LEDClassic 4-35W A60 E27 825 CL_G NDAPR	60 mm	106 mm

Product	D	C
LEDClA 7.5-60W A60 E27 2000K GOLD APR	60 mm	112 mm

### Operating and Electrical

Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s

### General Information

Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X

### Light Technical

Colour Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %

## Approval and Application

## Classic filament LEDbulbs

Order Code	Full Product Name	Energy	
		Consumption kWh/ 1000 h	Energy Efficiency Label (EEL)
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	5 kWh	A++
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	8 kWh	A+
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	7 kWh	A+

Order Code	Full Product Name	Energy	
		Consumption kWh/ 1000 h	Energy Efficiency Label (EEL)
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	- kWh	A++
929001941608	LEDClassic 4-35W ST64 E27 825 CL_G NDAPR	- kWh	A++

### Controls and Dimming

Order Code	Full Product Name	Dimmable
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	Yes
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	Yes
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	Yes

Order Code	Full Product Name	Dimmable
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	No
929001941608	LEDClassic 4-35W ST64 E27 825 CL_G NDAPR	No

### Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Wattage Equivalent	Power
				(Rated)
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	220-240 V	50 W	4.5 W
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	220-240 V	60 W	7.5 W
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	220-240 V	60 W	7 W

Order Code	Full Product Name	Voltage (Nom)	Wattage Equivalent	Power
				(Rated)
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	100-240 V	35 W	4 W
929001941608	LEDClassic 4-35W ST64 E27 825 CL_G NDAPR	100-240 V	35 W	4 W

### General Information

Order Code	Full Product Name	Cap-Base
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	E14
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	E27
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	E27

Order Code	Full Product Name	Cap-Base
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	E27
929001941608	LEDClassic 4-35W ST64 E27 825 CL_G NDAPR	E27

### Light Technical

Order Code	Full Product Name	Colour Code	Correlated Colour	
			Temperature (Nom)	Luminous Flux (Nom)
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	827	2700 K	470 lm
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	820	2000 K	600 lm
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	820	2000 K	630 lm

Order Code	Full Product Name	Colour Code	Correlated Colour	
			Temperature (Nom)	Luminous Flux (Nom)
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	825	2500 K	400 lm
929001941608	LEDClassic 4-35W ST64 E27 825 CL_G NDAPR	825	2500 K	400 lm

### Mechanical and Housing

## Classic filament LEDbulbs

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	Clear	B35
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	Gold Clear	A60
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	Gold Clear	G120

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001941508	LEDClassic 4-35W A60 E27 825 CL_G NDAPR	Transparent Amber	A60
929001941608	LEDClassic 4-35W ST64 E27 825 CL_G NDAPR	Transparent Amber	ST64

### Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001227208	LEDClassic 4.5-50W B35 E14 WW CL D APR	70 °C
929001228108	LEDClA 7.5-60W A60 E27 2000K GOLD APR	70 °C
929001229108	LEDClassic 7-60W G120 E27 2000K GOLD APR	70 °C
929001941508	LEDClassic 4-35W A60 E27 825 CL_G NDAPR	52 °C
929001941608	LEDClassic 4-35W ST64 E27 825 CL_G NDAPR	50 °C

